




## Thyristor/Thyristor (Super MAGN-A-PAK Power Modules), 570 A



Super MAGN-A-PAK

RoHS  
COMPLIANT

### FEATURES

- High current capability
- High surge capability
- Industrial standard package
- 3000 V<sub>RMS</sub> isolating voltage with non-toxic substrate
- Designed and qualified for industrial level
- UL approved file E78996 
- Material categorization: for definitions of compliance please see [www.vishay.com/doc?99912](http://www.vishay.com/doc?99912)

### TYPICAL APPLICATIONS

- Motor starters
- DC motor controls - AC motor controls
- Uninterruptible power supplies

### PRIMARY CHARACTERISTICS

$I_{T(AV)}$	570 A
Type	Modules - thyristor, standard
Package	Super MAGN-A-PAK

### MAJOR RATINGS AND CHARACTERISTICS

SYMBOL	CHARACTERISTICS	VALUES	UNITS
$I_{T(AV)}$	$T_C = 74\text{ }^\circ\text{C}$	570	A
$I_{T(RMS)}$	$T_C = 74\text{ }^\circ\text{C}$	895	
$I_{TSM}$	50 Hz	17 800	
	60 Hz	18 700	
$I^2t$	50 Hz	1591	kA <sup>2</sup> s
	60 Hz	1452	
$I^2\sqrt{t}$		15 910	kA <sup>2</sup> $\sqrt{s}$
$V_{RRM}$	Range	1800	V
$T_{Stg}$	Range	-40 to +135	$^\circ\text{C}$
$T_J$	Range	-40 to +135	

### ELECTRICAL SPECIFICATIONS

#### VOLTAGE RATINGS

TYPE NUMBER	VOLTAGE CODE	$V_{RRM}/V_{DRM}$ , MAXIMUM REPETITIVE PEAK REVERSE VOLTAGE V	$V_{RSM}$ , MAXIMUM NON-REPETITIVE PEAK REVERSE VOLTAGE V	$I_{RRM}/I_{DRM}$ MAXIMUM AT $T_J = T_J$ MAXIMUM mA
VS-VSKT570-18PbF	18	1800	1900	120



ON-STATE CONDUCTION						
PARAMETER	SYMBOL	TEST CONDITIONS			VALUES	UNITS
Maximum average on-state current at case temperature	$I_{T(AV)}$	180° conduction, half sine wave			570	A
					74	°C
Maximum RMS on-state current	$I_{T(RMS)}$	180° conduction, half sine wave at $T_C = 74\text{ °C}$			895	A
Maximum peak, one-cycle, non-repetitive on-state surge current	$I_{TSM}, I_{FSM}$	t = 10 ms	No voltage reapplied	Sinusoidal half wave, initial $T_J = T_J$ maximum	17.8	kA
		t = 8.3 ms			18.7	
		t = 10 ms	100 % $V_{RRM}$ reapplied		15.0	
		t = 8.3 ms			15.7	
Maximum $I^2t$ for fusing	$I^2t$	t = 10 ms	No voltage reapplied		1591	kA <sup>2</sup> s
		t = 8.3 ms			1452	
		t = 10 ms	100 % $V_{RRM}$ reapplied		1125	
		t = 8.3 ms			1027	
Maximum $I^2\sqrt{t}$ for fusing	$I^2\sqrt{t}$	t = 0.1 ms to 10 ms, no voltage reapplied			15 910	kA <sup>2</sup> √s
Low level value or threshold voltage	$V_{T(TO)1}$	(16.7 % $\times \pi \times I_{T(AV)} < I < \pi \times I_{T(AV)}$ ), $T_J = T_J$ maximum			0.864	V
High level value of threshold voltage	$V_{T(TO)2}$	(I $> \pi \times I_{T(AV)}$ ), $T_J = T_J$ maximum			0.97	
Low level value on-state slope resistance	$r_{t1}$	(16.7 % $\times \pi \times I_{T(AV)} < I < \pi \times I_{T(AV)}$ ), $T_J = T_J$ maximum			0.411	mΩ
High level value on-state slope resistance	$r_{t2}$	(I $> \pi \times I_{T(AV)}$ ), $T_J = T_J$ maximum			0.362	
Maximum on-state voltage drop	$V_{TM}$	$I_{pk} = 1500\text{ A}$ , $T_J = 25\text{ °C}$ , $t_p = 10\text{ ms}$ sine pulse			1.50	V
Maximum holding current	$I_H$	$T_J = 25\text{ °C}$ , anode supply 12 V resistive load			500	mA
Maximum latching current	$I_L$				1000	

SWITCHING						
PARAMETER	SYMBOL	TEST CONDITIONS			VALUES	UNITS
Maximum rate of rise of turned-on current	$di/dt$	$T_J = T_J$ maximum, $I_{TM} = 400\text{ A}$ , $V_{DRM}$ applied			1000	A/μs
Typical delay time	$t_d$	Gate current 1 A, $di_g/dt = 1\text{ A}/\mu\text{s}$ $V_d = 0.67\% V_{DRM}$ , $T_J = 25\text{ °C}$			2.0	μs
Typical turn-off time	$t_q$	$I_{TM} = 750\text{ A}$ ; $T_J = T_J$ maximum, $di/dt = -60\text{ A}/\mu\text{s}$ , $V_R = 50\text{ V}$ , $dV/dt = 20\text{ V}/\mu\text{s}$ , gate 0 V 100 Ω			200	

BLOCKING						
PARAMETER	SYMBOL	TEST CONDITIONS			VALUES	UNITS
Maximum critical rate of rise of off-state voltage	$dV/dt$	$T_J = T_J$ maximum, linear to $V_D = 80\% V_{DRM}$			1000	V/μs
RMS insulation voltage	$V_{INS}$	t = 1 s			3000	V
Maximum peak reverse and off-state leakage current	$I_{RRM}, I_{DRM}$	$T_J = T_J$ maximum, rated $V_{DRM}/V_{RRM}$ applied			120	mA



TRIGGERING				
PARAMETER	SYMBOL	TEST CONDITIONS	VALUES	UNITS
Maximum peak gate power	$P_{GM}$	$T_J = T_J$ maximum, $t_p \leq 5$ ms	10	W
Maximum peak average gate power	$P_{G(AV)}$	$T_J = T_J$ maximum, $f = 50$ Hz, $d \% = 50$	2.0	
Maximum peak positive gate current	$+I_{GM}$	$T_J = T_J$ maximum, $t_p \leq 5$ ms	3.0	A
Maximum peak positive gate voltage	$+V_{GM}$		20	
Maximum peak negative gate voltage	$-V_{GM}$		5.0	
Maximum DC gate current required to trigger	$I_{GT}$	$T_J = 25$ °C, $V_{ak}$ 12 V	200	mA
DC gate voltage required to trigger	$V_{GT}$		3.0	V
DC gate current not to trigger	$I_{GD}$	$T_J = T_J$ maximum	10	mA
DC gate voltage not to trigger	$V_{GD}$		0.25	V

THERMAL AND MECHANICAL SPECIFICATIONS				
PARAMETER	SYMBOL	TEST CONDITIONS	VALUES	UNITS
Maximum junction operating temperature range	$T_J$		-40 to +135	°C
Maximum storage temperature range	$T_{Stg}$		-40 to +135	
Maximum thermal resistance, junction to case per junction	$R_{thJC}$	DC operation	0.065	K/W
Maximum thermal resistance, case to heatsink per module	$R_{thC-hs}$	Mounting surface smooth, flat and greased	0.02	
Mounting torque $\pm 10$ %	Super MAGN-A-PAK to heatsink busbar to super MAGN-A-PAK	A mounting compound is recommended and the torque should be rechecked after a period of 3 hours to allow for the spread of the compound	6 to 8	Nm
			12 to 15	
Approximate weight			1500	g
Case style		See dimensions (link at the end of datasheet)	Super MAGN-A-PAK	

$\Delta R_{thJC}$ CONDUCTION				
CONDUCTION ANGLE	SINUSOIDAL CONDUCTION	RECTANGULAR CONDUCTION	TEST CONDITIONS	UNITS
180°	0.009	0.006	$T_J = T_J$ maximum	K/W
120°	0.011	0.011		
90°	0.014	0.015		
60°	0.021	0.022		
30°	0.037	0.038		

**Note**

- Table shows the increment of thermal resistance  $R_{thJC}$  when devices operate at different conduction angles than DC




Fig. 1 - Current Ratings Characteristics




Fig. 4 - On-State Power Loss Characteristics




Fig. 2 - Current Ratings Characteristics




Fig. 5 - Maximum Non-Repetitive Surge Current




Fig. 3 - On-State Power Loss Characteristics




Fig. 6 - Maximum Non-Repetitive Surge Current





Fig. 7 - On-State Power Loss Characteristics





Fig. 8 - On-State Voltage Drop Characteristics

Fig. 9 - Thermal Impedance  $Z_{thJC}$  Characteristics




Fig. 10 - Gate Characteristics



**ORDERING INFORMATION TABLE**

Device code	<b>VS-VS</b>	<b>KT</b>	<b>570</b>	<b>-</b>	<b>18</b>	<b>PbF</b>
	①	②	③		④	⑤

- 1** - Vishay Semiconductors product
- 2** - Circuit configuration (see below)
- 3** - Current rating
- 4** - Voltage code x 100 =  $V_{RRM}$
- 5** - Lead (Pb)-free


CIRCUIT CONFIGURATION		
CIRCUIT DESCRIPTION	CIRCUIT CONFIGURATION CODE	CIRCUIT DRAWING
Two SCRs doubler circuit	KT	

LINKS TO RELATED DOCUMENTS	
Dimensions	<a href="http://www.vishay.com/doc?95283">www.vishay.com/doc?95283</a>



## Super MAGN-A-PAK Thyristor/Diode

**DIMENSIONS** in millimeters (inches)





## **Disclaimer**

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Vishay products are not designed for use in life-saving or life-sustaining applications or any application in which the failure of the Vishay product could result in personal injury or death unless specifically qualified in writing by Vishay. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.