


## MTP IGBT Power Module Primary Rectifier and PFC



MTP


**RoHS**  
COMPLIANT

### FEATURES

- Input rectifier bridge
- PFC stage with warp 2 IGBT and FRED Pt® hyperfast diode
- Very low stray inductance design for high speed operation
- Integrated thermistor
- Isolated baseplate
- UL approved file E78996
- Designed and qualified for industrial level
- Material categorization: for definitions of compliance please see [www.vishay.com/doc?99912](http://www.vishay.com/doc?99912)

### BENEFITS

- Lower conduction losses and switching losses
- Optimized for welding, UPS, and SMPS applications
- PCB solderable terminals
- Direct mounting to heatsink

PRIMARY CHARACTERISTICS	
<b>INPUT BRIDGE DIODE, T<sub>J</sub> = 150 °C</b>	
V <sub>RRM</sub>	1200 V
I <sub>O</sub> at 80 °C	48 A
V <sub>FM</sub> at 25 °C at 20 A	1.05 V
<b>PFC IGBT, T<sub>J</sub> = 150 °C</b>	
V <sub>CES</sub>	600 V
V <sub>CE(on)</sub> at 25 °C at 40 A	1.93 V
I <sub>C</sub> at 80 °C	66 A
<b>FRED Pt® PFC DIODE, T<sub>J</sub> = 150 °C</b>	
V <sub>R</sub>	600 V
I <sub>F(DC)</sub> at 80 °C	55 A
V <sub>F</sub> at 25 °C at 40 A	1.76 V
<b>FRED Pt® AP DIODE, T<sub>J</sub> = 150 °C</b>	
V <sub>R</sub>	600 V
I <sub>F(DC)</sub> at 80 °C	13 A
V <sub>F</sub> at 25 °C at 4 A	1.1 V
Speed	30 kHz to 150 kHz
Package	MTP
Circuit configuration	Input rectifier bridge

ABSOLUTE MAXIMUM RATINGS					
	PARAMETER	SYMBOL	TEST CONDITIONS	MAX.	UNITS
Input Rectifier Bridge	Repetitive peak reverse voltage	V <sub>RRM</sub>		1200	V
	Maximum average output current T <sub>J</sub> = 150 °C maximum	I <sub>O</sub>	T <sub>C</sub> = 80 °C	48	A
	Surge current (Non-repetitive)	I <sub>FSM</sub>	Rated V <sub>RRM</sub> applied	250	
	Maximum I <sup>2</sup> t for fusing	I <sup>2</sup> t	10 ms, sine pulse	316	A <sup>2</sup> s
PFC IGBT	Collector to emitter voltage	V <sub>CES</sub>	T <sub>J</sub> = 25 °C	600	V
	Gate to emitter voltage	V <sub>GE</sub>	I <sub>GES</sub> max. ± 250 ns	± 20	
	Maximum continuous collector current at V <sub>GE</sub> = 15 V, T <sub>J</sub> = 150 °C maximum	I <sub>C</sub>	T <sub>C</sub> = 25 °C	96	A
			T <sub>C</sub> = 80 °C	66	
	Pulsed collector current	I <sub>CM</sub> <sup>(1)</sup>		250	
	Clamped inductive load current	I <sub>LM</sub>		250	
Maximum power dissipation	P <sub>D</sub>	T <sub>C</sub> = 25 °C	378	W	



ABSOLUTE MAXIMUM RATINGS					
	PARAMETER	SYMBOL	TEST CONDITIONS	MAX.	UNITS
PFC Diode	Repetitive peak reverse voltage	$V_{RRM}$		600	V
	Maximum continuous forward current $T_J = 150\text{ }^\circ\text{C}$ maximum	$I_F$	$T_C = 25\text{ }^\circ\text{C}$	82	A
			$T_C = 80\text{ }^\circ\text{C}$	55	
	Maximum power dissipation	$P_D$	$T_C = 25\text{ }^\circ\text{C}$	181	W
Maximum non-repetitive peak current	$I_{FSM}$	$T_C = 25\text{ }^\circ\text{C}$	360	A	
AP Diode	Repetitive peak reverse voltage	$V_{RRM}$		600	V
	Maximum continuous forward current $T_J = 150\text{ }^\circ\text{C}$ maximum	$I_F$	$T_C = 25\text{ }^\circ\text{C}$	21	A
			$T_C = 80\text{ }^\circ\text{C}$	13	
	Maximum power dissipation	$P_D$	$T_C = 25\text{ }^\circ\text{C}$	32	W
Maximum non-repetitive peak current	$I_{FSM}$	$T_C = 25\text{ }^\circ\text{C}$	60	A	
	Maximum operating junction temperature	$T_J$		150	$^\circ\text{C}$
	Storage temperature range	$T_{Stg}$		-40 to +150	
	RMS isolation voltage	$V_{ISOL}$	$V_{RMS} t = 1\text{ s}, T_J = 25\text{ }^\circ\text{C}$	3500	

$\Delta R$ CONDUCTION PER JUNCTION - SINGLE PHASE BRIDGE DIODE											
DEVICES	SINE HALF WAVE CONDUCTION					RECTANGULAR WAVE CONDUCTION					UNITS
	180°	120°	90°	60°	30°	180°	120°	90°	60°	30°	
70MT060WSP	0.273	0.302	0.322	0.338	0.350	0.236	0.288	0.294	0.287	0.235	$^\circ\text{C}/\text{W}$

ELECTRICAL SPECIFICATIONS ( $T_J = 25\text{ }^\circ\text{C}$ unless otherwise noted)							
	PARAMETER	SYMBOL	TEST CONDITIONS	MIN.	TYP.	MAX.	UNITS
Input Rectifier Bridge	Blocking voltage	$BV_{RRM}$	$I_R = 250\text{ }\mu\text{A}$	1200	-	-	V
	Reverse leakage current	$I_{RRM}$	$V_{RRM} = 1200\text{ V}$	-	-	0.1	mA
			$V_{RRM} = 1200\text{ V}, T_J = 150\text{ }^\circ\text{C}$	-	-	3.0	
	Forward voltage drop	$V_{FM}$	$I_F = 20\text{ A}$	-	1.05	1.2	V
			$I_F = 20\text{ A}, T_J = 150\text{ }^\circ\text{C}$	-	0.94	1.0	
Forward slope resistance	$r_t$	$T_J = 150\text{ }^\circ\text{C}$	-	-	8.7	$\text{m}\Omega$	
Conduction threshold voltage	$V_T$		-	-	0.94	V	
PFC IGBT	Collector to emitter breakdown voltage	$BV_{CES}$	$V_{GE} = 0\text{ V}, I_C = 0.5\text{ mA}$	600	-	-	V
	Temperature coefficient of breakdown voltage	$\Delta V_{BR(CES)}/\Delta T_J$	$I_C = 0.5\text{ mA} (25\text{ }^\circ\text{C} \text{ to } 125\text{ }^\circ\text{C})$	-	0.6	-	$\text{V}/^\circ\text{C}$
	Collector to emitter voltage	$V_{CE(on)}$	$V_{GE} = 15\text{ V}, I_C = 40\text{ A}$	-	1.93	2.15	V
			$V_{GE} = 15\text{ V}, I_C = 40\text{ A}, T_J = 125\text{ }^\circ\text{C}$	-	2.30	2.55	
	Gate threshold voltage	$V_{GE(th)}$	$V_{CE} = V_{GE}, I_C = 500\text{ }\mu\text{A}$	2.9	-	5.6	V
	Collector to emitter leakage current	$I_{CES}$	$V_{GE} = 0\text{ V}, V_{CE} = 600\text{ V}$	-	-	0.1	mA
$V_{GE} = 0\text{ V}, V_{CE} = 600\text{ V}, T_J = 125\text{ }^\circ\text{C}$			-	-	1		
Gate to emitter leakage	$I_{GES}$	$V_{GE} = \pm 20\text{ V}$	-	-	$\pm 100$	nA	
PFC Diode	Forward voltage drop	$V_{FM}$	$I_F = 40\text{ A}$	-	1.76	2.23	V
			$I_F = 40\text{ A}, T_J = 125\text{ }^\circ\text{C}$	-	1.34	1.62	
	Blocking voltage	$BV_{RM}$	$I_R = 0.5\text{ mA}$	600	-	-	
Reverse leakage current	$I_{RM}$	$V_{RRM} = 600\text{ V}$	-	-	75	$\mu\text{A}$	
		$V_{RRM} = 600\text{ V}, T_J = 125\text{ }^\circ\text{C}$	-	-	0.5	mA	
AP Diode	Forward voltage drop	$V_{FM}$	$I_F = 4\text{ A}$	-	1.1	1.28	V
			$I_F = 4\text{ A}, T_J = 125\text{ }^\circ\text{C}$	-	0.95	1.09	



<b>ELECTRICAL SPECIFICATIONS</b> ( $T_J = 25\text{ }^\circ\text{C}$ unless otherwise noted)							
	PARAMETER	SYMBOL	TEST CONDITIONS	MIN.	TYP.	MAX.	UNITS
<b>RECOVERY PARAMETER</b>							
PFC Diode	Peak reverse recovery current	$I_{rr}$	$I_F = 40\text{ A}$	-	4	7	A
	Reverse recovery time	$t_{rr}$	$di/dt = 200\text{ A}/\mu\text{s}$	-	59	79	ns
	Reverse recovery charge	$Q_{rr}$	$V_R = 200\text{ V}$	-	118	180	nC
	Peak reverse recovery current	$I_{rr}$	$I_F = 40\text{ A}, T_J = 125\text{ }^\circ\text{C}$	-	12	17	A
	Reverse recovery time	$t_{rr}$	$di/dt = 200\text{ A}/\mu\text{s}$	-	127	170	ns
	Reverse recovery charge	$Q_{rr}$	$V_R = 200\text{ V}$	-	733	1200	nC
AP Diode	Peak reverse recovery current	$I_{rr}$	$I_F = 4\text{ A}$	-	7	10	A
	Reverse recovery time	$t_{rr}$	$di/dt = 200\text{ A}/\mu\text{s}$	-	78	120	ns
	Reverse recovery charge	$Q_{rr}$	$V_R = 200\text{ V}$	-	290	600	nC

<b>SWITCHING CHARACTERISTICS</b> ( $T_J = 25\text{ }^\circ\text{C}$ unless otherwise noted)							
	PARAMETER	SYMBOL	TEST CONDITIONS	MIN.	TYP.	MAX.	UNITS
PFC IGBT	Total gate charge	$Q_g$	$I_C = 50\text{ A}$ $V_{CC} = 400\text{ V}$ $V_{GE} = 15\text{ V}$	-	320	-	nC
	Gate to source charge	$Q_{gs}$		-	42	-	
	Gate to drain (Miller) charge	$Q_{gd}$		-	110	-	
	Turn-on switching loss	$E_{on}$	$I_C = 70\text{ A}, V_{CC} = 360\text{ V}, V_{GE} = 15\text{ V}$ $R_g = 5\text{ }\Omega, L = 500\text{ }\mu\text{H}, T_J = 25\text{ }^\circ\text{C}$	-	0.13	-	mJ
	Turn-off switching loss	$E_{off}$		-	0.18	-	
	Total switching loss	$E_{tot}$		-	0.31	-	
	Turn-on delay time	$t_{d(on)}$		ns	-	193	-
	Rise time	$t_r$			-	35	-
	Turn-off delay time	$t_{d(off)}$			-	202	-
	Fall time	$t_f$			-	49	-
	Turn-on switching loss	$E_{on}$	$I_C = 70\text{ A}, V_{CC} = 360\text{ V}, V_{GE} = 15\text{ V}$ $R_g = 5\text{ }\Omega, L = 500\text{ }\mu\text{H}, T_J = 125\text{ }^\circ\text{C}$	-	0.25	-	mJ
	Turn-off switching loss	$E_{off}$		-	0.32	-	
	Total switching loss	$E_{tot}$		-	0.57	-	
	Turn-on delay time	$t_{d(on)}$		ns	-	193	-
	Rise time	$t_r$			-	35	-
	Turn-off delay time	$t_{d(off)}$			-	208	-
	Fall time	$t_f$			-	66	-
	Input capacitance	$C_{ies}$	$V_{GE} = 0\text{ V}$ $V_{CC} = 30\text{ V}$ $f = 1\text{ MHz}$	-	7430	-	pF
	Output capacitance	$C_{oes}$		-	530	-	
	Reverse transfer capacitance	$C_{res}$		-	94	-	
Reverse bias safe operating area	RBSOA	$I_C = 250\text{ A}, V_{CC} = 400\text{ V}, V_P = 600\text{ V},$ $R_g = 22\text{ }\Omega, V_{GE} = 15\text{ V}, L = 500\text{ }\mu\text{H},$ $T_J = 150\text{ }^\circ\text{C}$	Full square				

<b>THERMISTOR ELECTRICAL CHARACTERISTICS</b> ( $T_J = 25\text{ }^\circ\text{C}$ unless otherwise noted)							
PARAMETER	SYMBOL	TEST CONDITIONS	MIN.	TYP.	MAX.	UNITS	
Resistance	R	$T_J = 25\text{ }^\circ\text{C}$	-	30 000	-	$\Omega$	
B value	B	$T_J = 25\text{ }^\circ\text{C}/T_J = 85\text{ }^\circ\text{C}$	-	4000	-	K	

**Notes**

- Repetitive rating; pulsed with limited by maximum junction temperature

THERMAL AND MECHANICAL SPECIFICATIONS						
	SYMBOL	PARAMETER	MIN.	TYP.	MAX.	UNITS
Input rectifier bridge	$R_{thJC}$	Junction to case diode thermal resistance	-	-	0.9	°C/W
PFC IGBT		Junction to case IGBT thermal resistance	-	-	0.33	
PFC diode		Junction to case PFC diode thermal resistance	-	-	0.69	
AP diode		Junction to case AP diode thermal resistance	-	-	3.92	
	$R_{thCS}$	Case to sink, flat, greased surface per module	-	0.06	-	°C/W
		Mounting torque $\pm 10\%$ to heatsink <sup>(1)</sup>	-	-	4	Nm
		Approximate weight	-	65	-	g

### Notes

- A mounting compound is recommended and the torque should be rechecked after a period of 3 hours to allow for the spread of the compound. Lubricated threads




Fig. 1 - Single Phase Input Bridge Output Current Ratings Characteristics




Fig. 3 - Single Phase Input Bridge On-State Voltage Drop Characteristics




Fig. 2 - Single Phase Bridge On-State Power Loss Characteristics




Fig. 4 - Single Phase Input Bridge Maximum Non-Repetitive Surge Current (Per Junction)






Fig. 5 - Maximum Input Bridge Thermal Impedance  $Z_{thJC}$  Characteristics (Per Junction)



93410\_06


**ID - Continuous Collector Current (A)**

Fig. 6 - Maximum IGBT Continuous Collector Current vs. Case Temperature




93410\_08

Fig. 8 - Typical IGBT Output Characteristics,  $T_J = 25 \text{ } ^\circ\text{C}$




93410\_07

Fig. 7 - IGBT Reverse BIAS SOA  $T_J = 150 \text{ } ^\circ\text{C}$ ,  $V_{GE} = 15 \text{ V}$




93410\_09

Fig. 9 - Typical IGBT Output Characteristics,  $T_J = 125 \text{ } ^\circ\text{C}$




93410\_10

Fig. 10 - Typical IGBT Transfer Characteristics,  $T_J = 125\text{ }^\circ\text{C}$




93410\_13

Fig. 13 - Typical Diode Forward Voltage Characteristics of Antiparallel Diode,  $t_p = 500\text{ }\mu\text{s}$




93410\_11

Fig. 11 - Typical IGBT Zero Gate Voltage Collector Current




93410\_14

Fig. 14 - Maximum Continuous Forward Current vs. Case Temperature Antiparallel Diode




93410\_12

Fig. 12 - Typical IGBT Gate Threshold Voltage




93410\_15


Fig. 15 - Typical PFC Diode Forward Voltage




93410\_16  **$I_F$  - Continuous Forward Current (A)**  
Fig. 16 - Maximum Continuous Forward Current vs. Case Temperature PFC Diode




93410\_19  **$R_g$  (Ω)**  
Fig. 19 - Typical IGBT Energy Loss vs.  $R_g$   
 $T_J = 125^\circ\text{C}$ ,  $I_C = 70\text{ A}$ ,  $V_{CC} = 360\text{ V}$ ,  $V_{GE} = 15\text{ V}$ ,  $L = 500\ \mu\text{H}$ ,  $R_g = 5\ \Omega$




93410\_17  **$V_R$  (V)**  
Fig. 17 - Typical FRED Pt<sup>®</sup> Chopper Diode Reverse Current vs. Reverse Voltage




93410\_20  **$I_C$  (A)**  
Fig. 20 - Typical IGBT Switching Time vs.  $I_C$   
 $T_J = 125^\circ\text{C}$ ,  $V_{CC} = 360\text{ V}$ ,  $V_{GE} = 15\text{ V}$ ,  $L = 500\ \mu\text{H}$ ,  $R_g = 5\ \Omega$



93410\_18  **$I_C$  (A)**  
Fig. 18 - Typical IGBT Energy Loss vs.  $I_C$   
 $T_J = 125^\circ\text{C}$ ,  $V_{CC} = 360\text{ V}$ ,  $V_{GE} = 15\text{ V}$ ,  $L = 500\ \mu\text{H}$ ,  $R_g = 5\ \Omega$




93410\_21  **$R_g$  (Ω)**  
Fig. 21 - Typical IGBT Switching Time vs.  $R_g$   
 $T_J = 125^\circ\text{C}$ ,  $I_C = 70\text{ A}$ ,  $V_{CE} = 360\text{ V}$ ,  $V_{GE} = 15\text{ V}$ ,  $L = 500\ \mu\text{H}$




93410\_22

Fig. 22 - Typical  $t_{rr}$  Antiparallel Diode vs.  $di_F/dt$   
 $V_{rr} = 200$  V,  $I_F = 4$  A




93410\_25

Fig. 25 - Typical  $t_{rr}$  Chopper Diode vs.  $di_F/dt$ ,  $V_{rr} = 200$  V,  $I_F = 40$  A




93410\_23

Fig. 23 - Typical  $I_{rr}$  Antiparallel Diode vs.  $di_F/dt$   
 $V_{rr} = 200$  V,  $I_F = 4$  A




93410\_26

Fig. 26 - Typical  $I_{rr}$  Chopper Diode vs.  $di_F/dt$   
 $V_{rr} = 200$  V,  $I_F = 40$  A



93410\_24


Fig. 24 - Typical  $Q_{rr}$  Antiparallel Diode vs.  $di_F/dt$   
 $V_{rr} = 200$  V,  $I_F = 4$  A



93410\_27

Fig. 27 - Typical  $Q_{rr}$  Chopper Diode vs.  $di_F/dt$ ,  $V_{rr} = 200$  V,  $I_F = 40$  A





93410\_28

Fig. 28 - Maximum Thermal Impedance  $Z_{thJC}$  Characteristics (IGBT)




Fig. C.T.1 - Gate Charge Circuit (Turn-Off)




Fig. C.T.3 - S.C. SOA Circuit




Fig. C.T.2 - RBSOA Circuit




Fig. C.T.4 - Switching Loss Circuit





Fig. C.T.5 - Resistive Load Circuit

## CIRCUIT CONFIGURATION



## ORDERING INFORMATION

Device code

<b>VS-</b>	<b>70</b>	<b>MT</b>	<b>060</b>	<b>W</b>	<b>SP</b>
①	②	③	④	⑤	⑥

- 1** - Vishay Semiconductors product
- 2** - Current rating (70 = 70 A)
- 3** - Essential part number (MT = MTP package)
- 4** - Voltage code (060 = 600 V)
- 5** - Die IGBT technology (W = warp speed IGBT)
- 6** - Circuit configuration (SP = single phase bridge plus PFC)


### LINKS TO RELATED DOCUMENTS

Dimensions	<a href="http://www.vishay.com/doc?95383">www.vishay.com/doc?95383</a>
------------	--



### MTP - Full Pin

**DIMENSIONS** in millimeters



Use Self Tapping Screw  
or M2.5 x X.  
e.g. M2.5 x 6 or M2.5 x 8  
according to PCB  
thickness used

PINS POSITION  
WITH TOLERANCE  $\varnothing 0.6$



## **Disclaimer**

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.