

Water Cooled RF Power Pot Capacitors, External Cooling System



FEATURES

- High voltage, current, and power ratings
- Compact design reduces terminal self inductance and permits high frequency operation
- Increased power density is achieved through water cooling. Enhanced reliability is achieved with a rugged mechanical design

APPLICATIONS

Water cooled RF power pot capacitors are designed for use in the tank circuits of high power RF equipment such as induction heating and welding equipment, dielectric heating, and a variety of specialized RF applications.

DESIGN SUPPORT TOOLS AVAILABLE


[3D Models](#)

| QUICK REFERENCE DATA | | | | | | | | | | | | | |
|-----------------------|-------------------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| DESCRIPTION | VALUE | | | | | | | | | | | | |
| Ceramic class | 1 | | | | | | | | | | | | |
| Ceramic dielectric | R7, R16, R42, R85 | | | | | | | | | | | | |
| Type | TWX | | | | | | TWXF | | | | | | |
| Voltage (V_p) | 12 000 | 14 000 | 16 000 | 20 000 | 25 000 | 10 000 | 12 000 | 14 000 | 16 000 | 18 000 | 20 000 | 22 500 | 25 000 |
| Min. capacitance (pF) | 5000 | 100 | 4000 | 3000 | 2500 | 10 000 | 5000 | 100 | 4000 | 7600 | 3000 | 7500 | 2500 |
| Max. capacitance (pF) | 5000 | 5000 | 4000 | 3000 | 2500 | 10 000 | 5000 | 10 000 | 10 000 | 10 000 | 7600 | 7500 | 5000 |
| Mounting | Screw terminal | | | | | | | | | | | | |

PRODUCT DESCRIPTION

TWX and TWXF pot-styled capacitors dissipate the heat produced under load by means of water flow around the capacitor element. In order to provide protection from influences of the chemical / physical characteristics of the coolant, a glass passivation layer is applied over the cooled noble metal electrode. The ceramic capacitor element is housed in a rugged copper case.

The electrical terminations are directly soldered onto the noble metal electrodes, providing a strong, rigid connection of unsurpassed reliability. The TWX model is made with a contoured, glazed insulation rim designed for use in a clean, dry environment. The TWXF types feature an umbrella shaped coating rim made from silicone elastomer to minimize the adverse effects of moisture, dust, and other soiling in the working environment, and to improve the characteristics of the electrical field.

MARKING

Type designator, capacitance value and tolerance, rated RF voltage, ceramic material code, production date code, manufacturer logo, serial number.

ACCESSORIES ADDED

All water cooled pot capacitors are supplied with the necessary screws / nuts and contact plates to make the connection to the electrode terminals. Ferrules and sleeve nuts for the water supply connections are also included.

CAPACITANCE RANGE

100 pF to 10 nF

CAPACITANCE TOLERANCE

± 20 %; ± 10 %

CERAMIC DIELECTRICS

- R7 (TCC: +100 ppm/K)
- R16 (TCC: +100 ppm/K)
- R42 (TCC: -250 ppm/K)
- R85 (TCC: -750 ppm/K)

RATED VOLTAGE

- 10 kV_p
- 12 kV_p
- 14 kV_p
- 16 kV_p
- 18 kV_p
- 20 kV_p
- 22.5 kV_p
- 25 kV_p

DIELECTRIC STRENGTH TEST

200 % of rated AC voltage, 50 Hz

RF POWER TEST

125 % to 140 % of rated power, for 10 minutes in a test generator circuit

DISSIPATION FACTOR

R7: max. 0.07 %

R16: max. 0.04 %

R42, R85: max. 0.05 %

Measuring frequencies:

1 MHz (< 1 nF); 300 kHz or 100 kHz (≥ 1 nF)

INSULATION RESISTANCE

Min. 10 000 MΩ (at 25 °C)

OPERATING TEMPERATURE RANGE

Find details of water cooling under the “Guidelines” section in the [datasheet](#).



SAP PART NUMBER AND ELECTRICAL DATA


| PART NUMBER | CERAMIC | CAP. VALUES (pF) | RATED VOLTAGE (kV _p) | RATED POWER (kvar) | RATED CURRENT (A _{RMS}) | MIN. WATER FLOW RATE PER MINUTE (liter / US-gal.) | PERMISSIBLE INSTALLATION POS. ⁽¹⁾ | | | |
|--------------------|---------|------------------|----------------------------------|--------------------|-----------------------------------|---|--|------|------------|------------|
| TYPE TWX | | | | | | | | | | |
| WX095162WJ101##BF1 | R7 | 100 | 14 | 1100 | 150 | 1.0 / 0.27 | Only vertical, umbrella-up position is permitted | | | |
| WX095162WJ201##BF1 | | 200 | | | | | | | | |
| WX095162WJ401##BG1 | R16 | 400 | | 1500 | | | | | | |
| WX095187WJ102##BH1 | R42 | 1000 | | 1000 | | | | | | |
| WX095162WJ152##BJ1 | R85 | 1500 | | 1500 | | | | | | |
| WX095162WJ202##BJ1 | | 2000 | | | | | | | | |
| WX095162WJ252##BJ1 | | 2500 | | | | | | | | |
| WX135242WP302##BJ1 | | 3000 | | 20 | | | | 2000 | 200 | 1.4 / 0.38 |
| WX110250WJ472##BJ1 | | 4700 | | 14 | | | | 2000 | 200 | 1.4 / 0.38 |
| WX095220WF502##BJ1 | 5000 | 12 | | 1275 | | | | 150 | 1.0 / 0.27 | |
| WX110250WJ502##BJ1 | 5000 | 14 | 2000 | 200 | 1.4 / 0.38 | | | | | |

Note

(1) ## 14th to 15th digit: capacitance tolerance code ± 20 % = 38, ± 10 % = 36

DIMENSIONS in millimeters (inches)

| PART NUMBER | D ₁ | D ₃ | D ₄ | D ₅ | D ₆ | L ₁ | L ₂ | L ₃ | |
|--------------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|-----------|
| TYPE TWX | | | | | | | | | |
| WX095162WJ101##BF1 | 95 (3.74) | 94 (3.70) | 85 (3.35) | 30 (1.18) | 40 (1.57) | 162 (6.38) | 55 (2.17) | 18 (0.71) | |
| WX095162WJ201##BF1 | | | | | | | | | |
| WX095162WJ401##BG1 | | | | | | | | | |
| WX095187WJ102##BH1 | | | | | | 187 (7.36) | 80 (3.15) | | |
| WX095162WJ152##BJ1 | | | | | | | | | |
| WX095162WJ202##BJ1 | | | | | | | | | |
| WX095162WJ252##BJ1 | 162 (6.38) | 55 (2.17) | | | | | | | |
| WX135242WP302##BJ1 | | | 135 (5.31) | 135 (5.31) | 122 (4.80) | 50 (1.97) | 242 (9.53) | 108 (4.25) | 22 (0.87) |
| WX110250WJ472##BJ1 | | | 110 (4.33) | 108 (4.25) | 98 (3.86) | 45 (1.77) | 248 (9.76) | 115 (4.53) | 18 (0.71) |
| WX095220WF502##BJ1 | 95 (3.74) | 94 (3.70) | 85 (3.35) | 40 (1.57) | 220 (8.66) | | | | |
| WX110250WJ502##BJ1 | 110 (4.33) | 108 (4.25) | 98 (3.86) | 45 (1.77) | 248 (9.76) | | | | |





| SAP PART NUMBER AND ELECTRICAL DATA | | | | | | | | |
|-------------------------------------|---------|------------------|----------------------------------|--------------------|-----------------------------------|---|---|--------|
| PART NUMBER | CERAMIC | CAP. VALUES (pF) | RATED VOLTAGE (kV _p) | RATED POWER (kvar) | RATED CURRENT (A _{RMS}) | MIN. WATER FLOW RATE PER MINUTE (liter / US-gal.) | PERMISSIBLE INSTALLATION POS. (1)(2)(3) | |
| TYPE TWXF | | | | | | | | |
| WF095162WJ101##BF1 | R7 | 100 | 14 | 1100 | 150 | 1.0 / 0.27 | (1)(2)(3) | |
| WF095162WJ201##BF1 | | 200 | | 1500 | | | | |
| WF095162WJ401##BG1 | R16 | 400 | | | | | | |
| WF095187WJ102##BH1 | R42 | 1000 | | | | | | |
| WF095162WJ152##BJ1 | R85 | 1500 | | 1000 | | | | |
| WF095162WJ202##BJ1 | | 2000 | | 1500 | | | | |
| WF095162WJ252##BJ1 | | 2500 | | | | | | |
| WF135242BQ252##BJ1 | | 2500 | 25 | 2500 | 250 | 2.1 / 0.57 | | |
| WF135242WP302##BJ1 | | 3000 | 20 | 2000 | 200 | 1.4 / 0.38 | | |
| WF135218WL402##BJ1 | | 4000 | 16 | 2500 | 250 | 1.8 / 0.49 | | |
| WF110250WJ472##BJ1 | | 4700 | 14 | 2000 | 200 | 1.4 / 0.38 | | |
| WF095220WF502##BJ1 | | 5000 | 12 | 1275 | 150 | 1.0 / 0.27 | | |
| WF110250WJ502##BJ1 | | 5000 | 14 | 2000 | 200 | 1.4 / 0.38 | | |
| WF135250WL502##BJ1 | | 5000 | 16 | 2830 | 250 | 2.0 / 0.54 | | |
| WF135285WP502##BJ1 | | 5000 | 20 | 3000 | 250 | 2.1 / 0.57 | | |
| WF135373BQ502##BJ1 | | 5000 | 25 | 3200 | 250 | 2.3 / 0.62 | | |
| WF135272WL602##BJ1 | | 6000 | 16 | 2830 | 250 | 2.0 / 0.54 | | |
| WF165278WP602##BJ1 | | 6000 | 20 | 3000 | 270 | 2.1 / 0.57 | | (1) |
| WF165270WJ752##BJ1 | | 7500 | 14 | 3000 | 300 | 2.1 / 0.57 | | (1)(3) |
| WF165336WQ752##BJ1 | | 7500 | 22.5 | 4000 | 350 | 2.9 / 0.80 | | (1)(3) |
| WF125300WJ762##BJ1 | | 7600 | 14 | 2500 | 250 | 1.4 / 0.38 | (1)(2)(3) | |
| WF165270WL762##BJ1 | | 7600 | 16 | 2830 | 250 | 2.0 / 0.54 | (1) | |
| WF125420WN762##BJ1 | 7600 | 18 | 2500 | 250 | 2.0 / 0.54 | (1)(3) | | |
| WF165336WP762##BJ1 | 7600 | 20 | 3200 | 270 | 2.3 / 0.62 | (1) | | |
| WF125300BH103##BJ1 | 10 000 | 10 | 2000 | 280 | 1.4 / 0.38 | (1)(2)(3) | | |
| WF125405WJ103##BJ1 | 10 000 | 14 | 2800 | 290 | 2.1 / 0.57 | (1) | | |
| WF165335WL103##BJ1 | 10 000 | 16 | 3395 | 300 | 2.5 / 0.70 | (1)(3) | | |
| WF165420WN103##BJ1 | 10 000 | 18 | 2500 | 250 | 2.0 / 0.54 | (1)(3) | | |

Notes

14th to 15th digit: capacitance tolerance code ± 20 % = 38; ± 10 % = 36

Permissible installation position:



- (1) Only vertical, umbrella-up position is permitted
- (2) Vertical, umbrella-down position
- (3) Horizontal mounting, water connections topside

• Special versions with additional water-emptying screw or with ERMETO fittings are available on request. Please contact us.




| DIMENSIONS in millimeters (inches) | | | | | | | | | | | | | | | | | | | |
|------------------------------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|---------------|----------------|----------------|---------------|---------------|---|
| PART NUMBER | D ₁ | D ₂ | D ₄ | D ₅ | D ₆ | D ₇ | L ₁ | L ₂ | L ₃ | B ₁ | B ₂ | FIG. | | | | | | | |
| TYPE TWXF | | | | | | | | | | | | | | | | | | | |
| WF095162WJ101##BF1 | 95 (3.74) | 110 (4.33) | 85 (3.35) | 30 (1.18) | 40 (1.58) | 5.5 (0.217) | 162 (6.38) | 55 (2.17) | 18 (0.71) | | | 1 | | | | | | | |
| WF095162WJ201##BF1 | | | | | | | | | | | | 1 | | | | | | | |
| WF095162WJ401##BG1 | | | | | | | | | | | | 1 | | | | | | | |
| WF095187WJ102##BH1 | | | | | | | 187 (7.36) | 80 (3.15) | | | | 1 | | | | | | | |
| WF095162WJ152##BJ1 | | | | | | | 162 (6.38) | 55 (2.17) | | | | 1 | | | | | | | |
| WF095162WJ202##BJ1 | | | | | | | | | | | | 1 | | | | | | | |
| WF095162WJ252##BJ1 | | | | | | | | | | | | 1 | | | | | | | |
| WF135242BQ252##BJ1 | 135 (5.31) | 148 (5.83) | 122 (4.80) | 30 (1.18) | 50 (1.97) | 6.5 (0.217) | 242 (9.53) | 108 (4.25) | 22 (0.87) | | | 1 | | | | | | | |
| WF135242WP302##BJ1 | | | | | | | | | | | | 218 (8.58) | 1 | | | | | | |
| WF135218WL402##BJ1 | | | | | | | 45 (1.77) | 248 (9.76) | | | | 1 | | | | | | | |
| WF110250WJ472##BJ1 | 95 (3.47) | 110 (4.33) | 85 (3.35) | 30 (1.18) | 40 (1.58) | 5.5 (0.217) | 220 (8.66) | 115 (4.53) | 18 (0.71) | | | 1 | | | | | | | |
| WF095220WF502##BJ1 | 110 (4.33) | 125 (4.92) | 98 (3.86) | | | | | | | | | 45 (1.77) | 248 (9.76) | 1 | | | | | |
| WF110250WJ502##BJ1 | 250 (9.84) | 135 (5.31) | 148 (5.83) | | | | 122 (4.80) | 50 (1.97) | | | | 6.5 (0.256) | 285 (11.22) | 134 (5.28) | 22 (0.87) | | | 1 | |
| WF135250WL502##BJ1 | 285 (11.22) | | | 1 | | | | | | | | | | | | | | | |
| WF135285WP502##BJ1 | 373 (14.69) | | | 216 (8.50) | 1 | | | | | | | | | | | | | | |
| WF135373BQ502##BJ1 | 272 (10.71) | | | 134 (5.28) | 1 | | | | | | | | | | | | | | |
| WF135272WL602##BJ1 | - | 170 (6.69) | 148 (5.83) | 146 (5.75) | 45 (1.77) | 75 (2.95) | 9.5 (0.374) | 278 (10.94) | 136 (5.35) | 30 (1.18) | 165 (6.50) | 135 (5.31) | 2 | | | | | | |
| WF165278WP602##BJ1 | 6.5 (0.256) | | | | | | | | | | | | 270 (10.63) | 134 (5.28) | 22 (0.87) | - | - | 1 | |
| WF165270WJ752##BJ1 | 9.5 (0.374) | | | | | | 336 (13.23) | 194 (7.64) | 30 (1.18) | 165 (6.50) | 135 (5.31) | 303 (11.93) | 180 (7.09) | 2 | | | | | |
| WF165336WQ752##BJ1 | | | | | | | | | | | | | | | 270 (10.63) | 140 (5.51) | 2 | | |
| WF125300WJ762##BJ1 | | | | | | | | | | | | | | | 420 (16.54) | 280 (11.02) | 127 (5.00) | 98 (3.86) | 2 |
| WF165270WL762##BJ1 | | | | | | | | | | | | | | | 336 (13.23) | 194 (7.64) | 165 (6.50) | 135 (5.31) | 2 |
| WF125420WN762##BJ1 | | | | | | | | | | | | | | | 303 (11.93) | 180 (7.09) | 127 (5.00) | 98 (3.86) | 2 |
| WF165336WP762##BJ1 | | | | | | | | | | | | | | | 405 (15.94) | 280 (11.02) | 165 (6.50) | 135 (5.31) | 2 |
| WF125300BH103##BJ1 | | | | | | | | | | | | | | | 335 (13.19) | 208 (8.82) | 127 (5.00) | 98 (3.86) | 2 |
| WF125405WJ103##BJ1 | | | | | | | | | | | | | | | 420 (16.54) | 280 (11.02) | 165 (6.50) | 135 (5.31) | 2 |
| WF165335WL103##BJ1 | | | | | | | | | | | | | | | 420 (16.54) | 280 (11.02) | 165 (6.50) | 135 (5.31) | 2 |
| WF165420WN103##BJ1 | | | | | | | | | | | | | | | | | | | |

DIMENSIONS in millimeters (inches)




DERATING DIAGRAMS


WX095162WJ101##BF1, WF095162WJ101##BF1




WX095162WJ201##BF1, WF095162WJ201##BF1



WX095162WJ401##BG1, WF095162WJ401##BG1




WX095187WJ102##BH1, WF095187WJ102##BH1




DERATING DIAGRAMS


WX095162WJ152##BJ1, WF095162WJ152##BJ1




WX095162WJ202##BJ1, WF095162WJ202##BJ1




WX095162WJ252##BJ1, WF095162WJ252##BJ1




WF135242BQ252##BJ1




WX135242WP302##BJ1, WF135242WP302##BJ1




WF135218WL402##BJ1



WX110250WJ472##BJ1, WF110250WJ472##BJ1




WX095220WF502##BJ1, WF095220WF502##BJ1




DERATING DIAGRAMS


WX110250WJ502##BJ1, WF110250WJ502##BJ1




WF135250WL502##BJ1




WF135285WP502##BJ1




WF135273502BQ##BJ1




WF135272WL602##BJ1




WF165278WP602##BJ1



WF165270WJ752##BJ1




WF165336WQ752##BJ1




DERATING DIAGRAMS


WF125300WJ762##BJ1




WF165270WL762##BJ1




WF125420WN762##BJ1




WF165336WP762##BJ1




WF125300BH103##BJ1




WF125405WJ103##BJ1



WF165335WL103##BJ1



WF165420WN103##BJ1





GUIDELINES

ELECTRICAL DATA AND GUIDELINES

- The main physical and electrical characteristics of the capacitors and ceramic materials used, are listed in the tables on the general section and in the individual datasheets
- The continuous limit values of voltage, current, and power given in the diagrams must be observed.
- The rated voltage given in the tables is the peak value of the sinusoidal AC voltage or the sum of the DC and peak AC voltages for which the capacitor is rated under continuous operation.
- The rated current in the tables is the effective value of the sinusoidal current for which the current paths of the capacitor are designed.

INSTALLATION

- Water cooled pot capacitors (TWX and TWXF) are designed to be installed in a vertical, umbrella-up position. Other positions may be allowed as shown on the individual datasheets. For large generators requiring multiple capacitors we recommended a circular mounting pattern for optimum circuit performance.
- When capacitors are connected in parallel, care should be taken to mount the top electrodes of the capacitor away from the RF-bus bar to minimize the effects of stray electromagnetic fields. The capacitors elements must not exceed a temperature of more than +100 °C.
- The electrical connection to the inner electrode must be flexible in order to prevent the generation of the physical forces which could damage the capacitor elements. Such forces are often generated by the dimensional differences resulting from the normal physical tolerances of the capacitors. The capacitor’s inner electrode connector must not be used as a mechanical support for other devices or components.

COOLING

- The cooling system is designed to operate at a maximum water pressure of 4 bars (58 psi).
- The water outlet of the capacitor must always be located higher than the water inlet in a vertical installation. This allows any air to escape from the unit. Horizontal installations require that both water connections be at the top-side of the unit. To preserve the capacitors from frost damages during the transport, we offer special models with outlet screws for emptying the cooling water from the unit.
- The minimum water flow rates specified in the tables must be observed. When using antifreeze mixtures, the flow rate should be increased by at least 20 %.
- The cooling system is designed to have a water temperature increase of < 10 °C (water inlet to water outlet) when the capacitor is operated at full rated power and the minimum water flow rate. A water intake temperature of ≤ 30 °C is recommended. If the cooling system of several capacitors is connected in series, the intake temperature of the coolant must not exceed 50 °C for any capacitors.
- The pressure drop in a series connected cooling system is small. The table below illustrates the effects upon water flow rates as a function of the number of series connected TWXF 135285 capacitors in the system with a constant intake water pressure of 3 bars (43.5 psi).

| Number of cooling systems in series | 1 | 2 | 3 | 4 | 5 |
|-------------------------------------|------|------|------|------|------|
| Water flow rate (liters/minute) | 13.0 | 10.5 | 8.5 | 7.3 | 6.0 |
| Water flow rate (US-gal./minute) | 3.43 | 2.77 | 2.24 | 1.92 | 1.58 |

- Intake water temperature fluctuations in excess of 3 °C/s must be avoided to prevent damage to the capacitor elements.
- A coolant temperature rate monitor must provide a fail-safe on / off power control for the RF equipment.
- Normal tap water or de-mineralized water may be used for cooling. The water must be reasonably free of CaCO₃ and clear of foreign particles or milkiness. The pH-value of the coolant should be between 6 and 8.



QUALITY AND RELIABILITY

ELECTRICAL AND MECHANICAL SCREENING TESTS

All capacitors are subjected to the following tests prior to shipment:

- Capacitance value (1.0 MHz or 0.1 MHz, 20 V_{RMS}, 25 °C ± 5 °C)
- Dissipation factor (1.0 MHz or 0.3 MHz, 10 V_{RMS}, 25 °C ± 5 °C)
- Insulation resistance (100 V_{DC}, 25 °C ± 5 °C)
- Dielectric strength (200 % rated peak voltage, 50 Hz, 5 minutes)
- RF power test (125 % to 140 % rated power for 10 minutes in a test generator circuit)
- Pressure test (standard: 6 bars [87 psi] for 1 minute, 25 °C ± 5 °C)

WARRANTY STIPULATION FOR WATER COOLED CERAMIC POWER RF CAPACITORS

- Unless otherwise provided for hereinafter, warranty shall be governed by General Terms of Sale and Delivery.
- Warranty is assumed for capacitors which fail to operate owing to faults in material or production, and within the warranty period for capacitors
- Excluded from warranty are capacitors prematurely rendered unserviceable owing to improper treatment, overloading, circuit errors, as well as capacitors operated without observing the data given in our catalogue. Warranty is also excluded in cases where faults can no longer be recognized on the capacitor owing to third party interferences. Warranty is only effectively assumed when meeting the requirements referred to hereinafter.
- For claiming warranty, the defective capacitor should be returned to us, if possible in its original packing, within 14 days following the data of failure, being accompanied by the completely filled-in and signed Original Guarantee Certificate. The risks of transportation, as well as any shipping costs and other charges shall in any case be borne by the sender.
- Warranty can only become effective if the defective capacitor is received by us in the same condition as it was when it happened to fail.
- We have the right to inspect any records proving the use of the capacitor.
- The decision as to whether we are obliged to assume warranty for the capacitor shall exclusively rest with us.
- When acknowledging the warranty claim, any non-repairable capacitor shall remain our property. When refusing a warranty claim the defective capacitor will be returned at the customer's expense only if demanded so explicitly when asserting the warranty claim. In case examination required disassembly of the capacitor no claims for damage can be derived therefrom.
- The customer gives us the right to have the system checked in which the capacitor was operated.
- When acknowledging a warranty claim, restitution is made by supplying either a repaired and newly tested capacitor or by supplying a new one.
- Warranty shall only extend to the capacitor itself. Any further claims for damages are excluded.

CONDITIONS OF GUARANTEE

Pursuant to the foregoing stipulations we assume warranty for these water cooled pot capacitors up to a period of 5000 hours of operating service. Any claims for warranty, however will extinguish 24 months following the date of delivery.

| RELATED DOCUMENTS | |
|--------------------------|--|
| General Information | www.vishay.com/doc?22071 |



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.