



The DNA of tech.™

POWER RESISTORS

Vishay Draloric / Beyschlag

Vishay Draloric / Beyschlag Power Resistor Solutions for all Types of Applications



KEY BENEFITS

- Broad portfolio
- High performing products
- Standard, adjustable, and non-inductive types

FEATURES

- Resistor solutions for application-specific requirements, such as:
 - High power (up to 5 kW)
 - Very high temperature range (-55 °C to +450 °C)
 - High voltage
 - High reliability
 - Low ohmic (< 1 Ω)
 - Perfect humidity protection
 - Non-flammable
 - Fully green
 - AEC-Q200
 - MIL-PRF-26
 - Adjustable (E)
 - Non-inductive (Ni)
 - Fully welded construction

RESOURCES

- For technical questions contact: ww1resistors@vishay.com, powresistor@vishay.com



The DNA of tech.™

POWER RESISTORS

Vishay Draloric / Beyschlag

RESISTOR SOLUTIONS FOR SPECIFIC APPLICATION REQUIREMENTS

	Vitreous	Cemented
High Pulse Load	GBS GWS RW GWK G200	ZBS ZWS ZWK AC AC-AT
High Power	GBS GWS RW GWK G200	ZBS ZWS ZWK AC AC-AT
High Voltage	RW GWK	ZWK
High Temperature	GBS GWS RW GWK G200	ZBS ZWS ZWK AC AC-AT
High Reliability	FDG FDK FDP	
Low Ohmic: 0.1 Ω to < 1 Ω	GBS G200 RW	ZBS ZWS ZWK AC AC-AT
AEC-Q200		AC-AT
Green		ZBS ZWS ZWK AC AC-AT
MIL-PRF-26	RW	
Adjustable (E)	GBS E GWS E RW E	ZBS E ZWS E
Non-Inductive (Ni)	GWS Ni RW Ni GWK Ni	ZWS Ni ZWK Ni AC Ni AC-AT Ni




The DNA of tech.™

POWER RESISTORS

Vishay Draloric / Beyschlag

POWER RATINGS FOR STANDARD TYPES






The DNA of tech.™

POWER RESISTORS

Vishay Draloric / Beyschlag

POWER RATINGS FOR ADJUSTABLE (E) TYPES






The DNA of tech.™

POWER RESISTORS

Vishay Draloric / Beyschlag

POWER RATINGS FOR NON-INDUCTIVE (Ni) TYPES











The DNA of tech.™

POWER RESISTORS

Vishay Draloric / Beyschlag

POWER RESISTORS OVERVIEW

VITREOUS WIREWOUND RESISTORS

Series	Description	Features	Applications
GBS 	<ul style="list-style-type: none"> Vitreous wirewound resistors, corrugated ribbon Power rating: 50 W - 1000 W Resistance range: 0.10 Ω - 75 Ω Tolerance: $\pm 5\%$ - $\pm 10\%$ 	<ul style="list-style-type: none"> High power rating up to 1000 W Excellent pulse load capability Low ohmic values Adjustable type (E) available Corrugated ribbon construction for rapid cooling Non-flammable / enhanced humidity protection 	<ul style="list-style-type: none"> Inrush current limiter Capacitor charge / discharge Snubber resistor Brake resistor Filter resistor
GWS 	<ul style="list-style-type: none"> Vitreous wirewound resistors with lugs Power rating: 10 W - 500 W Resistance range: 3.3 Ω - 300 kΩ Tolerance: $\pm 2\%$ - $\pm 10\%$ Operating voltage U_{max}: 250 V - 3000 V 	<ul style="list-style-type: none"> Lugs with various termination styles Excellent pulse load capability Adjustable type (E) available Non-inductive type (Ni) available Non-flammable / enhanced humidity protection 	<ul style="list-style-type: none"> Inrush current limiter Capacitor charge / discharge Snubber resistor Brake resistor Filter resistor
RW 	<ul style="list-style-type: none"> Vitreous wirewound resistors acc. MIL-PRF-26 Power rating: 11 W - 480 W Resistance range: 0.39 Ω - 390 kΩ Tolerance: $\pm 5\%$ - $\pm 10\%$ Operating voltage U_{max}: 120 V - 6000 V 	<ul style="list-style-type: none"> Very high operating voltage Excellent pulse load capability Models acc. to MIL-PRF-26 available Adjustable type (E) available Non-inductive type (Ni) available Non-flammable / enhanced humidity protection 	<ul style="list-style-type: none"> Inrush current limiter Capacitor charge / discharge Snubber resistor Brake resistor Filter resistor HVDC
GWK 	<ul style="list-style-type: none"> Vitreous wirewound resistors with ferrules Power rating: 7 W - 260 W Resistance range: 1.8 Ω - 330 kΩ Tolerance: $\pm 2\%$ - $\pm 10\%$ Operating voltage U_{max}: 280 V - 4000 V 	<ul style="list-style-type: none"> Excellent pulse load capability Non-inductive type (Ni) available Different caps options Easy to change Non-flammable / enhanced humidity protection 	<ul style="list-style-type: none"> Inrush current limiter Capacitor charge / discharge Snubber resistor Brake resistor Filter resistor HVDC
G200 	<ul style="list-style-type: none"> Axial vitreous leaded wirewound resistors Power rating: 4 W - 17 W Resistance range: 0.1 Ω - 120 kΩ Tolerance: $\pm 2\%$ - $\pm 10\%$ Operating voltage U_{max}: 200 V - 650 V 	<ul style="list-style-type: none"> High power dissipation in a small design Excellent pulse load capability Completely welded construction Vitreous coating Non-flammable / enhanced humidity protection 	<ul style="list-style-type: none"> Inrush current limiter Power supplies Snubber resistor Filter resistor
FDG, FDK, FDP 	<ul style="list-style-type: none"> Axial vitreous leaded wirewound resistors Power rating: 3.5 W - 11.5 W Resistance range: 0.1 Ω - 68 kΩ Tolerance: $\pm 2\%$ - $\pm 5\%$ Operating voltage U_{max}: 100 V - 350 V 	<ul style="list-style-type: none"> IECQ-CECC approved to CECC 40 201-801 Established reliability, FRL E7 available Excellent pulse load capability Completely welded construction Vitreous coating Non-flammable / enhanced humidity protection 	<ul style="list-style-type: none"> Inrush current limiter Power supplies Snubber resistor Filter resistor







The DNA of tech.™

POWER RESISTORS

Vishay Draloric / Beyschlag

POWER RESISTORS OVERVIEW

CEMENTED WIREWOUND RESISTORS

Series	Description	Features	Applications
<p>ZBS</p> 	<ul style="list-style-type: none"> Cemented wirewound resistors, corrugated ribbon Power rating: 50 W - 500 W Resistance range: 0.13 Ω - 75 Ω Tolerance: ± 5 % - ± 10 % 	<ul style="list-style-type: none"> All-welded construction Power rating up to 500 W Corrugated ribbon construction for rapid cooling Adjustable type (E) available 	<ul style="list-style-type: none"> Inrush current limiter Capacitor charge / discharge Snubber resistor Brake resistor Filter resistor
<p>ZWS</p> 	<ul style="list-style-type: none"> Cemented wirewound resistors with lugs Power rating: 6 W - 250 W Resistance range: 0.15 Ω - 620 kΩ Tolerance: ± 2 % - ± 10 % Operating voltage U_{max}: 100 V - 12 400 V 	<ul style="list-style-type: none"> Lugs with various termination styles Excellent pulse load capability Adjustable type (E) available Non-inductive type (Ni) available Non-flammable coating according to UL94 V-0 	<ul style="list-style-type: none"> Inrush current limiter Capacitor charge / discharge Snubber resistor Brake resistor Filter resistor
<p>ZWK</p> 	<ul style="list-style-type: none"> Cemented wirewound resistors with ferrules Power rating: 10 W - 150 W Resistance range: 0.24 Ω - 360 kΩ Tolerance: ± 2 % - ± 10 % Operating voltage U_{max}: 470 V - 7400 V 	<ul style="list-style-type: none"> Excellent pulse load capability High operating voltage up to 7350 V Non-inductive type (Ni) available Different caps options Easy to change when mounted with spring clips Non-flammable coating according to UL94 V-0 	<ul style="list-style-type: none"> Inrush current limiter Capacitor charge / discharge Snubber resistor Brake resistor Filter resistor HVDC
<p>AC, AC-AT</p> 	<ul style="list-style-type: none"> Cemented leaded wirewound resistors Power rating: 1 W - 10 W Resistance range: 0.1 Ω - 27 kΩ Tolerance: ± 5 % Operating voltage U_{max}: 50 V - 520 V 	<ul style="list-style-type: none"> AEC-Q200 qualified AC-AT series High power dissipation in small design Non-flammable coating according to UL94 V-0 Excellent pulse load capability Non-inductive type (Ni) available WSZ-form for SMD Mounting 	<ul style="list-style-type: none"> Automotive electronics Industrial electronics Power supplies White goods Pre-charged / discharged applications











The DNA of tech.™

POWER RESISTORS

Vishay Draloric / Beyschlag

ELECTRICAL TERMINALS

	SL	SS	SB	SSB	FST	GDK	GZK	AXIAL
								
GBS	X							
GWS	X	X	X	X	X			
RW	X				X			
GWK						X	X	
G200								X ⁽¹⁾
FDG, FDK, FDP								X
ZBS	X							
ZWS	X	X	X	X	X			
ZWK						X	X	
AC, AC-AT								X ⁽¹⁾

Different mechanical mounting accessories are available, see the datasheet:

www.vishay.com/doc?21015

3D models are available on request, please inquire at

ww1resistors@vishay.com

⁽¹⁾ Various lead forms available:

- EK (single kink)



- DK (double kink)



- RT (radial taped)



- WSZ (Z-form)





The DNA of tech.™

POWER RESISTORS

Vishay Draloric / Beyschlag

STANDARD TYPE - VITREOUS WIREWOUND RESISTORS

Series	Type	Rated Dissipation	Resistance Range	Operating Voltage U _{max}
GBS 	GBS 20 / 100	80 W	0.13 Ω to 6.2 Ω	22 V
	GBS 20 / 165	160 W	0.27 Ω to 12 Ω	44 V
	GBS 20 / 265	300 W	0.47 Ω to 22 Ω	81 V
	GBS 30 / 100	150 W	0.10 Ω to 8.2 Ω	35 V
	GBS 30 / 133	200 W	0.15 Ω to 12 Ω	49 V
	GBS 30 / 165	250 W	0.20 Ω to 16 Ω	63 V
	GBS 30 / 215	300 W	0.27 Ω to 24 Ω	85 V
	GBS 30 / 265	375 W	0.30 Ω to 27 Ω	101 V
	GBS 30 / 330	450 W	0.39 Ω to 36 Ω	125 V
	GBS 45 / 370	750 W	0.75 Ω to 56 Ω	205 V
	GBS 60 / 370	1000 W	0.91 Ω to 75 Ω	274 V
	GWS 	GWS 15	15 W	4.3 Ω to 20 kΩ
GWS 20		20 W	3.6 Ω to 30 kΩ	300 V
GWS 25		25 W	3.6 Ω to 39 kΩ	300 V
GWS 35		30 W	5.1 Ω to 47 kΩ	400 V
GWS 50		40 W	3.3 Ω to 62 kΩ	400 V
GWS 75		65 W	7.5 Ω to 130 kΩ	800 V
GWS 100		80 W	6.8 Ω to 110 kΩ	600 V
GWS 220		160 W	13 Ω to 160 kΩ	1250 V
GWS 300		300 W	24 Ω to 300 kΩ	2500 V
GWS 500		500 W	39 Ω to 270 kΩ	3000 V
GWS 30 / 100		150 W	9.1 Ω to 100 kΩ	1600 V
GWS 30 / 133		200 W	13 Ω to 160 kΩ	2300 V
GWK 	GWK 10	10 W	1.8 Ω to 16 kΩ	280 V
	GWK 20	20 W	2.2 Ω to 27 kΩ	400 V
	GWK 40	30 W	3.3 Ω to 43 kΩ	580 V
	GWK 60	40 W	6.2 Ω to 82 kΩ	850 V
	GWK 100	80 W	8.2 Ω to 82 kΩ	1200 V
	GWK 150	100 W	12 Ω to 110 kΩ	1600 V
	GWK 200	160 W	20 Ω to 180 kΩ	2300 V
	GWK 300	260 W	36 Ω to 330 kΩ	4000 V



The DNA of tech.™

POWER RESISTORS

Vishay Draloric / Beyschlag

Series	Type	Rated Dissipation	Resistance Range	Operating Voltage U _{max.}
RW 	RW 10 / 44	18 W	1.0 Ω to 36 kΩ	400 V
	RW 12 / 25	11 W	0.39 Ω to 13 kΩ	120 V
	RW 12 / 38	15 W	1.0 Ω to 33 kΩ	350 V
	RW 12 / 51	25 W	1.0 Ω to 56 kΩ	600 V
	RW 12 / 76	45 W	2.0 Ω to 91 kΩ	1000 V
	RW 20 / 76	70 W	1.0 Ω to 75 kΩ	1000 V
	RW 20 / 102	90 W	3.0 Ω to 110 kΩ	1400 V
	RW 30 / 102	130 W	2.7 Ω to 160 kΩ	1600 V
	RW 30 / 152	220 W	4.7 Ω to 200 kΩ	2500 V
	RW 30 / 203	300 W	6.8 Ω to 270 kΩ	3600 V
	RW 30 / 267	400 W	8.2 Ω to 390 kΩ	5000 V
	RW 30 / 305	480 W	10 Ω to 300 kΩ	6000 V
	RW 29	11 W	4.3 Ω to 5.6 kΩ	400 V
	RW 30	11 W	3.6 Ω to 2.7 kΩ	120 V
	RW 31	14 W	3.9 Ω to 6.8 kΩ	350 V
	RW 32	17 W	4.3 Ω to 10 kΩ	600 V
	RW 33	26 W	8.2 Ω to 18 kΩ	1000 V
	RW 35	55 W	18 Ω to 43 kΩ	1400 V
	RW 36	78 W	24 Ω to 56 kΩ	1600 V
	RW 37	113 W	33 Ω to 91 kΩ	2500 V
	RW 38	159 W	47 Ω to 150 kΩ	3600 V
RW 47	210 W	75 Ω to 180 kΩ	5000 V	
G200 	G202	4 W	0.10 Ω to 10 kΩ	200 V
	G204	7 W	0.10 Ω to 39 kΩ	350 V
	G206	13 W	0.15 Ω to 68 kΩ	500 V
	G207	17 W	0.20 Ω to 120 kΩ	650 V
FDG, FDK, FDP 	FDG	3.5 W	0.10 Ω to 10 kΩ	100 V
	FDK	6.5 W	0.10 Ω to 39 kΩ	200 V
	FDP	11.5 W	0.15 Ω to 68 kΩ	350 V



The DNA of tech.™

POWER RESISTORS

Vishay Draloric / Beyschlag

STANDARD TYPE - CEMENTED WIREWOUND RESISTOR

Series	Type	Rated Dissipation	Resistance Range	Operating Voltage U _{max.}
ZBS 	ZBS 20 / 100	50 W	0.13 Ω to 6.2 Ω	18 V
	ZBS 20 / 165	100 W	0.27 Ω to 12 Ω	35 V
	ZBS 20 / 265	150 W	0.47 Ω to 22 Ω	57 V
	ZBS 30 / 100	75 W	0.1 Ω to 8.2 Ω	25 V
	ZBS 30 / 133	110 W	0.15 Ω to 12 Ω	36 V
	ZBS 30 / 165	150 W	0.20 Ω to 16 Ω	49 V
	ZBS 30 / 215	200 W	0.27 Ω to 24 Ω	69 V
	ZBS 30 / 265	250 W	0.30 Ω to 27 Ω	82 V
	ZBS 30 / 330	300 W	0.39 Ω to 36 Ω	104 V
	ZBS 45 / 370	375 W	0.75 Ω to 56 Ω	145 V
	ZBS 60 / 370	500 W	0.91 Ω to 75 Ω	194 V
ZWS 	ZWS 6	6 W	0.82 Ω to 13 kΩ	250 V
	ZWS 8	8 W	0.68 Ω to 20 kΩ	400 V
	ZWS 12	12 W	0.62 Ω to 27 kΩ	550 V
	ZWS 15	15 W	0.68 Ω to 33 kΩ	700 V
	ZWS 20	20 W	0.62 Ω to 43 kΩ	900 V
	ZWS 35	35 W	1.1 Ω to 82 kΩ	1500 V
	ZWS 50	50 W	1.3 Ω to 91 kΩ	2100 V
	ZWS 100	100 W	2.7 Ω to 200 kΩ	4450 V
	ZWS 150	150 W	4.7 Ω to 360 kΩ	7300 V
	ZWS 250	250 W	8.2 Ω to 620 kΩ	12 400 V
	ZWS 30 / 100	75 W	2.4 Ω to 180 kΩ	3650 V
	ZWS 30 / 133	110 W	3.3 Ω to 240 kΩ	5100 V
ZWK 	ZWK 10	10 W	0.47 Ω to 22 kΩ	470 V
	ZWK 15	15 W	0.47 Ω to 33 kΩ	705 V
	ZWK 20	20 W	0.75 Ω to 51 kΩ	1010 V
	ZWK 40	40 W	1.5 Ω to 100 kΩ	2000 V
	ZWK 60	60 W	1.8 Ω to 130 kΩ	2800 V
	ZWK 90	90 W	2.7 Ω to 200 kΩ	4300 V
	ZWK 150	150 W	4.7 Ω to 360 kΩ	7400 V
AC, AC-AT 	AC01, AC01-AT	1 W	0.10 Ω to 2.4 kΩ	50 V
	AC03, AC03-AT	3 W	0.10 Ω to 5.1 kΩ	130 V
	AC04, AC04-AT	4 W	0.10 Ω to 6.8 kΩ	170 V
	AC05, AC05-AT	5 W	0.10 Ω to 10 kΩ	230 V
	AC07, AC07-AT	7 W	0.10 Ω to 15 kΩ	330 V
	AC10, AC10-AT	10 W	0.22 Ω to 27 kΩ	520 V






The DNA of tech.™

POWER RESISTORS

Vishay Draloric / Beyschlag

ADJUSTABLE TYPE - VITREOUS WIREWOUND RESISTORS

Series	Type	Rated Dissipation	Resistance Range	Operating Voltage U _{max.}
GBS E 	GBS 20 / 100 E	50 W	0.13 Ω to 6.2 Ω	18 V
	GBS 20 / 165 E	100 W	0.27 Ω to 12 Ω	35 V
	GBS 20 / 265 E	180 W	0.47 Ω to 22 Ω	63 V
	GBS 30 / 100 E	90 W	0.10 Ω to 8.2 Ω	27 V
	GBS 30 / 133 E	120 W	0.15 Ω to 12 Ω	38 V
	GBS 30 / 165 E	150 W	0.20 Ω to 16 Ω	49 V
	GBS 30 / 215 E	200 W	0.27 Ω to 24 Ω	69 V
	GBS 30 / 265 E	250 W	0.30 Ω to 27 Ω	82 V
	GBS 30 / 330 E	350 W	0.39 Ω to 36 Ω	112 V
	GBS 45 / 370 E	550 W	0.75 Ω to 56 Ω	175 V
	GBS 60 / 370 E	700 W	0.91 Ω to 75 Ω	229 V
	GWS E 	GWS 15 E	10 W	4.3 Ω to 620 Ω
GWS 20 E		15 W	4.3 Ω to 1.0 kΩ	300 V
GWS 25 E		18 W	5.1 Ω to 1.3 kΩ	300 V
GWS 35 E		22 W	6.8 Ω to 1.6 kΩ	400 V
GWS 50 E		30 W	8.2 Ω to 2.0 kΩ	400 V
GWS 75 E		45 W	18 Ω to 3.9 kΩ	800 V
GWS 100 E		60 W	13 Ω to 5.1 kΩ	600 V
GWS 220 E		120 W	30 Ω to 10 kΩ	1250 V
GWS 300 E		200 W	56 Ω to 20 kΩ	2500 V
GWS 500 E		300 W	100 Ω to 36 kΩ	3000 V
GWS 30 / 100 E		110 W	22 Ω to 8.2 kΩ	1600 V
GWS 30 / 133 E		130 W	36 Ω to 13 kΩ	2300 V
RW E 	RW 10 / 44 E	11 W	1.0 Ω to 1.6 kΩ	400 V
	RW 12 / 38 E	14 W	4.3 Ω to 1.5 kΩ	350 V
	RW 12 / 51 E	17 W	1.0 Ω to 2.4 kΩ	600 V
	RW 12 / 76 E	27 W	2.0 Ω to 4.3 kΩ	1000 V
	RW 20 / 76 E	42 W	1.0 Ω to 6.8 kΩ	1000 V
	RW 20 / 102 E	55 W	3.0 Ω to 10 kΩ	1400 V
	RW 30 / 102 E	80 W	2.7 Ω to 15 kΩ	1600 V
	RW 30 / 152 E	130 W	4.7 Ω to 24 kΩ	2500 V
	RW 30 / 203 E	180 W	6.8 Ω to 36 kΩ	3600 V
	RW 30 / 267 E	240 W	8.2 Ω to 47 kΩ	5000 V
	RW 30 / 305 E	290 W	10 Ω to 56 kΩ	6000 V





The DNA of tech.™

POWER RESISTORS

Vishay Draloric / Beyschlag

ADJUSTABLE TYPE - CEMENTED WIREWOUND RESISTORS

Series	Type	Rated Dissipation	Resistance Range	Operating Voltage U _{max.}
ZBS E 	ZBS 20 / 100 E	50 W	0.13 Ω to 6.2 Ω	18 V
	ZBS 20 / 165 E	100 W	0.27 Ω to 12 Ω	35 V
	ZBS 20 / 265 E	150 W	0.47 Ω to 22 Ω	57 V
	ZBS 30 / 100 E	75 W	0.10 Ω to 8.2 Ω	25 V
	ZBS 30 / 133 E	110 W	0.15 Ω to 12 Ω	36 V
	ZBS 30 / 165 E	150 W	0.20 Ω to 16 Ω	49 V
	ZBS 30 / 215 E	200 W	0.27 Ω to 24 Ω	69 V
	ZBS 30 / 265 E	250 W	0.30 Ω to 27 Ω	82 V
	ZBS 30 / 330 E	300 W	0.39 Ω to 36 Ω	104 V
	ZBS 45 / 370 E	375 W	0.75 Ω to 56 Ω	145 V
	ZBS 60 / 370 E	500 W	0.91 Ω to 75 Ω	194 V
	ZWS E 	ZWS 6 E	6 W	0.82 Ω to 4.7 kΩ
ZWS 8 E		8 W	0.62 Ω to 6.8 kΩ	200 V
ZWS 12 E		12 W	0.56 Ω to 9.1 kΩ	300 V
ZWS 15 E		15 W	0.68 Ω to 11 kΩ	400 V
ZWS 20 E		20 W	0.62 Ω to 15 kΩ	500 V
ZWS 35 E		35 W	1.1 Ω to 27 kΩ	950 V
ZWS 50 E		50 W	1.3 Ω to 33 kΩ	1250 V
ZWS 100 E		100 W	2.7 Ω to 68 kΩ	2600 V
ZWS 150 E		150 W	4.7 Ω to 120 kΩ	4200 V
ZWS 250 E		250 W	8.2 Ω to 220 kΩ	7400 V
ZWS 30 / 100 E		75 W	2.4 Ω to 56 kΩ	2000 V
ZWS 30 / 133 E		110 W	3.3 Ω to 82 kΩ	3000 V



The DNA of tech.™

POWER RESISTORS

Vishay Draloric / Beyschlag

NON-INDUCTIVE TYPE - VITREOUS WIREWOUND RESISTORS

Series	Type	Rated Dissipation	Resistance Range	Operating Voltage U _{max.}
GWS Ni 	GWS 15 Ni	10 W	5.1 Ω to 910 Ω	250 V
	GWS 20 Ni	15 W	5.1 Ω to 1.3 kΩ	300 V
	GWS 25 Ni	18 W	6.8 Ω to 1.8 kΩ	300 V
	GWS 35 Ni	22 W	8.2 Ω to 2.4 kΩ	400 V
	GWS 50 Ni	30 W	10 Ω to 3.0 kΩ	400 V
	GWS 75 Ni	45 W	22 Ω to 6.2 kΩ	800 V
	GWS 100 Ni	60 W	24 Ω to 6.8 kΩ	600 V
	GWS 220 Ni	120 W	51 Ω to 16 kΩ	1250 V
	GWS 300 Ni	200 W	100 Ω to 30 kΩ	2500 V
RW Ni 	RW 10 / 44 Ni	11 W	6.2 Ω to 2.4 kΩ	400 V
	RW 12 / 38 Ni	14 W	5.6 Ω to 2.2 kΩ	350 V
	RW 12 / 51 Ni	17 W	9.1 Ω to 3.6 kΩ	600 V
	RW 12 / 76 Ni	27 W	16 Ω to 6.2 kΩ	1000 V
	RW 20 / 76 Ni	42 W	24 Ω to 10 kΩ	1000 V
	RW 20 / 102 Ni	55 W	36 Ω to 15 kΩ	1400 V
GWK Ni 	GWK 10 Ni	7 W	2.4 Ω to 1.0 kΩ	280 V
	GWK 20 Ni	13 W	4.7 Ω to 1.8 kΩ	400 V
	GWK 40 Ni	20 W	6.8 Ω to 2.7 kΩ	580 V
	GWK 60 Ni	25 W	13 Ω to 5.1 kΩ	850 V
	GWK 100 Ni	50 W	27 Ω to 10 kΩ	1200 V
	GWK 150 Ni	60 W	36 Ω to 15 kΩ	1600 V
	GWK 200 Ni	100 W	56 Ω to 22 kΩ	2300 V
	GWK 300 Ni	180 W	100 Ω to 43 kΩ	4000 V



The DNA of tech.™

POWER RESISTORS

Vishay Draloric / Beyschlag

NON-INDUCTIVE TYPE - CEMENTED WIREWOUND RESISTORS

Series	Type	Rated Dissipation	Resistance Range	Operating Voltage U _{max.}
ZWS Ni 	ZWS 6 Ni	6 W	0.15 Ω to 2.4 kΩ	100 V
	ZWS 8 Ni	8 W	0.24 Ω to 3.6 kΩ	150 V
	ZWS 12 Ni	12 W	0.33 Ω to 5.1 kΩ	200 V
	ZWS 15 Ni	15 W	0.39 Ω to 6.2 kΩ	300 V
	ZWS 20 Ni	20 W	0.47 Ω to 8.2 kΩ	400 V
	ZWS 35 Ni	35 W	0.91 Ω to 15 kΩ	700 V
	ZWS 50 Ni	50 W	1.1 Ω to 16 kΩ	850 V
	ZWS 100 Ni	100 W	2.2 Ω to 33 kΩ	1800 V
	ZWS 150 Ni	150 W	3.9 Ω to 62 kΩ	3000 V
	ZWS 250 Ni	250 W	6.8 Ω to 110 kΩ	5200 V
	ZWS 30 / 100 Ni	75 W	2.0 Ω to 30 kΩ	1500 V
ZWS 30 / 133 Ni	110 W	2.7 Ω to 43 kΩ	2150 V	
ZWK Ni 	ZWK 10 Ni	10 W	0.24 Ω to 3.9 kΩ	200 V
	ZWK 15 Ni	15 W	0.36 Ω to 5.6 kΩ	300 V
	ZWK 20 Ni	20 W	0.56 Ω to 9.1 kΩ	450 V
	ZWK 40 Ni	40 W	1.1 Ω to 18 kΩ	850 V
	ZWK 60 Ni	60 W	1.5 Ω to 24 kΩ	1200 V
	ZWK 90 Ni	90 W	2.2 Ω to 36 kΩ	1800 V
	ZWK 150 Ni	150 W	3.9 Ω to 62 kΩ	3050 V
AC Ni, AC-AT Ni 	AC01 Ni, AC01-AT Ni	1 W	0.10 Ω to 2.4 kΩ	50 V
	AC03 Ni, AC03-AT Ni	3 W	0.10 Ω to 5.1 kΩ	130 V
	AC04 Ni, AC04-AT Ni	4 W	0.10 Ω to 6.8 kΩ	170 V
	AC05 Ni, AC05-AT Ni	5 W	0.10 Ω to 10 kΩ	230 V
	AC07Ni, AC07-AT Ni	7 W	0.10 Ω to 15 kΩ	330 V
	AC10Ni, AC10-AT Ni	10 W	0.22 Ω to 27 kΩ	520 V



The DNA of tech.™

POWER RESISTORS

Vishay Draloric / Beyschlag

Vishay Intertechnology – A Global Industry Leader

Vishay Intertechnology components are used in virtually all types of electronic devices and equipment, in the industrial, computing, automotive, consumer, telecommunications, military, aerospace, power supplies, and medical markets. Vishay has manufacturing plants in the Americas, Asia, Europe, and Israel, as well as sales offices worldwide. Vishay Intertechnology has a diverse portfolio of semiconductors and passive components, including diodes, MOSFETs (metal-oxide semiconductor field-effect transistors), optoelectronic products, selected integrated circuits (ICs), resistors, inductors, and capacitors. This enables it to provide “one-stop shop” service and offer many different parts for each customer design. Its innovations in technology, successful acquisition strategy, superior product quality, and “one-stop shop” service to customers have made the Company a global industry leader.

www.vishay.com

Two of the most important manufacturers of fixed film resistors are the Vishay Draloric and the Vishay Beyschlag brands.

About Draloric

In 1900, in Germany, Mr. Philip Rosenthal, as a sideline to his established business of porcelain tableware, started to manufacture ceramics for electronic applications. Starting in 1910, these were also made in Selb, Germany. In 1936, this electronic ceramics activity was separated from Rosenthal AG and made part of a joint venture with AEG named Rosenthal Isolatoren GmbH, or “RIG.”

The RIG name lasted until 1974, when AEG took over all of RIG and renamed it “CRL” because of its portfolio of passive components. The name was changed again in 1974 to Draloric Electronic GmbH. With the acquisition of Draloric Electronic GmbH by the electronics division of Corning Glass Works in 1981, the name was changed to Corning-Draloric, which lasted until its acquisition by Vishay Intertechnology in 1987.

Vishay Draloric is a leading brand for MELF resistors and ceramic capacitor products. The Vishay Draloric product portfolio also includes thin film flat chip resistors, leaded film and wirewound resistors, and large ceramic power capacitors. As part of Vishay Intertechnology, Draloric Electronic has had production sites in Israel since 1989, and in the Czech Republic since 1991.

Draloric competitors Roederstein GmbH (resistors and capacitors), and Vitramon GmbH (capacitors only) were acquired by Vishay Intertechnology in 1993 and 1994, respectively, and merged with Draloric Electronic GmbH, which has its headquarters in Selb. Since then, the name Vishay Draloric has been used as a brand name for resistor products.

Visit us at: <http://www.vishay.com/company/brands/draloric>