


# Metallized Polyester Film Capacitors MKT Radial Potted Type



Dimensions in mm

## APPLICATIONS

Blocking, coupling and decoupling. Bypass and energy reservoir

## MARKING

C-value; tolerance; rated voltage; year and week of manufacturer; manufacturer's type designation, manufacturers logo or name, location

## DIELECTRIC

Polyester film

## ELECTRODES

Vacuum deposited aluminum

## ENCAPSULATION

Flame retardant plastic case and epoxy resin (UL-class 94 V-0)

## CONSTRUCTION

Wound mono construction

## LEADS

Tinned wire

## CAPACITANCE TOLERANCE

± 10 %; ± 5 %

## FEATURES

Pitch 5 mm available loose in box, ammopack and taped on reel.

- Material categorization:  
For definitions of compliance please see [www.vishay.com/doc?99912](http://www.vishay.com/doc?99912)

## CAPACITANCE RANGE (E12 SERIES)

0.001 µF to 1.2 µF

## RATED (DC) VOLTAGE

63 V; 100 V; 250 V; 400 V

## RATED (AC) VOLTAGE

40 V; 63 V; 160 V; 200 V

## CLIMATIC CATEGORY

55/125/56

## RATED TEMPERATURE

85 °C

## MAXIMUM APPLICATION TEMPERATURE

125 °C

## REFERENCE SPECIFICATIONS

IEC 60384-2

## PERFORMANCE GRADE


Grade 1 (long life)

## DETAIL SPECIFICATION

For more detailed data and test requirements contact: [dc-film@vishay.com](mailto:dc-film@vishay.com)



## COMPOSITION OF CATALOG NUMBER



## Note

- For detailed tape specification refer to packaging information [www.vishay.com/doc?27139](http://www.vishay.com/doc?27139)

## SPECIFIC REFERENCE DATA

| DESCRIPTION   | VALUE                   |                          |                          |                              |
|---|-------------------------|--------------------------|--------------------------|------------------------------|
| Tangent of loss angle:  | at 1 kHz                | at 10 kHz                | at 100 kHz               | at 1 MHz                     |
| C ≤ 0.1 μF  | ≤ 60 x 10 <sup>-4</sup> | ≤ 120 x 10 <sup>-4</sup> | ≤ 200 x 10 <sup>-4</sup> | ≤ 250 x 10 <sup>-4</sup> (1) |
| 0.1 μF < C ≤ 0.47 μF  | ≤ 60 x 10 <sup>-4</sup> | ≤ 120 x 10 <sup>-4</sup> | ≤ 200 x 10 <sup>-4</sup> | -                            |
| 0.47 μF < C ≤ 1.2 μF  | ≤ 60 x 10 <sup>-4</sup> | ≤ 120 x 10 <sup>-4</sup> | -                        | -                            |
| Rated voltage pulse slope (dU/dt) <sub>R</sub> at                           | 63 V <sub>DC</sub>      | 100 V <sub>DC</sub>      | 250 V <sub>DC</sub>      | 400 V <sub>DC</sub>          |
|   | 100 V/μs                | 160 V/μs                 | 400 V/μs                 | 800 V/μs                     |
| R between leads, for C ≤ 0.33 μF:   |                         |                          |                          |                              |
| at 10 V; 1 min  | > 15 000 MΩ             |                          |                          |                              |
| at 100 V; 1 min   |                         | > 15 000 MΩ              | > 15 000 MΩ              | > 15 000 MΩ                  |
| RC between leads, for C > 0.33 μF   |                         |                          |                          |                              |
| at 10 V; 1 min  | > 5000 s                |                          |                          |                              |
| at 100 V; 1 min   |                         | > 5000 s                 |                          |                              |
| R between interconnected leads and casing (foil method)                     | > 30 000 MΩ             | > 30 000 MΩ              | > 30 000 MΩ              | > 30 000 MΩ                  |
| Withstanding (DC) voltage (cut off current 10 mA) (2); rise time ≤ 1000 V/s | 100 V; 1 min            | 160 V; 1 min             | 400 V; 1 min             | 640 V; 1 min                 |
| Withstanding (DC) voltage between leads and case                            | 200 V; 1 min            | 200 V; 1 min             | 500 V; 1 min             | 800 V; 1 min                 |

## Notes

- (1) Only for 250 V and 400 V for C ≤ 0.01 μF  
 (2) See "Voltage Proof Test for Metalized Film Capacitors": [www.vishay.com/doc?28169](http://www.vishay.com/doc?28169)

Metallized Polyester Film Capacitors  
MKT Radial Potted Type

Vishay BCcomponents

 $U_{Rdc} = 63 \text{ V}$ ;  $U_{Rac} = 40 \text{ V}$ 

| C<br>(μF)   | DIMENSIONS<br>W x H x L<br>(mm) | MASS <sup>(1)</sup><br>(g) | CATALOG NUMBER 2222 470 ... AND PACKAGING                   |   |      |                     |              |            |
|---|---------------------------------|----------------------------|---|---|------|---------------------|--------------|------------|
|   |                                 |                            | AMMOPACK <sup>(2)</sup>                                     |   |      | REEL <sup>(2)</sup> | LOOSE IN BOX |            |
|   |                                 |                            | H = 18.5 mm   |   |      |                     | short leads  | long leads |
|   |                                 |                            | C-tol. = ± 10 %   | C-tol. = ± 5 %  | SPQ  | SPQ                 |              |            |
|   |                                 |                            | last 5 digits of<br>catalog number                          | last 5 digits of<br>catalog number                          |      |                     |              |            |
| Pitch = 5.0 ± 0.3 mm; d <sub>t</sub> = 0.50 ± 0.05 mm |                                 |                            |   |   |      |                     |              |            |
| 0.068<br>0.082<br>0.1                                 | 2.5 x 6.5 x 7.2                 | 0.25                       | 75683<br>75823<br>75104                                     | 76683<br>76823<br>76104                                     | 2000 | 2000                | 2000         | 1000       |
| 0.12<br>0.15<br>0.18<br>0.22<br>0.27<br>0.33<br>0.39  | 3.5 x 8.0 x 7.2                 | 0.35                       | 75124<br>75154<br>75184<br>75224<br>75274<br>75334<br>75394 | 76124<br>76154<br>76184<br>76224<br>76274<br>76334<br>76394 | 1500 | 1500                | 2000         | 1000       |
| 0.47<br>0.56<br>0.68                                  | 4.5 x 9.0 x 7.2                 | 0.45                       | 75474<br>75564<br>75684                                     | 76474<br>76564<br>76684                                     | 1000 | 1000                | 2000         | 1000       |
| 0.82<br>1<br>1.2                                      | 6.0 x 11.0 x 7.2                | 0.60                       | 75824<br>75105<br>75125                                     | 76824<br>76105<br>76125                                     | 750  | 1000                | 2000         | 1000       |

## Notes

<sup>(1)</sup> Net weight for short lead product only<sup>(2)</sup> H = In-tape height;  $P_0$  = Sprocket hole distance; for detailed specifications refer to Packaging Information

- SPQ = Standard packing quantity

 $U_{Rdc} = 100 \text{ V}$ ;  $U_{Rac} = 63 \text{ V}$ 

| C<br>(μF)   | DIMENSIONS<br>W x H x L<br>(mm) | MASS <sup>(1)</sup><br>(g) | CATALOG NUMBER 2222 470 ... AND PACKAGING          |  |      |                     |              |            |
|---|---------------------------------|----------------------------|--|--|------|---------------------|--------------|------------|
|   |                                 |                            | AMMOPACK <sup>(2)</sup>                            |  |      | REEL <sup>(2)</sup> | LOOSE IN BOX |            |
|   |                                 |                            | H = 18.5 mm  |  |      |                     | short leads  | long leads |
|   |                                 |                            | C-tol. = ± 10 %                                    | C-tol. = ± 5 %                                     | SPQ  | SPQ                 |              |            |
|   |                                 |                            | last 5 digits of<br>catalog number                 | last 5 digits of<br>catalog number                 |      |                     |              |            |
| Pitch = 5.0 ± 0.3 mm; d <sub>t</sub> = 0.50 ± 0.05 mm |                                 |                            |  |  |      |                     |              |            |
| 0.022<br>0.027<br>0.033<br>0.039<br>0.047<br>0.056    | 2.5 × 6.5 × 7.2                 | 0.25                       | 85223<br>85273<br>85333<br>85393<br>85473<br>85563 | 86223<br>86273<br>86333<br>86393<br>86473<br>86563 | 2000 | 2000                | 2000         | 1000       |
| 0.068<br>0.082<br>0.1<br>0.12                         | 3.5 × 8.0 × 7.2                 | 0.35                       | 85683<br>85823<br>85104<br>85124                   | 86683<br>86823<br>86104<br>86124                   | 1500 | 1500                | 2000         | 1000       |
| 0.15<br>0.18<br>0.22                                  | 4.5 × 9.0 × 7.2                 | 0.45                       | 85154<br>85184<br>85224                            | 86154<br>86184<br>86224                            | 1000 | 1000                | 2000         | 1000       |
| 0.27<br>0.33<br>0.39<br>0.47                          | 6.0 × 11.0 × 7.2                | 0.65                       | 85274<br>85334<br>85394<br>85474                   | 86274<br>86334<br>86394<br>86474                   | 750  | 1000                | 2000         | 1000       |

## Notes

<sup>(1)</sup> Net weight for short lead product only<sup>(2)</sup> H = In-tape height;  $P_0$  = Sprocket hole distance; for detailed specifications refer to Packaging Information

- SPQ = Standard packing quantity

# Vishay BCcomponents Metallized Polyester Film Capacitors

## MKT Radial Potted Type

$U_{Rdc} = 250\text{ V}$ ;  $U_{Rac} = 160\text{ V}$

| C<br>(μF)   | DIMENSIONS<br>W x H x L<br>(mm) | MASS <sup>(1)</sup><br>(g) | CATALOG NUMBER 2222 470 ... AND PACKAGING |                                    |      |                     |              |            |
|---|---------------------------------|----------------------------|---|------------------------------------|------|---------------------|--------------|------------|
|   |                                 |                            | AMMOPACK <sup>(2)</sup>                   |                                    |      | REEL <sup>(2)</sup> | LOOSE IN BOX |            |
|   |                                 |                            | H = 18.5 mm                               |                                    |      |                     | short leads  | long leads |
|   |                                 |                            | C-tol. = ± 10 %                           | C-tol. = ± 5 %                     | SPQ  | SPQ                 |              |            |
|   |                                 |                            | last 5 digits of<br>catalog number        | last 5 digits of<br>catalog number |      |                     |              |            |
| Pitch = 5.0 ± 0.3 mm; d <sub>t</sub> = 0.50 ± 0.05 mm |                                 |                            |   |                                    |      |                     |              |            |
| 0.01<br>0.012<br>0.015<br>0.018                       | 2.5 x 6.5 x 7.2                 | 0.25                       | 35103                                     | 36103                              | 2000 | 2000                | 2000         | 1000       |
| 35123   |                                 |                            | 36123                                     |                                    |      |                     |              |            |
| 35153   |                                 |                            | 36153                                     |                                    |      |                     |              |            |
| 35183   |                                 |                            | 36183                                     |                                    |      |                     |              |            |
| 0.022<br>0.027<br>0.033<br>0.039                      | 3.5 x 8.0 x 7.2                 | 0.35                       | 35223                                     | 36223                              | 1500 | 1500                | 2000         | 1000       |
| 35273   |                                 |                            | 36273                                     |                                    |      |                     |              |            |
| 35333   |                                 |                            | 36333                                     |                                    |      |                     |              |            |
| 35393   |                                 |                            | 36393                                     |                                    |      |                     |              |            |
| 0.047<br>0.056<br>0.068                               | 4.5 x 9.0 x 7.2                 | 0.45                       | 35473                                     | 36473                              | 1000 | 1000                | 2000         | 1000       |
| 35563   |                                 |                            | 36563                                     |                                    |      |                     |              |            |
| 35683   |                                 |                            | 36683                                     |                                    |      |                     |              |            |
| 0.082<br>0.1<br>0.12                                  | 6.0 x 11.0 x 7.2                | 0.60                       | 35823                                     | 36823                              | 750  | 1000                | 2000         | 1000       |
| 35104   |                                 |                            | 36104                                     |                                    |      |                     |              |            |
| 35124   |                                 |                            | 36124                                     |                                    |      |                     |              |            |

### Notes

<sup>(1)</sup> Net weight for short lead product only

<sup>(2)</sup> H = In-tape height;  $P_0$  = Sprocket hole distance; for detailed specifications refer to Packaging Information

- SPQ = Standard packing quantity

$U_{Rdc} = 400\text{ V}$ ;  $U_{Rac} = 200\text{ V}$

| C<br>(μF)   | DIMENSIONS<br>W x H x L<br>(mm) | MASS <sup>(1)</sup><br>(g) | CATALOG NUMBER 2222 470 ... AND PACKAGING  |  |      |                     |              |             |            |     |
|---|---------------------------------|----------------------------|--|--|------|---------------------|--------------|-------------|------------|-----|
|   |                                 |                            | AMMOPACK <sup>(2)</sup>  |  |      | REEL <sup>(2)</sup> | LOOSE IN BOX |             |            |     |
|   |                                 |                            | H = 18.5 mm  |  |      | SPQ                 | SPQ          | short leads | long leads |     |
|   |                                 |                            | C-tol. = ± 10 %  | C-tol. = ± 5 %   | SPQ  |                     |              | SPQ         | SPQ        | SPQ |
|   |                                 |                            | last 5 digits of<br>catalog number   | last 5 digits of<br>catalog number   |      |                     |              |             |            |     |
| Pitch = 5.0 ± 0.3 mm; d <sub>t</sub> = 0.50 ± 0.05 mm   |                                 |                            |  |  |      |                     |              |             |            |     |
| 0.001<br>0.0012<br>0.0015<br>0.0018<br>0.0022<br>0.0027<br>0.0033<br>0.0039<br>0.0047<br>0.0056<br>0.0068<br>0.0082 | 2.5 x 6.5 x 7.2                 | 0.25                       | 65102<br>65122<br>65152<br>65182<br>65222<br>65272<br>65332<br>65392<br>65472<br>65562<br>65682<br>65822 | 66102<br>66122<br>66152<br>66182<br>66222<br>66272<br>66332<br>66392<br>66472<br>66562<br>66682<br>66822 | 2000 | 2000                | 2000         | 1000        |            |     |
| 0.01<br>0.012<br>0.015  | 3.5 x 8.0 x 7.2                 | 0.35                       | 65103<br>65123<br>65153  | 66103<br>66123<br>66153  | 1500 | 1500                | 2000         | 1000        |            |     |
| 0.018<br>0.022<br>0.027   | 4.5 x 9.0 x 7.2                 | 0.45                       | 65183<br>65223<br>65273  | 66183<br>66223<br>66273  | 1000 | 1000                | 2000         | 1000        |            |     |
| 0.033<br>0.039<br>0.047   | 6.0 x 11.0 x 7.2                | 0.60                       | 65333<br>65393<br>65473  | 66333<br>66393<br>66473  | 750  | 1000                | 2000         | 1000        |            |     |

### Notes

<sup>(1)</sup> Net weight for short lead product only

<sup>(2)</sup> H = In-tape height;  $P_0$  = Sprocket hole distance; for detailed specifications refer to Packaging Information

- SPQ = Standard packing quantity

## MOUNTING

### Normal Use

The capacitors are designed for mounting on printed-circuit boards. The capacitors packed in bandoliers are designed for mounting in printed-circuit boards by means of automatic insertion machines.

For detailed tape specifications refer to: "Packaging Information": [www.vishay.com/doc?28139](http://www.vishay.com/doc?28139)

### Specific Method of Mounting to Withstand Vibration and Shock

In order to withstand vibration and shock tests, it must be ensured that the stand-off pips are in good contact with the printed-circuit board:


- For pitches  $\leq 15$  mm capacitors shall be mechanically fixed by the leads
- For larger pitches the capacitors shall be mounted in the same way and the body clamped

### Space Requirements on Printed-Circuit Board

The maximum space for length ( $l_{max.}$ ), width ( $w_{max.}$ ) and height ( $h_{max.}$ ) of film capacitors to take in account on the printed circuit board is shown in the drawings.

For products with pitch  $\leq 15$  mm,  $\Delta w = \Delta l = 0.3$  mm and  $\Delta h = 0.1$  mm

Eccentricity defined as in drawing. The maximum eccentricity is smaller than or equal to the lead diameter of the product concerned.



## SOLDERING

For general soldering conditions and wave soldering profile, we refer to the application note:

"Soldering Guidelines for Film Capacitors": [www.vishay.com/doc?28171](http://www.vishay.com/doc?28171)

### Storage Temperature

Storage temperature:  $T_{stg} = -25$  °C to  $+40$  °C with RH maximum 80 % without condensation


### Ratings and Characteristics Reference Conditions

Unless otherwise specified, all electrical values apply to an ambient temperature of  $23$  °C  $\pm 1$  °C, an atmospheric pressure of 86 kPa to 106 kPa and a relative humidity of  $50$  %  $\pm 2$  %.


For reference testing, a conditioning period shall be applied over  $96$  h  $\pm 4$  h by heating the products in a circulating air oven at the rated temperature and a relative humidity not exceeding 20 %.

**CHARACTERISTICS**


Capacitance as a function of frequency (typical curve)




Capacitance as a function of ambient temperature (typical curve)



Impedance as a function of frequency (typical curve)



Maximum DC and AC voltage as a function of temperature




Maximum RMS voltage as a function of frequency


Maximum RMS current as a function of frequency

# Metallized Polyester Film Capacitors MKT Radial Potted Type


Vishay BCcomponents




Maximum RMS voltage as a function of frequency





Maximum RMS current as a function of frequency




Maximum RMS voltage as a function of frequency




Maximum RMS current as a function of frequency



Maximum RMS voltage as a function of frequency



Maximum RMS current as a function of frequency



### MAXIMUM RMS CURRENT (SINEWAVE) AS A FUNCTION OF FREQUENCY

The maximum RMS current is defined by  $I_{ac} = \omega \times C \times U_{ac}$ .


$U_{ac}$  is the maximum AC voltage depending on the ambient temperature in the curves "Maximum RMS voltage and AC current as a function of frequency".




# Metallized Polyester Film Capacitors MKT Radial Potted Type

Vishay BCcomponents


Tangent of loss angle as a function of frequency (typical curve)



Insulation resistance as a function of ambient temperature (typical curve)



Maximum allowed component temperature rise ( $\Delta T$ ) as a function of the ambient temperature ( $T_{\text{amb}}$ )



Maximum DC and AC voltage as a function of temperature

**HEAT CONDUCTIVITY (G) AS A FUNCTION OF PITCH AND CAPACITOR BODY THICKNESS IN mW/°C**

| $W_{\max.}$<br>(mm) | HEAT CONDUCTIVITY (mW/°C) |
|---------------------|---------------------------|
|                     | PITCH 5 mm                |
| 2.5                 | 2.5                       |
| 3.5                 | 3.0                       |
| 4.5                 | 4.0                       |
| 6.0                 | 5.5                       |

**POWER DISSIPATION AND MAXIMUM COMPONENT TEMPERATURE RISE**

The power dissipation must be limited in order not to exceed the maximum allowed component temperature rise as a function of the free ambient temperature.


The power dissipation can be calculated according type detail specification “HQN-384-01/101: Technical Information Film Capacitors”.

The component temperature rise ( $\Delta T$ ) can be measured (see section “Measuring the Component Temperature” for more details) or calculated by  $\Delta T = P/G$ :

- $\Delta T$  = Component temperature rise (°C)
- $P$  = Power dissipation of the component (mW)
- $G$  = Heat conductivity of the component (mW/°C)

**MEASURING THE COMPONENT TEMPERATURE**

A thermocouple must be attached to the capacitor body as in:



The temperature is measured in unloaded ( $T_{\text{amb}}$ ) and maximum loaded condition ( $T_C$ ).

The temperature rise is given by  $\Delta T = T_C - T_{\text{amb}}$ .

To avoid radiation or convection, the capacitor should be tested in a wind-free box.

## APPLICATION NOTE AND LIMITING CONDITIONS

These capacitors are not suitable for mains applications as across-the-line capacitors without additional protection, as described hereunder. These mains applications are strictly regulated in safety standards and therefore electromagnetic interference suppression capacitors conforming the standards must be used.

For capacitors connected in parallel, normally the proof voltage and possibly the rated voltage must be reduced. For information depending of the capacitance value and the number of parallel connections contact: [dc-film@vishay.com](mailto:dc-film@vishay.com)

To select the capacitor for a certain application, the following conditions must be checked:

1. The peak voltage ( $U_P$ ) shall not be greater than the rated DC voltage ( $U_{RDC}$ ).
2. The peak-to-peak voltage ( $U_{P-P}$ ) shall not be greater than  $2\sqrt{2} \times U_{RAC}$  to avoid the ionization inception level.
3. The voltage pulse slope ( $dU/dt$ ) shall not exceed the rated voltage pulse slope in an RC-circuit at rated voltage and without ringing. If the pulse voltage is lower than the rated DC voltage, the rated voltage pulse slope may be multiplied by  $U_{RDC}$  and divided by the applied voltage.

For all other pulses following equation must be fulfilled:

$$2 \times \int_0^T \left( \frac{dU}{dt} \right)^2 \times dt < U_{Rdc} \times \left( \frac{dU}{dt} \right)_{rated}$$

T is the pulse duration.

The rated voltage pulse slope is valid for ambient temperatures up to 85 °C. For higher temperatures a derating factor of 3 % per K shall be applied.

4. The maximum component surface temperature rise must be lower than the limits (see graph "Max. allowed component temperature rise").
5. Since in circuits used at voltages over 280 V peak-to-peak the risk for an intrinsically active flammability after a capacitor breakdown (short circuit) increases, it is recommended that the power to the component is limited to 100 times the values mentioned in the table: "Heat Conductivity"
6. When using these capacitors as across-the-line capacitor in the input filter for mains applications the applicant must guarantee that the following conditions are fulfilled in any case (spikes and surge voltages from the mains or line card supply included).
7. For continuous use as series connection with an impedance to the mains, please refer to application note [www.vishay.com/doc?28153](http://www.vishay.com/doc?28153).

### Voltage Conditions for 6 Above

| ALLOWED VOLTAGES                             | $T_{amb} \leq 85\text{ °C}$ | $85\text{ °C} < T_{amb} \leq 100\text{ °C}$ | $100\text{ °C} < T_{amb} \leq 125\text{ °C}$ |
|--|-----------------------------|---|--|
| Maximum continuous RMS voltage               | $U_{RAC}$                   | $0.8 \times U_{RAC}$                        | $0.5 \times U_{RAC}$                         |
| Maximum temperature RMS-overvoltage (< 24 h) | $1.25 \times U_{RAC}$       | $U_{RAC}$                                   | $0.625 \times U_{RAC}$                       |
| Maximum peak voltage ( $V_{O-P}$ ) (< 2 s)   | $1.6 \times U_{RDC}$        | $1.3 \times U_{RDC}$                        | $0.8 \times U_{RDC}$                         |

## INSPECTION REQUIREMENTS

## General Notes:

Sub-clause numbers of tests and performance requirements refer to the “Sectional Specification, Publication IEC 60384-2 and Specific Reference Data”.

## Group C Inspection Requirements

| SUB-CLAUSE NUMBER AND TEST                          | CONDITIONS  | PERFORMANCE REQUIREMENTS   |
|---|---|--|
| <b>SUB-GROUP C1A PART OF SAMPLE OF SUB-GROUP C1</b> |   |  |
| 4.1 Dimensions (detail)                             |   | As specified in chapters “General Data” of this specification  |
| 4.3.1 Initial measurements                          | Capacitance<br>Tangent of loss angle for:<br>$C \leq 10 \text{ nF}$ at 1 MHz<br>$10 \text{ nF} < C \leq 470 \text{ nF}$ at 100 kHz<br>$C > 470 \text{ nF}$ at 10 kHz  | No visible damage  |
| 4.3 Robustness of terminations                      | Tensile: Load 10 N; 10 s<br>Bending: Load 5 N; 4 x 90°  |  |
| 4.4 Resistance to soldering heat                    | Method: 1A<br>Solder bath: 280 °C ± 5 °C<br>Duration: 10 s  |  |
| 4.14 Component solvent resistance                   | Isopropylalcohol at room temperature<br>Method: 2<br>Immersion time: 5 min ± 0.5 min<br>Recovery time: Min. 1 h, max. 2 h   |  |
| 4.4.2 Final measurements                            | Visual examination<br><br>Capacitance<br><br>Tangent of loss angle  | No visible damage<br>Legible marking<br><br>$ \Delta C/C  \leq 2 \%$ of the value measured initially<br><br>Increase of $\tan \delta$<br>$\leq 0.005$ for: $C \leq 10 \text{ nF}$ or<br>$\leq 0.003$ for: $10 \text{ nF} < C \leq 470 \text{ nF}$ or<br>$\leq 0.002$ for: $C > 470 \text{ nF}$<br>Compared to values measured in 4.3.1 |
| <b>SUB-GROUP C1B PART OF SAMPLE OF SUB-GROUP C1</b> |   |  |
| 4.6.1 Initial measurements                          | Capacitance<br>Tangent of loss angle for:<br>$C \leq 10 \text{ nF}$ at 1 MHz<br>$10 \text{ nF} < C \leq 470 \text{ nF}$ at 100 kHz<br>$C > 470 \text{ nF}$ at 10 kHz  |  |
| 4.6 Rapid change of temperature                     | $\theta A = -55 \text{ °C}$<br>$\theta B = +125 \text{ °C}$<br>5 cycles<br>Duration $t = 30 \text{ min}$  |  |
| 4.7 Vibration                                       | Visual examination<br>Mounting:<br>See section “Mounting” of this specification<br>Procedure B4<br>Frequency range: 10 Hz to 55 Hz<br>Amplitude: 0.75 mm or<br>Acceleration 98 m/s <sup>2</sup><br>(whichever is less severe)<br>Total duration 6 h | No visible damage  |
| 4.7.2 Final inspection                              | Visual examination  | No visible damage  |



# Metallized Polyester Film Capacitors Vishay BCcomponents

## MKT Radial Potted Type

| SUB-CLAUSE NUMBER AND TEST   | CONDITIONS   | PERFORMANCE REQUIREMENTS   |
|--|--|--|
| <b>SUB-GROUP C1B PART OF SAMPLE OF SUB-GROUP C1</b>  |  |  |
| 4.9 Shock<br><br>4.9.3 Final measurements  | Mounting:<br>See section "Mounting" of this specification<br>Pulse shape: Half sine<br>Acceleration: 490 m/s <sup>2</sup><br>Duration of pulse: 11 ms<br><br>Visual examination<br>Capacitance<br><br>Tangent of loss angle<br><br>Insulation resistance                         | No visible damage<br>$ \Delta C/C  \leq 5\%$ for $w = 2.5$ mm or<br>$ \Delta C/C  \leq 3\%$ for $w > 2.5$ mm of the value measured in 4.6.1<br>Increase of $\tan \delta$ :<br>$\leq 0.005$ for: $C \leq 10$ nF or<br>$\leq 0.003$ for: $10$ nF $< C \leq 470$ nF or<br>$\leq 0.002$ for: $C > 470$ nF<br>Compared to values measured in 4.6.1<br>As specified in section "Insulation Resistance" of this specification                           |
| <b>SUB-GROUP C1 COMBINED SAMPLE OF SPECIMENS OF SUB-GROUPS C1A AND C1B</b>   |  |  |
| 4.10 Climatic sequence<br>4.10.2 Dry heat<br><br>4.10.3 Damp heat cyclic<br>Test Db, first cycle<br>4.10.4 Cold<br><br>4.10.6 Damp heat cyclic<br>Test Db, remaining cycles<br>4.10.6.2 Final measurements | Temperature: + 125 °C<br>Duration: 16 h<br><br>Temperature: - 55 °C<br>Duration: 2 h<br><br>Voltage proof = $U_{RDC}$ for 1 min within 15 min after removal from test chamber<br>Visual examination<br><br>Capacitance<br><br>Tangent of loss angle<br><br>Insulation resistance | No breakdown or flash-over<br><br>No visible damage<br>Legible marking<br>$ \Delta C/C  \leq 5\%$ of the value measured in 4.4.2 or 4.9.3<br>Increase of $\tan \delta$ :<br>$\leq 0.008$ for: $C \leq 10$ nF or<br>$\leq 0.005$ for: $10$ nF $< C \leq 470$ nF or<br>$\leq 0.003$ for: $C > 470$ nF<br>Compared to values measured in 4.3.1 or 4.6.1<br>$\geq 50\%$ of values specified in section "Insulation Resistance" of this specification |
| <b>SUB-GROUP C2</b>  |  |  |
| 4.11 Damp heat steady state<br>4.11.1 Initial measurements<br><br>4.11.3 Final measurements  | 56 days, 40 °C, 90 % to 95 % RH<br>Capacitance<br>Tangent of loss angle at 1 kHz<br>Voltage proof = $U_{RDC}$ for 1 min within 15 min after removal from test chamber<br>Visual examination<br><br>Capacitance<br>Tangent of loss angle<br><br>Insulation resistance             | No breakdown or flash-over<br><br>No visible damage<br>Legible marking<br>$ \Delta C/C  \leq 5\%$ of the value measured in 4.11.1.<br>Increase of $\tan \delta$ :<br>$\leq 0.005$ for: $C \leq 470$ nF or<br>$\leq 0.003$ for: $C > 470$ nF<br>Compared to values measured in 4.11.1<br>$\geq 50\%$ of values specified in section "Insulation Resistance" of this specification   |

| SUB-CLAUSE NUMBER AND TEST |                      | CONDITIONS   | PERFORMANCE REQUIREMENTS   |   |
|----------------------------|----------------------|--|--|---|
| SUB-GROUP C3               |                      |  |  |   |
| 4.12                       | Endurance            | Duration: 2000 h<br>1.25 x U <sub>RDC</sub> at 85 °C<br>0.625 x U <sub>RDC</sub> at 125 °C                               |  |   |
| 4.12.1                     | Initial measurements | Capacitance<br>Tangent of loss angle for:<br>C ≤ 10 nF at 1 MHz<br>10 nF < C ≤ 470 nF at 100 kHz<br>C > 470 nF at 10 kHz | No visible damage<br>Legible marking<br><br> ΔC/C  ≤ 5 % compared to values measured in 4.12.1<br><br>Increase of tan δ:<br>≤ 0.005 for: C ≤ 10 nF or<br>≤ 0.003 for: 10 nF < C ≤ 470 nF or<br>≤ 0.002 for: C > 470 nF<br>Compared to values measured in 4.12.1<br><br>≥ 50 % of values specified in section “Insulation Resistance” of this specification |   |
| 4.12.5                     | Final measurements   | Visual examination<br><br>Capacitance<br><br>Tangent of loss angle<br><br><br>Insulation resistance                      |  |   |
| SUB-GROUP C4               |                      |  |  |   |
| 4.13                       | Charge and discharge | 10 000 cycles<br>Charged to U <sub>RDC</sub><br>Discharge resistance:<br>$R = \frac{U_R}{C \times 5 \times (dU/dt)_R}$   |  | ΔC/C  ≤ 3 % compared to values measured in 4.13.1<br><br>Increase of tan δ:<br>≤ 0.005 for: C ≤ 10 nF or<br>≤ 0.003 for: 10 nF < C ≤ 470 nF or<br>≤ 0.002 for: C > 470 nF<br>Compared to values measured in 4.13.1<br><br>≥ 50 % of values specified in section “Insulation Resistance” of this specification |
| 4.13.1                     | Initial measurements | Capacitance<br>Tangent of loss angle for:<br>C ≤ 10 nF at 1 MHz<br>10 nF < C ≤ 470 nF at 100 kHz<br>C > 470 nF at 10 kHz |  |   |
| 4.13.3                     | Final measurements   | Capacitance<br><br>Tangent of loss angle<br><br><br>Insulation resistance  |  |   |



## Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Vishay products are not designed for use in life-saving or life-sustaining applications or any application in which the failure of the Vishay product could result in personal injury or death unless specifically qualified in writing by Vishay. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.