

AC Motor Drive

Table of Contents

AC Input, Diode Bridges.....	3
AC Input, Power Factor Correction.....	4
AC Input, X/Y Capacitors.....	5
BIAS Supply (off-line, flyback), Discretes.....	6
BIAS Supply (off-line, flyback), Feedback.....	7
BIAS Supply (off-line, flyback), Power Semiconductors.....	8
Control and Gate Drive, Capacitors.....	9
Control and Gate Drive, Discretes.....	10
Control and Gate Drive, ESD Protection.....	11
Control and Gate Drive, Gate Drive.....	12
Control and Gate Drive, Isolation.....	13
Inverter (DC/AC) Output, Discretes.....	14
Inverter (DC/AC) Output, Power Semiconductors for 3- ϕ Driver Bridge.....	15

AC Motor Drive

VISHAY components used for Motor Drives can include:

- Power MOSFETS
 - High-Power Modules
 - Diodes and Rectifiers
 - Capacitors
 - Resistors
 - Thermistors
 - Visible LEDs
 - Optical Isolators
 - Inductors / EMI Filters
 - Shunt Resistors
 - ESD Protection Devices
 - LDOs
 - Communications Interface ICs
-

Application Overview

A motor can be a simple induction machine that rotates with the connection of a simple AC voltage. In applications that require more precise control of speed, torque, or positioning, it is more common to use a 3-phase motor. In order to control this type of motor, signals must be generated that cause the motor to spin properly, using feedback to close the loop and regulate the desired parameters.

AC Motor Drive : AC Input, Diode Bridges

Single Phase

Product Name	Status	Description	Features	Package	Q-Level
36MB60A		Glass Passivated Bridge Rectifier	600V, 35A	TH / Radial D-34	
GBPC3506A		Glass Passivated Bridge Rectifier	600V; 35A	TH / Radial GBPC	
GSIB1580		Glass Passivated Bridge Rectifier	800V; 15A	TH / Radial GSIB-5S	

AC Motor Drive : AC Input, Power Factor Correction

Aluminum Electrolytic Capacitors

Product Name	Status	Description	Features	Package	Q-Level
101/102 PHR-ST		Screw-Terminal Long useful life 25 V to 450 V	25 V to 450 V 220 µF to 1000000 µF Life@85°C=10000-15000h	Screw Term 35x60 - 90x220	
157 PUM-SI		Snap-In Long useful life 200 V to 450 V	200 V to 450 V 56 µF to 2200 µF Life at 85°C = 5000 h	Snap-In 22x25 to 35x60	

Bulk Capacitor

Product Name	Status	Description	Features	Package	Q-Level
MKP 1848 DC-Link	NEW	DC-link film capacitor	up to 400µF; up to 1200V no electrolyte, long life	TH / Radial	

PFC fast diode

Product Name	Status	Description	Features	Package	Q-Level
15ETX06		UltraFast Diode	600V, 15A, 18 nsec Trr	TH / Radial TO-220AC	
30EPH06		UltraFast Diode	600V, 30A, 35 nsec Trr	TH / Radial TO-247 (2 lead)	
HFA50PA60C		HexFRED Diode	600V, 50A, 75 nsec Trr	TH / Radial TO-247	
VS-8ETX06		UltraFast Diode	600V, 8A, 16 nsec Trr	TH / Radial TO-220AC	

PFC MOSFET

Product Name	Status	Description	Features	Package	Q-Level
IRF32N50K		Power MosFET	500V, Rds(on) = 160 Ω	TH / Radial TO-247	
IRFPS43N50K		Power MosFET	500V, Rds(on) = 90 mΩ	TH / Radial Super TO-247	

Shunt resistor

Product Name	Status	Description	Features	Package	Q-Level
WSL series		Power Metal Strip, for current sensing; low resistance values; tight tolerances; low TCR;	R0002 to R500, 1% TCR ± 75ppm P70 = 0.1W - 10W	SMD 0603-5931	

AC Motor Drive : AC Input, X/Y Capacitors

Film RFI caps

Product Name	Status	Description	Features	Package	Q-Level
BFC2 336 60103		Film capacitor Y2 polypropylene	300V; 10nF; 20%	TH / Radial 5.0x11.0x17.5mm	

AC Motor Drive : BIAS Supply (off-line, flyback), Discretes

Film RFI caps

Product Name	Status	Description	Features	Package	Q-Level
BFC2 336 60103		Film capacitor Y2 polypropylene	300V; 10nF; 20%	TH / Radial 5.0x11.0x17.5mm	

Power Transformer

Product Name	Status	Description	Features	Package	Q-Level
Custom Transformer		Dale Custom Magnetics PWM;PSM and FM Transformers; Power;Filter; Switchmode Transformers;	up to 500MHz 10 Amp max. 50-400Hz, up to 100VA;	TH / SMD Custom	UL; CSA; IEEE; VDE;

Shunt resistor

Product Name	Status	Description	Features	Package	Q-Level
WSHM2818		Power Metal Strip Shunts; Very High Power- Small Size; Low Thermal EMF;	R001...R1, 1% TCR \pm 75ppm P70 = 7W	SMD 2818	AEC-Q200

Tantalum Capacitors

Product Name	Status	Description	Features	Package	Q-Level
592D		Solid Tantalum Chip Capacitors, TANTAMOUNT®, Conformal Coated, Low Profile; Maximum C/V,	4 - 35 V; 1 μ F - 3300 μ F; Cas Hight 2.5mm -1.3mm	SMD A - X Case	
595D		Solid Tantalum Chip Capacitors, TANTAMOUNT®, Conformal Coated, Maximum CV, Low ESR	4 - 50 V; 0,1 μ F - 1500 μ F	SMD T - R Case	

TVS and ESD protection

Product Name	Status	Description	Features	Package	Q-Level
GSOT03 to GSOT36		ESD Protection Diode Low Capacitance; Single Line	VZT=3.3-36V, C=80-800pF	SMD SOT-23	
P4KE series		Transient Voltage Suppressor Diodes	Clamps at 10.5 to 772V	TH / Axial DO-204AL (DO-41)	

AC Motor Drive : BIAS Supply (off-line, flyback), Feedback

Opto Isolator

Product Name	Status	Description	Features	Package	Q-Level
4N25		Optocoupler, Phototransistor Output	Isolation Test Voltage: 5300 VRMS	SMD SMD-6, DIP-6	
CNY17-3		Optocoupler, Phototransistor Output	Isolation Test Voltage: 5300 VRMS	SMD SMD-6, DIP-6	

AC Motor Drive : BIAS Supply (off-line, flyback), Power Semiconductors

Flyback Diode

Product Name	Status	Description	Features	Package	Q-Level
V20100S	NEW	Schottky	100V, 20A, single	TH / Radial TO-220AC	
VS-16CTQ100		Schottky	100V, 16A, dual	TH / Radial TO-220AC	

Flyback Switch

Product Name	Status	Description	Features	Package	Q-Level
IRFIBE30G		Power MosFET	800V, Rds(on) = 3 Ω	TH / Radial FullPak TO-220	
IRFPE40		Power MosFET	800V, Rds(on) = 2 Ω	TH / Radial TO-247	
IRFPE50		Power MosFET	800V, Rds(on) = 1.2 Ω	TH / Radial TO-247	

AC Motor Drive : Control and Gate Drive, Capacitors

Tantalum Capacitors

Product Name	Status	Description	Features	Package	Q-Level
592D		Solid Tantalum Chip Capacitors, TANTAMOUNT®, Conformal Coated, Low Profile; Maximum C/V,	4 - 35 V; 1 μ F - 3300 μ F; Cas Hight 2.5mm -1.3mm	SMD A - X Case	
595D		Solid Tantalum Chip Capacitors, TANTAMOUNT®, Conformal Coated, Maximum CV, Low ESR	4 - 50 V; 0,1 μ F - 1500 μ F	SMD T - R Case	

AC Motor Drive : Control and Gate Drive, Discretes

Switching diode

Product Name	Status	Description	Features	Package	Q-Level
1N4148WS		Small Signal Switching Diodes	VRRM= 50-75Volts; IFRM = 350mA;	SMD SOD-323	
BAS16WS-V		Space saving SMD Packages in SOD323	VRRM= 75Volts	SMD SOD-323	
BAV19WS		Fast Switching	VRRM= 120-250Volts; IFRM=625mA	SMD SOD-323	

Zener clamp diodes

Product Name	Status	Description	Features	Package	Q-Level
SMZJ series		Low Impedance Surface Mount Zener	1.5Watt, 9.1 to 68 Vz	SMD SMBJ	

AC Motor Drive : Control and Gate Drive, ESD Protection

ESD Protection Diodes

Product Name	Status	Description	Features	Package	Q-Level
GSOT03 to GSOT36		ESD Protection Diode Low Capacitance; Single Line	VZT=3.3-36V, C=80-800pF	SMD SOT-23	

AC Motor Drive : Control and Gate Drive, Gate Drive

Gate Drivers

Product Name	Status	Description	Features	Package	Q-Level
LPE-3325		gate drive transformer	Surface Mount Transformer	SMD 6.5x8.2x5.21mm	
VO3120	Soon	Opto IGBT & MOSFET Driver	2.5A drive current	SMD SO-8, DIP-8	

AC Motor Drive : Control and Gate Drive, Isolation

Opto Isolator

Product Name	Status	Description	Features	Package	Q-Level
4N25		Optocoupler, Phototransistor Output	Isolation Test Voltage: 5300 VRMS	SMD SMD-6, DIP-6	
CNY17-3		Optocoupler, Phototransistor Output	Isolation Test Voltage: 5300 VRMS	SMD SMD-6, DIP-6	

AC Motor Drive : Inverter (DC/AC) Output, Discretes

Aluminum Electrolytic Capacitors

Product Name	Status	Description	Features	Package	Q-Level
101/102 PHR-ST		Screw-Terminal Long useful life	25 V to 450 V 220 µF to 1000000 µF Life@85°C=10000-15000h	Screw Terminal 35x60 - 90x220	
157 PUM-SI		Snap-In Long useful life	200 V to 450 V 56 µF to 2200 µF Life at 85°C = 5000 h	Snap-In 22x25 to 35x60	

Braking Resistor

Product Name	Status	Description	Features	Package	Q-Level
RSO 30x250 series		Wirewound High Power Resistor	5R1 - 10R 350W	TH / Screwed Tubes 30x250mm	
RW 20x117 series		Wirewound High Power vitreous resistor	3K3 - 3K9 80W	TH / Screwed Tubes 20x117mm	
VACR		Aluminium Housed Compact Wirewound Resistor	Power Rating up to 500W Humidity Protection High overload capacity		

De-Saturation diodes

Product Name	Status	Description	Features	Package	Q-Level
US1M		Surface Mount Ultrafast Rectifier	1000V, 1A, 75nsec	SMD SMA	

Film caps

Product Name	Status	Description	Features	Package	Q-Level
2222 368 series		Snubber capacitor	1200V 1µF 20%	TH / Radial 22.0x38.0x44.0mm	

Temp Sensor

Product Name	Status	Description	Features	Package	Q-Level
2381 645 90169		NTC Thermistor, Lug Sensor	10KΩ nominal; 5% tolerance	TH / Radial Ring-tongue Lug	

Ultrafast Bootstrap diodes

Product Name	Status	Description	Features	Package	Q-Level
US1J		Surface Mount Ultrafast Rectifier	600V, 1A, 75 nsec	SMD SMA	

AC Motor Drive : Inverter (DC/AC) Output, Power Semiconductors for 3- Driver Bridge

Braking or Inverter Switch

Product Name	Status	Description	Features	Package	Q-Level
IRFP32N50K		Power MosFET	500V, Rds(on) = 160 mΩ	TH / Radial TO-247	
IRFPS40N60K		Power MOSFET	600V, Rds(on) = 130 mΩ	TH / Radial Super TO-247	

Recirculating Diodes

Product Name	Status	Description	Features	Package	Q-Level
VS-HFA25PB60		HexFRED Diode	600V, 25V, 75 nsec trr	TH / Radial TO-247 (2 lead)	