


Metal Film Resistors, Axial, Industrial, Flame Retardant



MATERIAL SPECIFICATIONS

Element	Vacuum-deposited nickel-chrome alloy
Core	Fire-cleaned high purity ceramic
Coating	Flame retardant epoxy, with flameproof undercoat; formulated for higher power, with superior moisture and mechanical protection
Solderability	Continuous satisfactory coverage when tested in accordance with MIL-R-10509

FEATURES

- Flame retardant epoxy coating (UL 94 V-0)
- Especially suited for circuitry where functions, environments and duty cycles demand power resistors
- Controlled temperature coefficient
- Excellent high frequency characteristics
- Exceptionally low noise; typically 0.10 $\mu\text{V/V}$
- Low voltage coefficient to ± 5 ppm/V
- Operating temperature range: -55°C to $+175^\circ\text{C}$
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912


RoHS*
Available

Note

* This datasheet provides information about parts that are RoHS-compliant and / or parts that are non-RoHS-compliant. For example, parts with lead (Pb) terminations are not RoHS-compliant. Please see the information / tables in this datasheet for details.

STANDARD ELECTRICAL SPECIFICATIONS

GLOBAL MODEL	POWER RATING ⁽¹⁾ $P_{25^\circ\text{C}}$ W	POWER RATING ⁽¹⁾ $P_{70^\circ\text{C}}$ W	POWER RATING ⁽¹⁾ $P_{125^\circ\text{C}}$ W	MAXIMUM WORKING VOLTAGE V	RESISTANCE RANGE Ω	TOLERANCE $\pm \%$	TEMPERATURE COEFFICIENT $\pm \text{ppm}/^\circ\text{C}$
CMF65..146	2.5	1.75	1.25	500	1 to 15M	1, 2, 5	100
CMF70..146	3	2	1.5	500	1 to 15M	1, 2, 5	100

Note

⁽¹⁾ Continuous working voltage shall be $\sqrt{P \times R}$ or maximum working voltage, whichever is less.

TECHNICAL SPECIFICATIONS

PARAMETER	UNIT	CMF65...146	CMF70...146
Maximum Working Voltage	V _≡	≤ 500	
Insulation Voltage (1 min)	V _{eff}	> 500	
Voltage Coefficient (Max.)	ppm/V	± 5 (measured between 10 % and full rated voltage)	
Dielectric Strength	V _{AC}	900	
Insulation Resistance	Ω	$\geq 10^{11}$	
Operating Temperature Range	$^\circ\text{C}$	-55 to $+175$	
Terminal Strength (Pull test)	lb	2	5
Noise	dB	0.10 $\mu\text{V/V}$ over a decade of frequency, with low and intermediate resistance values typically below 0.5 $\mu\text{V/V}$	
Weight (Max.)	g	1.20	1.30

GLOBAL PART NUMBER INFORMATION

Global Part Numbering: CMF6551K100FKCP146 (preferred part numbering format)

C M F 6 5 5 1 K 1 0 0 F K C P 1 4 6

GLOBAL MODEL
CMF65
CMF70

RESISTANCE VALUE
R = Ω
K = k Ω
M = M Ω
10R000 = 10 Ω
1K3300 = 1.33 k Ω
1M0000 = 1.0 M Ω

TOLERANCE CODE
F = $\pm 1 \%$
G = $\pm 2 \%$
J = $\pm 5 \%$


TEMP. COEFFICIENT
K = 100 ppm

PACKAGING
EK = lead (Pb)-free, bulk
EA = lead (Pb)-free, T/R (1000 pieces)
BF = tin/lead, bulk
CP = tin/lead, T/R (1000 pieces)

SPECIAL
(Dash number)
146 = flame retardant

Note



- For additional information on packaging, refer to the Through Hole Resistor Packaging document (www.vishay.com/doc?31544).

**DIMENSIONS** in inches (millimeters)

GLOBAL MODEL	A	B	C (Max.)	D
CMF65..146	0.562 ± 0.031 (14.27 ± 0.79)	0.215 ± 0.015 (5.46 ± 0.38)	0.687 (17.45)	0.025 ± 0.002 (0.64 ± 0.05)
CMF70..146	0.562 ± 0.031 (14.27 ± 0.79)	0.230 ± 0.015 (5.84 ± 0.38)	0.687 (17.45)	0.032 ± 0.002 (0.81 ± 0.05)

Note

(1) Lead length for product in bulk pack. For product supplied in tape and reel, the actual lead length would be based on body size, tape spacing, and lead trim.

DERATING**THERMAL RESISTANCE****PERFORMANCE**

TEST (TEST METHODS - MIL-STD-202)	AT +70 °C	AT +125 °C
	MAXIMUM ΔR (TYPICAL TEST LOTS)	
Short Time Overload	± 0.05 %	± 0.05 %
Low Temperature Operation	± 0.05 %	± 0.05 %
Moisture Resistance	± 0.05 %	± 0.05 %
Shock	± 0.01 %	± 0.01 %
Vibration	± 0.04 %	± 0.04 %
Temperature Cycling	± 0.15 %	± 0.15 %
Load Life	± 1.0 %	± 1.0 %
Dielectric Withstanding Voltage	± 0.01 %	± 0.01 %
Effect of Solder	± 0.03 %	± 0.03 %

MARKING

CMF65-146, CMF70-146: (5 lines):

DALE Manufacturer

C65-146 Model (C65-146 = CMF65-146, C70-146 = CMF70-146)

49.9KΩ Value

1% T1 Tolerance and TC (T1 = 100 ppm)

1308 4-digit date code



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.