


Metallized Polypropylene Filter Film Capacitors

MKP Radial Potted Type

for Surge Voltage Applications



Dimensions in mm

APPLICATIONS

Low losses due to low contact resistance and low loss dielectric result in applications where high frequency occur or high stability is preferred. Their small dimensions make them suitable for circuits with high packaging density.

MARKING

C-value; rated voltage; tolerance; code for manufacturer; year and week of manufacture; manufacturers type designation

DIELECTRIC

Polypropylene film

ELECTRODES

Vacuum deposited aluminum

ENCAPSULATION

Flame retardant plastic case and epoxy resin (UL-class 94 V-0)

CONSTRUCTION

Wound mono construction

LEADS

Tinned wire

CAPACITANCE RANGE (E24 SERIES)

0.001 to 0.047 μ F

FEATURES

7.5 and 10 mm lead pitch. Supplied loose in box and ammpack. Withstand surge voltages up to 1.5 kV.

Lead (Pb)-free product

RoHS-compliant product



RoHS
COMPLIANT

CAPACITANCE TOLERANCE

$\pm 5 \%$; $\pm 2 \%$

RATED (DC) VOLTAGE

630 V

RATED (AC) VOLTAGE

160 V

RATED PEAK-TO-PEAK VOLTAGE

450 V

CLIMATIC CATEGORY

55/085/56

RATED TEMPERATURE (DC)

85 °C

RATED TEMPERATURE (AC)

85 °C

MAXIMUM APPLICATION TEMPERATURE

85 °C

REFERENCE SPECIFICATIONS

IEC 60384-16

PERFORMANCE GRADE

Grade 1 (long life)

STABILITY GRADE

Grade 1

DETAIL SPECIFICATION

For more detailed data and test requirements contact:
filmcaps.roeselare@vishay.com



Metallized Polypropylene Filter Film Capacitors Vishay BCcomponents
MKP Radial Potted Type
for Surge Voltage Applications

COMPOSITION OF CATALOG NUMBER

TYPE AND PITCHES	
422	7.5 mm
	10.0 mm

CAPACITANCE (numerically)

MULTIPLIER (nF)	
0.01	2
0.1	3

Example:

103 = 100 x 1 = 100 nF

2222	422	XX	XX	X
BFC2*	422	XX	XX	X

* Use this partnumber for those with access to the Vishay's SAP system and Partners website within the Americas

TYPE	PACKAGING	LEAD CONFIGURATION	PREFERRED TYPES	
			C-TOL	630 V
422	Ammopack	H = 18.5 mm; P ₀ = 12.7 mm	± 2 %	1
				ON REQUEST
422	Ammopack	H = 18.5 mm; P ₀ = 12.7 mm	± 5 %	0
	Loose in box	lead length 4.0 +1.0/-0.5 mm	± 5 %	3
			± 2 %	4

SPECIFIC REFERENCE DATA

DESCRIPTION	VALUE	
Tangent of loss angle: C ≤ 0.0047 μF	at 10 kHz	at 100 kHz
	≤ 5 × 10 ⁻⁴	≤ 15 × 10 ⁻⁴
Rated voltage pulse slope (dU/dt) _R at 630 V (DC)	50 V/μs	
R between leads at 500 V; 1 minute	> 100000 MΩ	
R between interconnected leads and case at 500 V; 1 minute	> 100000 MΩ	
Withstanding (DC) voltage (cut off current 10 mA); rise time 100 V/s	1000 V; 1 minute	
Withstanding (DC) voltage between leads and case	2840 V; 1 minute	

Vishay BCcomponents Metallized Polypropylene Filter Film Capacitors
MKP Radial Potted Type
for Surge Voltage Applications


$U_{Rdc} = 630 \text{ V}$; $U_{Rac} = 160 \text{ V}$; $U_{p-p} = 450 \text{ V}$

C (E 24) (μF)	DIMENSIONS b × h × l (mm)	MASS (g)	CATALOGUE NUMBER AND PACKAGING		
			AMMOPACK		LOOSE IN BOX
			H = 18.5 mm		It = 4.0 + 1.0/– 0.5 mm
			C-tol = ± 2 %	SPQ	SPQ
			last 5 digits of catalog number		
Pitch = 7.5 ± 0.4 mm; d _t = 0.50 ± 0.05 mm					
0.001 0.0011 0.0012 0.0013 0.0015 0.0016 0.0018 0.002 0.0022 0.0024 0.0027	4.0 × 9.0 × 10.0	0.50	11002 11102 11202 11302 11502 11602 11802 12002 12202 12402 12702	1250	1500
0.003 0.0033 0.0036 0.0039	5.0 × 10.5 × 10.0	0.90	13002 13302 13602 13902	1000	1000
0.0043 0.0047	6.0 × 11.5 × 10.0	1.0	14302 14702	750	750
Pitch = 10.0 ± 0.4 mm; d _t = 0.60 ± 0.06 mm					
0.0051 0.0056 0.0062 0.0068 0.0075 0.0082 0.01 0.011 0.012 0.013 0.015 0.016	4.0 × 10.0 × 12.5	0.60	15102 15602 16202 16802 17502 18202 11003 11103 11203 11303 11503 11603	750	1000
0.018 0.02 0.022 0.024	5.0 × 11.0 × 12.5	0.85	11803 12003 12203 12403	600	1000
0.027 0.03 0.033 0.036 0.039 0.043 0.047	6.0 × 12.0 × 12.5	1.10	12703 13003 13303 13603 13903 14303 14703	500	750




Metallized Polypropylene Filter Film Capacitors Vishay BCcomponents
MKP Radial Potted Type
for Surge Voltage Applications


MAXIMUM RMS VOLTAGE (SINEWAVE) AS A FUNCTION OF FREQUENCY



CAPACITANCE



IMPEDANCE





Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Vishay products are not designed for use in life-saving or life-sustaining applications or any application in which the failure of the Vishay product could result in personal injury or death unless specifically qualified in writing by Vishay. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.