

Thick Film Chip Resistors, Zero Ohm Jumper, Industrial / High Reliability



MATERIAL SPECIFICATIONS	
Resistive element	Conductive metal
Encapsulation	Epoxy
Substrate	96 % alumina
Termination	Solder-coated nickel barrier
Solder finish	Pure tin or tin / lead solder alloy

FEATURES

- Same materials and construction as MIL-PRF-32159 jumpers
- Undergoes group A testing to MIL-PRF-32159 (precap visual inspection, thermal shock, DC resistance, 100 % visual inspection) prior to shipping
- Termination: tin / lead wraparound termination over nickel barrier. Also available with lead (Pb)-free wraparound terminations
- Capability to develop specific reliability programs designed to customer requirements
- Size, packaging and materials can be customized for special customer requirements
- Operating temperature range: -65 °C to +155 °C
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912


RoHS*
Available

HALOGEN FREE
Note

* This datasheet provides information about parts that are RoHS-compliant and / or parts that are non RoHS-compliant. For example, parts with lead (Pb) terminations are not RoHS-compliant. Please see the information / tables in this datasheet for details

STANDARD ELECTRICAL SPECIFICATIONS					
GLOBAL MODEL	HISTORICAL MODEL	CASE SIZE	POWER RATING ⁽¹⁾ $P_{70\text{ }^{\circ}\text{C}}$ W	CURRENT RATING A	MAXIMUM RESISTANCE Ω
RCWP0201...99	RCWP-0201-99	0201	0.05	0.5	50m
RCWP0302...99	RCWP-0302-99	0302	0.04	1.1	30m
RCWP0402...99	RCWP-0402-99	0402	0.05	1.2	30m
RCWP0502...99	RCWP-0502-99	0502	0.05	1.3	30m
RCWP0540...99	RCWP-540-99	0504	0.08	2.2	20m
RCWP0603...99	RCWP-0603-99	0603	0.10	1.5	30m
RCWP0550...99	RCWP-550-99	0505	0.125	2.2	20m
RCWP0575...99	RCWP-575-99	0705 ⁽²⁾	0.15	2.7	20m
RCWP5100...99	RCWP-5100-99	1005	0.20	2.8	25m
RCWP1206...99	RCWP-1206-99	1206	0.25	3.2	25m
RCWP5150...99	RCWP-5150-99	1505	0.35	2.1	35m
RCWP1100...99	RCWP-1100-99	1010	0.50	5.0	20m
RCWP1210...99	RCWP-1210-99	1210	0.50	5.0	20m
RCWP7225...99	RCWP-7225-99	2208	0.60	2.5	35m
RCWP2010...99	RCWP-2010-99	2010	0.80	5.7	25m
RCWP2512...99	RCWP-2512-99	2512	1.0	6.3	25m

Notes

⁽¹⁾ Power rating depends on the max. temperature at the solder point, the component placement density and the substrate material


⁽²⁾ MIL case size 0705 and EIA case size 0805 are dimensionally the same





GLOBAL PART NUMBER INFORMATION					
New Global Part Numbering: RCWP5100000ZSWB99 (preferred part numbering format)					
R	C	W	P	5	1 0 0 0 0 0 0 Z S W B 9 9
GLOBAL MODEL (see Standard Electrical Specifications table)	RESISTANCE VALUE 0000 = 0 Ω jumper	TOLERANCE CODE Z = 0 Ω jumper	TEMPERATURE COEFFICIENT S = special, 0 Ω jumper	PACKAGING CODE (1)	
				TP = tin / lead, T/R, plastic tape (full reel; all except 0201 and 1210) S3 = tin / lead, T/R, plastic tape (1000 pieces; all except 0201 and 1210) WB = tin / lead, waffle tray S2 = tin / lead, T/R, plastic tape (500 pieces; all except 0201 and 1210) S6 = tin / lead, T/R, plastic tape (300 pieces; all except 0201 and 1210) UA = tin / lead, T/R, paper tape (full reel; 0201 and 1210 only) UD = tin / lead, T/R, paper tape (1000 pieces; 0201 and 1210 only) UC = tin / lead, T/R, paper tape (500 pieces; 0201 and 1210 only) UB = tin / lead, T/R, paper tape (300 pieces; 0201 and 1210 only) EA = lead (Pb)-free, T/R (full) EB = lead (Pb)-free, T/R (1000 pieces) ET = lead (Pb)-free, waffle tray EC = lead (Pb)-free, T/R (500 pieces) ED = lead (Pb)-free, T/R (300 pieces)	
				SPECIAL 99 = 0 Ω jumper	
Historical Part Number: RCWP-5100-99 (will continue to be accepted)					
RCWP-5100-99			T03		
HISTORICAL MODEL			PACKAGING CODE		

Notes

- For additional information on packaging, refer to the Surface Mount Resistor Packaging document (www.vishay.com/doc?31543)
- (1) Tape and reel packaging with plastic tape standard for all case sizes except 0201 and 1210. For the 0201 and 1210 case sizes, the product is only offered in tape and reel packaging with paper tape



DIMENSIONS in inches (millimeters)					
					
GLOBAL MODEL	A (LENGTH)	B (WIDTH)	C (HEIGHT)	D (TOP TERM)	E (BOTTOM TERM)
RCWP0201...99	0.024 ± 0.002 (0.61 ± 0.05)	0.012 ± 0.002 (0.30 ± 0.05)	0.009 ± 0.002 (0.23 ± 0.05)	0.006 ± 0.003 (0.15 ± 0.08)	0.006 + 0.002 - 0.004 (0.15 + 0.05 - 0.10)
RCWP0302...99	0.034 ± 0.004 (0.86 ± 0.10)	0.021 ± 0.003 (0.53 ± 0.08)	0.013 ± 0.003 (0.33 ± 0.08)	0.007 ± 0.005 (0.18 ± 0.13)	0.008 ± 0.005 (0.20 ± 0.13)
RCWP0402...99	0.039 ± 0.003 (0.99 ± 0.08)	0.020 ± 0.003 (0.51 ± 0.08)	0.013 ± 0.003 (0.33 ± 0.08)	0.010 ± 0.005 (0.25 ± 0.13)	0.010 ± 0.005 (0.25 ± 0.13)
RCWP0502...99	0.055 ± 0.005 (1.40 ± 0.13)	0.023 ± 0.003 (0.58 ± 0.08)	0.015 ± 0.003 (0.38 ± 0.08)	0.010 ± 0.005 (0.25 ± 0.13)	0.015 ± 0.005 (0.38 ± 0.13)
RCWP0540...99	0.055 ± 0.005 (1.40 ± 0.13)	0.040 ± 0.005 (1.02 ± 0.13)	0.020 ± 0.005 (0.51 ± 0.13)	0.010 ± 0.005 (0.25 ± 0.13)	0.010 ± 0.005 (0.25 ± 0.13)
RCWP0550...99	0.055 ± 0.005 (1.40 ± 0.13)	0.050 ± 0.005 (1.27 ± 0.13)	0.020 ± 0.005 (0.51 ± 0.13)	0.010 ± 0.005 (0.25 ± 0.13)	0.015 ± 0.005 (0.38 ± 0.13)
RCWP0575...99	0.080 ± 0.005 (2.03 ± 0.13)	0.050 ± 0.005 (1.27 ± 0.13)	0.020 ± 0.005 (0.51 ± 0.13)	0.016 ± 0.008 (0.41 ± 0.20)	0.015 ± 0.005 (0.38 ± 0.13)
RCWP0603...99	0.063 ± 0.005 (1.60 ± 0.13)	0.032 ± 0.005 (0.81 ± 0.13)	0.018 ± 0.005 (0.46 ± 0.13)	0.012 ± 0.005 (0.30 ± 0.13)	0.015 ± 0.005 (0.38 ± 0.13)
RCWP1100...99	0.105 ± 0.005 (2.67 ± 0.13)	0.100 ± 0.005 (2.54 ± 0.13)	0.020 ± 0.005 (0.51 ± 0.13)	0.015 ± 0.005 (0.38 ± 0.13)	0.015 ± 0.005 (0.38 ± 0.13)
RCWP1206...99	0.125 ± 0.005 (3.18 ± 0.13)	0.063 ± 0.005 (1.60 ± 0.13)	0.020 ± 0.005 (0.51 ± 0.13)	0.015 ± 0.005 (0.38 ± 0.13)	0.015 ± 0.005 (0.38 ± 0.13)
RCWP1210...99	0.126 ± 0.008 (3.20 ± 0.20)	0.098 ± 0.008 (2.50 ± 0.20)	0.022 ± 0.002 (0.55 ± 0.05)	0.016 ± 0.008 (0.40 ± 0.20)	0.018 ± 0.008 (0.45 ± 0.20)
RCWP2010...99	0.197 ± 0.006 (5.00 ± 0.15)	0.098 ± 0.005 (2.49 ± 0.13)	0.020 ± 0.005 (0.51 ± 0.13)	0.020 ± 0.005 (0.51 ± 0.13)	0.020 ± 0.005 (0.51 ± 0.13)
RCWP2512...99	0.250 ± 0.006 (6.35 ± 0.15)	0.124 ± 0.005 (3.15 ± 0.13)	0.020 ± 0.005 (0.51 ± 0.13)	0.020 ± 0.005 (0.51 ± 0.13)	0.020 ± 0.005 (0.51 ± 0.13)
RCWP5100...99	0.105 ± 0.005 (2.67 ± 0.13)	0.050 ± 0.005 (1.27 ± 0.13)	0.020 ± 0.005 (0.51 ± 0.13)	0.015 ± 0.005 (0.38 ± 0.13)	0.015 ± 0.005 (0.38 ± 0.13)
RCWP5150...99	0.155 ± 0.005 (3.94 ± 0.13)	0.050 ± 0.005 (1.27 ± 0.13)	0.020 ± 0.005 (0.51 ± 0.13)	0.015 ± 0.005 (0.38 ± 0.13)	0.015 ± 0.005 (0.38 ± 0.13)
RCWP7225...99	0.230 ± 0.005 (5.84 ± 0.13)	0.075 ± 0.005 (1.91 ± 0.13)	0.020 ± 0.005 (0.51 ± 0.13)	0.020 ± 0.005 (0.51 ± 0.13)	0.020 ± 0.005 (0.51 ± 0.13)



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Vishay products are not designed for use in life-saving or life-sustaining applications or any application in which the failure of the Vishay product could result in personal injury or death unless specifically qualified in writing by Vishay. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.