



# HIGH TEMPERATURE ALUMINUM

SMD, RADIAL, AND AXIAL: +125 AND +150 °C

# IN A NUTSHELL



AEC-Q200  
QUALIFIED  
WITH PPAP  
AVAILABLE




LEAD (PB)-FREE  
SOLDERING  
ACCORDING TO  
JEDEC-J-STD-020

### FEATURES

- up to 6800 µF
- up to 100 V
- up to 2000 h / 150°C

### CASE SIZES (mm)

- SMD 8 x 10 up to 18 x 21
- Radial 10 x 12 up to 18 x 40
- Axial 10 x 30 up to 21 x 38



## APPLICATIONS

### INDUSTRIAL



CONTROL UNITS



MACHINERY



AUTOMATION



MOTOR DRIVES




WELDING

### AUTOMOTIVE



UNDER THE HOOD



CHASSIS



POWER TRAIN

## HAPPY HIGH TEMPERATURE CAPS



150 °C  
125 °C



Aluminum electrolytic capacitors for harsh and high temperature operating conditions