

## Low Profile, High Current Coupled Inductor



### LINKS TO ADDITIONAL RESOURCES



3D Models



Calculators

| STANDARD ELECTRICAL SPECIFICATIONS                            |                                                                               |                                       |                                       |                                                            |                                                        |
|---------------------------------------------------------------|-------------------------------------------------------------------------------|---------------------------------------|---------------------------------------|------------------------------------------------------------|--------------------------------------------------------|
|                                                               | $L_0$<br>INDUCTANCE<br>$\pm 20\%$ AT<br>100 kHz,<br>0.25 V, 0 A<br>( $\mu$ H) | DCR<br>NOM.<br>25 °C<br>(m $\Omega$ ) | DCR<br>MAX.<br>25 °C<br>(m $\Omega$ ) | HEAT<br>RATING<br>CURRENT<br>DC TYP.<br>(A) <sup>(1)</sup> | SATURATION<br>CURRENT<br>DC TYP.<br>(A) <sup>(2)</sup> |
| $L_{1-2}$                                                     | 4.7                                                                           | 30.5                                  | 33                                    | 6.1                                                        | 7.2                                                    |
| $L_{3-4}$                                                     | 4.7                                                                           | 30.5                                  | 33                                    | 6.1                                                        | 9.2                                                    |
| $L_{1-4}$<br>( $L_{2-3}$ shorted)                             | 19                                                                            | 61                                    | 65                                    | 4                                                          | 3                                                      |
| $L_{1-3}$<br>( $L_{2-4}$ shorted)                             | 0.6                                                                           | 61                                    | 65                                    | 4                                                          | See note <sup>(3)</sup>                                |
| $L_{\text{Common Mode}}$<br>(1-3 and<br>2-4 shorted)          | 4.7                                                                           | 15.25                                 | 16.2                                  | 10                                                         | 8                                                      |
| $L_{\text{Differential}}$<br>Mode<br>(1-4 and<br>2-3 shorted) | 0.0                                                                           | 15.25                                 | 16.2                                  | 10                                                         | See note <sup>(3)</sup>                                |

#### Notes

- All test data is referenced to 25 °C ambient
  - Operating temperature range -55 °C to +155 °C
  - The part temperature (ambient + temp. rise) should not exceed 155 °C under worst case operating conditions. Circuit design, component placement, PWB trace size and thickness, airflow and other cooling provisions all affect the part temperature. Part temperature should be verified in the end application
  - Rated operating voltage (across inductor) = 50 V
  - SEPIC operation can generate up to 2x the input or output voltage across the inductor. Please limit  $V_{IN}$  and  $V_{OUT}$  to 25 V max. for SEPIC operation
- (1) DC current (A) that will cause an approximate  $\Delta T$  of 40 °C
- (2) DC current (A) that will cause  $L_0$  to drop approximately 20 %
- (3) In this configuration, current flowing opposite directions through coils cancels and the 0.6  $\mu$ H inductance is very stable with varying current. Observe the heat rating current to avoid excessive temperature rise in this configuration

**PATENT(S):** [www.vishay.com/patents](http://www.vishay.com/patents)

This Vishay product is protected by one or more United States and international patents.

### FEATURES

- High temperature, up to 155 °C
- Shielded construction
- Frequency range up to 5.0 MHz
- Lowest DCR/ $\mu$ H in this package size
- Handles high transient current spikes without saturation
- Ultra low buzz noise, due to composite construction
- Coupling is > 90 % - optimized for SEPIC converters
- AEC-Q200 qualified
- IHCL design; PATENT(S): [www.vishay.com/patents](http://www.vishay.com/patents)
- Material categorization: for definitions of compliance please see [www.vishay.com/doc?99912](http://www.vishay.com/doc?99912)


AUTOMOTIVE  
GRADE

**RoHS**  
COMPLIANT  
HALOGEN  
**FREE**  
**GREEN**  
(5-2008)

### APPLICATIONS

- SEPIC converters
- DC/DC converters
- Common mode applications
- LED lighting

### DIMENSIONS in inches [millimeters]








## DESCRIPTION

|                       |                              |                              |              |                                |
|-----------------------|------------------------------|------------------------------|--------------|--------------------------------|
| <b>IHCL-4040DZ-5A</b> | <b>4.7 <math>\mu</math>H</b> | <b><math>\pm 20\%</math></b> | <b>ER</b>    | <b>e3</b>                      |
| MODEL                 | INDUCTANCE VALUE             | INDUCTANCE TOLERANCE         | PACKAGE CODE | JEDEC® LEAD (Pb)-FREE STANDARD |

## GLOBAL PART NUMBER

|                |   |   |   |      |   |   |   |   |   |              |   |                  |   |   |      |        |   |
|----------------|---|---|---|------|---|---|---|---|---|--------------|---|------------------|---|---|------|--------|---|
| I              | H | C | L | 4    | 0 | 4 | 0 | D | Z | E            | R | 4                | R | 7 | M    | 5      | A |
| PRODUCT FAMILY |   |   |   | SIZE |   |   |   |   |   | PACKAGE CODE |   | INDUCTANCE VALUE |   |   | TOL. | SERIES |   |

## PERFORMANCE GRAPHS





## Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Vishay products are not designed for use in life-saving or life-sustaining applications or any application in which the failure of the Vishay product could result in personal injury or death unless specifically qualified in writing by Vishay. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.