


High Precision Wraparound - ± 2 ppm/ $^{\circ}\text{C}$ TCR Thin Film Chip Resistors



LINKS TO ADDITIONAL RESOURCES



For low noise and precision applications, superior stability, low temperature coefficient of resistance, and low voltage coefficient, Vishay Sfernice's proven precision thin film wraparound resistors exceed requirements of MIL-PRF-55342G characteristics typical ± 2 ppm/ $^{\circ}\text{C}$ (-55°C ; $+155^{\circ}\text{C}$).

FEATURES

- Load life stability 0.05 % typical at 2000 h at 70°C under P_n
- Low temperature coefficient: ± 2 ppm/ $^{\circ}\text{C}$ (-55°C ; $+155^{\circ}\text{C}$)
- Very low noise < -35 dB and voltage coefficient < 0.01 ppm/V
- Wide resistance range: 100 Ω to 3.05 M Ω depending on size
- Tolerances to ± 0.01 %
- Termination: thin film technology
- Sulfur resistant (per ASTM B809-95 humid vapor test)
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912



RoHS*
Available

**HALOGEN
FREE**
Available

**GREEN
(5-2008)**
Available

Note

* This datasheet provides information about parts that are RoHS-compliant and / or parts that are non RoHS-compliant. For example, parts with lead (Pb) terminations are not RoHS-compliant. Please see the information / tables in this datasheet for details

STANDARD ELECTRICAL SPECIFICATIONS

MODEL	SIZE	RESISTANCE RANGE (Ω)	RATED POWER W P_n (1)	RATED POWER W P_d (1)	LIMITING ELEMENT VOLTAGE V	TOLERANCE $\pm$ %
P2TC0402	0402	100 to 35K	0.063	0.040	50	0.01, 0.02, 0.05, 0.1, 0.25, 0.5, 1, 2, 5
P2TC0603	0603	100 to 128K	0.125	0.100	75	0.01, 0.02, 0.05, 0.1, 0.25, 0.5, 1, 2, 5
P2TC0805	0805	100 to 291K	0.200	0.125	150	0.01, 0.02, 0.05, 0.1, 0.25, 0.5, 1, 2, 5
P2TC1206	1206	100 to 1.09M	0.330	0.250	200	0.01, 0.02, 0.05, 0.1, 0.25, 0.5, 1, 2, 5
P2TC2010	2010	100 to 3.05M	1	0.500	300	0.01, 0.02, 0.05, 0.1, 0.25, 0.5, 1, 2, 5

Notes

- (1) P_n = nominal power : P_d = derated power intended to improve stability
(2) For ohmic range versus tolerance and TCR see detailed table on next page

CLIMATIC SPECIFICATIONS

Operating temperature range	-55°C ; $+155^{\circ}\text{C}$
-----------------------------	--

Note


- For temperature up to 230°C , see PHT datasheet (www.vishay.com/doc?53050)

PERFORMANCE VS. HUMID SULFUR VAPOR


Test conditions	$50^{\circ}\text{C} \pm 2^{\circ}\text{C}$, 85 % ± 4 % RH, exposure time 500 h
Test results	Resistance drift $< (0.05$ % $R + 0.05$ Ω), no corrosion products observed

MECHANICAL SPECIFICATIONS

Substrate	Alumina
Technology	Thin film
Film	Nickel chromium with mineral passivation
Protection	Epoxy + silicone
Terminations	N type: SnAg over nickel barrier for solder reflow G type: gold over nickel barrier for other applications B type: SnPb over nickel barrier for solder reflow

DIMENSIONS in millimeters (inches)


CASE SIZE	A	B	C	D/E	
	MAX. TOL. +0.152 (+0.006) MIN. TOL. -0.152 (-0.006)	MAX. TOL. +0.127 (+0.005) MIN. TOL. -0.127 (-0.005)			
	NOMINAL	NOMINAL		NOMINAL	TOLERANCE
0402	1.00 (0.039)	0.60 (0.024)	0.5 (0.02) ± 0.127 (0.005)	0.25 (0.010)	0.1 (0.004)
0603	1.52 (0.060)	0.85 (0.033)		0.38 (0.015)	0.13 (0.005)
0805	1.91 (0.075)	1.27 (0.050)		0.40 (0.016)	
1206	3.06 (0.120)	1.60 (0.063)		0.48 (0.019)	
2010	5.08 (0.200)	2.54 (0.100)			


SUGGESTED LAND PATTERN (to IPC-7351A)


CHIP SIZE	DIMENSIONS in millimeters (inches)		
	Z _{max.}	G _{min.}	X _{max.}
0402	1.55 (0.061)	0.15 (0.006)	0.73 (0.029)
0603	2.37 (0.093)	0.35 (0.014)	0.98 (0.039)
0805	2.76 (0.109)	0.74 (0.029)	1.40 (0.055)
1206	3.91 (0.154)	1.85 (0.073)	1.73 (0.068)
2010	5.93 (0.233)	3.71 (0.146)	2.67 (0.105)

TEMPERATURE COEFFICIENT

TYPICAL TCR (ppm/°C)	TYPICAL TCR AND MAX. SPREAD (ppm/°C)
± 2	± 2 ± 2

POWER DERATING CURVE



BEST TOLERANCE AND TCR VS. OHMIC VALUE

STYLE	RANGE (Ω)	TOLERANCE ($\pm$ %)
0402	100 to < 250	0.02; 0.05; 0.1; 0.25; 0.5; 1; 2; 5
	250 to 35K	0.01; 0.02; 0.05; 0.1; 0.25; 0.5; 1; 2; 5
0603	100 to < 250	0.02; 0.05; 0.1; 0.25; 0.5; 1; 2; 5
	250 to 128K	0.01; 0.02; 0.05; 0.1; 0.25; 0.5; 1; 2; 5
0805	100 to < 250	0.02; 0.05; 0.1; 0.25; 0.5; 1; 2; 5
	250 to 291K	0.01; 0.02; 0.05; 0.1; 0.25; 0.5; 1; 2; 5
1206	100 to < 250	0.02; 0.05; 0.1; 0.25; 0.5; 1; 2; 5
	250 to 1M09	0.01; 0.02; 0.05; 0.1; 0.25; 0.5; 1; 2; 5
2010	100 to < 250	0.02; 0.05; 0.1; 0.25; 0.5; 1; 2; 5
	250 to 3M05	0.01; 0.02; 0.05; 0.1; 0.25; 0.5; 1; 2; 5

POPULAR OPTIONS

For any option it is recommended to consult Vishay Sfernice for availability first.

Option: Marking

Option to order 0013:

Marking of ohmic value and tolerance:

Sizes 0805: 3 digits marking according to IEC 60062

Sizes 1206 and 2010: 4 digits marking according to IEC 60062

Tolerance indicated according to IEC 60062.

Option to order 0014:

Marking of ohmic value:

Sizes 0805: 3 digits marking according to IEC 60062

Sizes 1206 and 2010: 4 digits marking according to IEC 60062

No standard marking available for smaller sizes.

A price adder will apply to the unit price of the parts for options 0013 and 0014.

**PACKAGING**

ESD packaging available: waffle-pack, and plastic tape and reel (low conductivity).

SIZE	MOQ	NUMBER OF PIECES PER PACKAGE			TAPE WIDTH
		WAFFLE PACK 2" x 2"	TAPE AND REEL		
			MIN.	MAX.	
0402	100	340	100	5000	8 mm
0603		100		4000	
0805		140		2000	
1206		60			
2010					12 mm

PACKAGING RULES**Waffle Pack**




Can be filled up to maximum quantity indicated in the table here above, taking into account the minimum order quantity. When quantity ordered exceeds maximum quantity of a single waffle pack, the waffle packs are stacked up on the top of each other and closed by one single cover.

To get “not stacked up” waffle pack in case of ordered quantity > maximum number of pieces per package: Please consult Vishay Sfernice for specific ordering code.




Tape and Reel

See Part Numbering information to get the quantity desired by tape.

PERFORMANCE			
TESTS	CONDITIONS	MIL OR CECC REQUIREMENTS	TYPICAL PERFORMANCES
Thermal shock	MIL-PRF-55342G MIL-STD-202 F-Method 107 F	± 0.05 %	± 0.02 %
Short time overload	MIL-PRF-55342G PARA 3.10.4.7.5	± 0.05 %	± 0.01 %
Low temperature operation	MIL-PRF-55342G PARA 3.9 and 4.7.4	± 0.05 %	± 0.01 %
Resistance to solder heat	MIL-PRF-55342G PARA 3.12, 4.7.7, 4.7.1.2	± 0.05 %	± 0.03 %
Moisture resistance	MIL-PRF-55342G PARA 3.13 and 4.7.8 MIL-STD-202 F-Method 106 E	± 0.10 %	± 0.01 %
	CECC 56 days / 40 °C / 93 % RH	± 0.10 %	± 0.01 %
High temperature	MIL-PRF-55342G PARA 3.11 and 4.7.6	± 0.05 %	± 0.05 %
Load life	MIL-PRF-55342G 8000 h Pn at 70 °C MIL-STD-202 F-Method 108 A	± 0.5 %	± 0.1 % ⁽²⁾

Maximum permissible pulse load P_i max. for single pulse ⁽¹⁾

Energy for single pulse ⁽¹⁾

Maximum permissible pulse voltage U_i max. for single pulse ⁽¹⁾

Note

⁽¹⁾ One should apply the datas mentioned on the 3 curves together to get the right performances

Maximum permissible pulse load P_i max.

1.2/50 μ s lightning surge

10/700 μ s lightning surge




GLOBAL PART NUMBER INFORMATION

New Global Part Numbering: P2TC1206D1003BNT99

P	2	T	C	1	2	0	6	D	1	0	0	3	B	N	T	9	9
GLOBAL MODEL		SIZE	TCR	VALUE				TOLERANCE		TERMINATION		PACKAGING		OPTION			
P2TC		0402 0603 0805 1206 2010	D = ± 2 ppm	The first three digits are significant figures and the last digit specifies the number of zeros to follow, R designates decimal point Examples: 1000 = 100 Ω 3901 = 3900 Ω 1004 = 1 MΩ				L = ± 0.01 % P = ± 0.02 % W = ± 0.05 % B = ± 0.1 % C = ± 0.25 % D = ± 0.5 % F = ± 1 % G = ± 2 % J = ± 5 %		N: SnAg over nickel barrier G: gold over nickel barrier B: SnPb over nickel barrier		For more information see “Codification of packaging” table		For more information see “Codification of packaging” table Leave blank if no option			

CODIFICATION OF OPTIONS ON TWO DIGITS

OPTION	OPTION 2 DIGITS
..	..
0099	99
0100	0A
0101	0A
0102	0C
0103	0D
0104	0E
0105	0F
..	..
0124	0Y
0125	0Z
0126	1A
0127	1B
0128	1C
..	..
0320	8M
0321	8N
0322	8O
0323	8P
0324	8Q
0325	8R
..	..

CODIFICATION OF SIZES

CODE 18	CODE 40
9	0402
C	0603
D	0805
H	1206
J	2010

CODIFICATION OF PACKAGING

CODE 18	PACKAGING
WAFFLE PACK	
W	100 min., 1 mult.
WA	100 min., 100 mult. (available only in size 1206)
PLASTIC TAPE (in standard for all sizes)	
T	100 min., 1 mult.
TA	100 min., 100 mult.
TB	250 min., 250 mult.
TC	500 min., 500 mult.
TD	1000 min., 1000 mult.
TE	2500 min., 2500 mult.
TF	Full tape (quantity depending on size of chips)



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Vishay products are not designed for use in life-saving or life-sustaining applications or any application in which the failure of the Vishay product could result in personal injury or death unless specifically qualified in writing by Vishay. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.