P-Channel 20 V (D-S) MOSFET

PRODUCT SUMMARY			
V_{DS} (V)	$R_{DS(on)}$ (Ω) Max.	I_D (A)	Q_g (Typ.)
- 20	0.078 at V_{GS} = - 4.5 V	- 1.4	12.1 nC
	0.098 at V_{GS} = - 2.5 V	- 1	
	0.130 at V_{GS} = - 1.8 V	- 1	
	0.188 at V_{GS} = - 1.5 V	- 0.3	

FEATURES


- TrenchFET® Power MOSFET
- Typical ESD Performance 2500 V
- 100 % R_g Tested
- Material categorization:
  For definitions of compliance please see
  www.vishay.com/doc?99912

Pb-free
RoHS COMPLIANT
HALOGEN FREE

APPLICATIONS


- Load Switch for Portable Devices
- Power Management


SC-89 (6-LEADS)



Top View

Marking Code





P-Channel MOSFET

Ordering Information: Si1077X-T1-GE3 (Lead (Pb)-free and Halogen-free)

ABSOLUTE MAXIMUM RATINGS (T_A = 25 °C, unless otherwise noted)				
Parameter		**Symbol**	**Limit**	**Unit**
Drain-Source Voltage		V_{DS}	- 20	V
Gate-Source Voltage		V_{GS}	± 8	
Continuous Drain Current (T_J = 150 °C)	T_A = 25 °C	I_D	- 1.75[b, c]	A
	T_A = 70 °C		- 1.4[b, c]	
Pulsed Drain Current (t = 300 µs)		I_{DM}	- 8	
Continuous Source-Drain Diode Current	T_A = 25 °C	I_S	- 0.28[b, c]	
Maximum Power Dissipation	T_A = 25 °C	P_D	0.33[b, c]	W
	T_A = 70 °C		0.21[b, c]	
Operating Junction and Storage Temperature Range		T_J, T_{stg}	- 55 to 150	°C

THERMAL RESISTANCE RATINGS					
Parameter		**Symbol**	**Typical**	**Maximum**	**Unit**
Maximum Junction-to-Ambient[a, b]	t ≤ 5 s	R_{thJA}	300	375	°C/W
	Steady State		360	450	

Notes:
a. Maximum under steady state conditions is 450 °C/W.
b. Surface mounted on 1" x 1" FR4 board.
c. t = 5 s.

This document is subject to change without notice.
THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000


SPECIFICATIONS (T_J = 25 °C, unless otherwise noted)						
Parameter	**Symbol**	**Test Conditions**	**Min.**	**Typ.**	**Max.**	**Unit**
Static						
Drain-Source Breakdown Voltage	V_{DS}	V_{GS} = 0 V, I_D = - 250 µA	- 20			V
V_{DS} Temperature Coefficient	$\Delta V_{DS}/T_J$	I_D = - 250 µA		- 11		mV/°C
$V_{GS(th)}$ Temperature Coefficient	$\Delta V_{GS(th)}/T_J$			2.4		
Gate-Source Threshold Voltage	$V_{GS(th)}$	V_{DS} = V_{GS}, I_D = - 250 µA	- 0.4		- 1	V
Gate-Source Leakage	I_{GSS}	V_{DS} = 0 V, V_{GS} = ± 8 V			± 10	µA
		V_{DS} = 0 V, V_{GS} = ± 4.5 V			± 1	
Zero Gate Voltage Drain Current	I_{DSS}	V_{DS} = - 20 V, V_{GS} = 0 V			- 1	
		V_{DS} = - 20 V, V_{GS} = 0 V, T_J = 85 °C			- 10	
On-State Drain Current[a]	$I_{D(on)}$	V_{DS} = ≥ - 5 V, V_{GS} = - 4.5 V	- 8			A
Drain-Source On-State Resistance[a]	$R_{DS(on)}$	V_{GS} = - 4.5 V, I_D = - 1.8 A		0.065	0.078	Ω
		V_{GS} = - 2.5 V, I_D = - 1 A		0.081	0.098	
		V_{GS} = - 1.8 V, I_D = - 1 A		0.100	0.130	
		V_{GS} = - 1.5 V, I_D = - 0.3 A		0.125	0.188	
Forward Transconductance	g_{fs}	V_{DS} = - 10 V, I_D = - 1.8 A		10		S
Dynamic[b]						
Input Capacitance	C_{iss}	V_{DS} = - 10 V, V_{GS} = 0 V, f = 1 MHz		965		pF
Output Capacitance	C_{oss}			110		
Reverse Transfer Capacitance	C_{rss}			101		
Total Gate Charge	Q_g	V_{DS} = - 10 V, V_{GS} = - 8 V, I_D = - 1.75 A		20.7	31.1	nC
		V_{DS} = - 10 V, V_{GS} = - 4.5 V, I_D = - 1.75 A		12.1	18.2	
Gate-Source Charge	Q_{gs}			1.85		
Gate-Drain Charge	Q_{gd}			2.21		
Gate Resistance	R_g	f = 1 MHz	3.6	18	36	Ω
Turn-On Delay Time	$t_{d(on)}$	V_{DD} = - 10 V, R_L = 7.1 Ω I_D ≅ - 1.4 A, V_{GEN} = - 4.5 V, R_g = 1 Ω		24	36	ns
Rise Time	t_r			17	26	
Turn-Off Delay Time	$t_{d(off)}$			95	145	
Fall Time	t_f			28	42	
Turn-On Delay Time	$t_{d(on)}$	V_{DD} = - 10 V, R_L = 7.1 Ω I_D = - 1.4 A, V_{GEN} = - 8 V, R_g = 1 Ω		5	10	ns
Rise Time	t_r			8	16	
Turn-Off Delay Time	$t_{d(off)}$			115	173	
Fall Time	t_f			26	39	
Drain-Source Body Diode Characteristics						
Pulse Diode Forward Current[a]	I_{SM}				- 8	A
Body Diode Voltage	V_{SD}	I_S = - 1.4 A		- 0.75	- 1.2	V
Body Diode Reverse Recovery Time	t_{rr}	I_F = - 1.4 A, dI/dt = 100 A/µs		16	24	ns
Body Diode Reverse Recovery Charge	Q_{rr}			7	14	nC
Reverse Recovery Fall Time	t_a			9		ns
Reverse Recovery Rise Time	t_b			7		

Notes:
a. Pulse test; pulse width ≤ 300 µs, duty cycle ≤ 2 %.
b. Guaranteed by design, not subject to production testing.


Stresses beyond those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated in the operational sections of the specifications is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.

This document is subject to change without notice.
THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000


TYPICAL CHARACTERISTICS (T_A = 25 °C, unless otherwise noted)




Gate Current vs. Gate-Source Voltage




Gate Current vs. Gate-to-Source Voltage




Output Characteristics



Transfer Characteristics Curves vs. Temperature




On-Resistance vs. Drain Current




Capacitance

This document is subject to change without notice.
THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000


TYPICAL CHARACTERISTICS (T_A = 25 °C, unless otherwise noted)




Gate Charge




On-Resistance vs. Junction Temperature




Source-Drain Diode Forward Voltage



On-Resistance vs. Gate-to-Source Voltage




Threshold Voltage




Single Pulse Power, Junction-to-Ambient

This document is subject to change without notice.
THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000


TYPICAL CHARACTERISTICS (T_A = 25 °C, unless otherwise noted)



Safe Operating Area, Junction-to-Ambient



Power Junction-to-Ambient




Normalized Thermal Transient Impedance, Junction-to-Ambient

Vishay Siliconix maintains worldwide manufacturing capability. Products may be manufactured at one of several qualified locations. Reliability data for Silicon Technology and Package Reliability represent a composite of all qualified locations. For related documents such as package/tape drawings, part marking, and reliability data, see www.vishay.com/ppg?63254.

This document is subject to change without notice.
THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000

SC-89 6-Leads (SOT-563F)



Notes

1. Dimensions in millimeters.

2. Dimension D does not include mold flash, protrusions or gate burrs. Mold flush, protrusions or gate burrs shall not exceed 0.15 mm per dimension E1 does not include interlead flash or protrusion, interlead flash or protrusion shall not exceed 0.15 mm per side.

3. Dimensions D and E1 are determined at the outmost extremes of the plastic body exclusive of mold flash, the bar burrs, gate burrs and interlead flash, but including any mismatch between the top and the bottom of the plastic body.

4. Datums A, B and D to be determined 0.10 mm from the lead tip.

5. Terminal numbers are shown for reference only.


6. These dimensions apply to the flat section of the lead between 0.08 mm and 0.15 mm from the lead tip.

DIM.	MILLIMETERS		
	MIN.	NOM.	MAX.
A	0.56	0.58	0.60
A1	0	0.02	0.10
b	0.15	0.22	0.30
c	0.10	0.14	0.18
D	1.50	1.60	1.70
E	1.50	1.60	1.70
E1	1.15	1.20	1.25
e	0.45	0.50	0.55
e1	0.95	1.00	1.05
L	0.25	0.35	0.50
L1	0.10	0.20	0.30
C14-0439-Rev. C, 11-Aug-14 DWG: 5880			

For technical questions, contact: analogswitchtechsupport@vishay.com

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000

RECOMMENDED MINIMUM PADS FOR SC-89: 6-Lead



Recommended Minimum Pads
Dimensions in Inches/(mm)

Return to Index

APPLICATION NOTE

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, “Vishay”), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

© 2024 VISHAY INTERTECHNOLOGY, INC. ALL RIGHTS RESERVED