

LED DISPLAY MODULES

LED-128G032-1



LED Display Modules

LED-128G032-1

128 x 32 Graphics Display with Drive Electronics and +5 V HC CMOS Level Video Interface

The LED-128G032-1 is an LED replacement for the popular APD-128G032 plasma display module. It is designed to offer high brightness and superior viewing characteristics in a slim package. This display is ideal for low to medium level information content and is ideal for applications such as arcade games, process control, POS terminals, medical equipment, message centers and ATM machines.

The LED-128G032-1 LED display offers high contrast, wide viewing angle, and long distance readability. It emits a brilliant orange color which catches the attention of the viewer, but is yet comfortable to the eye.

The LED-128G032-1 LED display has a video type interface and is driven in a standard row/column refresh method. Pixel data is clocked for a row, and rows are scanned sequentially. Signals are presented for SERIAL DATA, DOT CLOCK, COLUMN LATCH, ROW DATA, ROW CLOCK and DISPLAY ENABLE. The SERIAL DATA is entered with the DOT CLOCK up to frequencies as high as 8 MHz. After a row of 128 pixels is clocked in, the COLUMN LATCH signal is toggled and the data is latched. At the time the data is latched, the display is briefly disabled using the DISPLAY ENABLE signal, then the row pointer is advanced with the ROW CLOCK signal. Once each frame the ROW DATA must be asserted to synchronize the column serial data with the beginning row. The recommended scanning frequency is approximately 70 Hz, but may be as high as 200 Hz.

Features

- LED replacement for the popular APD-128G032 plasma display module
- + 5 V HC CMOS level video interface
- Large characters
- Highly visible for long distance viewing
- > 30:1 contrast ratio
- Brilliant neon orange color

| Standard Electrical Specifications* | | | | | |
|---|--------|------------|-------|------------|-------|
| Description | Symbol | Min. | Тур. | Max. | Units |
| Logic and LED Drive Voltage | Vcc | + 4.5 | + 5.0 | + 5.5 | VDC |
| Logic and LED Drive Current (Fully Lit) | lcc | _ | 1.1 | 1.3 | ADC |
| Logic 1 Input | Vih | 0.7 Vcc | _ | _ | VDC |
| Logic 0 Input | Vil | _ | _ | 0.2 Vcc | VDC |

^{*} Recommended operating voltages. All maximums are absolute maximum.

- Slim profile
- Reduced power and brightness version

Electrical Specifications

Voltage(s) Required: + 5 VDC (Vcc)

Power Required (Fully Lit): Typical = 5.5 watts

Maximum = 6.5 watts

Optical Specifications

Viewing Area: 12.75" [323.8 mm] W x 3.15" [80.01 mm] L Character Size (5x7): 0.65" [16.51 mm] H x 0.45" [11.43 mm] W Pixel Size: 0.063" [1.6 mm] H x 0.031" [0.8 mm] W

Pixel Pitch: 0.100" [2.54 mm]

Luminance: 100 foot-lamberts minimum

Color: Neon Orange

Viewing Angle: > 150°

Environmental Specifications

Operating Temperature: $-40 \,^{\circ}\text{C}$ to $+85 \,^{\circ}\text{C}$ Storage Temperature: $-40 \,^{\circ}\text{C}$ to $+85 \,^{\circ}\text{C}$

Relative Operating Humidity: To 95 % non-condensing


Mechanical Shock: 30G Vibration: 3G


Operating Altitude: 10 000 feet

Interface Signal Description

DOT CLOCK - This signal enters the SERIAL DATA on each low to high transition. A total of 128 DOT CLOCK transitions must be present for each line of column/anode data.

SERIAL DATA - This signal presents the pixel data in positive logic format. A logic one represents a lit pixel and a logic







zero represents an extinguished pixel. Data is entered from right to left. The first pixel data entered will represent the left most pixel in the row.

COLUMN LATCH - This signal latches the pixel data into the driver outputs. When the COLUMN LATCH signal goes to logic one the data entered previously will fall through to the driver outputs. When the signal returns to a logic zero the data is latched and the shift register is now ready to accept the next row of data. Must be held low while entering new SERIAL DATA.

DISPLAY ENABLE - This signal enables the output drivers. Using a duty cycle control, this signal may also be used for intensity control. The DISPLAY ENABLE must be at logic zero before the COLUMN LATCH signal transitions. To avoid display blurring, the ROW CLOCK signal should also transition while DISPLAY ENABLE is a logic zero.

ROW DATA - This signal is the first line marker for the scan. This input should be held high to correspond to the first row of pixel data.

ROW CLOCK - This signal clocks ROW DATA on the falling edge. The ROW CLOCK signal is repetitive and must be present for proper scanning of the display module. The LED-128G032-1 has an unique input protection circuit that assures the column drivers stay blanked on power up. The protection circuit unblanks the column drivers when the ROW CLOCK signal begins (i.e the display begins scanning.)

Pin Description

J1 - Power Connector Tyco AMP #640445-8 or equivalent. Mates with Tyco AMP 640428-8, MOLEX 09-05-3081 or equivalent.

| | or order or order | | | | | |
|-------|---|----------|----------------------------|--|--|--|
| | Pin | Signal | Description | | | |
| | 1 | n/c | No connection | | | |
| 2 n/c | | n/c | No connection | | | |
| | 3 | Key | Used to key connector | | | |
| | 4 | GND | GND | | | |
| | 5 | GND | GND | | | |
| | 6 | Vcc | Logic and LED drive supply | | | |
| | 7 | RESERVED | No connection | | | |
| | 8 | n/c | No connection | | | |

J2 - Data Connector


Tyco AMP #103309-2 or equivalent. Mates with Tyco AMP 746195-2, MOLEX 39-27-1146 or equivalent.

| Pin | Description | Pin | Description | | |
|-----|----------------|-----|-------------|--|--|
| 1 | DISPLAY ENABLE | 2 | GROUND | | |
| 3 | ROW DATA | 4 | GROUND | | |
| 5 | ROW CLOCK | 6 | GROUND | | |
| 7 | COLUMN LATCH | 8 | GROUND | | |
| 9 | DOT CLOCK | 10 | GROUND | | |
| 11 | SERIAL DATA | 12 | GROUND | | |
| 13 | NO CONNECT | 14 | GROUND | | |

J3 - Power Connector

Tyco AMP #641737-1 or equivalent. Mates with Tyco AMP 1-480424-0 housing and 60617-4 socket terminals.

| Pin | Signal | Description |
|-----|----------|----------------------------|
| 1 | RESERVED | No connection |
| 2 | GND | |
| 3 | GND | |
| 4 | Vcc | Logic and LED drive supply |



| Parameter | Min. | Тур. | Max. | Units |
|----------------|------|------|------|-------|
| t ₁ | 100 | _ | _ | nS |
| t ₂ | 5 | _ | _ | uS |
| t ₃ | 1 | _ | _ | uS |
| t ₄ | _ | 70 | 200 | Hz |
| t ₅ | 25 | _ | _ | nS |
| t ₆ | 75 | _ | _ | nS |
| t ₇ | 75 | _ | _ | nS |

Ordering Information

| Description | <u>Part Number</u> |
|---|--------------------|
| Display, Driver Electronics and + 5 V HC CMOS Interface J2 Data Connector Kit | |
| (2 pcs. recommended) | 280105-05 |
| J1 Power Connector Kit | 280108-12 |
| J3 Power Connector Kit | 280108-05 |

NOTICE Specifications of the products displayed herein are subject to change without notice. Vishay Intertechnology, Inc., or anyone on its behalf, assumes no responsibility or liability for liability for nap errors or inaccuracies. Information contained herein is intended to provide a product description only. No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document. Except as provided in Vishay's terms and conditions of sale for such products, Vishay assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of Vishay products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right. The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications do so at their own risk and agree to fully indemnify Vishay for any damages resulting from such improper use or sale.

PASSIVE COMPONENTS:

Resistive Products • Magnetics • Capacitors • Strain Gage Transducers and Stress Analysis Systems



One of the World's Largest Manufacturers

of Discrete Semiconductors and Passive Components

THE AMERICAS

UNITED STATES

VISHAY AMERICAS ONE GREENWICH PLACE SHELTON, CT 06484 UNITED STATES PH: +1-402-563-6866

PH: +1-402-563-6866 FAX: +1-402-563-6296

ASIA

SINGAPORE

VISHAY INTERTECHNOLOGY ASIA PTE LTD. 25 TAMPINES STREET 92 KEPPEL BUILDING #02-00 SINGAPORE 528877 PH: +65-6788-6668 FAX: +65-6788-0988

P.R.C.

VISHAY TRADING (SHANGHAI) CO., LTD. (SHANGHAI REPRESENTATIVE OFFICE) ROOM D, 15F, SUN TONG INFOPORT PLAZA 55 HUAI HAI WEST ROAD 200030 SHANGHAI P.R.C.

PH: +86-21-5258-5000 FAX: +86-21-5258-7979

JAPAN

VISHAY JAPAN CO., LTD. MG IKENOHATA BLDG. 4F 1-2-18, IKENOHATA TAITO-KU TOKYO 110-0008 JAPAN

PH: +81-3-5832-6210 FAX: +81-3-5832-6260

EUROPE

GERMANY

VISHAY EUROPE SALES GMBH GEHEIMRAT-ROSENTHAL-STR. 100 95100 SELB GERMANY PH: +49-9287-71-0 FAX: +49-9287-70435

FRANCE

VISHAY S.A.
199, BLVD DE LA MADELEINE
06003 NICE, CEDEX 1
FRANCE
PUb. 123, 4, 0227, 2000

PH: +33-4-9337-2920 FAX: +33-4-9337-2997

NETHERLANDS

VISHAY BCCOMPONENTS B.V. HURKESTRAAT 31 P.O. BOX 8766 5652 AH EINDHOVEN NETHERLANDS PH: +31-40-2590-700 FAX: +31-40-2590-777

www.vishay.com