

Complementary MOSFET Half-Bridge (N- and P-Channel)

PRODUCT SUMMARY


	V_{DS} (V)	$R_{DS(on)}$ (Ω)	I_D (A)
N-Channel	20	0.020 at $V_{GS} = 4.5$ V	9.1
		0.030 at $V_{GS} = 2.5$ V	7.5
P-Channel	- 20	0.060 at $V_{GS} = - 4.5$ V	- 5.3
		0.100 at $V_{GS} = - 2.5$ V	- 4.1

FEATURES


- Halogen-free According to IEC 61249-2-21 Definition
- TrenchFET® Power MOSFET
- Compliant to RoHS Directive 2002/95/EC



RoHS
COMPLIANT
HALOGEN
FREE
Available



Ordering Information: Si4500BDY-T1-E3 (Lead (Pb)-free)
Si4500BDY-T1-GE3 (Lead (Pb)-free and Halogen-free)



ABSOLUTE MAXIMUM RATINGS $T_A = 25$ °C, unless otherwise noted

Parameter		Symbol	N-Channel		P-Channel		Unit
			10 s	Steady State	10 s	Steady State	
Drain-Source Voltage		V _{DS}	20		- 20		V
Gate-Source Voltage		V _{GS}	± 12		± 12		
Continuous Drain Current (T _J = 150 °C) ^{a,b}	T _A = 25 °C	I _D	9.1	6.6	- 5.3	- 3.8	A
	T _A = 70 °C		7.3	5.3	- 4.9	- 3.1	
Pulsed Drain Current		I _{DM}	30		- 20		
Continuous Source Current (Diode Conduction) ^{a,b}		I _S	2.1	1.1	- 2.1	- 1.1	
Maximum Power Dissipation ^{a,b}	T _A = 25 °C	P _D	2.5	1.3	2.5	1.3	W
	T _A = 70 °C		1.6	0.8	1.6	0.8	
Operating Junction and Storage Temperature Range		T _J , T _{stg}	- 55 to 150				°C

THERMAL RESISTANCE RATINGS

Parameter		Symbol	N-Channel		P-Channel		Unit
			Typ.	Max.	Typ.	Max.	
Maximum Junction-to-Ambient ^a	$t \leq 10$ s	R_{thJA}	40	50	41	50	°C/W
	Steady State		75	95	75	95	
Maximum Junction-to-Foot (Drain)	Steady State	R_{thJF}	20	22	23	26	

Notes:

a. Surface Mounted on FR4 board.

b. $t \leq 10$ s.

SPECIFICATIONS T _J = 25 °C, unless otherwise noted							
Parameter	Symbol	Test Conditions		Min.	Typ. ^a	Max.	Unit
Static							
Gate Threshold Voltage	V _{GS(th)}	V _{DS} = V _{GS} , I _D = 250 μA	N-Ch	0.6		1.5	V
		V _{DS} = V _{GS} , I _D = - 250 μA	P-Ch	- 0.6		- 1.5	
Gate-Body Leakage	I _{GSS}	V _{DS} = 0 V, V _{GS} = ± 12 V	N-Ch			± 100	nA
			P-Ch			± 100	
Zero Gate Voltage Drain Current	I _{DSS}	V _{DS} = 20 V, V _{GS} = 0 V	N-Ch			1	μA
		V _{DS} = - 20 V, V _{GS} = 0 V	P-Ch			- 1	
		V _{DS} = 20 V, V _{GS} = 0 V, T _J = 55 °C	N-Ch			5	
		V _{DS} = - 20 V, V _{GS} = 0 V, T _J = 55 °C	P-Ch			- 5	
On-State Drain Current ^b	I _{D(on)}	V _{DS} = 5 V, V _{GS} = 4.5 V	N-Ch	30			A
		V _{DS} = - 5 V, V _{GS} = - 4.5 V	P-Ch	- 20			
Drain-Source On-State Resistance ^b	R _{DS(on)}	V _{GS} = 4.5 V, I _D = 9.1 A	N-Ch		0.016	0.020	Ω
		V _{GS} = - 4.5 V, I _D = - 5.3 A	P-Ch		0.048	0.060	
		V _{GS} = 2.5 V, I _D = 3.3 A	N-Ch		0.024	0.030	
		V _{GS} = - 2.5 V, I _D = - 1 A	P-Ch		0.082	0.100	
Forward Transconductance ^b	g _{fs}	V _{DS} = 15 V, I _D = 9.1 A	N-Ch		29		S
		V _{DS} = - 15 V, I _D = - 5.3 A	P-Ch		11		
Diode Forward Voltage ^b	V _{SD}	I _S = 2.1 A, V _{GS} = 0 V	N-Ch		0.8	1.2	V
		I _S = - 2.1 A, V _{GS} = 0 V	P-Ch		- 0.8	- 1.2	
Dynamic ^a							
Total Gate Charge	Q _g	N-Channel V _{DS} = 10 V, V _{GS} = 4.5 V, I _D = 9.1 A	N-Ch		11	17	nC
Gate-Source Charge	Q _{gs}		P-Ch		6.0	9	
		Gate-Drain Charge	Q _{gd}	P-Channel V _{DS} = - 10 V, V _{GS} = - 4.5 V, I _D = - 5.3 A	N-Ch		
P-Ch					1.3		
Turn-On Delay Time	t _{d(on)}	N-Channel V _{DD} = 10 V, R _L = 10 Ω I _D ≅ 1 A, V _{GEN} = 10 V, R _g = 6 Ω	N-Ch		35	50	ns
			P-Ch		20	30	
Rise Time	t _r		N-Ch		50	80	
			P-Ch		35	60	
Turn-Off Delay Time	t _{d(off)}	P-Channel V _{DD} = - 10 V, R _L = 10 Ω I _D ≅ - 1 A, V _{GEN} = - 4.5 V, R _g = 6 Ω	N-Ch		31	50	
			P-Ch		55	85	
Fall Time	t _f		N-Ch		15	30	
			P-Ch		35	60	
Source-Drain Reverse Recovery Time	t _{rr}	I _F = 2.1 A, dI/dt = 100 A/μs	N-Ch		30	60	
		I _F = - 2.1 A, dI/dt = 100 A/μs	P-Ch		25	50	







Notes:


a. Guaranteed by design, not subject to production testing.

b. Pulse test; pulse width $\leq 300\text{ }\mu\text{s}$, duty cycle $\leq 2\%$.


Stresses beyond those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated in the operational sections of the specifications is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.

N-CHANNEL TYPICAL CHARACTERISTICS 25 °C, unless otherwise noted




N-CHANNEL TYPICAL CHARACTERISTICS 25 °C, unless otherwise noted



V_{SD} - Source-to-Drain Voltage (V)
Source-Drain Diode Forward Voltage



V_{GS} - Gate-to-Source Voltage (V)
On-Resistance vs. Gate-to-Source Voltage





T_J - Temperature ($^{\circ}\text{C}$)
Threshold Voltage







**Single Pulse Power**

* $V_{GS} >$ minimum V_{GS} at which $R_{DS(on)}$ is specified


Safe Operating Area

N-CHANNEL TYPICAL CHARACTERISTICS 25 °C, unless otherwise noted




P-CHANNEL TYPICAL CHARACTERISTICS 25 °C, unless otherwise noted**Output Characteristics****Transfer Characteristics****On-Resistance vs. Drain Current****Capacitance****Gate Charge****On-Resistance vs. Junction Temperature**


P-CHANNEL TYPICAL CHARACTERISTICS 25 °C, unless otherwise noted




Source-Drain Diode Forward Voltage




On-Resistance vs. Gate-to-Source Voltage



Threshold Voltage





Single Pulse Power



* $V_{GS} >$ minimum V_{GS} at which $R_{DS(on)}$ is specified

Safe Operating Area

P-CHANNEL TYPICAL CHARACTERISTICS 25 °C, unless otherwise noted

Vishay Siliconix maintains worldwide manufacturing capability. Products may be manufactured at one of several qualified locations. Reliability data for Silicon Technology and Package Reliability represent a composite of all qualified locations. For related documents such as package/tape drawings, part marking, and reliability data, see www.vishay.com/ppg?72281.



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Vishay products are not designed for use in life-saving or life-sustaining applications or any application in which the failure of the Vishay product could result in personal injury or death unless specifically qualified in writing by Vishay. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.