

N- and P-Channel 20-V (D-S) MOSFET

PRODUCT SUMMARY

	V _{DS} (V)	R _{DS(on)} (Ω)	I _D (A)	Q _g (Typ.)
N-Channel	20	0.040 at V _{GS} = 4.5 V	4.5 ^a	3.7 nC
		0.065 at V _{GS} = 2.5 V	4.5 ^a	
P-Channel	-20	0.090 at V _{GS} = -4.5 V	-4.5 ^a	5.3 nC
		0.137 at V _{GS} = -2.5 V	-4.5 ^a	


FEATURES

- TrenchFET® Power MOSFETs
- Typical ESD Protection: N-Channel 2000 V
P-Channel 1000 V
- 100 % R_g Tested
- Material categorization:
For definitions of compliance please see
www.vishay.com/doc?99912





RoHS
COMPLIANT
HALOGEN
FREE

PowerPAK® SC-70-6 Dual



Marking Code



N-Channel MOSFET

P-Channel MOSFET

Ordering Information: SiA519EDJ-T1-GE3 (Lead (Pb)-free and Halogen-free)

ABSOLUTE MAXIMUM RATINGS (T_A = 25 °C, unless otherwise noted)

Parameter		Symbol	N-Channel	P-Channel	Unit
Drain-Source Voltage		V _{DS}	20	- 20	V
Gate-Source Voltage		V _{GS}	± 12		
Continuous Drain Current (T _J = 150 °C)	T _C = 25 °C	I _D	4.5 ^a	- 4.5 ^a	A
	T _C = 70 °C		4.5 ^a	- 4.5 ^a	
	T _A = 25 °C		4.5 ^{a, b, c}	- 3.7 ^{b, c}	
	T _A = 70 °C		4.4 ^{b, c}	- 3 ^{b, c}	
Pulsed Drain Current		I _{DM}	15	- 15	
Source Drain Current Diode Current	T _C = 25 °C	I _S	4.5 ^a	- 4.5 ^a	
	T _A = 25 °C		1.6 ^{b, c}	- 1.6 ^{b, c}	
Maximum Power Dissipation	T _C = 25 °C	P _D	7.8	7.8	W
	T _C = 70 °C		5	5	
	T _A = 25 °C		1.9 ^{b, c}	1.9 ^{b, c}	
	T _A = 70 °C		1.2 ^{b, c}	1.2 ^{b, c}	
Operating Junction and Storage Temperature Range		T _J , T _{stg}	- 55 to 150		°C
Soldering Recommendations (Peak Temperature) ^{d, e}			260		

THERMAL RESISTANCE RATINGS

Parameter		Symbol	N-Channel		P-Channel		Unit
			Typ.	Max.	Typ.	Max.	
Maximum Junction-to-Ambient ^{b, f}	t ≤ 5 s	R _{thJA}	52	65	52	65	°C/W
Maximum Junction-to-Case (Drain)	Steady State	R _{thJC}	12.5	16	12.5	16	

Notes:

a. Package limited.

b. Surface mounted on 1" x 1" FR4 board.

c. t = 5 s.

d. See solder profile (www.vishay.com/doc?73257). The PowerPAK SC-70 is a leadless package. The end of the lead terminal is exposed copper (not plated) as a result of the singulation process in manufacturing. A solder fillet at the exposed copper tip cannot be guaranteed and is not required to ensure adequate bottom side solder interconnection.

e. Rework conditions: manual soldering with a soldering iron is not recommended for leadless components.

f. Maximum under steady state conditions is 110 °C/W.

SPECIFICATIONS ($T_J = 25\text{ }^{\circ}\text{C}$, unless otherwise noted)

Parameter	Symbol	Test Conditions		Min.	Typ.	Max.	Unit	
Static								
Drain-Source Breakdown Voltage	V _{DS}	V _{GS} = 0 V, I _D = 250 μA	N-Ch	20			V	
		V _{GS} = 0 V, I _D = - 250 μA	P-Ch	- 20				
V _{DS} Temperature Coefficient	ΔV _{DS} /T _J	I _D = 250 μA	N-Ch		23		mV/°C	
		I _D = - 250 μA	P-Ch		- 11			
V _{GS(th)} Temperature Coefficient	ΔV _{GS(th)} /T _J	I _D = 250 μA	N-Ch		- 3.3			
		I _D = - 250 μA	P-Ch		2.6			
Gate Threshold Voltage	V _{GS(th)}	V _{DS} = V _{GS} , I _D = 250 μA	N-Ch	0.6		1.4	V	
		V _{DS} = V _{GS} , I _D = - 250 μA	P-Ch	- 0.5		- 1.3		
Gate-Body Leakage	I _{GSS}	V _{DS} = 0 V, V _{GS} = ± 4.5 V	N-Ch			± 0.5		
			P-Ch			± 0.5		
		V _{DS} = 0 V, V _{GS} = ± 12 V	N-Ch			± 90		
			P-Ch			± 8		
Zero Gate Voltage Drain Current	I _{DSS}	V _{DS} = 20 V, V _{GS} = 0 V	N-Ch			1	μA	
		V _{DS} = - 20 V, V _{GS} = 0 V	P-Ch			- 1		
		V _{DS} = 20 V, V _{GS} = 0 V, T _J = 55 °C	N-Ch			10		
		V _{DS} = - 20 V, V _{GS} = 0 V, T _J = 55 °C	P-Ch			- 10		
On-State Drain Current ^b	I _{D(on)}	V _{DS} ≥ 5 V, V _{GS} = 4.5 V	N-Ch	10			A	
		V _{DS} ≤ - 5 V, V _{GS} = - 4.5 V	P-Ch	- 10				
Drain-Source On-State Resistance ^b	R _{DS(on)}	V _{GS} = 4.5 V, I _D = 4.2 A	N-Ch		0.032	0.040	Ω	
		V _{GS} = - 4.5 V, I _D = - 2.9 A	P-Ch		0.074	0.090		
		V _{GS} = 2.5 V, I _D = 3.3 A	N-Ch		0.053	0.065		
		V _{GS} = - 2.5 V, I _D = - 2.3 A	P-Ch		0.113	0.137		
Forward Transconductance ^b	g _{fs}	V _{DS} = 10 V, I _D = 4.2 A	N-Ch		12		S	
		V _{DS} = - 10 V, I _D = - 2.9 A	P-Ch		7			
Dynamic ^a								
Input Capacitance	C _{iss}	N-Channel V _{DS} = 10 V, V _{GS} = 0 V, f = 1 MHz	N-Ch		350		pF	
			P-Ch		340			
Output Capacitance	C _{oss}	P-Channel V _{DS} = - 10 V, V _{GS} = 0 V, f = 1 MHz	N-Ch		82			
			P-Ch		105			
Reverse Transfer Capacitance	C _{rss}		N-Ch		50			
			P-Ch		95			
Total Gate Charge	Q _g	V _{DS} = 10 V, V _{GS} = 10 V, I _D = 5.5 A	N-Ch		7.7	12	nC	
		V _{DS} = - 10 V, V _{GS} = - 10 V, I _D = - 3.7 A	P-Ch		10.5	16		
		N-Channel V _{DS} = 10 V, V _{GS} = 4.5 V, I _D = 5.5 A	N-Ch		3.7	6		
			P-Ch		5.3	8		
Gate-Source Charge	Q _{gs}	P-Channel V _{DS} = - 10 V, V _{GS} = - 4.5 V, I _D = - 3.7 A	N-Ch		0.85			
			P-Ch		0.75			
Gate-Drain Charge	Q _{gd}		N-Ch		0.95			
			P-Ch		2			
Gate Resistance	R _g	f = 1 MHz	N-Ch	0.7	3.5	7	Ω	
			P-Ch	0.2	10	20		

Notes:

a. Guaranteed by design, not subject to production testing.

b. Pulse test; pulse width $\leq 300\text{ }\mu\text{s}$, duty cycle $\leq 2\%$.









SPECIFICATIONS (T _J = 25 °C, unless otherwise noted)								
Parameter	Symbol	Test Conditions	Min.	Typ.	Max.	Unit		
Dynamic ^a								
Turn-On Delay Time	t _{d(on)}	N-Channel V _{DD} = 10 V, R _L = 2.3 Ω I _D ≅ 4.4 A, V _{GEN} = 4.5 V, R _g = 1 Ω	N-Ch		10	15	ns	
			P-Ch		20	30		
Rise Time	t _r		N-Ch		12	20		
			P-Ch		20	30		
Turn-Off Delay Time	t _{d(off)}	P-Channel V _{DD} = - 10 V, R _L = 3.3 Ω I _D ≅ - 3 A, V _{GEN} = - 4.5 V, R _g = 1 Ω	N-Ch		21	35		
			P-Ch		25	40		
Fall Time	t _f		N-Ch		16	25		
			P-Ch		10	15		
Turn-On Delay Time	t _{d(on)}	N-Channel V _{DD} = 10 V, R _L = 2.3 Ω I _D ≅ 4.4 A, V _{GEN} = 10 V, R _g = 1 Ω	N-Ch		5	10		
			P-Ch		5	10		
Rise Time	t _r		N-Ch		10	15		
			P-Ch		10	15		
Turn-Off Delay Time	t _{d(off)}	P-Channel V _{DD} = - 10 V, R _L = 3.3 Ω I _D ≅ - 3 A, V _{GEN} = - 10 V, R _g = 1 Ω	N-Ch		15	25		
			P-Ch		20	30		
Fall Time	t _f		N-Ch		10	15		
			P-Ch		10	15		
Drain-Source Body Diode Characteristics								
Continuous Source-Drain Diode Current	I _S	T _C = 25 °C	N-Ch			4.5	A	
			P-Ch			- 4.5		
Pulse Diode Forward Current ^a	I _{SM}		N-Ch			15		
			P-Ch			- 15		
Body Diode Voltage	V _{SD}	I _S = 4.4 A, V _{GS} = 0 V	N-Ch		0.8	1.2	V	
		I _S = - 3 A, V _{GS} = 0 V	P-Ch		- 0.8	- 1.2		
Body Diode Reverse Recovery Time	t _{rr}	N-Channel I _F = 4.4 A, di/dt = 100 A/μs, T _J = 25 °C	N-Ch		15	30	ns	
			P-Ch		26	50		
Body Diode Reverse Recovery Charge	Q _{rr}		P-Channel I _F = - 3 A, di/dt = - 100 A/μs, T _J = 25 °C	N-Ch		8	20	nC
				P-Ch		13	25	
Reverse Recovery Fall Time	t _a			N-Ch		8		ns
				P-Ch		14		
Reverse Recovery Rise Time	t _b			N-Ch		7		
				P-Ch		12		

Notes:


a. Guaranteed by design, not subject to production testing.

b. Pulse test; pulse width $\leq 300\text{ }\mu\text{s}$, duty cycle $\leq 2\%$.


Stresses beyond those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated in the operational sections of the specifications is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.

N-CHANNEL TYPICAL CHARACTERISTICS (25 °C, unless otherwise noted)**Gate Current vs. Gate-Source Voltage****Gate Current vs. Gate-Source Voltage****Output Characteristics****Transfer Characteristics****On-Resistance vs. Drain Current and Gate Voltage****Capacitance**


N-CHANNEL TYPICAL CHARACTERISTICS (25 °C, unless otherwise noted)




Gate Charge




On-Resistance vs. Junction Temperature




Source-Drain Diode Forward Voltage






On-Resistance vs. Gate-to-Source Voltage



Threshold Voltage




Single Pulse Power (Junction-to-Ambient)


N-CHANNEL TYPICAL CHARACTERISTICS (25 °C, unless otherwise noted)**Safe Operating Area, Junction-to-Ambient****Current Derating*****Power Derating**

* The power dissipation P_D is based on $T_{J(max.)} = 150\text{ °C}$, using junction-to-case thermal resistance, and is more useful in settling the upper dissipation limit for cases where additional heatsinking is used. It is used to determine the current rating, when this rating falls below the package limit.







N-CHANNEL TYPICAL CHARACTERISTICS (25 °C, unless otherwise noted)









Normalized Thermal Transient Impedance, Junction-to-Ambient




Normalized Thermal Transient Impedance, Junction-to-Case



P-CHANNEL TYPICAL CHARACTERISTICS (25 °C, unless otherwise noted)**Gate Current vs. Gate-Source Voltage****Gate Current vs. Gate-Source Voltage****Output Characteristics****Transfer Characteristics****On-Resistance vs. Drain Current and Gate Voltage****Capacitance**

P-CHANNEL TYPICAL CHARACTERISTICS (25 °C, unless otherwise noted)




P-CHANNEL TYPICAL CHARACTERISTICS (25 °C, unless otherwise noted)


* $V_{GS} >$ minimum V_{GS} at which $R_{DS(on)}$ is specified


Safe Operating Area, Junction-to-Ambient

Current Derating*

Power Derating

* The power dissipation P_D is based on $T_{J(max.)} = 150\text{ }^{\circ}\text{C}$, using junction-to-case thermal resistance, and is more useful in settling the upper dissipation limit for cases where additional heatsinking is used. It is used to determine the current rating, when this rating falls below the package limit.

P-CHANNEL TYPICAL CHARACTERISTICS (25 °C, unless otherwise noted)



Normalized Thermal Transient Impedance, Junction-to-Ambient




Normalized Thermal Transient Impedance, Junction-to-Case


Vishay Siliconix maintains worldwide manufacturing capability. Products may be manufactured at one of several qualified locations. Reliability data for Silicon Technology and Package Reliability represent a composite of all qualified locations. For related documents such as package/tape drawings, part marking, and reliability data, see www.vishay.com/ppg?65176.




PowerPAK® SC70-6L



BACKSIDE VIEW OF SINGLE




BACKSIDE VIEW OF DUAL



Notes:

1. All dimensions are in millimeters
2. Package outline exclusive of mold flash and metal burr
3. Package outline inclusive of plating

DIM	SINGLE PAD						DUAL PAD					
	MILLIMETERS			INCHES			MILLIMETERS			INCHES		
	Min	Nom	Max	Min	Nom	Max	Min	Nom	Max	Min	Nom	Max
A	0.675	0.75	0.80	0.027	0.030	0.032	0.675	0.75	0.80	0.027	0.030	0.032
A1	0	-	0.05	0	-	0.002	0	-	0.05	0	-	0.002
b	0.23	0.30	0.38	0.009	0.012	0.015	0.23	0.30	0.38	0.009	0.012	0.015
C	0.15	0.20	0.25	0.006	0.008	0.010	0.15	0.20	0.25	0.006	0.008	0.010
D	1.98	2.05	2.15	0.078	0.081	0.085	1.98	2.05	2.15	0.078	0.081	0.085
D1	0.85	0.95	1.05	0.033	0.037	0.041	0.513	0.613	0.713	0.020	0.024	0.028
D2	0.135	0.235	0.335	0.005	0.009	0.013						
E	1.98	2.05	2.15	0.078	0.081	0.085	1.98	2.05	2.15	0.078	0.081	0.085
E1	1.40	1.50	1.60	0.055	0.059	0.063	0.85	0.95	1.05	0.033	0.037	0.041
E2	0.345	0.395	0.445	0.014	0.016	0.018						
E3	0.425	0.475	0.525	0.017	0.019	0.021						
e	0.65 BSC			0.026 BSC			0.65 BSC			0.026 BSC		
K	0.275 TYP			0.011 TYP			0.275 TYP			0.011 TYP		
K1	0.400 TYP			0.016 TYP			0.320 TYP			0.013 TYP		
K2	0.240 TYP			0.009 TYP			0.252 TYP			0.010 TYP		
K3	0.225 TYP			0.009 TYP								
K4	0.355 TYP			0.014 TYP								
L	0.175	0.275	0.375	0.007	0.011	0.015	0.175	0.275	0.375	0.007	0.011	0.015
T							0.05	0.10	0.15	0.002	0.004	0.006
ECN: C-07431 – Rev. C, 06-Aug-07												
DWG: 5934												



Dimensions in mm (inches)



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.