
# High Speed Infrared Emitting Diode, 890 nm, Surface Emitter Technology



94 8390

## FEATURES

- Package type: leaded
- Package form: T-1¾
- Dimensions (in mm): Ø 5
- Leads with stand-off
- Peak wavelength: $\lambda_p$ = 890 nm
- High reliability
- High radiant power
- High radiant intensity
- Angle of half intensity: φ = ± 10°
- Low forward voltage
- Good spectral matching to Si photodetectors
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912

RoHS COMPLIANT
HALOGEN FREE
GREEN (5-2008)

## DESCRIPTION

TSHF5211 is an infrared, 890 nm emitting diode in surface emitter chip technology with high radiant power and high speed, molded in a clear, untinted plastic package.

## APPLICATIONS

- Industrial sensors

| PRODUCT SUMMARY | | | | |
|---|---|---|---|---|
| COMPONENT | $I_e$ (mW/sr) | φ (°) | $\lambda_p$ (nm) | $t_r$ (ns) |
| TSHF5211 | 235 | ± 10 | 890 | 15 |

**Note**

- Test conditions see table “Basic Characteristics“

| ORDERING INFORMATION | | | |
|---|---|---|---|
| ORDERING CODE | PACKAGING | REMARKS | PACKAGE FORM |
| TSHF5211 | Bulk | MOQ: 4000 pcs, 1000 pcs/reel | T-1¾ |
| TSHF5211-MS21 | Tape and reel | MOQ: 5000 pcs, 1000 pcs/reel | T-1¾ |
| TSHF5211-MSZ | Ammopack | MOQ: 5000 pcs, 1000 pcs/reel | T-1¾ |

**Note**

- MOQ: minimum order quantity

| ABSOLUTE MAXIMUM RATINGS ($T_{amb}$ = 25 °C, unless otherwise specified) | | | | |
|---|---|---|---|---|
| PARAMETER | TEST CONDITION | SYMBOL | VALUE | UNIT |
| Forward current | | $I_F$ | 100 | mA |
| Peak forward current | $t_p/T$ = 0.5, $t_p$ = 100 µs | $I_{FM}$ | 200 | mA |
| Surge forward current | $t_p$ = 100 µs | $I_{FSM}$ | 1.0 | A |
| Power dissipation | | $P_V$ | 170 | mW |
| Junction temperature | | $T_j$ | 100 | °C |
| Ambient temperature range | | $T_{amb}$ | -40 to +85 | °C |
| Storage temperature range | | $T_{stg}$ | -40 to +100 | °C |
| Soldering temperature | t ≤ 5 s, 2 mm from case | $T_{sd}$ | 260 | °C |
| Thermal resistance junction to ambient (1) | EIA / JESD51 | $R_{thJA}$ | 230 | K/W |

**Note**

(1) The emitted optical signal was not considered



For technical questions, contact: emittertechsupport@vishay.com

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000





Fig. 1 - Power Dissipation vs. Ambient Temperature





Fig. 2 - Forward Current vs. Ambient Temperature

| **BASIC CHARACTERISTICS** ($T_{amb}$ = 25 °C, unless otherwise specified) | | | | | | |
|---|---|---|---|---|---|---|
| **PARAMETER** | **TEST CONDITION** | **SYMBOL** | **MIN.** | **TYP.** | **MAX.** | **UNIT** |
| Forward voltage | $I_F$ = 100 mA, $t_p$ = 20 ms | $V_F$ | - | 1.5 | 1.7 | V |
| | $I_F$ = 1 A, $t_p$ = 100 µs | $V_F$ | - | 2.5 | - | V |
| Temperature coefficient of $V_F$ | $I_F$ = 1 mA | $TK_{VF}$ | - | -1.0 | - | mV/K |
| Reverse current | | $I_R$ | Not designed for reverse operation | | | |
| Junction capacitance | $V_R$ = 0 V, f = 1 MHz, E = 0 | $C_j$ | - | 45 | - | pF |
| Radiant intensity | $I_F$ = 100 mA, $t_p$ = 20 ms | $I_e$ | 150 | 235 | 340 | mW/sr |
| | $I_F$ = 1 A, $t_p$ = 100 µs | $I_e$ | - | 1800 | - | mW/sr |
| Radiant power | $I_F$ = 100 mA, $t_p$ = 20 ms | $\phi_e$ | - | 50 | - | mW |
| Temperature coefficient of $\phi_e$ | $I_F$ = 100 mA | $TK\phi_e$ | - | -0.2 | - | %/K |
| Angle of half intensity | | $\varphi$ | - | ± 10 | - | ° |
| Peak wavelength | $I_F$ = 100 mA | $\lambda_p$ | - | 890 | - | nm |
| Spectral bandwidth | $I_F$ = 100 mA | $\Delta\lambda$ | - | 40 | - | nm |
| Temperature coefficient of $\lambda_p$ | $I_F$ = 100 mA | $TK\lambda_p$ | - | 0.3 | - | nm/K |
| Rise time | $I_F$ = 100 mA | $t_r$ | - | 15 | - | ns |
| Fall time | $I_F$ = 100 mA | $t_f$ | - | 15 | - | ns |


For technical questions, contact: emittertechsupport@vishay.com
THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000

**BASIC CHARACTERISTICS** ($T_{amb}$ = 25 °C, unless otherwise specified)





Fig. 3 - Forward Current vs. Forward Voltage





Fig. 6 - Relative Radiant Intensity vs. Ambient Temperature





Fig. 4 - Forward Voltage vs. Ambient Temperature





Fig. 7 - Relative Radiant Intensity vs. Wavelength





Fig. 5 - Relative Radiant Intensity vs. Forward Current





Fig. 8 - Relative Radiant Intensity vs. Angular Displacement


For technical questions, contact: emittertechsupport@vishay.com
THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000





Fig. 9 - Pulse Forward Current vs. Pulse Duration at 25 °C






Fig. 10 - Pulse Forward Current vs. Pulse Duration at 85 °C

## **PACKAGE DIMENSIONS** in millimeters




6.544-5258.16-4
Issue: 1; 06.10.16


For technical questions, contact: emittertechsupport@vishay.com
THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000

# Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, “Vishay”), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

*© 2024 VISHAY INTERTECHNOLOGY, INC. ALL RIGHTS RESERVED*