


SC-70: 5- and 6-Leads (T1 and T3 Methods)



Notes

- (1) 10 sprocket hole pitch cumulative tolerance ± 0.2 mm.
- (2) Camber not to exceed 1 mm in 100 mm, also not to exceed 1.5 cm in 1 m actually.
- (3) Material: black conductive or black static dissipative.
- (4) A_0 and B_0 measured on a plane 0.3 mm above the bottom of the pocket except 3M carrier tape.
- (5) K_0 measured from a plane on the inside bottom of the pocket to the top surface of the carrier.
- (6) Should be measured from:
 - a) sprocket hole to pocket center, and
 - b) sprocket hole to pocket hole.
- (7) All size in mm unless specified.
- (8) Tolerances will be ± 0.1 mm unless specified.
- (9) Vishay part number must be labeled at all reels of carrier tape.
- (10) Surface resistivity: 10^4 to 10^{11} Ω .

QUANTITY PER REEL		
T1		3000
T3 (1)		10 000

Note

- (1) Not standard offering. Please contact local sales office for availability.

ECN: C15-0523-Rev. J, 08-Jun-15
 DWG: 93-5213-X