


TSOP: 5/6-LEAD (SC-59)



$A_O = 3.30$ mm
 $B_O = 3.20$ mm
 $K_O = 1.40$ mm

Notes

- (1) 10 sprocket hole pitch cumulative tolerance ± 0.2 mm.
- (2) Camber not to exceed 1 mm in 100 mm, also not to exceed 1.5 cm in 1 m actually.
- (3) Material: black conductive or black static dissipative.
- (4) A_O and B_O measured on a plane 0.3 mm above the bottom of the pocket except 3M carrier tape.
- (5) K_O measured from a plane on the inside bottom of the pocket to the top surface of the carrier.
- (6) It should be measured from:
 - a. sprocket hole to pocket center
 - and
 - b. sprocket hole to pocket hole
- (7) All sizes in mm unless specified.
- (8) Tolerances will be ± 0.1 mm unless specified.
- (9) Vishay part number must be labeled at all reels of carrier tape.
- (10) Surface resistivity: 10^4 to 10^{11} Ω .

QUANTITY PER REEL	
T1	3000
T3 (1)	10 000

Note

- (1) Not standard offering. Please contact local sales office for availability.

ECN: C15-0524-Rev. H, 06-Jul-15
 DWG: 93-2345-X