


TSSOP-14, 16/PowerPAK TSSOP-16



$$\begin{aligned} A_0 &= 6.8 \text{ mm} \pm 0.1 \\ B_0 &= 5.4 \text{ mm} \pm 0.1 \\ K_0 &= 1.6 \text{ mm} \pm 0.1 \\ K_1 &= 1.3 \text{ mm} \pm 0.1 \end{aligned}$$

Notes

1. 10 sprocket hole pitch cumulative tolerance ± 0.2 .
2. Camber not to exceed 1 mm in 100 mm.
3. Material: static dissipative black advantek polystyrene.
4. A_0 and B_0 measured on a plane 0.3 mm above the bottom of the pocket.
5. K_0 measured from a plane on the inside bottom of the pocket to the top surface of the carrier.
6. Pocket position relative to sprocket hole measured as true position of pocket, not pocket hole.
7. All size in mm unless specified.
8. Reel length: 101 m.

QUANTITY PER REEL	
3000	
ECN: S-80229-Rev. F, 11-Feb-08	
DWG: 90-2347-x	