

Powered-off Protection, 0.7 Ω , 1.8 V to 5.5 V, SPST Analog Switch

DESCRIPTION

The DG2715E, DG2716E are single-pole, single-throw (SPST) analog switches designed for +1.8 V to +5.5 V operation with a single power rail. Fabricated with high density CMOS technology, the device achieves low on resistance of 0.7 Ω at a 5 V power supply, fast switching speeds (t_{ON} , t_{OFF} at 13 ns and 11 ns), and low power consumption.

The DG2715E, DG2716E feature low control logic input threshold. This logic inputs can go over $V+$ up to 5.5 V. Additionally, on-resistance flatness (0.15 Ω) offer high accuracy between channels.

The DG2715E contains a normally open (NO) switch, and the DG2716E contains a normally closed switch. All switches conduct both analog and digital signals equally well in either directions when on, permit signals with amplitudes of up to $V+$, and block up to the power supply level when off. The DG2715E, DG2716E can withstand greater than 7 kV (human body model). A powered-off protection circuit is built into the switch to prevent an abnormal current flow from COM pin to $V+$ during the power-down condition. The powered-off protection feature plus the switch's high ESD and latch up current capabilities make it more reliable in designs where the part sits close to the interface. Operation temperature is specified from -40 $^{\circ}\text{C}$ to +85 $^{\circ}\text{C}$. The DG2715E, DG2716E are available in the compact SC-70-5 package.

FEATURES


- Low switch on-resistance (0.7 Ω at 5 V)
- 1.8 V to 5.5 V single supply operation
- Powered-off protection
- Control logic inputs can go over $V+$ up to 5.5 V
- Low charge injection (7 pC)
- Latch-up performance exceeds 300 mA per JESD 78
- ESD tested
 - 7000 V human body model (JS-001)
 - 1000 V charge device model (JS-002)
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912


RoHS
COMPLIANT

APPLICATIONS



- Smartphones and tablets
- Consumer and computing
- Portable instrumentation
- Audio and video signal routing
- Medical equipment

FUNCTIONAL BLOCK DIAGRAM AND PIN CONFIGURATION




Top view

Device marking: H5


 Device marking: H5XXX
XXX = date / lot traceability code


Top view

Device marking: H6


 Device marking: H6XXX
XXX = date / lot traceability code

TRUTH TABLE (DG2715E)	
LOGIC	SWITCH
0	Off
1	On

TRUTH TABLE (DG2716E)	
LOGIC	SWITCH
0	On
1	Off

ORDERING INFORMATION		
TEMP. RANGE	PACKAGE	PART NUMBER
-40 $^{\circ}\text{C}$ to +85 $^{\circ}\text{C}$	SC-70-5	DG2715EDL-T1-GE3
		DG2716EDL-T1-GE3



ABSOLUTE MAXIMUM RATINGS			
PARAMETER		LIMIT	UNIT
V+, COM, NC, NO, IN reference to GND		-0.3 to 6	V
Continuous current (NO, NC, and COM pins)		± 200	mA
Peak current (pulsed at 1 ms, 10 % duty cycle)		± 300	
Storage temperature	(D suffix)	-65 to +150	°C
Power dissipation (packages) ^a	5-pin SC-70 ^b	250	mW
ESD / HBM	JS-001	7000	V
ESD / CDM	JS-002	1000	
Latch up	Per JESD78 with 1.5 x voltage clamp	200	mA

Notes

- a. All leads welded or soldered to PC board
b. Derate 3.1 mW/°C above 70 °C

Stresses beyond those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated in the operational sections of the specifications is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.

SPECIFICATIONS (V ₊ = 5 V)								
PARAMETER	SYMBOL	TEST CONDITIONS UNLESS OTHERWISE SPECIFIED V ₊ = 5 V, ± 10 %, V _{IN} = 0.8 V or 2.4 V ^e	TEMP. ^a	LIMITS -40 °C to +85 °C			UNIT	
				MIN. ^b	TYP. ^c	MAX. ^b		
Analog Switch								
Analog signal range ^d	V _{NO} , V _{NC} , V _{COM}		Full	0	-	V ₊	V	
On-resistance	R _{ON}	V ₊ = 4.5 V, V _{COM} = 0.5 V / 2.5 V, I _{NO} , I _{NC} = 10 mA	Room Full ^d	- -	0.7 -	1.1 1.2	Ω	
R _{ON} flatness ^d	R _{ON} flatness	V ₊ = 4.5 V, V _{COM} = 0 V to V ₊ , I _{NO} , I _{NC} = 10 mA	Room	-	0.11	-		
Switch off leakage current ^f	I _{NO(off)} , I _{NC(off)}	V ₊ = 5 V, V _{NO} , V _{NC} = 0.5 V / 4.5 V, V _{COM} = 4.5 V / 0.5 V	Room Full	-5 -25	- -	5 25	nA	
	I _{COM(off)}		Room Full ^d	-5 -25	- -	5 25		
Channel-on leakage current ^f	I _{COM(on)}	V ₊ = 5 V, V _{NO} , V _{NC} = V _{COM} = 0.5 V / 4.5 V	Room Full ^d	-5 -20	- -	5 20		
			Power down leakage	I _{COM(PD)}	V ₊ = 0 V, V _{COM} = 4.5 V, V _{IN} = GND	Full ^d		-1
Digital Control								
Input high voltage	V _{INH}		Full	2.4	-	-	V	
Input low voltage	V _{INL}		Full	-	-	0.8		
Input capacitance ^d	C _{IN}		Full	-	2	-	pF	
Input current ^f	I _{INL} or I _{INH}	V _{IN} = 0 V or V ₊	Full	-1	-	1	μA	
Dynamic Characteristics								
Turn-on time ^d	t _{ON}	V _{NO} or V _{NC} = 3 V, R _L = 300 Ω, C _L = 35 pF	Room Full ^d	- -	13 -	20 25	ns	
			Turn-off time ^d	t _{OFF}	Room Full ^d	- -		11 -
Charge injection ^d	Q _{INJ}	C _L = 1 nF, V _{GEN} = 0 V, R _{GEN} = 0 Ω			Room	-		-7
Off-isolation ^d	OIRR	R _L = 50 Ω, C _L = 5 pF, f = 1 MHz	Room	-	-57	-		dB
NO, NC off capacitance ^d	C _{NO(off)} , C _{NC(off)}	V _{IN} = 0 V or V ₊ , f = 1 MHz	Room	-	29	-	pF	
Channel-on capacitance ^d	C _{ON}		Room	-	73	-		
Power Supply								
Power supply current	I ₊	V _{IN} = 0 V or V ₊	Full	-	0.00005	1	μA	

Notes

- a. Room = 25 °C, full = as determined by the operating suffix
b. The algebraic convention whereby the most negative value is a minimum and the most positive a maximum, is used in this datasheet
c. Typical values are for design aid only, not guaranteed nor subject to production testing
d. Guarantee by design, nor subjected to production test
e. V_{IN} = input voltage to perform proper function
f. Guaranteed by 5 V leakage testing, not production tested



SPECIFICATIONS ($V_+ = 3\text{ V}$)							
PARAMETER	SYMBOL	TEST CONDITIONS UNLESS OTHERWISE SPECIFIED $V_+ = 3\text{ V}, \pm 10\%, V_{IN} = 0.5\text{ V}$ or 1.4 V^e	TEMP. ^a	LIMITS -40 °C to +85 °C			UNIT
				MIN. ^b	TYP. ^c	MAX. ^b	
Analog Switch							
Analog signal range ^d	V_{NO}, V_{NC}, V_{COM}		Full	0	-	V_+	V
On-resistance	R_{ON}	$V_+ = 2.7\text{ V}, V_{COM} = 1.5\text{ V}, I_{NO}, I_{NC} = 100\text{ mA}$	Room	-	0.96	1.2	Ω
			Full	-	-	1.3	
R_{ON} flatness	R_{ON} flatness	$V_+ = 2.7\text{ V}, V_{COM} = 0.6\text{ V}, 1.5\text{ V}, 2.1\text{ V}, I_{NO}, I_{NC} = 100\text{ mA}$	Room	-	0.15	-	
Switch off leakage current	$I_{NO(off)}, I_{NC(off)}$	$V_+ = 3.3\text{ V}, V_{NO}, V_{NC} = 0.3\text{ V} / 3\text{ V}, V_{COM} = 3\text{ V} / 0.3\text{ V}$	Room	-3	-	3	nA
			Full	-10	-	10	
	$I_{COM(off)}$		Room	-3	-	3	
			Full	-10	-	10	
Channel-on leakage current	$I_{COM(on)}$	$V_+ = 3.3\text{ V}, V_{NO}, V_{NC} = V_{COM} = 0.3\text{ V} / 3\text{ V}$	Room	-3	-	3	
			Full	-10	-	10	
Digital Control							
Input high voltage	V_{INH}		Full	1.4	-	-	V
Input low voltage	V_{INL}		Full	-	-	0.5	
Input capacitance ^d	C_{IN}		Full	-	2	-	pF
Input current	I_{INL} or I_{INH}	$V_{IN} = 0\text{ V}$ or V_+	Full	-1	-	1	μA
Dynamic Characteristics							
Turn-on time	t_{ON}	V_{NO} or $V_{NC} = 1.5\text{ V}, R_L = 50\ \Omega, C_L = 35\text{ pF}$	Room	-	20	25	ns
			Full	-	-	30	
Turn-off time	t_{OFF}		Room	-	15	21	
			Full	-	-	28	
Charge injection ^d	Q_{INJ}	$C_L = 1\text{ nF}, V_{GEN} = 0\text{ V}, R_{GEN} = 0\ \Omega$	Room	-	-12	-	pC
Off-isolation ^d	OIRR	$R_L = 50\ \Omega, C_L = 5\text{ pF}, f = 1\text{ MHz}$	Room	-	-57	-	dB
NO, NC off capacitance ^d	$C_{NO(off)}, C_{NC(off)}$	$V_{IN} = 0\text{ V}$ or $V_+, f = 1\text{ MHz}$	Room	-	30	-	pF
Channel-on capacitance ^d	C_{ON}		Room	-	73	-	
Power Supply							
Power supply current	I_+	$V_+ = 3.6\text{ V}, V_{IN} = 0\text{ V}$ or V_+	Full	-	0.00003	1	μA

Notes

- a. Room = 25 °C, full = as determined by the operating suffix
- b. The algebraic convention whereby the most negative value is a minimum and the most positive a maximum, is used in this datasheet
- c. Typical values are for design aid only, not guaranteed nor subject to production testing
- d. Guarantee by design, nor subjected to production test
- e. V_{IN} = input voltage to perform proper function
- f. Guaranteed by 3 V leakage testing, not production tested




SPECIFICATIONS (V+ = 1.8 V)							
PARAMETER	SYMBOL	TEST CONDITIONS UNLESS OTHERWISE SPECIFIED V+ = 1.8 V, ± 10 %, VIN = 0.4 V or 1 V ^e	TEMP. ^a	LIMITS -40 °C to +85 °C			UNIT
				MIN. ^b	TYP. ^c	MAX. ^b	
Analog Switch							
Analog signal range ^d	V _{NO} , V _{NC} , V _{COM}		Full	0	-	V+	V
On-resistance	R _{ON}	V+ = 1.8 V, V _{COM} = 0.9 V, I _{NO} , I _{NC} = 10 mA	Room	-	4	7	Ω
			Full ^d	-	-	11	
Switch off leakage current ^f	I _{NO(off)} , I _{NC(off)}	V+ = 2 V, V _{NO} , V _{NC} = 0.2 V / 1.8 V, V _{COM} = 1.8 V / 0.2 V	Room	-2	-	2	nA
			Full ^d	-5	-	5	
	Room		-2	-	2		
	Full ^d		-5	-	5		
Channel-on leakage current ^f	I _{COM(on)}	V+ = 2 V, V _{NO} , V _{NC} = V _{COM} = 0.2 V / 1.8 V	Room	-2	-	2	nA
			Full ^d	-5	-	5	
Digital Control							
Input high voltage	V _{INH}		Full	1	-	-	V
Input low voltage	V _{INL}		Full	-	-	0.4	
Input capacitance ^d	C _{IN}		Full	-	2	-	pF
Input current ^f	I _{INL} or I _{INH}	V _{IN} = 0 V or V+	Full	-1	-	1	μA
Dynamic Characteristics							
Turn-on time ^d	t _{ON}	V _{NO} or V _{NC} = 1.5 V, R _L = 50 Ω, C _L = 35 pF	Room	-	35	40	ns
			Full ^d	-	-	43	
Turn-off time ^d	t _{OFF}		Room	-	27	40	
			Full ^d	-	-	43	
Charge injection ^d	Q _{INJ}	C _L = 1 nF, V _{GEN} = 0 V, R _{GEN} = 0 Ω	Room	-	-9	-	pC
Off-isolation ^d	OIRR	R _L = 50 Ω, C _L = 5 pF, f = 1 MHz	Room	-	-57	-	dB
NO, NC off capacitance ^d	C _{NO(off)} , C _{NC(off)}	V _{IN} = 0 V or V+, f = 1 MHz	Room	-	31	-	pF
Channel-on capacitance ^d	C _{ON}		Room	-	70	-	

Notes


- a. Room = 25 °C, full = as determined by the operating suffix
- b. The algebraic convention whereby the most negative value is a minimum and the most positive a maximum, is used in this datasheet
- c. Typical values are for design aid only, not guaranteed nor subject to production testing
- d. Guarantee by design, nor subjected to production test
- e. V_{IN} = input voltage to perform proper function
- f. Guaranteed by 3 V leakage testing, not production tested




TYPICAL CHARACTERISTICS (T_A = 25 °C, unless otherwise noted)




R_{DS(on)} vs. V_{COM} vs. V₊




R_{DS(on)} vs. V_{COM}, and Temperature




R_{DS(on)} vs. V_{COM}, and Temperature



R_{DS(on)} vs. V_{COM}, and Temperature




Supply Current vs. Temperature




Supply Current vs. Temperature




TYPICAL CHARACTERISTICS (T_A = 25 °C, unless otherwise noted)




Leakage Current vs. Temperature




Leakage Current vs. Temperature




Leakage Current vs. Temperature



Switching Time vs. Temperature




Supply Current vs. Input Switching Frequency




Insertion Loss, Off-Isolation vs. Frequency




TYPICAL CHARACTERISTICS (T_A = 25 °C, unless otherwise noted)




Switching Threshold vs. Supply Voltage




Supply Current vs V_{IN}



Charge Injection vs. Analog Voltage




Power Down Leakage Current vs. Temperature




Power Down Leakage Current vs. V_{COM}

TEST CIRCUITS





C_L (includes fixture and stray capacitance)

$$V_{OUT} = V_{COM} \left(\frac{R_L}{R_L + R_{ON}} \right)$$




Logic "1" = Switch On
 Logic input waveforms inverted for switches that have the opposite logic sense.

Fig. 1 - Switching Time



IN depends on switch configuration: input polarity determined by sense of switch.

Fig. 2 - Charge Injection



$$\text{Off Isolation} = 20 \log \frac{V_{COM}}{V_{NO/NC}}$$

Fig. 3 - Off-Isolation

TEST CIRCUITS




Fig. 4 - Channel Off / On Capacitance



PRODUCT SUMMARY		
Part number	DG2715E	DG2716E
Status code	2	2
Configuration	SPST x 1, NO	SPST x 1, NC
Single supply min. (V)	1.8	1.8
Single supply max. (V)	5.5	5.5
Dual supply min. (V)	-	-
Dual supply max. (V)	-	-
On-resistance (Ω)	0.7	0.7
Charge injection (pC)	-7	-7
Source on capacitance (pF)	73	73
Source off capacitance (pF)	29	29
Leakage switch on typ. (nA)	-	-
Leakage switch off max. (nA)	-5	5
-3 dB bandwidth (MHz)	-	-
Package	SC-70-5	SC-70-5
Functional circuit / applications	Multi purpose, instrumentation, medical and healthcare, portable	Multi purpose, instrumentation, medical and healthcare, portable
Interface	Parallel	Parallel
Single supply operation	Yes	Yes
Dual supply operation	-	-
Turn on time max. (ns)	25	25
Crosstalk and off isolation	-57	-57

Vishay Siliconix maintains worldwide manufacturing capability. Products may be manufactured at one of several qualified locations. Reliability data for Silicon Technology and Package Reliability represent a composite of all qualified locations. For related documents such as package / tape drawings, part marking, and reliability data, see www.vishay.com/ppg?75025.



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.