


Optocoupler, Phototransistor Output (Dual, Quad Channel)

Dual Channel



Quad Channel





FEATURES

- Alternate source to TLP621-2, TLP621-4 and TLP621GB-2, TLP621GB-4
- High collector emitter voltage, BV_{CEO} = 70 V
- Dual and quad packages feature:
  - Lower pin and parts count
  - Better channel to channel CTR match
  - Improved common mode rejection
- Isolation rated voltage 4420 V_{RMS}
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912

Pb-free

e3

RoHS COMPLIANT

AGENCY APPROVALS

- UL
- cUL
- DIN EN 60747-5-5 (VDE 0884-5), available with option 1
- CQC GB4943.1
- CQC GB8898
- FIMKO

LINKS TO ADDITIONAL RESOURCES

Related Documents

DESCRIPTION

The ILD621, ILQ621, ILD621GB, ILQ621GB are multi-channel phototransistor optocouplers that use GaAs IRED emitters and high gain NPN silicon phototransistors. These devices are constructed using double molded insulation technology.

The ILD621, ILQ621GB is well suited for CMOS interfacing given the CTR_{CEsat} of 30 % minimum at I_F of 1.0 mA. High gain linear operation is guaranteed by a minimum CTR_{CE} of 100 % at 5.0 mA. The ILD621, ILQ621 has a guaranteed CTR_{CE} 50 % minimum at 5.0 mA. The transparent ion shield insures stable DC gain in applications such as power supply feedback circuits, where constant DC V_{IO} voltages are present.


ORDERING INFORMATION

I	L	x	6	2	1	x	x	-	X	0	#	#

PART NUMBER

x = D (Dual) or Q (Quad)

PACKAGE OPTION



AGENCY CERTIFIED / PACKAGE	DUAL CHANNEL		QUAD CHANNEL	
	CTR (%)			
UL, cUL, CSA, CQC, FIMKO	**> 50**	**> 100**	**> 50**	**> 100**
DIP-8	-	ILD621GB	-	-
SMD-8, option 7	ILD621-X007T	ILD621GB-X007T	-	-
DIP-16	-	-	ILQ621	ILQ621GB
DIP-16, option 6	-	-	ILQ621-X006	-
SMD-16, option 7	-	-	ILQ621-X007T	-
SMD-16, option 9	-	-	-	ILQ621GB-X009
VDE, UL, cUL, CSA, CQC, FIMKO	**> 50**	**> 100**	**> 50**	**> 100**
DIP-16	-	-	-	ILQ621GB-X001
SMD-16, option 7	-	-	-	ILQ621GB-X017T

Note

- For additional information on the available options refer to option information

For technical questions, contact: optocoupler.answers@vishay.com

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000

ABSOLUTE MAXIMUM RATINGS (T_{amb} = 25 °C, unless otherwise specified)					
PARAMETER	**TEST CONDITION**	**PART**	**SYMBOL**	**VALUE**	**UNIT**
INPUT					
Reverse voltage			V_R	6.0	V
Forward current			I_F	60	mA
Surge current			I_{FSM}	1.5	A
Power dissipation			P_{diss}	100	mW
Derate from 25 °C				1.33	mW/°C
OUTPUT					
Collector emitter reverse voltage			V_{CEO}	70	V
Collector current			I_C	50	mA
	t < 1.0 ms		I_C	100	mA
Power dissipation			P_{diss}	150	mW
Derate from 25 °C				-2.0	mW/°C
COUPLER					
Package dissipation		ILD621		400	mW
		ILD621GB		400	mW
Derate from 25 °C				5.33	mW/°C
Package dissipation		ILQ621		500	mW
		ILQ621GB		500	mW
Derate from 25 °C				6.67	mW/°C
Storage temperature			T_{stg}	-55 to +150	°C
Operating temperature			T_{amb}	-55 to +100	°C
Junction temperature			T_j	100	°C
Soldering temperature [1]	2.0 mm from case bottom		T_{sld}	260	°C

Notes

- Stresses in excess of the absolute maximum ratings can cause permanent damage to the device. Functional operation of the device is not implied at these or any other conditions in excess of those given in the operational sections of this document. Exposure to absolute maximum ratings for extended periods of the time can adversely affect reliability.

(1) Refer to reflow profile for soldering conditions for surface mounted devices (SMD). Refer to wave profile for soldering conditions for through hole devices (DIP).

ELECTRICAL CHARACTERISTICS (T_{amb} = 25 °C, unless otherwise specified)							
PARAMETER	**TEST CONDITION**	**PART**	**SYMBOL**	**MIN.**	**TYP.**	**MAX.**	**UNIT**
INPUT							
Forward voltage	I_F = 10 mA		V_F	1.0	1.15	1.3	V
Reverse current	V_R = 6.0 V		I_R	-	0.01	10	µA
Capacitance	V_R = 0 V, f = 1.0 MHz		C_O	-	40	-	pF
Thermal resistance, junction to lead			R_{THJL}	-	750	-	K/W
OUTPUT							
Collector emitter capacitance	V_{CE} = 5.0 V, f = 1.0 MHz		C_{CE}	-	6.8	-	pF
Collector emitter leakage current	V_{CE} = 24 V		I_{CEO}	-	10	100	nA
			I_{CEO}	-	20	50	µA
Thermal resistance, junction to lead			R_{THJL}	-	500	-	K/W
COUPLER							
Capacitance (input to output)	V_{IO} = 0 V, f = 1.0 MHz		C_{IO}	0.8	-	-	pF
Insulation resistance	V_{IO} = 500 V			10^{12}	-	-	Ω
Channel to channel insulation				500	-	-	VAC
Collector emitter saturation voltage	I_F = 8.0 mA, I_{CE} = 2.4 mA	ILD621	V_{CEsat}	-	-	0.4	V
		ILQ621					
	I_F = 1.0 mA, I_{CE} = 0.2 mA	ILD621GB	V_{CEsat}	-	-	0.4	V
		ILQ621GB					

Note

- Minimum and maximum values are testing requirements. Typical values are characteristics of the device and are the result of engineering evaluation. Typical values are for information only and are not part of the testing requirements.

For technical questions, contact: optocoupler.answers@vishay.com
THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000

CURRENT TRANSFER RATIO

PARAMETER	TEST CONDITION	PART	SYMBOL	MIN.	TYP.	MAX.	UNIT
Channel/channel CTR match	I_F = 5.0 mA, V_{CE} = 5.0 V		CTRX/CTRY	1 to 1	-	3 to 1	%
Current transfer ratio (collector emitter saturated)	I_F = 1.0 mA, V_{CE} = 0.4 V	ILD621	CTR_{CEsat}	-	60	-	%
		ILQ621	CTR_{CEsat}	-	60	-	%
		ILD621GB	CTR_{CEsat}	30	-	-	%
		ILQ621GB	CTR_{CEsat}	30	-	-	%
Current transfer ratio (collector emitter)	I_F = 5.0 mA, V_{CE} = 5.0 V	ILD621	CTR_{CE}	50	80	600	%
		ILQ621	CTR_{CE}	50	80	600	%
		ILD621GB	CTR_{CE}	100	200	600	%
		ILQ621GB	CTR_{CE}	100	200	600	%

SWITCHING CHARACTERISTICS

PARAMETER	TEST CONDITION	SYMBOL	MIN.	TYP.	MAX.	UNIT
NON-SATURATED						
On time	I_F = 10 mA, V_{CC} = 5.0 V, R_L = 75 Ω, 50 % of V_{PP}	t_{on}	-	3.0	-	µs
Rise time	I_F = 10 mA, V_{CC} = 5.0 V, R_L = 75 Ω, 50 % of V_{PP}	t_r	-	2.0	-	µs
Off time	I_F = 10 mA, V_{CC} = 5.0 V, R_L = 75 Ω, 50 % of V_{PP}	t_{off}	-	2.3	-	µs
Fall time	I_F = 10 mA, V_{CC} = 5.0 V, R_L = 75 Ω, 50 % of V_{PP}	t_f	-	2.0	-	µs
Propagation H to L	I_F = 10 mA, V_{CC} = 5.0 V, R_L = 75 Ω, 50 % of V_{PP}	t_{PHL}	-	1.1	-	µs
Propagation L to H	I_F = 10 mA, V_{CC} = 5.0 V, R_L = 75 Ω, 50 % of V_{PP}	t_{PLH}	-	2.5	-	µs
SATURATED						
On time	I_F = 10 mA, V_{CC} = 5.0 V, R_L = 1 kΩ, V_{TH} = 1.5 V	t_{on}	-	4.3	-	µs
Rise time	I_F = 10 mA, V_{CC} = 5.0 V, R_L = 1 kΩ, V_{TH} = 1.5 V	t_r	-	2.8	-	µs
Off time	I_F = 10 mA, V_{CC} = 5.0 V, R_L = 1 kΩ, V_{TH} = 1.5 V	t_{off}	-	2.5	-	µs
Fall time	I_F = 10 mA, V_{CC} = 5.0 V, R_L = 1 kΩ, V_{TH} = 1.5 V	t_f	-	11	-	µs
Propagation H to L	I_F = 10 mA, V_{CC} = 5.0 V, R_L = 1 kΩ, V_{TH} = 1.5 V	t_{PHL}	-	2.6	-	µs
Propagation L to H	I_F = 10 mA, V_{CC} = 5.0 V, R_L = 1 kΩ, V_{TH} = 1.5 V	t_{PLH}	-	7.2	-	µs

COMMON MODE TRANSIENT IMMUNITY

PARAMETER	TEST CONDITION	SYMBOL	MIN.	TYP.	MAX.	UNIT
Common mode rejection, output high	V_{CM} = 50 V_{P-P}, R_L = 1.0 kΩ, I_F = 0 mA	CM_H	-	5000	-	V/µs
Common mode rejection, output low	V_{CM} = 50 V_{P-P}, R_L = 1.0 kΩ, I_F = 10 mA	CM_L	-	5000	-	V/µs

SAFETY AND INSULATION RATINGS

PARAMETER	TEST CONDITION	SYMBOL	VALUE	UNIT
Climatic classification	According to IEC 68 part 1		55 / 100 / 21	
Comparative tracking index		CTI	175	
Maximum rated withstanding isolation voltage	t = 1 min	V_{ISO}	4420	V_{RMS}
Isolation test voltage	t = 1.0 s	V_{ISO}	5300	V_{RMS}
Maximum transient isolation voltage		V_{IOTM}	10 000	V_{peak}
Maximum repetitive peak isolation voltage		V_{IORM}	890	V_{peak}
Isolation resistance	V_{IO} = 500 V, T_{amb} = 25 °C	R_{IO}	≥ 10^{12}	Ω
	V_{IO} = 500 V, T_{amb} = 100 °C	R_{IO}	≥ 10^{11}	Ω
Output safety power		P_{SO}	400	mW
Input safety current		I_{SI}	275	mA
Safety temperature		T_S	175	°C
Creepage distance			≥ 7	mm
Clearance distance			≥ 7	mm
Insulation thickness		DTI	≥ 0.4	mm

Note

- As per IEC 60747-5-5, § 7.4.3.8.2, this optocoupler is suitable for “safe electrical insulation” only within the safety ratings. Compliance with the safety ratings shall be ensured by means of protective circuits.

For technical questions, contact: optocoupler.answers@vishay.com
THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000

TYPICAL CHARACTERISTICS (T_{amb} = 25 °C, unless otherwise specified)




Fig. 1 - Non-Saturated Switching Timing

*




Fig. 2 - Non-Saturated Switching Timing




Fig. 3 - Saturated Switching Timing




Fig. 4 - Saturated Switching Timing




Fig. 5 - Maximum LED Current vs. Ambient Temperature




Fig. 6 - Maximum LED Power Dissipation

For technical questions, contact: optocoupler.answers@vishay.com
THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000




Fig. 7 - Forward Voltage vs. Forward Current




Fig. 10 - Propagation Delay vs. Collector Load Resistor




Fig. 8 - Collector Emitter Current vs. Temperature and LED Current




Fig. 11 - Maximum Detector Power Dissipation




Fig. 9 - Collector Emitter Leakage vs. Temperature




Fig. 12 - Maximum Collector Current vs. Collector Voltage

For technical questions, contact: optocoupler.answers@vishay.com
THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000




Fig. 13 - Normalization Factor for Non-Saturated and Saturated CTR vs. I_F




Fig. 14 - Normalization Factor for Non-Saturated and Saturated CTR vs. I_F






Fig. 15 - Normalization Factor for Non-Saturated and Saturated CTR vs. I_F


For technical questions, contact: optocoupler.answers@vishay.com
THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000

PACKAGE DIMENSIONS in millimeters







Option 6



Option 7





Option 9



For technical questions, contact: optocoupler.answers@vishay.com
THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000

PACKAGE MARKING





Note

- XXXX = LMC (lot marking code)

For technical questions, contact: optocoupler.answers@vishay.com
THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, “Vishay”), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

© 2024 VISHAY INTERTECHNOLOGY, INC. ALL RIGHTS RESERVED