

Bidirectional Symmetrical (BiSy) Low Capacitance, Dual-Line ESD Protection Diode in SOT-323



22742


22743 SOT-323

FEATURES


- For CAN FD and FLEX-bus applications
- Small SOT-323 package
- 2-line ESD protection
- Working range ± 33 V
- Low leakage current I_R < 0.05 µA
- Low load capacitance C_D < 5.2 pF at V_R = 5 V
- ESD immunity acc. IEC 61000-4-2
  ± 30 kV contact discharge
  ± 30 kV air discharge
- ESD capability according to AEC-Q101: human body model: class H3B: > 8 kV
- e3 - pins plated with tin (Sn)
- AEC-Q101 qualified available
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912

Pb-free

e3

RoHS COMPLIANT

MARKING (example only)



22744

ABC = type code (see table below)
WW = date code working week
VY = date code year

LINKS TO ADDITIONAL RESOURCES

3D Models

ORDERING INFORMATION

PART NUMBER (EXAMPLE)	ENVIRONMENTAL AND QUALITY CODE				PACKAGING CODE		ORDERING CODE (EXAMPLE)
	AEC-Q101 QUALIFIED	RoHS-COMPLIANT + LEAD (Pb)-FREE TERMINATIONS		TIN PLATED	3K PER 7" REEL (8 mm TAPE) 15K/BOX = MOQ	10K PER 13" REEL (8 mm TAPE) 10K/BOX = MOQ	
		STANDARD	GREEN				
VCAN33C2-03G	-	E		3	-08		VCAN33C2-03G-E3-08
VCAN33C2-03G	H	E		3	-08		VCAN33C2-03GHE3-08
VCAN33C2-03G	-	E		3		-18	VCAN33C2-03G-E3-18
VCAN33C2-03G	H	E		3		-18	VCAN33C2-03GHE3-18

PACKAGE DATA

DEVICE NAME	PACKAGE NAME	TYPE CODE	WEIGHT	MOLDING COMPOUND FLAMMABILITY RATING	MOISTURE SENSITIVITY LEVEL	SOLDERING CONDITIONS
VCAN33C2-03G	SOT-323	33C	5.65 mg	UL 94 V-0	MSL level 1 (according J-STD-020)	Peak temperature max. 260 °C

ABSOLUTE MAXIMUM RATINGS

PARAMETER	TEST CONDITIONS	SYMBOL	VALUE	UNIT
Peak pulse current	T_A = 25 °C, acc. IEC 61000-4-5; t_p = 8/20 µs; single shot	I_{PPM}	2	A
Peak pulse power	T_A = 25 °C; pin 1 or 2 to pin 3; acc. IEC 61000-4-5; t_p = 8/20 µs; single shot	P_{PP}	120	W
ESD immunity	Contact discharge acc. IEC 61000-4-2; 10 pulses, T_A = 25 °C	V_{ESD}	± 30	kV
	Air discharge acc. IEC 61000-4-2; 10 pulses, T_A = 25 °C		± 30	kV
Operating temperature	Junction temperature	T_J	-55 to +175	°C
Storage temperature		T_{STG}	-55 to +175	°C

For technical questions, contact: ESDprotection@vishay.com
THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000

ELECTRICAL CHARACTERISTICS (pin 1 to 3, 3 to 1, 2 to 3, or 3 to 2) (T_{amb} = 25 °C, unless otherwise specified)						
PARAMETER	**TEST CONDITIONS/REMARKS**	**SYMBOL**	**MIN.**	**TYP.**	**MAX.**	**UNIT**
Protection paths	Number of lines which can be protected	$N_{channel}$	-	-	2	lines
Reverse stand-off voltage	Max. reverse working voltage	V_{RWM}	-	-	33	V
Reverse voltage	At I_R = 0.05 µA	V_R	33	-	-	V
Reverse current	At V_{RWM} = 33 V	I_R	-	-	0.05	µA
Reverse breakdown voltage	At I_R = 1 mA	V_{BR}	36	38	40	V
Reverse clamping voltage	At I_{PP} 1 A; t_p = 8/20 µs	V_C	-	43	47	V
	At $I_{PP} = I_{PPM}$ = 2 A; t_p = 8/20 µs	V_C	-	50	60	V
Capacitance	At V_R = 0 V, f = 1 MHz	C_D	-	6	8	pF
	At V_R = 5 V, f = 1 MHz	C_D	-	4.2	5.2	pF
	Diode capacitance matching at V_R = 5 V, C_{D13} vs. C_{D23}	dC_D	-	-	2	%

TYPICAL CHARACTERISTICS (T_{amb} = 25 °C, unless otherwise specified)




Fig. 1 - ESD Discharge Current Wave Form acc. IEC 61000-4-2 (330 Ω / 150 pF)




Fig. 2 - 8/20 µs Peak Pulse Current Wave Form acc. IEC 61000-4-5




Fig. 3 - Typical Capacitance vs. Reverse Voltage




Fig. 4 - Typical Reverse Voltage vs. Reverse Current

For technical questions, contact: ESDprotection@vishay.com
THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000




Fig. 5 - Typical Peak Clamping Voltage vs. Peak Pulse Current




Fig. 6 - Typical Peak Clamping Voltage vs. Peak Pulse Current






Fig. 7 - Typical Clamping Voltage vs. Peak Pulse Current

For technical questions, contact: ESDprotection@vishay.com
THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000

PACKAGE DIMENSIONS in millimeters (inches) SOT-323




foot print recommendation:



Document no.: 6.541-5040.02-4
Rev. 1 - Date: 06. April 2010
21113


ORIENTATION IN CARRIER TAPE SOT-323




Document no.: S8-V-3717.08-002 (4)
Created - Date: 09. Feb. 2010
22761

For technical questions, contact: ESDprotection@vishay.com
THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000

CARRIER TAPE SOT-323



B-B Section



Document no.: S8-V-3717.08-002 (4)
Created - Date: 09. Feb. 2010
22762

For technical questions, contact: ESDprotection@vishay.com

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, “Vishay”), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

© 2024 VISHAY INTERTECHNOLOGY, INC. ALL RIGHTS RESERVED