



# Power MOSFET

**TO-220AB**


N-Channel MOSFET

## FEATURES

- Extremely low  $R_{DS(on)}$
- Compact plastic package
- Fast switching
- Low drive current
- Ease of paralleling
- Excellent temperature stability
- Parts per million quality
- Material categorization: for definitions of compliance please see [www.vishay.com/doc?99912](http://www.vishay.com/doc?99912)


**RoHS\***  
Available

## Note

\* This datasheet provides information about parts that are RoHS-compliant and / or parts that are non RoHS-compliant. For example, parts with lead (Pb) terminations are not RoHS-compliant. Please see the information / tables in this datasheet for details

## DESCRIPTION

The technology has expanded its product base to serve the low voltage, very low  $R_{DS(on)}$  MOSFET transistor requirements. Vishay's highly efficient geometry and unique processing have been combined to create the lowest on resistance per device performance. In addition to this feature all have documented reliability and parts per million quality!

The transistor also offer all of the well established advantages of MOSFETs such as voltage control, very fast switching, ease of paralleling, and temperature stability of the electrical parameters.

They are well suited for applications such as switching power supplies, motor controls, inverters, choppers, audio amplifiers, high energy pulse circuits, and in systems that are operated from low voltage batteries, such as automotive, portable equipment, etc.

## PRODUCT SUMMARY

$V_{DS}$ (V)	50	
$R_{DS(on)}$ ( $\Omega$ )	$V_{GS} = 10\text{ V}$	0.10
$Q_g$ (Max.) (nC)	17	
$Q_{gs}$ (nC)	9.0	
$Q_{gd}$ (nC)	3.0	
Configuration	Single	

## ORDERING INFORMATION

Package	TO-220AB
Lead (Pb)-free	IRFZ20PbF
Lead (Pb)-free and halogen-free	IRFZ20PbF-BE3

## ABSOLUTE MAXIMUM RATINGS

PARAMETER	SYMBOL	LIMIT	UNIT
Drain-source voltage <sup>a</sup>	$V_{DS}$	50	V
Gate-source voltage <sup>a</sup>	$V_{GS}$	$\pm 20$	
Continuous drain current	$V_{GS} \text{ at } 10\text{ V}$	$T_C = 25\text{ }^\circ\text{C}$	A
		$T_C = 100\text{ }^\circ\text{C}$	
Pulsed drain current <sup>b</sup>	$I_{DM}$	60	
Single pulse avalanche energy <sup>c</sup>	$E_{AS}$	5	mJ
Linear derating factor (see fig. 16)		0.32	W/ $^\circ\text{C}$
Maximum power dissipation (see fig. 16)	$T_C = 25\text{ }^\circ\text{C}$	$P_D$	40
Operating junction and storage temperature range	$T_J, T_{stg}$	-55 to +150	$^\circ\text{C}$
Soldering recommendations (peak temperature)	For 10 s	300 (0.063" (1.6 mm) from case)	

## Notes

a.  $T_J = 25\text{ }^\circ\text{C}$  to  $150\text{ }^\circ\text{C}$



b. Repetitive rating: Pulse width limited by max. junction temperature. See transient temperature impedance curve (see fig. 11)

c. Starting  $T_J = 25\text{ }^\circ\text{C}$ ,  $L = 0.07\text{ mH}$ ,  $R_g = 25\text{ }\Omega$ ,  $I_{AS} = 12\text{ A}$

**THERMAL RESISTANCE RATINGS**

PARAMETER	SYMBOL	TYP.	MAX.	UNIT
Typical socket mount, junction-to-ambient	$R_{thJA}$	-	80	°C/W
Case-to-sink, mounting surface flat, smooth, and greased	$R_{thCS}$	1.0	-	
Junction-to-case	$R_{thJC}$	-	3.12	





**SPECIFICATIONS** ( $T_J = 25\text{ }^{\circ}\text{C}$ , unless otherwise noted)

PARAMETER	SYMBOL	TEST CONDITIONS		MIN.	TYP.	MAX.	UNIT
Static							
Drain-source breakdown voltage	V <sub>DS</sub>	V <sub>GS</sub> = 0 V, I <sub>D</sub> = 250 μA		50	-	-	V
V <sub>DS</sub> temperature coefficient	V <sub>GS(th)</sub>	V <sub>DS</sub> = V <sub>GS</sub> , I <sub>D</sub> = 250 μA		2.0	-	4.0	V
Gate-source threshold voltage	I <sub>GSS</sub>	V <sub>GS</sub> = ± 20 V		-	-	± 500	nA
Gate-source leakage	I <sub>DSS</sub>	V <sub>DS</sub> > Max. Rating, V <sub>GS</sub> = 0 V		-	-	250	μA
Zero gate voltage drain current		V <sub>DS</sub> = Max. Rating x 0.8, V <sub>GS</sub> = 0 V, T <sub>C</sub> = 125 °C		-	-	1000	
		I <sub>D(on)</sub>	V <sub>GS</sub> = 10 V	V <sub>DS</sub> > I <sub>D(on)</sub> x R <sub>DS(on)</sub> max.	-	-	15
Drain-source on-state resistance <sup>b</sup>	R <sub>DS(on)</sub>	V <sub>GS</sub> = 10 V	I <sub>D</sub> = 10 A	-	0.080	0.10	Ω
Forward transconductance <sup>b</sup>	g <sub>fs</sub>	V <sub>DS</sub> > I <sub>D(on)</sub> x R <sub>DS(on)</sub> max., I <sub>D</sub> = 9.0 A		5.0	6.0	-	S
Dynamic							
Input capacitance	C <sub>iss</sub>	V <sub>GS</sub> = 0 V, V <sub>DS</sub> = 25 V, f = 1.0 MHz, see fig. 11		-	560	860	pF
Output capacitance	C <sub>oss</sub>			-	250	350	
Reverse transfer capacitance	C <sub>rss</sub>			-	60	100	
Total gate charge	Q <sub>g</sub>	V <sub>GS</sub> = 10 V	I <sub>D</sub> = 20 A, V <sub>DS</sub> = 0.8 max. rating, see fig. 18 for test circuit (Gate charge is essentially independent of operating temperature)	-	12	17	nC
Gate-source charge	Q <sub>gs</sub>			-	9.0	-	
Gate-drain charge	Q <sub>gd</sub>			-	3.0	-	
Turn-on delay time	t <sub>d(on)</sub>	V <sub>DD</sub> = 25 V, I <sub>D</sub> = 9.0 A, Z <sub>0</sub> = 50 Ω, see fig. 5 <sup>b</sup>		-	15	30	ns
Rise time	t <sub>r</sub>			-	45	90	
Turn-off delay time	t <sub>d(off)</sub>			-	20	40	
Fall time	t <sub>f</sub>			-	15	30	
Internal drain inductance	L <sub>D</sub>	Modified MOSFET symbol showing the internal device inductances 		-	3.5	-	nH
Internal source inductance	L <sub>S</sub>			-	4.5	-	
Drain-Source Body Diode Characteristics							
Continuous source-drain diode current	I <sub>S</sub>	MOSFET symbol showing the integral reverse p - n junction rectifier 		-	-	15	A
Pulsed diode forward current <sup>a</sup>	I <sub>SM</sub>			-	-	60	
Body diode voltage <sup>b</sup>	V <sub>SD</sub>	T <sub>C</sub> = 25 °C, I <sub>S</sub> = 15 A, V <sub>GS</sub> = 0 V		-	-	1.5	V
Body diode reverse recovery time	t <sub>rr</sub>	T <sub>J</sub> = 150 °C, I <sub>F</sub> = 15 A, dI <sub>F</sub> /dt = 100 A/μs		-	100	-	ns
Body diode reverse recovery charge	Q <sub>rr</sub>			-	0.4	-	μC
Forward turn-on time	t <sub>on</sub>	Intrinsic turn-on time is negligible (turn-on is dominated by L <sub>S</sub> and L <sub>D</sub> )					

**Notes**

a. Repetitive rating: Pulse width limited by max. junction temperature. See transient temperature impedance curve (see fig. 5)

b. Pulse test: Pulse width  $\leq 300\text{ }\mu\text{s}$ ; duty cycle  $\leq 2\%$

**TYPICAL CHARACTERISTICS** (25 °C, unless otherwise noted)

**Fig. 1 - Typical Output Characteristics**

**Fig. 1 - Typical Transfer Characteristics**

**Fig. 2 - Typical Saturation Characteristics**

**Fig. 2 - Normalized On-Resistance vs. Temperature**




Fig. 3 - Typical Capacitance vs. Drain-to-Source Voltage




Fig. 5 - Typical Source-Drain Diode Forward Voltage




Fig. 4 - Typical Gate Charge vs. Gate-to-Source Voltage










Fig. 6 - Maximum Safe Operating Area


**Fig. 7 - Maximum Drain Current vs. Case Temperature**

**Fig. 10a - Switching Time Test Circuit**

**Fig. 10b - Switching Time Waveforms**

**Fig. 11 - Maximum Effective Transient Thermal Impedance, Junction-to-Case vs. Pulse Duration**

**Fig. 12a - Clamped Inductive Test Circuit**

**Fig. 12b - Unclamped Inductive Waveforms**




Fig. 13 - Typical Transconductance vs. Drain Current




Fig. 14 - Breakdown Voltage vs. Temperature




Fig. 16 - Power vs. Temperature Derating Curve




Fig. 15 - Typical On-Resistance vs. Drain Current






Fig. 17 - Gate Charge Test Circuit

**Peak Diode Recovery dV/dt Test Circuit**

**Note**

a.  $V_{GS} = 5\text{ V}$  for logic level devices

**Fig. 14 - For N-Channel**

Vishay Siliconix maintains worldwide manufacturing capability. Products may be manufactured at one of several qualified locations. Reliability data for Silicon Technology and Package Reliability represent a composite of all qualified locations. For related documents such as package/tape drawings, part marking, and reliability data, see <http://www.vishay.com/ppg?91340>.





## Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.