

## SCR/Diode (MAGN-A-PAK Power Modules), 320 A


**MAGN-A-PAK**

### FEATURES

- High voltage
- Electrically isolated base plate
- 3500 V<sub>RMS</sub> isolating voltage
- Industrial standard package
- Simplified mechanical designs, rapid assembly
- High surge capability
- Large creepage distances
- Designed and qualified for industrial level
- Material categorization: for definitions of compliance please see [www.vishay.com/doc?999912](http://www.vishay.com/doc?999912)


**RoHS**  
COMPLIANT

### DESCRIPTION

This VSK series of MAGN-A-PAK modules uses high voltage power thyristor/thyristor and thyristor / diode in seven basic configurations. The semiconductors are electrically isolated from the metal base, allowing common heatsinks and compact assemblies to be built. They can be interconnected to form single phase or three phase bridges or as AC-switches when modules are connected in anti-parallel mode. These modules are intended for general purpose applications such as battery chargers, welders, motor drives, UPS, etc.


PRIMARY CHARACTERISTICS	
$I_{T(AV)}$ or $I_{F(AV)}$	320 A
Type	Modules - thyristor, standard
Package	MAGN-A-PAK

MAJOR RATINGS AND CHARACTERISTICS			
SYMBOL	CHARACTERISTICS	VALUES	UNITS
$I_{T(AV)}/I_{F(AV)}$	70 °C	320	A
$I_{T(RMS)}$		502	
$I_{TSM}/I_{FSM}$	50 Hz	9000	
	60 Hz	9420	kA <sup>2</sup> s
$I^2t$	50 Hz	405	
	60 Hz	370	kA <sup>2</sup> √s
$I^2\sqrt{t}$		4050	
$V_{DRM}/V_{RRM}$		1600	V
$T_J$	Range	-40 to +130	°C

### ELECTRICAL SPECIFICATIONS

VOLTAGE RATINGS				
TYPE NUMBER	VOLTAGE CODE	$V_{RRM}/V_{DRM}$ , MAXIMUM REPETITIVE PEAK REVERSE AND OFF-STATE BLOCKING VOLTAGE V	$V_{RSM}$ , MAXIMUM NON-REPETITIVE PEAK REVERSE VOLTAGE V	$I_{RRM}/I_{DRM}$ AT 130 °C MAXIMUM mA
VS-VSKH320-	16	1600	1700	50



ON-STATE CONDUCTION						
PARAMETER	SYMBOL	TEST CONDITIONS			VALUES	UNITS
Maximum average on-state current at case temperature (thyristor)	$I_{T(AV)}$	180° conduction, half sine wave			320	A
Maximum average forward current (diode)	$I_{F(AV)}$				70	°C
Maximum RMS on-state current	$I_{O(RMS)}$	As AC switch 			704	
Maximum peak, one-cycle on-state non-repetitive, surge current	$I_{TSM}$	t = 10 ms	No voltage reapplied	Sinusoidal half wave, initial $T_J = T_J$ maximum	9000	A
		t = 8.3 ms			9420	
		t = 10 ms	100 % $V_{RRM}$ reapplied		7570	
		t = 8.3 ms			7920	
Maximum $I^2t$ for fusing	$I^2t$	t = 10 ms	No voltage reapplied		405	kA <sup>2</sup> s
		t = 8.3 ms			370	
		t = 10 ms	100 % $V_{RRM}$ reapplied		287	
		t = 8.3 ms			262	
Maximum $I^2\sqrt{t}$ for fusing	$I^2\sqrt{t}$	t = 0.1 ms to 10 ms, no voltage reapplied			4050	kA <sup>2</sup> √s
Low level value or threshold voltage	$V_{T(TO)1}$	$(16.7 \% \times \pi \times I_{T(AV)} < I < \pi \times I_{T(AV)})$ , $T_J = T_J$ maximum			0.80	V
High level value of threshold voltage	$V_{T(TO)2}$	$(I > \pi \times I_{T(AV)} < I < \pi \times I_{T(AV)})$ , $T_J = T_J$ maximum			1.03	
Low level value on-state slope resistance	$r_{t1}$	$(16.7 \% \times \pi \times I_{T(AV)} < I < \pi \times I_{T(AV)})$ , $T_J = T_J$ maximum			0.75	mΩ
High level value on-state slope resistance	$r_{t2}$	$(I > \pi \times I_{T(AV)} < I < \pi \times I_{T(AV)})$ , $T_J = T_J$ maximum			0.53	
Maximum on-state voltage drop	$V_{TM}, V_{FM}$	$I_{TM} = \pi \times I_{T(AV)}$ , $I_{FM} = \pi \times I_{F(AV)}$ , $T_J = T_J$ maximum, 180° conduction			1.50	V
Maximum holding current	$I_H$	Anode supply = 12 V, initial $I_T = 30$ A, $T_J = 25$ °C			500	mA
Maximum latching current	$I_L$	Anode supply = 12 V, resistive load = 1 Ω, gate pulse: 10 V, 100 μs, $T_J = 25$ °C			1000	

SWITCHING				
PARAMETER	SYMBOL	TEST CONDITIONS	VS-VSKH320	UNITS
Typical delay time	$t_d$	$T_J = 25$ °C, gate current = 1 A $dI_g/dt = 1$ A/μs $V_d = 0.67 \% V_{DRM}$	1.0	μs
Typical rise time	$t_r$		2.0	
Typical turn-off time	$t_q$	$I_{TM} = 300$ A; $dI/dt = 15$ A/μs; $T_J = T_J$ maximum; $V_R = 50$ V; $dV/dt = 20$ V/μs; gate 0 V, 100 Ω	200 to 350	

BLOCKING				
PARAMETER	SYMBOL	TEST CONDITIONS	VS-VSKH320	UNITS
Maximum peak reverse and off-state leakage current	$I_{RRM}, I_{DRM}$	$T_J = T_J$ maximum	50	mA
RMS insulation voltage	$V_{INS}$	50 Hz, circuit to base, all terminals shorted, 25 °C, 1 s	3000	V
Critical rate of rise of off-state voltage	$dV/dt$	$T_J = T_J$ maximum, exponential to 67 % rated $V_{DRM}$	1000	V/μs



TRIGGERING					
PARAMETER	SYMBOL	TEST CONDITIONS		VS-VSKH320	UNITS
Maximum peak gate power	P <sub>GM</sub>	t <sub>p</sub> ≤ 5 ms, T <sub>J</sub> = T <sub>J</sub> maximum		10.0	W
Maximum average gate power	P <sub>G(AV)</sub>	f = 50 Hz, T <sub>J</sub> = T <sub>J</sub> maximum		2.0	
Maximum peak gate current	+ I <sub>GM</sub>	t <sub>p</sub> ≤ 5 ms, T <sub>J</sub> = T <sub>J</sub> maximum		3.0	A
Maximum peak negative gate voltage	- V <sub>GT</sub>	t <sub>p</sub> ≤ 5 ms, T <sub>J</sub> = T <sub>J</sub> maximum		5.0	V
Maximum required DC gate voltage to trigger	V <sub>GT</sub>	T <sub>J</sub> = - 40 °C	Anode supply = 12 V, resistive load; R <sub>a</sub> = 1 Ω	4.0	
		T <sub>J</sub> = 25 °C		3.0	
		T <sub>J</sub> = T <sub>J</sub> maximum		2.0	
Maximum required DC gate current to trigger	I <sub>GT</sub>	T <sub>J</sub> = - 40 °C	Anode supply = 12 V, resistive load; R <sub>a</sub> = 1 Ω	350	mA
		T <sub>J</sub> = 25 °C		200	
		T <sub>J</sub> = T <sub>J</sub> maximum		100	
Maximum gate voltage that will not trigger	V <sub>GD</sub>	T <sub>J</sub> = T <sub>J</sub> maximum, rated V <sub>DRM</sub> applied		0.25	V
Maximum gate current that will not trigger	I <sub>GD</sub>	T <sub>J</sub> = T <sub>J</sub> maximum, rated V <sub>DRM</sub> applied		10.0	mA
Maximum rate of rise of turned-on current	di/dt	T <sub>J</sub> = T <sub>J</sub> maximum, I <sub>TM</sub> = 400 A, rated V <sub>DRM</sub> applied		500	A/μs

THERMAL AND MECHANICAL SPECIFICATIONS					
PARAMETER	SYMBOL	TEST CONDITIONS		VS-VSKH320	UNITS
Junction operating and storage temperature range	$T_J, T_{Stg}$			-40 to +130	$^\circ\text{C}$
Maximum thermal resistance, junction to case per junction	$R_{thJC}$	DC operation		0.125	K/W
Typical thermal resistance, case to heatsink per module	$R_{thCS}$	Mounting surface flat, smooth, and greased		0.02	
Mounting torque $\pm 10\%$	MAGN-A-PAK to heatsink busbar to MAGN-A-PAK	A mounting compound is recommended and the torque should be rechecked after a period of about 3 hours to allow for the spread of the compound.		4 to 6	Nm
Approximate weight				500 17.8	g oz.
Case style				MAGN-A-PAK	

$\Delta R$ CONDUCTION PER JUNCTION											
DEVICES	SINUSOIDAL CONDUCTION AT $T_J$ MAXIMUM					RECTANGULAR CONDUCTION AT $T_J$ MAXIMUM					UNITS
	180°	120°	90°	60°	30°	180°	120°	90°	60°	30°	
VS-VSKH320-	0.009	0.010	0.014	0.020	0.032	0.007	0.011	0.015	0.020	0.033	K/W

**Note**

- Table shows the increment of thermal resistance  $R_{thJC}$  when devices operate at different conduction angles than DC




Fig. 1 - Current Ratings Characteristics




Fig. 4 - On-State Power Loss Characteristics




Fig. 2 - Current Ratings Characteristics




Fig. 5 - Maximum Non-Repetitive Surge Current




Fig. 3 - On-State Power Loss Characteristics




Fig. 6 - Maximum Non-Repetitive Surge Current





Fig. 7 - On-State Voltage Drop Characteristics


Fig. 8 - Thermal Impedance  $Z_{thJC}$  Characteristics


## ORDERING INFORMATION TABLE

Device code	VS-VS	KH	320	-	16	PbF
	①	②	③		④	⑤
①	- Vishay Semiconductors product					
②	- Circuit configuration (see end of datasheet)					
③	- Current rating					
④	- Voltage code x 100 = $V_{RRM}$ (see Voltage Ratings table)					
⑤	<ul style="list-style-type: none"> <li>• None = Standard production</li> <li>• PbF = Lead (Pb)-free</li> </ul>					

### Note

- To order the optional hardware go to [www.vishay.com/doc?95172](http://www.vishay.com/doc?95172)




CIRCUIT CONFIGURATION		
CIRCUIT DESCRIPTION	CIRCUIT CONFIGURATION CODE	CIRCUIT DRAWING
SCR/diode doubler circuit, positive control	KH	

LINKS TO RELATED DOCUMENTS	
Dimensions	<a href="http://www.vishay.com/doc?95086">www.vishay.com/doc?95086</a>
Application Note	<a href="http://www.vishay.com/doc?95557">www.vishay.com/doc?95557</a>

## MAGN-A-PAK

**DIMENSIONS** in millimeters (inches)



### Notes

- Dimensions are nominal
- Full engineering drawings are available on request
- UL identification number for gate and cathode wire: UL 1385
- UL identification number for package: UL 94 V-0



## Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.