

# High Performance Schottky Rectifier, 1.0 A


**SMB (DO-214AA)**


## FEATURES

- Low forward voltage drop
- Guard ring for enhanced ruggedness and long term reliability
- 125 °C  $T_J$  operation ( $V_R < 5$  V)
- Optimized for OR-ing applications
- High frequency operation
- High purity, high temperature epoxy encapsulation for enhanced mechanical strength and moisture resistance
- Meets MSL level 1, per J-STD-020, LF maximum peak of 260 °C
- Meets JESD 201 class 2 whisker test
- AEC-Q101 qualified
- Material categorization: for definitions of compliance please see [www.vishay.com/doc?99912](http://www.vishay.com/doc?99912)



**RoHS**  
COMPLIANT  
HALOGEN  
**FREE**

## PRIMARY CHARACTERISTICS

$I_{F(AV)}$	1.0 A
$V_R$	15 V
$V_F$ at $I_F$	0.21 V
$I_{RM}$	35 mA at 100 °C
$T_J$ max.	125 °C
$E_{AS}$	1.0 mJ
Package	SMB (DO-214AA)
Circuit configuration	Single

## DESCRIPTION / APPLICATIONS

The VS-10BQ015HM3 surface mount Schottky rectifier has been designed for applications requiring low forward drop and very small foot prints on PC boards. The proprietary barrier technology allows for reliable operation up to 125 °C junction temperature. Typical applications are in disk drives, switching power supplies, converters, freewheeling diodes, battery charging, and reverse battery protection.

## MAJOR RATINGS AND CHARACTERISTICS

SYMBOL	CHARACTERISTICS	VALUES	UNITS
$I_{F(AV)}$	Rectangular waveform	1.0	A
$V_{RRM}$		15	V
$I_{FSM}$	$t_p = 5 \mu s$ sine	140	A
$V_F$	1.0 A <sub>pk</sub> , $T_J = 125$ °C	0.21	V
$T_J$	Range	-55 to +125	°C

## VOLTAGE RATINGS

PARAMETER	SYMBOL	VS-10BQ015HM3	UNITS
Maximum DC reverse voltage	$V_R$	15	V
Maximum working peak reverse voltage	$V_{RWM}$	25	

## ABSOLUTE MAXIMUM RATINGS

PARAMETER	SYMBOL	TEST CONDITIONS	VALUES	UNITS
Maximum average forward current See fig. 5	$I_{F(AV)}$	50 % duty cycle at $T_L = 134$ °C, rectangular waveform	1.0	A
Maximum peak one cycle non-repetitive surge current See fig. 7	$I_{FSM}$	5 $\mu s$ sine or 3 $\mu s$ rect. pulse	140	A
		10 ms sine or 6 ms rect. pulse	40	
Non-repetitive avalanche energy	$E_{AS}$	$T_J = 25$ °C, $I_{AS} = 1$ A, $L = 2$ mH	1.0	mJ
Repetitive avalanche current	$I_{AR}$	Current decaying linearly to zero in 1 $\mu s$ Frequency limited by $T_J$ maximum $V_A = 1.5 \times V_R$ typical	1.0	A

**ELECTRICAL SPECIFICATIONS**

PARAMETER	SYMBOL	TEST CONDITIONS	VALUES	UNITS
Maximum forward voltage drop See fig. 1	$V_{FM}^{(1)}$	1 A	0.33	V
		2 A	0.39	
		1 A	0.21	
		2 A	0.29	
Maximum reverse leakage current See fig. 2	$I_{RM}$	$T_J = 25\text{ }^{\circ}\text{C}$	0.5	mA
		$T_J = 100\text{ }^{\circ}\text{C}$	35	
Threshold voltage	$V_{F(TO)}$	$T_J = T_J \text{ maximum}$	-	V
Forward slope resistance	$r_t$		-	m $\Omega$
Typical junction capacitance	$C_T$	$V_R = 5\text{ V}_{DC}$ , (test signal range 100 kHz to 1 MHz), $25\text{ }^{\circ}\text{C}$	390	pF
Typical series inductance	$L_S$	Measured lead to lead 5 mm from package body	2.0	nH
Maximum voltage rate of change	dV/dt	Rated $V_R$	10 000	V/ $\mu$ s

**Note**

(1) Pulse width = 300  $\mu$ s, duty cycle = 2 %

**THERMAL - MECHANICAL SPECIFICATIONS**

PARAMETER	SYMBOL	TEST CONDITIONS	VALUES	UNITS
Maximum junction temperature range	$T_J^{(1)}$		-55 to +125	$^{\circ}\text{C}$
Maximum storage temperature range	$T_{Stg}$		-55 to +150	
Maximum thermal resistance, junction to lead	$R_{thJL}^{(2)}$	DC operation See fig. 4	36	$^{\circ}\text{C/W}$
Maximum thermal resistance, junction to ambient	$R_{thJA}$	DC operation	80	
Approximate weight			0.10	g
			0.003	oz.
Marking device		Case style SMB (DO-214AA)	1C	

**Notes**

(1)  $\frac{dP_{tot}}{dT_J} < \frac{1}{R_{thJA}}$  thermal runaway condition for a diode on its own heatsink

(2) Mounted 1" square PCB




Fig. 1 - Maximum Forward Voltage Drop Characteristics




Fig. 2 - Typical Peak Reverse Current vs. Reverse Voltage





Fig. 3 - Typical Junction Capacitance vs. Reverse Voltage


Fig. 4 - Maximum Thermal Impedance  $Z_{thJC}$  Characteristics (Per Leg)




Fig. 5 - Maximum Average Forward Current vs. Allowable Lead Temperature




Fig. 6 - Maximum Average Forward Dissipation vs. Average Forward Current




Fig. 7 - Maximum Non-Repetitive Surge Current

#### Note

- (1) Formula used:  $T_C = T_J - (P_d + P_{dREV}) \times R_{thJC}$ ;  
 $P_d$  = Forward power loss =  $I_{F(AV)} \times V_{FM}$  at  $(I_{F(AV)}/D)$  (see fig. 6);  
 $P_{dREV}$  = Inverse power loss =  $V_{R1} \times I_R (1 - D)$ ;  $I_R$  at  $V_{R1} = 80\%$  rated  $V_R$

**ORDERING INFORMATION TABLE**

Device code	<b>VS-</b>	<b>10</b>	<b>B</b>	<b>Q</b>	<b>015</b>	<b>H</b>	<b>M3</b>
	①	②	③	④	⑤	⑥	⑦

- |          |   |
|----------|---|
| <b>1</b> | - Vishay Semiconductors product   |
| <b>2</b> | - Current rating  |
| <b>3</b> | - B = SMB   |
| <b>4</b> | - Q = Schottky "Q" series   |
| <b>5</b> | - Voltage rating (015 = 15 V)   |
| <b>6</b> | - H = AEC-Q101 qualified  |
| <b>7</b> | - Environmental digit:<br>M3 = halogen-free, RoHS compliant and terminations lead (Pb)-free |

**ORDERING INFORMATION** (Example)



PREFERRED P/N	PREFERRED PACKAGE CODE	MINIMUM ORDER QUANTITY	PACKAGING DESCRIPTION
VS-10BQ015HM3/5BT	5BT	3200	13" diameter plastic tape and reel

**LINKS TO RELATED DOCUMENTS**

Dimensions	<a href="http://www.vishay.com/doc?95401">www.vishay.com/doc?95401</a>
Part marking information	<a href="http://www.vishay.com/doc?95403">www.vishay.com/doc?95403</a>
Packaging information	<a href="http://www.vishay.com/doc?95404">www.vishay.com/doc?95404</a>
SPICE model	<a href="http://www.vishay.com/doc?95666">www.vishay.com/doc?95666</a>

## SMB

**DIMENSIONS** in inches (millimeters)





## Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.