

High Voltage AC Power Capacitors 3-Phase Units



FEATURES

- Latest technology
- High quality materials
- Low losses design
- Dielectric liquid biodegradable

APPLICATIONS

- Power factor correction
- Harmonic filtering
- Motor compensation
- Industrial converter
- Thermal power station
- Solar
- Wind

QUICK REFERENCE DATA

Series	Pha... HVAC 3-phase
Description	High voltage power capacitors, indoor
Type	High voltage AC power capacitors, 3-phase units
Technology	All-film polypropylene / aluminum foil
Voltage min. (V)	1000
Voltage max. (V)	17 500
Frequency min. (Hz)	50
Frequency max. (Hz)	60
Output min. (kvar)	25
Output max. (kvar)	900

TECHNICAL DATA

Rated frequency	50 Hz or 60 Hz (other frequencies on request)
Insulation class	7.2 kV / 12 kV / 17.5 kV
Internal connection	Star or delta
Average losses	< 0.15 W/kvar
Discharge resistors	Internal (75 V/10 min)
Temperature category	-50 °C to +55 °C
Capacitance tolerance	-5 % / +10 %
Internal connection	Star or delta
Impregnating agent	Synthetic oil (non-PCB)
Protection	Pressure monitoring device
Inrush current	100 x I _N max.
Standards	IEC 60871, ANSI/IEEE 18, CSA C22.2 No. 190
Bushings	Porcelain, screw or welded type, M12 / M16
Casing	Stainless steel
Standard color	RAL 7033 / other colors available upon request

FORMS OF CONSTRUCTION

IP00 3-phase capacitor are provided with three bushings, dead casing with grounding connection point. They are connected either in star or in delta, with pressure monitoring device.



Form 1




Form 2




Form 3

CONNECTIONS



Star



Delta

CORROSION PROTECTION

Case material: stainless steel case AISI 409 (AISI 304 as option)

Thickness of material 1.5 mm, top cover and bottom 2.0 mm

Standard case dimensions: 345 mm x 110 mm / 135 mm / 175 mm x H mm

Special dimensions on request (replacement market)



DIMENSION AND WEIGHT

3-PHASE CAPACITORS UP TO 7.2 kV, IP00								
RATED VOLTAGE U _N (kV)	OUTPUT Q _n AT 50 Hz (kvar)	OUTPUT Q _n AT 60 Hz (kvar)	IMPULSE (kVp)	CURRENT AT 50 Hz (A)	CURRENT AT 60 Hz (A)	CASING DIMENSIONS L x W x H (mm)	WEIGHT (kg)	FORM
7.2	25	30	60	2	2	345 x 110 x 300	22	1
7.2	50	60	60	4	5	345 x 110 x 300	22	1
7.2	75	90	60	6	7	345 x 110 x 300	22	1
7.2	100	120	60	8	10	345 x 110 x 330	24	1
7.2	150	180	60	12	14	345 x 135 x 370	30	1
7.2	200	240	60	16	19	345 x 135 x 470	36	1
7.2	300	360	60	24	29	345 x 135 x 630	47	1
7.2	400	480	60	32	39	345 x 175 x 635	58	1
7.2	550	660	60	44	53	345 x 175 x 825	73	1
7.2	700	840	60	56	67	345 x 175 x 1010	88	1
7.2	800	960	60	64	77	345 x 175 x 1155	100	1

3-PHASE CAPACITORS UP TO 12 kV, IP00								
RATED VOLTAGE U _N (kV)	OUTPUT Q _n AT 50 Hz (kvar)	OUTPUT Q _n AT 60 Hz (kvar)	IMPULSE (kVp)	CURRENT AT 50 Hz (A)	CURRENT AT 60 Hz (A)	CASING DIMENSIONS L x W x H (mm)	WEIGHT (kg)	FORM
12	50	60	75	2	3	450 x 110 x 335	30	2
12	75	90	75	4	4	450 x 110 x 340	30	2
12	100	120	75	5	6	450 x 110 x 350	31	2
12	150	180	75	7	9	450 x 110 x 445	37	2
12	200	240	75	10	12	450 x 135 x 470	45	2
12	300	360	75	14	17	450 x 135 x 650	59	2
12	400	480	75	19	23	450 x 175 x 650	73	2
12	550	660	75	26	32	450 x 175 x 815	90	2
12	700	840	75	34	40	450 x 175 x 1015	110	2
12	800	960	75	38	46	450 x 175 x 1130	122	2

3-PHASE CAPACITORS UP TO 17.5 kV, IP00								
RATED VOLTAGE U _N (kV)	OUTPUT Q _n AT 50 Hz (kvar)	OUTPUT Q _n AT 60 Hz (kvar)	IMPULSE (kVp)	CURRENT AT 50 Hz (A)	CURRENT AT 60 Hz (A)	CASING DIMENSIONS L x W x H (mm)	WEIGHT (kg)	FORM
17.5	50	60	95	2	2	450 x 110 x 460	41	3
17.5	75	90	95	2	3	450 x 110 x 475	43	3
17.5	100	120	95	3	4	450 x 110 x 495	44	3
17.5	150	180	95	5	6	450 x 110 x 495	44	3
17.5	200	240	95	7	8	450 x 110 x 560	48	3
17.5	300	360	95	10	12	450 x 135 x 675	65	3
17.5	400	480	95	13	16	450 x 135 x 825	77	3
17.5	550	660	95	18	22	450 x 175 x 825	95	3
17.5	700	840	95	23	28	450 x 175 x 995	113	3



TYPE NOMENCLATURE											
P	h	a	f	s	o	6.3	/	200	/	1	D
1	2	3	4	5	6	7	8	9			
Ph: power capacitor	a = all film dielectric	f: outdoor n. E.: indoor	s: live casing n. E.: dead casing	o: non PCB impregnating agent	Rated voltage (kV)	Rated output (kvar) Rated capacitance (μF)	1 = 1-phase capacitor n. E. = 3-phase capacitor	D = over pressure device			

Note

- n. E. = no entry



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.