

# High Voltage Class 1 Ceramic AC and DC Disc Capacitors, 10 kV<sub>DC</sub> to 50 kV<sub>DC</sub> / 7 kV<sub>AC</sub> to 34 kV<sub>AC</sub>, Screw Terminal Mounting



## FEATURES

- Low dissipation factor of 0.2 % at 1 kHz
- N4700 (T3M) class 1, strontium-based ceramic dielectric
- Negligible piezoelectric / electrostrictive effect
- Low inductance
- High insulation resistance
- Epoxy coating
- Screw terminal mounting
- Ceramic singlelayer capacitor
- Material categorization: for definitions of compliance please see [www.vishay.com/doc?99912](http://www.vishay.com/doc?99912)


**RoHS**  
COMPLIANT

## DESIGN SUPPORT TOOLS

[click logo to get started](#)
**3D**  
Models  
Available

## APPLICATIONS

- High voltage power supplies
- CO<sub>2</sub> lasers
- X-ray equipment
- Welding equipment
- Industrial

## QUICK REFERENCE DATA

DESCRIPTION	VALUE					
Ceramic Class	1					
Ceramic Dielectric	N4700					
Type	715C10KT###	715C15KT###	715C20KT###	715C30KT###	715C40KT###	715C50KT###
Voltage (V <sub>DC</sub> )	10 000	15 000	20 000	30 000	40 000	50 000
Min. Capacitance (pF)	560	370	200	190	100	100
Max. Capacitance (pF)	8000	5300	4000	2700	2000	1700
Mounting	Screw terminal					

## DIELECTRIC STRENGTH

150 % of rated voltage, charging current limited to 50 mA

## DISSIPATION FACTOR $\tan \delta$

 $\leq 2 \times 10^{-3}$  (1 kHz)

## INSULATION RESISTANCE

 Min. 200 000 M $\Omega$  or 1000  $\Omega$ F min. at 25 °C

## CORONA LIMIT

 $< 5$  pC at 50 % of rated AC voltage

## OPERATING TEMPERATURE RANGE

-30 °C to +85 °C

## CAPACITANCE RANGE

100 pF to 8 nF

## CAPACITANCE TOLERANCES

 $\pm 20$  %

## CERAMIC DIELECTRIC

N4700 (class 1)

## RATED VOLTAGE <sup>(1)</sup>

- 10 kV<sub>DC</sub> (7 kV<sub>RMS</sub>)
- 15 kV<sub>DC</sub> (10 kV<sub>RMS</sub>)
- 20 kV<sub>DC</sub> (14 kV<sub>RMS</sub>)
- 30 kV<sub>DC</sub> (20 kV<sub>RMS</sub>)
- 40 kV<sub>DC</sub> (27 kV<sub>RMS</sub>)
- 50 kV<sub>DC</sub> (34 kV<sub>RMS</sub>)

### Note

<sup>(1)</sup> All kV<sub>RMS</sub> values up to 60 Hz

## MATERIAL

Capacitor elements made from class 1 ceramic in a molded epoxy case. Screw terminals: brass, silver plated.

## MARKING

Type designator, capacitance value, rated DC voltage, ceramic material code, production date code, Cera-Mite logo.

## POWER DISSIPATION

Limit to 20 °C rise above ambient, measured on case.

**DIMENSIONS** in millimeters (inches)

**Notes**

- (1) Use #8-32, 3/16" long screw to prevent bottoming  
 (2) To order metric terminals add "M4" or "M5" suffix to model number, use screw length of 4 mm or 5 mm respectively to prevent bottoming

ORDERING INFORMATION				
<b>715C15KTD33</b>	<b>15 kV<sub>DC</sub></b>	<b>3300 pF</b>	<b>± 20 %</b>	<b>N4700</b>
MODEL	RATED VOLTAGE	CAPACITANCE VALUE	TOLERANCE	CERAMIC


SAP PART NUMBER, ELECTRICAL, AND DIMENSIONAL DATA								
MODEL	CERAMIC	CAPACITANCE VALUES (pF)	RATED VOLTAGE (kV <sub>DC</sub> )	RATED VOLTAGE (kV <sub>RMS</sub> )	D ± 1 mm (0.04")	H WITH #8-32 TERMINALS ± 1 mm (0.04")	H WITH M4 METRIC TERMINALS ± 1 mm (0.04")	H WITH M5 METRIC TERMINALS ± 1 mm (0.04")
<b>715C10KT###</b>								
715C10KTT56	N4700	560	10	7	21 (0.83)	18 (0.71)	16 (0.63)	n/a
715C10KTT68		680			21 (0.83)			
715C10KTT82		820			25 (0.98)			
715C10KTD10		1000			25 (0.98)			
715C10KTD12		1200			30 (1.18)			
715C10KTD18		1800			30 (1.18)			
715C10KTD22		2200			37 (1.46)			
715C10KTD28		2800			37 (1.46)			
715C10KTD39		3900			44 (1.73)			
715C10KTD50		5000			52 (2.05)			
715C10KTD68		6800			56 (2.20)			
715C10KTD80		8000			60 (2.36)			
715C10KTD19		1900			37 (1.46)			
715C10KTD27		2700			44 (1.73)			
715C10KTD33	3300	48 (1.89)						
715C10KTD34	3400	52 (2.05)						
715C10KTD47	4700	56 (2.20)						
715C10KTD53	5300	60 (2.36)						
<b>715C15KT###</b>								
715C15KTT37	N4700	370	15	10	21 (0.83)	20 (0.79)	18 (0.71)	n/a
715C15KTT56		560			25 (0.98)			
715C15KTT75		750			30 (1.18)			
715C15KTD10		1000			32 (1.26)			
715C15KTD11		1100			32 (1.26)			
715C15KTD15		1500			37 (1.46)			
715C15KTD19		1900			37 (1.46)			
715C15KTD27		2700			44 (1.73)			
715C15KTD33		3300			48 (1.89)			
715C15KTD34		3400			52 (2.05)			
715C15KTD47		4700			56 (2.20)			
715C15KTD53		5300			60 (2.36)			
715C15KTD19		1900			37 (1.46)			
715C15KTD27		2700			44 (1.73)			
715C15KTD33		3300			48 (1.89)			
715C15KTD34		3400			52 (2.05)			
715C15KTD47	4700	56 (2.20)						
715C15KTD53	5300	60 (2.36)						
715C15KTD19	1900	37 (1.46)	15	10	37 (1.46)	20 (0.79)	18 (0.71)	22 (0.87)
715C15KTD27	2700	44 (1.73)	15	10	44 (1.73)	20 (0.79)	18 (0.71)	22 (0.87)
715C15KTD33	3300	48 (1.89)	15	10	48 (1.89)	20 (0.79)	18 (0.71)	22 (0.87)
715C15KTD34	3400	52 (2.05)	15	10	52 (2.05)	20 (0.79)	18 (0.71)	22 (0.87)
715C15KTD47	4700	56 (2.20)	15	10	56 (2.20)	20 (0.79)	18 (0.71)	22 (0.87)
715C15KTD53	5300	60 (2.36)	15	10	60 (2.36)	20 (0.79)	18 (0.71)	22 (0.87)




SAP PART NUMBER, ELECTRICAL, AND DIMENSIONAL DATA													
MODEL	CERAMIC	CAPACITANCE VALUES (pF)	RATED VOLTAGE (kV <sub>DC</sub> )	RATED VOLTAGE (kV <sub>RMS</sub> )	D ± 1 mm (0.04")	H WITH #8-32 TERMINALS ± 1 mm (0.04")	H WITH M4 METRIC TERMINALS ± 1 mm (0.04")	H WITH M5 METRIC TERMINALS ± 1 mm (0.04")					
<b>715C20KT###</b>													
715C20KTT20	N4700	200	20	14	21 (0.83)	23 (0.91)	21 (0.83)	n/a					
715C20KTT28		280			21 (0.83)								
715C20KTT40		400			25 (0.98)								
715C20KTT56		560			25 (0.98)								
715C20KTT70		700			30 (1.18)								
715C20KTT88		880			30 (1.18)								
715C20KTD10		1000			32 (1.26)								
715C20KTD14		1400			37 (1.46)								
715C20KTD17		1700			44 (1.73)								
715C20KTD22		2200			48 (1.89)								
715C20KTD25		2500			48 (1.89)								
715C20KTD33		3300			56 (2.20)								
715C20KTD40		4000			60 (2.36)								
<b>715C30KT###</b>													
715C30KTT19		N4700			190			30	20	21 (0.83)	27 (1.06)	25 (0.98)	n/a
715C30KTT20	200		21 (0.83)										
715C30KTT33	330		25 (0.98)										
715C30KTT40	400		32 (1.26)										
715C30KTT59	590		32 (1.26)										
715C30KTT70	700		37 (1.46)										
715C30KTT94	940		37 (1.46)										
715C30KTD12	1200		44 (1.73)										
715C30KTD15	1500		48 (1.89)										
715C30KTD17	1700		48 (1.89)										
715C30KTD22	2200		56 (2.20)										
715C30KTD27	2700		60 (2.36)										
<b>715C40KT###</b>													
715C40KTT10	N4700		100	40	27	21 (0.83)	31 (1.22)			29 (1.14)			n/a
715C40KTT14			140			21 (0.83)							
715C40KTT20		200	25 (0.98)										
715C40KTT30		300	32 (1.26)										
715C40KTT40		400	32 (1.26)										
715C40KTT44		440	32 (1.26)										
715C40KTT56		560	37 (1.46)										
715C40KTT70		700	37 (1.46)										
715C40KTT85		850	44 (1.73)										
715C40KTD10		1000	44 (1.73)										
715C40KTD13		1300	48 (1.89)										
715C40KTD15		1500	52 (2.05)										
715C40KTD20		2000	60 (2.36)										
<b>715C50KT###</b>													
715C50KTT10		N4700	100			50		34	21 (0.83)	34 (1.34)	32 (1.26)	n/a	
715C50KTT15	150		21 (0.83)										
715C50KTT20	200		25 (0.98)										
715C50KTT33	330		30 (1.18)										
715C50KTT40	400		32 (1.26)										
715C50KTT47	470		37 (1.46)										
715C50KTT56	560		37 (1.46)										
715C50KTT70	700		44 (1.73)										
715C50KTT85	850		44 (1.73)										
715C50KTD10	1000		48 (1.89)										
715C50KTD13	1300		52 (2.05)										
715C50KTD15	1500		56 (2.20)										
715C50KTD17	1700		60 (2.36)										
<b>715C50KTT###</b>													
715C50KTT10	N4700		100	50	34		21 (0.83)		34 (1.34)		32 (1.26)	n/a	
715C50KTT15		150	21 (0.83)										
715C50KTT20		200	25 (0.98)										
715C50KTT33		330	30 (1.18)										
715C50KTT40		400	32 (1.26)										
715C50KTT47		470	37 (1.46)										
715C50KTT56		560	37 (1.46)										
715C50KTT70		700	44 (1.73)										
715C50KTT85		850	44 (1.73)										
715C50KTD10		1000	48 (1.89)										
715C50KTD13		1300	52 (2.05)										
715C50KTD15		1500	56 (2.20)										
715C50KTD17		1700	60 (2.36)										




**CAPACITANCE CHANGE VS. TEMPERATURE** (typical)



**DISSIPATION FACTOR VS. TEMPERATURE** (typical)




**CAPACITANCE CHANGE VS. VOLTAGE** (typical)





**CAPACITANCE CHANGE VS. FREQUENCY** (typical)



**DISSIPATION FACTOR VS. FREQUENCY** (typical)





<b>TEST METHODS</b>				
<b>NO.</b>	<b>ITEM</b>	<b>SPECIFICATION</b>	<b>SAMPLE SIZE</b>	<b>TEST METHOD</b>
<b>100 % TEST LOT BY LOT</b>				
1	Appearance	No remarkable damage	100 %	Visual check
2	Capacitance	Within the specified tolerance	100 %	Measured at 22 °C ± 2 °C with max. 5 V <sub>RMS</sub> at 1.0 kHz ± 0.1 kHz
3	Dissipation factor	0.2 % max.	100 %	Measured at 22 °C ± 2 °C with max. 5 V <sub>RMS</sub> at 1.0 kHz ± 0.1 kHz
4	Insulation resistance	200 GΩ min.	100 %	Measured with DC 180 V within 60 s of charging
5	Dielectric strength between terminals	No failure	100 %	Tested with 150 % of rated DC-voltage for min. 3 s in insulating fluid or oil (charge / discharge current < 50 mA)
<b>SAMPLE TEST LOT BY LOT</b>				
6	Partial discharge	5 pC max.	10 pieces	Measured with 50 % of rated AC voltage
7	Temperature characteristics	ΔC = -4700 ppm/K ± 1000 ppm/K (temp. range: +20 °C to +85 °C)	2 pieces	Measured at 20 °C / 50 °C / 85 °C / 20 °C Capacitance change at 85 °C shall not exceed the specified limit
8	Strength of terminals	#8-32 and M4: > 1.5 Nm; M5: > 2 Nm	10 pieces	Tested with a torque meter
9	Life test	No failure	3 pieces	Tested with 125 % of rated DC voltage for 100 h +24 h / -0 h at 85 °C ± 2 °C in oil
<b>TYPE TEST / ON DEMAND TEST</b>				
10	Dielectric strength between terminals	No failure	100 %	Tested with 150 % of rated AC voltage for min. 30 s in insulating fluid or oil
11	Lightning pulse 1.2/50 μs	No failure	100 %	Tested with 150 % of rated DC voltage 5 x positive plus 1 x negative
12	Temperature cycle	No failure (no. 1 to 6 within spec. after test)	5 pieces per lot	10 cycles -30 °C / +85 °C Dwell 60 min., rise / fall 60 min.
13	Humidity	No failure (no. 1 to 5 within spec. after test)	5 pieces per lot	Tested with 0 applied voltage for 500 h +24 h / -0 h at 93 % ± 2 % RH and 40 °C ± 2 °C
<b>DESTRUCTIVE TEST / RELEASE TEST</b>				
14	AC breakdown	No failure < 200 % of rated AC voltage	10 pieces per lot	Raise AC voltage with 500 V/s ± 100 V/s until breakdown. Tested in insulating fluid or oil
15	DC breakdown	No failure < 200 % of rated DC voltage	10 pieces per lot	Raise DC voltage with 500 V/s ± 100 V/s until breakdown. Tested in insulating fluid or oil
16	Lightning pulse 1.2/50 μs	No failure < 200 % of rated DC voltage	10 pieces per lot	Start at 150 % of rated DC voltage 1 x positive plus 1 x negative Raise voltage by 5 kV per step
17	Life test	No failure	5 pieces per lot	Tested with 125 % of rated DC voltage for 250 h +24 h / -0 h at 85 °C ± 2 °C in oil

<b>RELATED DOCUMENTS</b>	
General Information	<a href="http://www.vishay.com/doc?23140">www.vishay.com/doc?23140</a>



## Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.