

## EMI Suppression Capacitor, Ceramic Disc, Class X1, 400 V<sub>AC</sub>, Class Y4, 125 V<sub>AC</sub>



### QUICK REFERENCE DATA

DESCRIPTION	VALUE	
Ceramic Class	2	
Ceramic Dielectric	Y5V	
Voltage (V <sub>AC</sub> )	125	400
Min. Capacitance (pF)	1000	
Max. Capacitance (pF)	50 000	
Mounting	Radial	

### INSULATION RESISTANCE

Min. 1000 ΩF

### TOLERANCE ON CAPACITANCE

± 20 %

### DISSIPATION FACTOR

2.0 % max. at 1 kHz; 1 V

### CERAMIC DIELECTRIC

Y5V (Class 2)

### CLIMATIC CATEGORY ACC. TO EN 60068-1

25/125/21

### OPERATING TEMPERATURE RANGE

-30 °C to +125 °C <sup>(1)</sup>

#### Note

<sup>(1)</sup> For explanation about the difference of operating temperature range and temperature characteristic of capacitance, please see [www.vishay.com/doc?48299](http://www.vishay.com/doc?48299)

### FEATURES

- Complying with IEC 60384-14
- High reliability
- Complete range of capacitance values
- Radial leads
- Singlelayer AC disc safety capacitors
- Material categorization: for definitions of compliance please see [www.vishay.com/doc?99912](http://www.vishay.com/doc?99912)


**RoHS**  
COMPLIANT

### APPLICATIONS

- X1, Y4 according to IEC 60384-14
- Line-to-line filtering (Class X)
- Line-to-ground filtering (Class Y)
- Primary and secondary coupling (SMPS)
- EMI / RFI suppression and filtering

### DESIGN

The capacitors consist of a ceramic disc of which both sides are silver-plated. Connection leads are made of tinned copper having a diameter of 0.032" (0.81 mm) or 0.025" (0.64 mm). The capacitors may be supplied with radial kinked or straight leads having a lead spacing of 0.375" (9.5 mm) or 0.250" (6.4 mm). The standard tolerance is ± 20 %. Coating is made of flame retardant epoxy resin in accordance with "UL 94 V-0".

### CAPACITANCE RANGE

1.0 nF to 0.050 μF

### RATED VOLTAGE

IEC 60384-14:

- X1: 400 V<sub>AC</sub>, 50 Hz
- Y4: 125 V<sub>AC</sub>, 50 Hz

### DIELECTRIC STRENGTH BETWEEN LEADS

Component test, 100 % test at production line:

2000 V<sub>AC</sub>, 50 Hz, 2 s

As repeated test at customer side admissible only once with:


1800 V<sub>AC</sub>, 50 Hz, 2 s

Random sampling test (destructive test):

2000 V<sub>AC</sub>, 50 Hz, 60 s

### DIELECTRIC STRENGTH OF BODY INSULATION

2300 V<sub>AC</sub>, 50 Hz, 60 s (destructive test)

**DIMENSIONS** in inches (millimeters)

**ORDERING INFORMATION, CERAMIC X1 / Y4 CAPACITORS 125L**

C (pF)	TOL. (%)	D <sub>max.</sub> DIAMETER INCH (mm)	T <sub>max.</sub> THICKNESS INCH (mm)	WIRE SIZE		LS LEAD SPACE INCH (mm) ± 1 mm	LO LEAD OFFSET INCH (mm) ± 0.5 mm	ORDERING CODE
				AWG	INCH (mm)			
1000	± 20	0.330 (8.4)	0.195 (5.0)	20	0.032 (0.81)	0.250 (6.4)	0.094 (2.4)	125LD10-R
1500		0.330 (8.4)	0.195 (5.0)				0.098 (2.5)	125LD15-R
2000		0.330 (8.4)	0.188 (4.8)				0.091 (2.3)	125LD20-R
2200		0.330 (8.4)	0.182 (4.7)				0.083 (2.1)	125LD22-R
3300		0.365 (9.3)	0.195 (5.0)				0.094 (2.4)	125LD33-R
4700		0.400 (10.2)	0.185 (4.7)				0.087 (2.2)	125LD47-R
5000		0.430 (11.0)	0.195 (5.0)			0.375 (9.5)	0.094 (2.4)	125LD50-R
6800		0.490 (12.5)	0.198 (5.1)				0.098 (2.5)	125LD68-R
8200		0.530 (13.5)	0.193 (5.0)				0.094 (2.4)	125LD82-R
0.010 µF		0.560 (14.3)	0.195 (5.0)				0.098 (2.5)	125LS10-R
0.015 µF		0.720 (18.3)	0.205 (5.3)				0.102 (2.6)	125LS15-R
0.018 µF		0.790 (20.1)	0.205 (5.3)				0.106 (2.7)	125LS18-R
0.020 µF		0.720 (18.3)	0.250 (6.4)	22	0.025 (0.64)		0.087 (2.2)	125LS20-R
0.022 µF		0.790 (20.1)	0.192 (4.9)	20	0.032 (0.81)		0.094 (2.4)	125LS22-R
0.030 µF		0.720 (18.3)	0.240 (6.1)	22	0.025 (0.64)		0.087 (2.2)	125LS30-R
0.050 µF		0.925 (23.5)	0.275 (7.0)	22	0.025 (0.64)		0.087 (2.2)	125LS50-R

**Notes**

- Alternate lead spacings of 7.5 mm and 10 mm are available bulk or tape and reel on request
- Minimum lead clearance according to IEC 60384-14: 0.118" (3 mm)

**TAPE AND REEL OPTIONS**

Part number codes and specifications for tape and reel packaging are found in the general information document [www.vishay.com/doc?23140](http://www.vishay.com/doc?23140).

**APPROVALS**

IEC 60384-14 - Safety tests

This approval together with CB test certificate substitutes all national approvals.

**CB Certificate** ([www.vishay.com/doc?22234](http://www.vishay.com/doc?22234))

Y4-capacitor: CB test certificate:	DE1-63495	1 nF to 50 nF	125 V <sub>AC</sub>
X1-capacitor: CB test certificate:	DE1-63495	1 nF to 50 nF	400 V <sub>AC</sub>

**VDE** ([www.vishay.com/doc?22235](http://www.vishay.com/doc?22235))

Y4-capacitor: VDE marks approval:	40003976	1 nF to 50 nF	125 V <sub>AC</sub>
X1-capacitor: VDE marks approval:	40003976	1 nF to 50 nF	400 V <sub>AC</sub>



DIN EN 60384-14 VDE 0565-1-1 - Safety tests

**Underwriters Laboratories Inc.** ([www.vishay.com/doc?22236](http://www.vishay.com/doc?22236))

Y4-capacitor: UL test certificate:	E99264	1 nF to 50 nF	125 V <sub>AC</sub>
X1-capacitor: UL test certificate:	E99264	1 nF to 50 nF	400 V <sub>AC</sub>




UL 60384-14, CSA E60384-1, CSA E60384-14

Fixed capacitors for electromagnetic interference suppression and connection to the supply mains.

**MARKING**

Sample



PN:125LD68-R  
 Cap.:6800PF ±20%  
 Ur.:Y4(125~),X1(400~)  
 Qty.:250  
 IEC 60384-14:2013:

LOT1:34810157 DC1:1949  
 LOT2: DC2:  
 BATCH NO.:201949CZ  
 R.C.:7032 S.L.:0010

PO:0034810157/0001


SN:29213292D006

**Notes**


- Marking IEC 60384-14 does not apply for  $\varnothing \leq 9$  mm
- "XX - XXX" is a placeholder for date code and lot number:  
 "XX -" is the year and month according to IEC 60062  
 "- XXX" is the last 3 digits of the lot number









## CAPACITANCE CHANGE VS. TEMPERATURE (Typical)



## INSERTION LOSS VS. FREQUENCY (Typical)



## AC CURRENT VS. VOLTAGE (Typical)





## STORAGE

The capacitors must not be stored in a corrosive atmosphere, where sulphide or chloride gas, acid, alkali or salt are present. Exposure of the components to moisture, should be avoided. The solderability of the leads is not affected by storage of up to 24 months (temperature +10 °C to +40 °C, relative humidity up to 60 % RH). Class 2 ceramic dielectric capacitors are also subject to aging see general information ([www.vishay.com/doc?23140](http://www.vishay.com/doc?23140)).

## SOLDERING

SOLDERING SPECIFICATIONS		
Soldering test for capacitors with wire leads: (according to IEC 60068-2-20, solder bath method)		
	SOLDERABILITY	RESISTANCE TO SOLDERING HEAT
Soldering temperature	(235 ± 5) °C	(260 ± 5) °C
Soldering duration	(2 ± 0.5) s	(10 ± 1) s
Distance from component body	≥ 2 mm	≥ 5 mm

## SOLDERING RECOMMENDATIONS

Ceramic capacitors are very sensitive to rapid changes in temperature (thermal shock) therefore the solder heat resistance specification (see table above) should not be exceeded. Exposing the capacitor to excessive heating may result in thermal shocks that can crack the ceramic body. Similarly, excessive heating can cause the internal solder junction to melt.

When soldering radial leaded ceramic capacitors with a soldering iron, it should be performed under the following conditions and should not exceed:

- Maximum temperature of iron-tip: 400 °C
- Maximum soldering iron wattage: 50 W
- Maximum soldering time: 3.5 s

Failure to follow the above cautions may result, in worst case, in short circuit or cause fuming or thermo-mechanical damage when the product is used.

Leaded ceramic capacitors are not designed for reflow process or dipping the body into a solder melt.

## CLEANING

The components should be cleaned immediately following the soldering operation with vapor degreasers.

### CLEANING (ULTRASONIC CLEANING)

To perform ultrasonic cleaning, observe the following conditions:

- Maximum rinse bath capacity output: 20 W/liter
- Maximum rinsing time: 300 s
- Do not vibrate the PCB/PWB directly
- Excessive ultrasonic cleaning may lead to mechanical damage

## SOLVENT RESISTANCE

The coating and marking of the capacitors are resistant to the following test method:

IEC 60068-2-45 (method XA)

## MOUNTING

We do not recommend modifying the lead terminals, e.g. bending or cropping. This action could break the coating or crack the ceramic insert. In order to avoid such failures we are offering different lead wire designs (e.g. straight, inline, inside crimp, outside crimp etc.) If however, the lead must be modified in any way, we recommend support of the lead with a clamping fixture next to the coating. If a defined product stop is required for mounting on a PCB, a mechanically formed product stop or a mounting tool should be used.

**OPERATING VOLTAGE**

In case the voltage is applied to the circuit, starting as well as stopping, may generate irregular voltage for a transit period because of resonance or switching. Be sure to use a capacitor with a rated voltage range that includes these irregular voltages.

**OPERATING TEMPERATURE AND SELF-GENERATED HEAT**

Keep the surface temperature of a capacitor below the upper limit of its rated operating temperature range. Be sure to take into account the heat generated by the capacitor itself. When the capacitor is used in a high frequency, pulse, or similar application, it may have self-generated heat due to dielectric dissipation.

Temperature increase due to self-generated heating should not exceed 20 °C while operating at an atmosphere temperature of 25 °C.

When measuring, the surface temperature, make sure that the capacitor is not affected by radiant, conductive and convective heat by its surroundings. Excessive heat may lead to thermo-mechanical deterioration of the capacitor's characteristics and reliability.

RELATED DOCUMENTS	
General Information	<a href="http://www.vishay.com/doc?23140">www.vishay.com/doc?23140</a>
CB Test Certificate	<a href="http://www.vishay.com/doc?22234">www.vishay.com/doc?22234</a>
VDE Marks Approval	<a href="http://www.vishay.com/doc?22235">www.vishay.com/doc?22235</a>
UL Test Certificate	<a href="http://www.vishay.com/doc?22236">www.vishay.com/doc?22236</a>



## Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Vishay products are not designed for use in life-saving or life-sustaining applications or any application in which the failure of the Vishay product could result in personal injury or death unless specifically qualified in writing by Vishay. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.