

Power Electronic AC Capacitors (PEC)



FEATURES

- Overpressure disconnecter
- Self-healing properties
- High reliability
- Cylindrical aluminum case
- Plastic self-extinguishing sealing covers

APPLICATIONS

- Power electronic AC applications with high current and harmonics distortion with long life expectancy
- Inverter
- Filtering
- Switching

LINKS TO ADDITIONAL RESOURCES


[3D Models](#)

QUICK REFERENCE DATA	
DESCRIPTION	VALUE
Rated AC voltage min.	350 V _{AC}
Rated AC voltage max.	1700 V _{AC}
Capacitance min.	6.8 μF
Capacitance max.	600 μF
Capacitance tolerance	± 5 %
Technology	Metallized polypropylene film, self-healing
Dielectric loss factor (dielectric only)	$\tan \delta_0 \cdot 2 \times 10^{-4}$
Operating temperature min.	-40 °C
Operating temperature max.	+85 °C (hotspot)
Climatic category	3K22 (IBB design), 3K21 (IBP / IAP design) according to IEC 60721-3-3
Life time expectancy	100 000 h at U _{RMS} , θ _{hs} = 70 °C
Reliability	300 FIT
DC test voltage (terminal to terminal)	2.15 x U _N , 10 s
AC test voltage (terminal to case)	According to IEC 61071-1, 2 x U _i + 1000
Filling	Biodegradable vegetable oil (non PCB)
Standard	IEC 61071, IEC 61881-1, UL 94 V-0 (plastic isolator of the bushing)



TYPE DESCRIPTION												
TYPE ACMKP...-... IBB / IBP / IAP	C _N (μF)	I _{max.} (A)	\hat{i} (kA)	\hat{I}_S (kA)	R _S (mΩ)	R _{th} (K/W)	DIA. (mm)	H (mm)	d (mm)	TERMINAL	MOQ / PU (PCS)	DRAWING NO.
ACMKP 350; U_N = 350 V; U_{RMS} = 250 V												
ACMKP 350-30	30	23	0.3	0.9	1.83	14.6	50	75	23	Faston	25	3
ACMKP 350-40	40	25	0.4	1.1	1.65	13.4	50	75	23	Faston	25	3
ACMKP 350-50	50	30	0.5	1.5	1.41	10.8	64	75	23.5	M6	9	2
ACMKP 350-60	60	33	0.6	1.8	1.33	9.5	64	75	23.5	M6	9	2
ACMKP 350-70	70	33	0.6	1.8	1.3	9.6	64	75	23.5	M6	9	2
ACMKP 350-80	80	30	0.6	1.7	1.6	9.3	64	82.5	23.5	M6	9	2
ACMKP 350-100	100	31	0.6	1.9	1.52	9	64	82.5	23.5	M6	9	2
ACMKP 350-150	150	50	1	3	1.4	4.5	64	145	23.5	M6	9	2
ACMKP 350-200	200	52	1.3	3.8	1.3	3.8	64	145	23.5	M6	9	2
ACMKP 350-250	250	64	2.3	6.8	0.69	4.3	84	120	35	M10	4	1
ACMKP 350-300	300	64	2.2	6.5	0.83	3.7	84	145	35	M10	4	1
ACMKP 350-400	400	60	2.2	6.5	0.96	3.4	84	168	35	M10	4	1
ACMKP 350-500	500	60	2.4	7.4	0.94	3.4	84	168	35	M10	4	1
ACMKP 350-600	600	80	3.3	9.8	0.71	2.2	84	245	35	M10	4	1
ACMKP 465; U_N = 465 V; U_{RMS} = 330 V												
ACMKP 465-20	20	20	0.2	0.7	2.1	16	50	75	23	Faston	25	3
ACMKP 465-25	25	22	0.3	0.8	2	14.4	50	75	23	Faston	25	3
ACMKP 465-30	30	22	0.3	0.9	1.9	14.4	50	75	23	Faston	25	3
ACMKP 465-40	40	31	0.5	1.4	1.47	9.7	64	75	23.5	M6	9	2
ACMKP 465-50	50	28	0.4	1.3	1.83	9.8	64	82.5	23.5	M6	9	2
ACMKP 465-60	60	24	0.4	1.2	2.25	10	64	95	23.5	M6	9	2
ACMKP 465-70	70	26	0.5	1.4	2.08	9.2	64	95	23.5	M6	9	2
ACMKP 465-80	80	24	0.4	1.3	2.47	8.6	64	108	23.5	M6	9	2
ACMKP 465-100	100	45	0.9	2.6	1.45	4.5	64	145	23.5	M6	9	2
ACMKP 465-120	120	40	0.8	2.4	1.73	4.4	64	165	23.5	M6	9	2
ACMKP 465-150	150	32	0.8	2.5	1.42	7.6	84	105	35	M10	4	1
ACMKP 465-200	200	58	1.7	5.2	0.88	4.1	84	145	35	M10	4	1
ACMKP 465-250	250	54	1.7	5.1	1.04	3.7	84	168	35	M10	4	1
ACMKP 465-300	300	50	1.7	5	1.2	3.4	84	193	35	M10	4	1
ACMKP 465-400	400	80	2.7	8.1	0.75	2.3	84	243	35	M10	4	1
ACMKP 465-500	500	60	2.7	8.2	1.04	2.7	100	193	35	M10	4	1
ACMKP 640; U_N = 640 V; U_{RMS} = 450 V												
ACMKP 640-10	10	16	0.2	0.6	1.92	18.4	50	70	23	Faston	25	3
ACMKP 640-15	15	18	0.2	0.7	2.24	15.8	50	75	23	Faston	25	3
ACMKP 640-20	20	17	0.2	0.7	2.83	14.1	50	82.5	20	M6	25	2
ACMKP 640-25	25	17	0.2	0.6	3.54	12.6	50	95	20	M6	25	2
ACMKP 640-30	30	16	0.2	0.6	4.24	11.2	50	108	20	M6	25	2
ACMKP 640-40	40	22	0.3	1	2.54	10.4	64	95	23.5	M6	9	2
ACMKP 640-50	50	21	0.3	1	2.91	9.2	64	108	23.5	M6	9	2
ACMKP 640-70	70	42	0.7	2.2	1.55	4.8	64	145	23.5	M6	9	2
ACMKP 640-80	80	50	1.2	3.6	1.15	4.1	84	120	35	M10	4	1
ACMKP 640-100	100	54	1.5	4.4	0.77	5	84	120	35	M10	4	1
ACMKP 640-150	150	46	1.3	2.8	1.15	4.2	84	168	35	M10	4	1
ACMKP 640-200	200	56	1.2	6.6	0.84	3.7	100	145	35	M10	4	1
ACMKP 640-250	250	52	2.1	6.4	0.98	3.4	100	168	35	M10	4	1
ACMKP 640-400	400	50	2.8	8.3	0.75	3.3	116	193	35	M10	4	1
ACMKP 640-500	500	75	4.2	12.7	0.46	2.5	116	243	35	M10	4	1




TYPE DESCRIPTION												
TYPE ACMKP...-... IBB / IBP / IAP	C _N (μF)	I _{max.} (A)	\hat{i} (kA)	\hat{I}_S (kA)	R _S (mΩ)	R _{th} (K/W)	DIA. (mm)	H (mm)	d (mm)	TERMINAL	MOQ / PU (PCS)	DRAWING NO.
ACMKP 680; U_N = 680 V; U_{RMS} = 480 V												
ACMKP 680-10	10	16	0.2	0.6	1.89	18.2	50	62.5	23	Faston	25	3
ACMKP 680-15	15	16	0.2	0.5	3.34	15.5	50	82.5	23	Faston	25	3
ACMKP 680-20	20	17	0.2	0.6	3.21	13.4	50	87.5	23	Faston	25	3
ACMKP 680-25	25	21	0.3	0.9	2.33	12.5	64	82.5	23.5	M6	9	2
ACMKP 680-30	30	23	0.4	1	2.09	11.2	64	82.5	23.5	M6	9	2
ACMKP 680-40	40	22	0.4	1	2.49	10	64	95	23.5	M6	9	2
ACMKP 680-50	50	21	0.4	1.1	2.86	8.9	64	108	23.5	M6	9	2
ACMKP 680-60	60	40	0.7	2.1	1.58	4.9	64	145	23.5	M6	9	2
ACMKP 680-68	68	48	1.1	3.3	1.18	4.3	84	120	35	M10	4	1
ACMKP 680-70	70	36	0.6	1.9	1.93	4.7	64	170	23.5	M6	9	2
ACMKP 680-80	80	52	1.3	3.8	0.8	5.3	84	120	35	M10	4	1
ACMKP 680-100	100	48	1.2	3.5	1	4.8	84	145	35	M10	4	1
ACMKP 680-150	150	54	1.7	5.2	0.88	4	100	145	35	M10	4	1
ACMKP 680-200	200	50	1.8	5.4	1.02	3.5	100	168	35	M10	4	1
ACMKP 680-250	250	75	2.9	8.7	0.65	2.6	100	205	35	M10	4	1
ACMKP 680-300	300	50	2.6	7.9	0.67	3.7	116	168	35	M10	4	1
ACMKP 680-350	350	75	4	11.8	0.41	3	116	205	35	M10	4	1
ACMKP 680-400	400	75	3.6	10.8	0.48	2.6	116	243	35	M10	4	1
ACMKP 750; U_N = 750 V; U_{RMS} = 530 V												
ACMKP 750-10	10	17	0.2	0.5	2.74	16.4	50	75	23	Faston	25	3
ACMKP 750-15	15	23	0.3	0.9	1.91	13	64	75	26.5	Faston	9	3
ACMKP 750-20	20	21	0.3	0.8	2.42	12	64	82.5	26.5	Faston	9	3
ACMKP 750-30	30	22	0.3	0.9	2.69	9.9	64	95	23.5	M6	9	2
ACMKP 750-40	40	22	0.4	1.1	2.89	8.3	64	108	23.5	M6	9	2
ACMKP 750-50	50	20	0.3	1	3.95	7.3	64	132.5	23.5	M6	9	2
ACMKP 750-60	60	26	0.5	1.6	2.25	7.3	84	105	35	M10	4	1
ACMKP 750-65	65	27	0.6	1.7	2.16	6.9	84	105	35	M10	4	1
ACMKP 750-70	70	28	0.6	1.8	1.77	7.7	84	105	35	M10	4	1
ACMKP 750-75	75	33	0.8	2.4	1.2	7.4	100	93	35	M10	4	1
ACMKP 750-80	80	50	1.1	3.3	1.37	3.7	84	143	35	M10	4	1
ACMKP 750-100	100	54	1.4	4.1	1.28	3.2	100	143	35	M10	4	1
ACMKP 750-150	150	56	2.1	6.2	0.86	3.6	116	143	35	M10	4	1
ACMKP 750-200	200	56	2.1	6.4	1.21	2.6	116	168	35	M10	4	1
ACMKP 750-220	220	56	2.3	6.8	1.2	2.6	116	168	35	M10	4	1
ACMKP 750-250	250	52	2.1	6.4	0.83	3.2	116	193	35	M10	4	1
ACMKP 750-300	300	81	3.2	9.7	1	1.6	116	243	35	M10	4	1
ACMKP 750-350	350	75	3.1	9.2	1.08	1.6	116	280	35	M10	4	1
ACMKP 750-400	400	70	4.3	12.9	0.48	2.5	136	243	35	M10	2	1
ACMKP 750-500	500	70	4.4	13.2	0.54	2.1	136	280	35	M10	2	1
ACMKP 850; U_N = 850 V; U_{RMS} = 600 V												
ACMKP 850-10	10	15	0.3	1	2.37	12.9	64	82.5	26.5	Faston	9	3
ACMKP 850-15	15	15	0.5	1.5	1.9	10.6	64	82.5	26.5	Faston	9	3
ACMKP 850-20	20	27	0.5	1.5	1.96	9.4	64	95	26.5	Faston	9	3
ACMKP 850-25	25	30	0.6	1.8	1.76	8.3	64	95	23.5	M6	9	2
ACMKP 850-30	30	27	0.6	1.8	2.03	7.7	64	108	23.5	M6	9	2
ACMKP 850-40	40	26	0.6	1.7	2.65	6.7	64	132.5	23.5	M6	9	2
ACMKP 850-47	47	37	1.1	3.3	1.03	7.5	84	93	35	M10	4	1
ACMKP 850-50	50	34	1	3	1.26	7.4	84	105	35	M10	4	1
ACMKP 850-60	60	40	1.5	4.3	0.92	6.6	100	93	35	M10	4	1
ACMKP 850-70	70	50	1.7	5.1	1.01	4	84	168	35	M10	4	1
ACMKP 850-80	80	50	2	5.8	0.98	3.8	84	168	35	M10	4	1
ACMKP 850-100	100	60	2.4	7.2	0.92	3.4	100	168	35	M10	4	1
ACMKP 850-120	120	62	2.9	8.7	0.89	3.1	100	168	35	M10	4	1
ACMKP 850-130	130	62	3.1	9.4	0.88	3	100	168	35	M10	4	1
ACMKP 850-150	150	60	2.9	8.8	1.01	2.8	100	193	35	M10	4	1
ACMKP 850-200	200	60	3.9	11.7	0.66	3.1	116	193	35	M10	4	1
ACMKP 850-250	250	60	3.5	10.4	0.86	2.6	116	243	35	M10	4	1
ACMKP 850-300	300	80	7.2	21.7	0.4	2.5	136	243	35	M10	2	1




TYPE DESCRIPTION												
TYPE ACMKP...-... IBB / IBP / IAP	C _N (μF)	I _{max.} (A)	\hat{i} (kA)	\hat{I}_S (kA)	R _S (mΩ)	R _{th} (K/W)	DIA. (mm)	H (mm)	d (mm)	TERMINAL	MOQ / PU (PCS)	DRAWING NO.
ACMKP 1.02; U_N = 1020 V; U_{RMS} = 720 V												
ACMKP 1.02-10	10	21	0.3	0.8	2.27	13.7	50	95	20	M6	25	2
ACMKP 1.02-20	20	27	0.6	1.7	1.29	11.3	84	93	35	M10	4	1
ACMKP 1.02-25	25	30	0.7	2.2	1.12	10	84	93	35	M10	4	1
ACMKP 1.02-33	33	34	0.9	2.8	0.98	8.7	84	93	35	M10	4	1
ACMKP 1.02-50	50	30	0.8	2.5	1.78	6.2	84	132.5	35	M10	4	1
ACMKP 1.02-60	60	38	1.4	4.1	1.08	5.8	100	105	35	M10	4	1
ACMKP 1.02-70	70	60	2	6.1	0.96	3.3	100	168	35	M10	4	1
ACMKP 1.02-80	80	60	2.3	7	0.93	3.2	100	168	35	M10	4	1
ACMKP 1.02-100	100	56	2.4	7	1.06	2.9	100	193	35	M10	4	1
ACMKP 1.02-150	150	62	3.5	10.5	0.69	2.8	100	193	35	M10	4	1
ACMKP 1.02-200	200	80	4.7	14	0.49	2.2	116	280	35	M10	4	1
ACMKP 1.02-250	250	63	7	21	0.42	2.5	136	243	35	M10	2	1
ACMKP 1.1; U_N = 1100 V; U_{RMS} = 780 V												
ACMKP 1.1-10	10	21	0.3	0.9	2.55	11.2	64	95	23.5	M6	9	2
ACMKP 1.1-15	15	25	0.5	1.4	2	9.7	84	93	35	M10	4	1
ACMKP 1.1-20	20	29	0.6	1.9	1.73	8.1	84	93	35	M10	4	1
ACMKP 1.1-25	25	32	0.8	2.4	1.57	7	84	93	35	M10	4	1
ACMKP 1.1-33	33	32	0.8	2.5	1.38	7.3	84	105	35	M10	4	1
ACMKP 1.1-47	47	36	1.2	3.6	1.16	6.1	100	105	35	M10	4	1
ACMKP 1.1-68	68	56	2.1	6.4	0.95	3.3	100	168	35	M10	4	1
ACMKP 1.1-75	75	58	2.4	7.1	0.93	3.2	100	168	35	M10	4	1
ACMKP 1.1-100	100	80	3.1	9.4	0.71	2.2	100	243	35	M10	4	1
ACMKP 1.1-150	150	80	4.7	14.1	0.67	2	116	243	35	M10	4	1
ACMKP 1.2; U_N = 1200 V; U_{RMS} = 850 V												
ACMKP 1.2-6,8	6.8	18	0.2	0.7	2.83	13.4	50	95	20	M6	25	2
ACMKP 1.2-10	10	22	0.3	1	2.09	11.9	64	95	23.5	M6	9	2
ACMKP 1.2-15	15	24	0.4	12.3	2.17	9.5	64	108	23.5	M6	9	2
ACMKP 1.2-20	20	30	0.7	2	1.33	8.9	84	93	35	M10	4	1
ACMKP 1.2-25	25	28	0.7	2	1.55	8	84	105	35	M10	4	1
ACMKP 1.2-33	33	46	1.1	3.3	1.17	4.5	84	168	35	M10	4	1
ACMKP 1.2-40	40	50	1.4	4.1	1.09	4	84	168	35	M10	4	1
ACMKP 1.2-47	47	50	1.6	4.8	1.04	3.3	84	168	35	M10	4	1
ACMKP 1.2-50	50	46	1.4	4.1	1.26	3.7	84	193	35	M10	4	1
ACMKP 1.2-60	60	54	2	6.1	0.97	3.4	100	168	35	M10	4	1
ACMKP 1.2-68	68	72	2.3	6.9	0.77	2.5	84	243	35	M10	4	1
ACMKP 1.2-80	80	80	2.7	8.1	0.73	2.3	100	243	35	M10	4	1
ACMKP 1.2-100	100	50	2.7	8.2	1.04	3	116	193	35	M10	4	1
ACMKP 1.2-150	150	60	5.1	15.2	0.44	2.7	136	243	35	M10	2	1
ACMKP 1.2-200	200	57	5.5	16.4	0.49	2.3	136	280	35	M10	2	1
ACMKP 1.4; U_N = 1400 V; U_{RMS} = 1000 V												
ACMKP 1.4-15	15	30	0.6	1.9	1.41	8.4	84	93	35	M10	4	1
ACMKP 1.4-22	22	25	0.6	1.7	2.37	6.5	84	132.5	35	M10	4	1
ACMKP 1.4-30	30	30	0.8	2.3	1.92	5.6	100	132.5	35	M10	4	1
ACMKP 1.4-47	47	54	1.6	5	1.18	3	100	193	35	M10	4	1
ACMKP 1.4-60	60	81	2.6	7.8	0.75	2.1	100	243	35	M10	4	1
ACMKP 1.7; U_N = 1700 V; U_{RMS} = 1200 V												
ACMKP 1.7-30	30	81	3	9	0.73	1.9	100	243	35	M10	4	1
ACMKP 1.7-40	40	81	4	12	0.7	1.7	116	243	35	M10	4	1
ACMKP 1.7-60	60	81	3.3	9.9	1	1.4	116	355	35	M10	4	1
ACMKP 1.7-90	90	81	4.9	14.7	0.92	1.3	136	355	35	M10	2	1


DIMENSIONS in millimeters



Drawing 1
ACMKP...-...IBB



Drawing 2
ACMKP...-...IBP



Drawing 3
ACMKP...-...IAP

Note

- For the diameters 50 mm and 64 mm you can choose between M6 bolts and faston terminal solution

Contact Us

Other voltage, current, and capacitance values are available on request without additional cost and lead time for the individual design.



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.