




High Voltage (Up to 3 kV) Thick Film Chip Resistors



FEATURES

- High operating voltage (up to 3 kV)
- Low voltage coefficient of resistance (VCR): 25 ppm/V
- RCV-AT series AEC-Q200 qualified
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912



RoHS COMPLIANT HALOGEN FREE

The RCV e3 high voltage thick film chip resistors series are the perfect choice for modern electronics with high voltage requirements. Typical applications include automotive inverters for H(EV) cars, voltage measurement systems as implemented in on board chargers, and DC-DC converters.

APPLICATIONS

- Inverters for (H)EV cars
- On board chargers
- DC-DC converters

TECHNICAL SPECIFICATIONS		
DESCRIPTION	RCV2010-AT e3	RCV2512-AT e3
Imperial size	2010	2512
Metric size code	RR5025M	RR6332M
Resistance range	100 kΩ to 100 MΩ	
Resistance tolerance	± 5 %; ± 1 %	
Temperature coefficient	± 200 ppm/K; ± 100 ppm/K	
Voltage coefficient	25 ppm/V	
Rated dissipation, P_{70} ⁽¹⁾	0.75 W	1.0 W
Operating voltage, U_{max} . AC _{RMS} /DC	2000 V	3000 V
Permissible film temperature, $\vartheta_{F max}$ ⁽¹⁾	155 °C	
Operating temperature range	-55 °C to +155 °C	
Max. resistance change at P_{70} for resistance range, $ \Delta R/R $ after:		
1000 h	≤ 2.0 %	≤ 2.0 %

Note

⁽¹⁾ Please refer to APPLICATION INFORMATION below

APPLICATION INFORMATION


When the resistor dissipates power, a temperature rise above the ambient temperature occurs, dependent on the thermal resistance of the assembled resistor together with the printed circuit board. The rated dissipation applies only if the permitted film temperature is not exceeded.

These resistors do not feature a limited lifetime when operated within the permissible limits. However, resistance value drift increasing over operating time may result in exceeding a limit acceptable to the specific application, thereby establishing a functional lifetime.



TEMPERATURE COEFFICIENT AND RESISTANCE RANGE				
TYPE / SIZE	TCR	TOLERANCE	RESISTANCE	E-SERIES
RCV2010-AT e3	± 200 ppm/K	± 5 %	100 kΩ to 100 MΩ	E24
	± 100 ppm/K	± 1 %	100 kΩ to 10 MΩ	E24; E96
RCV2512-AT e3	± 200 ppm/K	± 5 %	100 kΩ to 100 MΩ	E24
	± 100 ppm/K	± 1 %	100 kΩ to 10 MΩ	E24; E96

PACKAGING						
TYPE / SIZE	CODE	QUANTITY	PACKAGING STYLE	WIDTH	PITCH	PACKAGING DIMENSIONS
RCV2010-AT e3	EF = E02	4000	Blister tape according to IEC 60286-3, type 2a	12 mm	4 mm	Ø 180 mm / 7"
RCV2512-AT e3	EG = E67	2000		12 mm	8 mm	Ø 180 mm / 7"
	EH = E82	4000			4 mm	





DESCRIPTION

Production is strictly controlled and follows an extensive set of instructions established for reproducibility. A cermet film layer and a glass-over are deposited on a high grade (Al₂O₃) ceramic substrate. Specially designed inner contacts are deposited on both sides. A special laser is used to achieve the target value by smoothly fine trimming the resistive layer without damaging the ceramics. The resistor elements are covered by a protective coating designed for electrical, mechanical, and climatic protection. The terminations receive a final pure tin on nickel plating. The result of the determined production is verified by an extensive testing procedure on 100 % of the individual chip resistors. Only accepted products are laid directly into the tape in accordance with **IEC 60286-3 type 1a and 2a** ⁽¹⁾.

ASSEMBLY

The resistors are suitable for processing on automatic SMD assembly systems. They are suitable for automatic soldering using wave, reflow or vapor phase as shown in **IEC 61760-1** ⁽¹⁾. The encapsulation is resistant to all cleaning solvents commonly used in the electronics industry, including alcohols, esters, and aqueous solutions. The suitability of conformal coatings, potting compounds and their processes, if applied, shall be qualified by appropriate means to ensure the long-term stability of the whole system.

The resistors are RoHS-compliant, the pure tin plating provides compatibility with lead (Pb)-free and lead-containing soldering processes. Solderability is specified for 2 years after production or requalification. The permitted storage time is 20 years. The immunity of the plating against tin whisker growth has been proven under extensive testing.

MATERIALS

Vishay acknowledges the following systems for the regulation of hazardous substances:

- IEC 62474, Material Declaration for Products of and for the Electrotechnical Industry, with the list of declarable substances given therein ⁽²⁾
- The Global Automotive Declarable Substance List (GADSL) ⁽³⁾
- The REACH regulation (1907/2006/EC) and the related list of substances with very high concern (SVHC) ⁽⁴⁾ for its supply chain

The products do not contain any of the banned substances as per IEC 62474, GADSL, or the SVHC list, see www.vishay.com/how/leadfree.

Notes

- ⁽¹⁾ The quoted IEC standards are also released as EN standards with the same number and identical contents
- ⁽²⁾ The IEC 62474 list of declarable substances is maintained in a dedicated database, which is available at <http://std.iec.ch/iec62474>
- ⁽³⁾ The Global Automotive Declarable Substance List (GADSL) is maintained by the American Chemistry Council and available at www.gadsl.org
- ⁽⁴⁾ The SVHC list is maintained by the European Chemical Agency (ECHA) and available at <http://echa.europa.eu/candidate-list-table>

Hence the products fully comply with the following directives:

- 2000/53/EC End-of-Life Vehicle Directive (ELV) and Annex II (ELV II)
- 2011/65/EU Restriction of the Use of Hazardous Substances Directive (RoHS) with amendment 2015/863/EU
- 2012/19/EU Waste Electrical and Electronic Equipment Directive (WEEE)

Vishay pursues the elimination of conflict minerals from its supply chain, see the Conflict Minerals Policy at www.vishay.com/doc?49037.

APPROVALS


The resistors are qualified according to AEC-Q200.

Where applicable, the resistors are tested in accordance with **EN 140401-802** which refers to **EN 60115-1**, **EN 60115-8** and the variety of environmental test procedures of the **IEC 60068** ⁽¹⁾ series.


RELATED PRODUCTS

For high voltage thin film products, please refer to latest edition of TNPV e3, High Voltage Thin Film Chip Resistors datasheet, www.vishay.com/doc?28881.

DERATING



NOMINAL OPERATING VOLTAGE



The permissible operating voltage U_{max} equals the rated voltage.
For ambient temperatures above 70 °C power derating must be considered

TESTS AND REQUIREMENTS

All executed tests are carried out in accordance with the following specifications:

- EN 60115-1, generic specification
- EN 60115-8 (successor of EN 140400), sectional specification
- EN 140401-802, detail specification
- IEC 60068-2-xx, test methods

The parameters stated in the “Test Procedures and Requirements” table are based on the required tests and permitted limits of EN 140401-802. The table presents only the most important tests, for the full test schedule refer to the documents listed above. However, some additional tests and a number of improvements against those minimum requirements have been included.

The testing also covers most of the requirements specified by EIA/IS-703 and JIS-C-5201-1.

The tests are carried out under standard atmospheric conditions in accordance with IEC 60068-1, 4.3, whereupon the following values are applied:

- Temperature: 15 °C to 35 °C
- Relative humidity: 25 % to 75 %
- Air pressure: 86 kPa to 106 kPa (860 mbar to 1060 mbar)
- A climatic category LCT / UCT / 56 is applied, defined by the lower category temperature (LCT), the upper category temperature (UCT), and the duration of exposure in the damp heat, steady state test (56 days).




TEST PROCEDURES AND REQUIREMENTS										
EN 60115-1 CLAUSE	IEC 60082-2 (1) TEST METHOD	TEST	PROCEDURE			REQUIREMENTS PERMISSIBLE CHANGE (ΔR)				
						STABILITY CLASS 1 OR BETTER	STABILITY CLASS 2 OR BETTER			
			Stability for product types:			100 k Ω to 100 M Ω				
			RVC-AT e3							
4.5	-	Resistance	-			$\pm 1 \%$	$\pm 5 \%$			
4.8	-	Temperature coefficient	At (20 / -55 / 20) °C and (20 / 155 / 20) °C			± 100 ppm/K	± 200 ppm/K			
4.25.1	-	Endurance at 70 °C	$U = P_{70} \times R$ or $U = U_{max.}$ whichever is the less severe; 1.5 h on; 0.5 h off; 70 °C; 1000 h; 70 °C; 8000 h			$\pm (2 \% R + 0.1 \Omega)$ $\pm (4 \% R + 0.1 \Omega)$				
4.25.3	-	Endurance at upper category temperature	155 °C; 1000 h			$\pm (2 \% R + 0.1 \Omega)$				
4.24	78 (Cab)	Damp heat, steady state	(40 \pm 2) °C; 56 days; (93 \pm 3) % RH			$\pm (2 \% R + 0.1 \Omega)$				
4.37	67 (Cy)	Damp heat, steady state, accelerated power operation mode	(85 \pm 2) °C; (85 \pm 5) % RH $U = (0.1 \times P_{85} \times R)^{1/2} \leq 0.3 \times U_{max.}$; 1000 h			$\pm (2 \% R + 0.1 \Omega)$				
4.23	-	Climatic sequence:				$\pm (2 \% R + 0.1 \Omega)$				
4.23.2	2 (Bb)	Dry heat						125 °C; 16 h		
4.23.3	30 (Db)	Damp heat, cyclic						55 °C; 24 h; ≥ 90 % RH; 1 cycle		
4.23.4	1 (Ab)	Cold						-55 °C; 2 h		
4.23.5	13 (M)	Low air pressure						8.5 kPa; 2 h; (25 \pm 10) °C		
4.23.6	30 (Db)	Damp heat, cyclic						55 °C; 5 days; > 90 % RH; 5 cycles		
4.23.7	-	DC load						$U = (P_{70} \times R)^{1/2} \leq U_{max.}$; 1 min		
-	1 (Aa)	Cold	-55 °C; 2 h			$\pm (0.5 \% R + 0.05 \Omega)$				
4.19	14 (Na)	Rapid change of temperature	30 min. at -55 °C and 30 min. at 125 °C; 1000 cycles			$\pm (1 \% R + 0.05 \Omega)$ no visible damage				
4.13	-	Short time overload	$U = 2.5 \times (P_{70} \times R)^{1/2} \leq 2 \times U_{max.}$; whichever is the less severe; 5 s			$\pm (2 \% R + 0.05 \Omega)$				
			Style	Duration	Maximum U_{OL}					
			RVC2010-AT	5 s	3000					
			RVC2512-AT	5 s	4000					
4.27	-	Single pulse high voltage overload	Severity no. 4: $U = 10 \times (P_{70} \times R)^{1/2}$ or $U = 2 \times U_{max.}$; whichever is the less severe; 10 pulses 10 μ s / 700 μ s			$\pm (2 \% R + 0.1 \Omega)$ no visible damage				
4.39	-	Periodic electric overload	$U = 15 \times P_{70} \times R$ or $U = 2 \times U_{max.}$; whichever is the less severe; 0.1 s on; 2.5 s off; 1000 cycles			$\pm (2 \% R + 0.05 \Omega)$				
4.38	-	Electrostatic discharge (human body model)	IEC 61340-3-1 (1); 3 positive + 3 negative discharges; RVC2010: 12 kV RVC2512: 25 kV			$\pm (1 \% R + 0.05 \Omega)$				
4.22	6 (Fc)	Vibration	Endurance by sweeping; 10 Hz to 2000 Hz; no resonance; amplitude ≤ 1.5 mm or ≤ 200 m/s ² ; 7.5 h			$\pm (0.25 \% R + 0.05 \Omega)$ no visible damage	$\pm (0.5 \% R + 0.05 \Omega)$ no visible damage			
4.17	58 (Td)	Solderability	Solder bath method, SnPb40; non-activated flux (235 \pm 5) °C; (2 \pm 0.2) s			Good tinning (≥ 95 % covered); no visible damage				
			Solder bath method, Sn96.5Ag3Cu0.5; non-activated flux (245 \pm 5) °C; (3 \pm 0.3) s							


TEST PROCEDURES AND REQUIREMENTS						
EN 60115-1 CLAUSE	IEC 60082-2 ⁽¹⁾ TEST METHOD	TEST	PROCEDURE	REQUIREMENTS PERMISSIBLE CHANGE (ΔR)		
				STABILITY CLASS 1 OR BETTER	STABILITY CLASS 2 OR BETTER	
				100 k Ω to 100 M Ω		
4.18	58 (Td)	Resistance to soldering heat	Soldering bath method; (260 \pm 5) °C; (10 \pm 1) s	\pm (0.25 % R + 0.05 Ω)	\pm (0.5 % R + 0.05 Ω)	
4.29	45 (XA)	Component solvent resistance	Isopropyl alcohol +50 °C; method 2	No visible damage		
4.32	21 (Uu ₃)	Shear (adhesion)	17.7 N	No visible damage		
4.33	21 (Uu ₁)	Substrate bending	Depth 2 mm; 3 times	\pm (1 % R + 0.05 Ω) no visible damage, no open circuit in bent position		
4.7	-	Voltage proof	$U = 1.4 \times U_{ins}$; 60 s	No flashover or breakdown		
4.35	-	Flammability, needle flame test	IEC 60695-11-5 ⁽¹⁾ ; 10 s	No burning after 30 s		

Note

⁽¹⁾ The quoted IEC standards are also released as EN standards with the same number and identical contents

DIMENSIONS


DIMENSIONS AND MASS						
TYPE / SIZE	L (mm)	W (mm)	H (mm)	T1 (mm)	T2 (mm)	MASS (mg)
RCV2010-AT e3	5.0 \pm 0.15	2.5 \pm 0.15	0.6 \pm 0.10	0.6 \pm 0.20	0.45 \pm 0.20	25.5
RCV2512-AT e3	6.3 \pm 0.20	3.15 \pm 0.15	0.6 \pm 0.10	0.6 \pm 0.20	0.45 \pm 0.20	42

SOLDER PAD DIMENSIONS


RECOMMENDED SOLDER PAD DIMENSIONS								
TYPE / SIZE	WAVE SOLDERING				REFLOW SOLDERING			
	G (mm)	Y (mm)	X (mm)	Z (mm)	G (mm)	Y (mm)	X (mm)	Z (mm)
RCV2010-AT e3	3.60	1.65	2.85	6.90	3.70	1.20	2.70	6.10
RCV2512-AT e3	4.90	1.60	3.50	8.10	5.00	1.25	3.35	7.50

Note

- Utilization of the full specified operating voltage may require special considerations on the creepage and clearance distance between conductors at different potential levels



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.