


Jumper, Wire Bridges



FEATURES


- Copper (Cu) wire with 100 % tin (Sn) coating
- Suitable for automatic insertion
- Excellent soldering performance
- Lead (Pb)-free solder contacts
- Pure tin plating provides compatibility with lead (Pb)-free and lead containing soldering processes
- Compliant to RoHS directive 2002/95/EC



RoHS
COMPLIANT

STANDARD ELECTRICAL SPECIFICATIONS		
MODEL	$I_{max.}$ A	$R_{max.}$ mΩ
DB1U	5	6.0
DB2U	8	4.5
DB4U	12	2.5

DIMENSIONS [in millimeters]



MODEL	B	T	d	A
DB1U	53 ± 1.5	6.0 ± 0.5	0.5	5.0 ± 0.5
DB2U	53 ± 1.5	6.0 ± 0.5	0.6	5.0 ± 0.5
DB4U	53 ± 1.5	6.0 ± 0.5	0.8	5.0 ± 0.5

PART NUMBER AND PRODUCT DESCRIPTION

PART NUMBER: DB1U000000000D000

D	B	1	U	0	0	0	0	0	0	0	0	0	0	D	0	0	0
---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---

MODEL/SIZE	VARIANT	TCR/MATERIAL	VALUE	TOLERANCE	PACKAGING	SPECIAL
DB1U000 DB2U000 DB4U000	0 = Neutral	0 = Neutral	4 digit value 0000	1 digit 0 = Neutral	D0 = R0 = 10 000 pieces on reel D5 = R5 = 5000 pieces on reel	00 = Standard

PRODUCT DESCRIPTION: DB1 U 0R0 R0

<table border="1" style="width: 100%; border-collapse: collapse;"> <tr><td style="text-align: center;">DB1U</td></tr> <tr><td style="text-align: center;">MODEL/SIZE</td></tr> <tr><td style="text-align: center;">DB1U DB2U DB4U</td></tr> </table>	DB1U	MODEL/SIZE	DB1U DB2U DB4U	<table border="1" style="width: 100%; border-collapse: collapse;"> <tr><td style="text-align: center;">0R0</td></tr> <tr><td style="text-align: center;">RESISTANCE VALUE</td></tr> <tr><td style="text-align: center;">0R0 = 0 Ω</td></tr> </table>	0R0	RESISTANCE VALUE	0R0 = 0 Ω	<table border="1" style="width: 100%; border-collapse: collapse;"> <tr><td style="text-align: center;">R0</td></tr> <tr><td style="text-align: center;">PACKAGING</td></tr> <tr><td style="text-align: center;">R0 R5</td></tr> </table>	R0	PACKAGING	R0 R5
DB1U											
MODEL/SIZE											
DB1U DB2U DB4U											
0R0											
RESISTANCE VALUE											
0R0 = 0 Ω											
R0											
PACKAGING											
R0 R5											

Note

(1) Please refer to table PACKAGING for complete information.

- The PART NUMBER shown above is to facilitate the unified part numbering system for ordering products.

PACKAGING		
TYPE	QUANTITY PER REEL	CODE
DB1U	10 000	D0
DB2U	10 000	D0
DB4U	5000	D5



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Vishay products are not designed for use in life-saving or life-sustaining applications or any application in which the failure of the Vishay product could result in personal injury or death unless specifically qualified in writing by Vishay. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.