

NTC Thermistors, Inrush Current Limiters



DESCRIPTION

The standard surge limiter series comprises devices engineered to protect electrical systems by mitigating the impact of potentially harmful power surges. These surge limiters have received UL certification, attesting to their safety and performance.

FEATURES

- Enhanced protection
- Recognized by UL
- Can withstand up to 10 A of continuous current and 80 J of input energy
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912

RoHS
COMPLIANT

APPLICATIONS


- Residential
- Commercial
- Industrial
- Healthcare
- Renewable energy
- Electric vehicle

QUICK REFERENCE DATA

PART NUMBER	RESISTANCE AT 25 °C (R_{25}) (Ω)	TOLERANCE ON R_{25} VALUE (%)	MAX. STEADY-STATE CURRENT UP TO 65 °C (A)	MAX. RECOMMENDED ENERGY RATING (J)	MAX. VOLTAGE (V_{RMS})	MAX. CAPACITANCE AT 120 V_{AC} (μF)
SL121R008	1	± 20	8	40	265	2778
SL121R010	1	± 20	10	28	265	1900
SL121R308	1.3	± 20	8	40	265	2778
SL122R505	2.5	± 25	5	3	265	2500
SL122R507	2.5	± 25	7	25	265	1736
SL125R002	5	± 20	2	25	265	1736
SL125R004	5	± 20	4	40	265	2778
SL125R005	5	± 20	5	40	265	2778
SL128R003	8	± 20	3	25	265	1736
SL128R004	8	± 20	2	25	265	1736
SL1210004	10	± 20	4	40	265	2778
SL1210005	10	± 20	5	60	265	1389
SL1210006	10	± 20	6	40	265	2778
SL1210006B	10	± 20	6	40	265	2778
SL121000603	10	± 20	6	40	265	2778
SL1212004	12	± 20	4	40	265	2778
SL1215004	15	± 15	4	40	265	2778
SL1217004	17.5	± 25	4	30	265	2083
SL1220002	20	± 20	2	30	265	2431
SL1220003	20	± 20	3	35	265	2431
SL1225002	25	± 20	2	30	265	2083
SL1225003	25	± 15	3	45	265	3100
SL1240002	40	± 25	2	20	265	1389
SL1250002	50	± 20	2	20	265	1389
SL1280002	80	± 20	2	30	265	2083
SL1212101	120	± 20	1	25	265	1736
SL1212102	120	± 20	2	25	265	1736
SL1212103	120	± 20	3	25	265	1736
SL1215102	150	± 20	2	10	265	692
SL1222101	220	± 20	1	30	265	2083
SL1222101AT	220	± 20	1	30	265	2083
SL1222101B	220	± 20	1	30	265	2083

**ELECTRICAL SPECIFICATIONS**

PART NUMBER	RESISTANCE AT 100 % MAX. CURRENT (Ω)	RESISTANCE AT 50 % MAX. CURRENT (Ω)	BODY TEMP. AT 100 % MAX. CURRENT ($^{\circ}\text{C}$)	DISSIPATION FACTOR ($\text{mW}/^{\circ}\text{C}$)	THERMAL TIME CONSTANT (s)	MATERIAL TYPE (FOR BETA AND CURVE)
SL121R008	0.043	0.094	176	13.22	40	A
SL121R010	0.03	0.06	182	12.7	47	A
SL121R308	0.04	0.09	150	13.2	40	A
SL122R505	0.1	0.26	146	12.7	47	B
SL122R507	0.06	0.23	167	12.7	47	B
SL125R002	0.3	0.6	152	12.7	47	B
SL125R004	0.07	0.15	182	12.5	22	B
SL125R005	0.07	0.15	182	12.5	22	B
SL128R003	0.17	0.32	129	12.7	47	C
SL128R004	0.3	0.6	152	12.7	47	C
SL1210004	0.19	0.48	162	12.7	47	C
SL1210005	0.15	0.39	162	12.7	47	C
SL1210006	0	0.24	177	13.5	42	C
SL1210006B	0	0.24	177	13.5	42	C
SL121000603	0.12	0.24	177	13.5	42	C
SL1212004	0.4	0.85	173	12.8	26	C
SL1215004	0.16	0.34	152	13.9	54	C
SL1217004	0.16	0.34	152	12.7	47	G
SL1220002	0.45	0.85	132	12.7	40	H
SL1220003	0.49	1.11	139	47	265	H
SL1225002	0.55	0.93	142	12.7	40	H
SL1225003	0.42	0.63	142	12.7	47	H
SL1240002	0.45	0.96	148	12.7	47	I
SL1250002	1	1.33	142	12.7	47	I
SL1280002	0.85	1.63	142	12.7	47	I
SL1212101	2.34	5	129	12	30	M
SL1212102	2.34	5	129	12	30	M
SL1212103	0.88	1.67	179	12	30	M
SL1215102	0.96	-	137	11.4	40	M
SL1222101	4	8.14	142	12	50	L
SL1222101AT	4	8.14	142	12	50	L
SL1222101B	4	8.14	142	12	50	L

MECHANICAL SPECIFICATIONS in millimeters


PART NUMBER	B	C	D	L	S	T	LEAD DIAMETER	LEAD STYLE
SL121R008	5.0 nom.	2.15 ± 0.3	12.0 ± 1.0	38.0 ± 9.0	7.8 ± 2.0	4.0 ± 0.2	0.8 ± 0.05	Straight
SL121R010	5.0 nom.	2.15 nom.	12.0 max.	38.0 nom.	7.8 nom.	4.0 max.	0.8 nom.	Straight
SL121R308	5.0 nom.	2.15 nom.	13.0 max.	38.0 nom.	7.8 nom.	4.5 max.	0.8 nom.	Straight
SL122R505	5.0 nom.	3.5 nom.	13.0 max.	38.0 nom.	7.8 nom.	5.0 max.	0.8 nom.	Straight
SL122R507	5.0 nom.	3.42 ± 0.5	12.0 ± 0.5	38.0 ± 9.0	7.8 ± 2.0	5.1 ± 0.2	0.8 ± 0.1	Straight
SL125R002	5.0 nom.	2.95 nom.	13.0 max.	38.0 nom.	7.8 nom.	5.0 max.	0.8 nom.	Straight
SL125R004	5.0 nom.	2.95 nom.	12.0 max.	38.0 nom.	7.8 nom.	5.0 max.	0.8 nom.	Straight
SL125R005	5.0 nom.	2.95 nom.	12.0 max.	38.0 nom.	7.8 nom.	5.0 max.	0.8 nom.	Straight
SL128R003	5.0 nom.	3.42 ± 0.5	12.0 ± 0.5	38.0 nom.	7.8 ± 2.0	5.0 ± 0.5	0.8 ± 0.1	Straight
SL128R004	5.0 nom.	3.5 nom.	13.0 max.	38.0 nom.	7.8 nom.	6.0 max.	0.8 nom.	Straight
SL1210004	5.0 nom.	3.42 nom.	13.0 max.	38.0 nom.	7.8 nom.	5.5 max.	0.8 nom.	Straight
SL1210005	5.0 nom.	3.2 ± 0.5	12.0 ± 1.0	38.0 ± 9.0	7.8 ± 2.0	5.1 max.	0.8 ± 0.1	Straight
SL1210006	5.0 nom.	3.78 nom.	12.3 max.	38.0 nom.	7.8 nom.	5.5 max.	0.8 nom.	Straight
SL1210006B	6.35 nom.	3.78 nom.	12.3 max.	38.0 nom.	7.8 nom.	5.5 max.	0.8 nom.	Outside kinked
SL121000603	5.0 nom.	3.9 nom.	13.0 max.	38.0 nom.	7.8 nom.	6.0 max.	1.0 nom.	Straight
SL1212004	5.0 nom.	3.5 max.	12.5 max.	38.0 min.	7.8 nom.	5.0 max.	0.8 nom.	Straight
SL1215004	5.0 nom.	2.82 ± 0.5	12.0 ± 0.5	38.0 nom.	7.8 ± 2.0	5.0 ± 0.5	0.8 ± 0.1	Straight
SL1217004	5.0 nom.	3.42 nom.	11.5 max.	38.0 nom.	7.8 nom.	5.1 max.	1.0 nom.	Straight
SL1220002	5.0 nom.	3.42 nom.	12.0 max.	38.0 nom.	7.8 nom.	5.1 max.	0.8 nom.	Straight
SL1220003	5.0 nom.	3.42 nom.	13.0 max.	38.0 nom.	7.8 nom.	5.5 max.	0.8 nom.	Straight
SL1225002	5.0 nom.	3.42 nom.	13.0 max.	38.0 nom.	7.8 nom.	5.5 max.	0.8 nom.	Straight
SL1225003	5.0 nom.	3.42 ± 0.5	12.0 ± 0.5	38.0 ± 9.0	7.8 ± 2.0	5.1 ± 0.2	0.8 ± 0.1	Straight
SL1240002	5.0 nom.	3.42 ± 0.5	12.0 ± 0.5	38.0 nom.	7.8 ± 2.0	5.0 ± 0.5	0.8 ± 0.1	Straight
SL1250002	5.0 nom.	3.42 nom.	13.0 max.	38.0 nom.	7.8 nom.	5.0 max.	0.8 nom.	Straight
SL1280002	5.0 nom.	4.1 nom.	13.0 max.	38.0 nom.	7.8 nom.	6.0 max.	0.8 nom.	Straight
SL1212101	5.0 nom.	3.6 nom.	12.0 max.	38.0 nom.	7.8 nom.	5.0 max.	0.8 nom.	Straight
SL1212102	5.0 nom.	3.6 nom.	12.0 max.	38.0 nom.	7.8 nom.	5.0 max.	0.8 nom.	Straight
SL1212103	5.0 nom.	3.6 nom.	12.0 max.	38.0 nom.	7.8 nom.	5.0 max.	0.8 nom.	Straight
SL1215102	5.0 nom.	3.42 ± 0.5	12.0 ± 1.0	39.0 ± 9.0	7.8 ± 2.0	5.0 ± 0.5	0.8 ± 0.1	Straight
SL1222101	5.0 nom.	3.42 ± 0.5	12.0 ± 0.5	38.0 nom.	7.8 nom.	5.5 ± 0.5	0.8 ± 0.1	Straight
SL1222101AT	6.35 nom.	3.42 ± 0.5	12.0 ± 0.5	38.0 nom.	7.8 nom.	5.5 ± 0.5	0.8 ± 0.1	Inside kinked
SL1222101B	6.35 nom.	3.42 ± 0.5	12.0 ± 0.5	38.0 nom.	7.8 nom.	5.5 ± 0.5	0.8 ± 0.1	Outside kinked



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Vishay products are not designed for use in life-saving or life-sustaining applications or any application in which the failure of the Vishay product could result in personal injury or death unless specifically qualified in writing by Vishay. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.