

NTC Thermistors, Inrush Current Limiters



DESCRIPTION

The standard surge limiter series comprises devices engineered to protect electrical systems by mitigating the impact of potentially harmful power surges.

FEATURES

- Enhanced protection
- Can withstand up to 12 A of continuous current and 240 J of input energy
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912

RoHS
COMPLIANT

APPLICATIONS


- Residential
- Commercial
- Industrial
- Healthcare
- Renewable energy
- Electric vehicle

QUICK REFERENCE DATA

PART NUMBER	RESISTANCE AT 25 °C (R_{25}) (Ω)	TOLERANCE ON R_{25} VALUE (%)	MAX. STEADY-STATE CURRENT UP TO 65 °C (A)	MAX. RECOMMENDED ENERGY RATING (J)	MAX. VOLTAGE (V_{AC})	MAX. CAPACITANCE AT 120 V_{AC} (μF)
SL180R712	0.7	± 25	12	100	265	6900
SL182R508	2.5	± 20	8	90	265	6251
SL185R006	5	± 20	6	75	265	5209
SL187R005	7	± 20	5	75	265	5209
SL187R010	7	± 20	10	50	265	3473
SL1810005	10	± 20	5	75	265	5209
SL1816004	16	± 20	4	75	265	5209
SL1830006	30	± 25	6	65	265	4500
SL1847003	47	± 25	3	45	265	3100

ELECTRICAL SPECIFICATIONS

PART NUMBER	RESISTANCE AT 100 % MAX. CURRENT (Ω)	RESISTANCE AT 50 % MAX. CURRENT (Ω)	BODY TEMP. AT 100 % MAX. CURRENT (°C)	DISSIPATION FACTOR (mW/°C)	THERMAL TIME CONSTANT (s)	MATERIAL TYPE (FOR BETA AND CURVE)
SL180R712	0.02	0.06	180	25	100	A
SL182R508	0.06	0.14	180	25	100	B
SL185R006	0.01	0.27	180	25	100	C
SL187R005	0.16	0.4	180	25	120	C
SL187R010	0.07	0.13	172	25	120	G
SL1810005	0.21	0.56	180	25	100	G
SL1816004	0.27	0.65	180	25	100	H
SL1830006	0.15	0.31	-	18.0	40	I
SL1847003	0	1.2	180	25	100	M

MECHANICAL SPECIFICATIONS in millimeters


PART NUMBER	B	C	D	L	S	T	LEAD DIAMETER	LEAD STYLE
SL180R712	10.0 nom.	3.85 nom.	19.0 max.	38.0 nom.	7.8 nom.	6.0 max.	1.0 nom.	Straight
SL180R712A					9.9 nom.			Inside kinked
SL180R712B								Outside kinked
SL182R508	10.0 nom.	3.85 nom.	19.0 max.	38.0 nom.	7.8 nom.	6.0 max.	1.0 nom.	Straight
SL182R508A					9.9 nom.			Inside kinked
SL182R508B								Outside kinked
SL185R006	10.0 nom.	3.9 nom.	19.0 max.	38.0 nom.	7.8 nom.	6.0 max.	1.0 nom.	Straight
SL185R006A					9.9 nom.			Inside kinked
SL185R006B								Outside kinked
SL187R005	10.0 nom.	3.85 nom.	19.0 max.	38.0 nom.	7.8 nom.	6.0 max.	1.0 nom.	Straight
SL187R005A					9.9 nom.			Inside kinked
SL187R005B								Outside kinked
SL187R010	10.0 nom.	4.0 nom.	19.0 max.	38.0 nom.	7.8 nom.	6.0 max.	1.0 nom.	Straight
SL187R010A					9.9 nom.			Inside kinked
SL187R010B								Outside kinked
SL1810005	10.0 nom.	3.7 ± 0.5	19.0 max.	38.0 ± 9.0	7.8 nom.	6.0 max.	1.0 ± 0.1	Straight
SL1810005A					9.9 nom.			Inside kinked
SL1810005B								Outside kinked
SL1816004	10.0 nom.	3.85 nom.	19.0 max.	38.0 nom.	7.8 nom.	6.0 max.	1.0 nom.	Straight
SL1816004A					9.9 nom.			Inside kinked
SL1816004B								Outside kinked
SL1830006	10.0 nom.	4.10 nom.	19.0 max.	38.0 ± 5.0	7.8 nom.	6.0 max.	1.0 nom.	Straight
SL1830006A					9.9 nom.			Inside kinked
SL1830006B								Outside kinked
SL1847003	10.0 nom.	5.5 nom.	19.0 max.	38.0 nom.	7.8 nom.	6.0 max.	1.0 nom.	Straight
SL1847003A					9.9 nom.			Inside kinked
SL1847003B								Outside kinked



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Vishay products are not designed for use in life-saving or life-sustaining applications or any application in which the failure of the Vishay product could result in personal injury or death unless specifically qualified in writing by Vishay. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.