


## Axial Vitreous Leaded Wirewound Resistors with CECC Approval, Available with Established Reliability



The FDG, FDK and FDP resistors, with completely welded construction, are the perfect choice for high continuous power dissipation up to 11.5 W. The established reliability and failure rate level E0 and E7 is demonstrated within CECC qualification. The components of this series are well suited for harsh environments and exhibit a long lifetime. With their high pulse power capability, they are the ideal choice for inrush limiters. Typical applications include but are not limited to power supplies, voltage dividers, AC filters, and snubber resistors. Particular requirements can be submitted to a Vishay Draloric application engineer specifying peak voltage, pulse shape, pulse duration, and environmental conditions for review.

### FEATURES

- CECC 40201-801 approval options:
  - Version A, failure rate level E0
  - Version E, with established reliability, failure rate level E7
- High power dissipation in a small design
- Excellent pulse load capability
- Vitreous coating
- Non-flammable and enhanced humidity protection
- Material categorization: for definitions of compliance please see [www.vishay.com/doc?99912](http://www.vishay.com/doc?99912)



**RoHS**  
COMPLIANT  
HALOGEN  
**FREE**

### APPLICATIONS

- Inrush current limiter
- Power supplies
- Snubber resistor
- Filter resistor

TECHNICAL SPECIFICATION						
TYPE	RATED DISSIPATION $P_{25}$	RATED DISSIPATION $P_{70}$	RESISTANCE RANGE <sup>(1)</sup>	RESISTANCE TOLERANCE	OPERATING VOLTAGE $U_{max.}$	TEMPERATURE COEFFICIENT
FDG	3.5 W	3.0 W	0.10 $\Omega$ to 10.0 k $\Omega$	$\pm 5\%$	100 V	+100 ppm/K to +180 ppm/K
			0.10 $\Omega$ to 10.0 k $\Omega$	$\pm 2\%$		
FDK	6.5 W	5.5 W	0.10 $\Omega$ to 39.0 k $\Omega$	$\pm 5\%$	200 V	
			0.10 $\Omega$ to 22.0 k $\Omega$	$\pm 2\%$		
FDP	11.5 W	10 W	0.15 $\Omega$ to 68.0 k $\Omega$	$\pm 5\%$	350 V	
			0.15 $\Omega$ to 33.0 k $\Omega$	$\pm 2\%$		

#### Notes

- The operating temperature range for these resistors is from -55 °C up to 350 °C
- The failure rate level E7 ( $10^{-7}/h$ ,  $\pi Q = 0.1$ ) corresponds to MIL Level R, is superior to level E6 ( $10^{-6}/h$ ,  $\pi Q = 0.3$ ) or level E5 ( $10^{-5}/h$ ,  $\pi Q = 1$ ) and thus may be used as a replacement

<sup>(1)</sup> Resistance values are to be selected for  $\pm 5\%$  from the E12 series, and for  $\pm 2\%$  from the E24 series



PACKAGING							
TYPE	CODE	DESCRIPTION	QUANTITY	PACKAGING STYLE	WIDTH	PITCH	PACKAGING DIMENSIONS
FDG	4C	AC G73	500	Taped acc. IEC 60286-1, fan-folded in a box	73 mm	10 mm	324 mm x 101 mm x 49 mm
	F1	R1 R73	1000	Taped acc. IEC 60286-1, on a reel	73 mm	10 mm	Ø 271 mm x 108 mm
FDK	4B	AB G73	250	Taped acc. IEC 60286-1, fan-folded in a box	73 mm	10 mm	324 mm x 101 mm x 49 mm
	7B	AB G88	250		88 mm	10 mm	324 mm x 111 mm x 75 mm
	FC	RC R73	500	Taped acc. IEC 60286-1, on a reel	73 mm	10 mm	Ø 271 mm x 108 mm
	IC	RC R88	500		88 mm	10 mm	Ø 271 mm x 118 mm
FDP	LA	LA	100	Bulk	-	-	225 mm x 140 mm x 70 mm

**Notes**

- Width is the nominal spacing between tapes, with the nominal tape width on both sides being 6 mm, and pitch is the nominal standard spacing between components; tolerances apply according to IEC 60286-1
- On reels, the flanges are regular octagons with a span of 250 mm, and the arbor hole is Ø 20 mm

PART NUMBER AND PRODUCT DESCRIPTION																	
<b>PART NUMBER: FDPCEE031809JLA000</b>																	
F	D	P	C	E	E	0	3	1	8	0	9	J	L	A	0	0	0
TYPE FDG FDK FDP		VERSION CEE0 = CECC 40201-801, Version A CEE7 = CECC 40201-801, Version E failure rate level E7			VARIANT 3 = +100 ppm/K to +180 ppm/K		RESISTANCE 3 digit value 1 digit multiplier MULTIPLIER 7 = *10 <sup>-3</sup> 8 = *10 <sup>-2</sup> 9 = *10 <sup>-1</sup> 0 = *10 <sup>0</sup> 1 = *10 <sup>1</sup> 2 = *10 <sup>2</sup> 3 = *10 <sup>3</sup>			TOLERANCE G = ± 2 % J = ± 5 %		PACKAGING 4C F1 4B 7B FC IC LA		SPECIAL 000 = standard 3 digit code = customized version			
<b>PRODUCT DESCRIPTION: G206 18R 5 % LA CECC 40201-801S FDP E0</b>																	
G206		18R			5 %		LA			CECC 40201-801S FDP E0							
TYPE G202 = FDG G204 = FDK G206 = FDP		RESISTANCE 1R2 = 1.2 Ω 12K = 12 kΩ			TOLERANCE ± 2 % ± 5 %		PACKAGING AC G.. R1 R.. AB G.. RC R.. LA			VERSION CECC 40201-801S FDP E0 = Version A CECC 40201-801S FDP E7 = Version E failure rate level E7							

**Note**

- The products can be ordered using either the PRODUCT DESCRIPTION or the PART NUMBER



## DESCRIPTION

Vitreous wirewound resistors are best suited for the use in demanding environmental conditions. Their rugged design and durable coatings enable these resistors to withstand extreme environmental stress. The vitreous coating is designed for high stability and a long lifetime in humid environments. The coating is resistant to all cleaning chemicals commonly used in the electronic industry.

Production is strictly controlled and follows an extensive set of instructions established for reproducibility. The winding is done with specific materials on a specially developed fine ceramic body ( $Al_2O_3$ ). The ceramic meets the highest requirements against mechanical resistance, thermal shocks, dielectric strength, and insulation resistance at high temperatures. With different diameters and turn spacings, a large ohmic value range can be offered. The glaze is fired layer by layer, several times, at a high temperature ( $> 600\text{ }^\circ\text{C}$ ). The resistors are marked with resistance and tolerance, and in addition the FDG, FDK and FDP are marked with the failure rate level. Product quality is verified by resistance measurement, performed on 100 % of the individual resistors.

Established reliability products within a package unit are from the same production lot and carry the same date code.

Resistance is measured on the lead wires at a distance of 6 mm from the resistor body. If a greater length of lead wire is used in the application, the user may need to consider the additional wire resistance, particularly with low resistance products.

## MATERIALS

Vishay acknowledges the following systems for the regulation of hazardous substances:

- IEC 62474, Material Declaration for Products of and for the Electrotechnical Industry, with the list of declarable substances given therein <sup>(1)</sup>
- The Global Automotive Declarable Substance List (GADSL) <sup>(2)</sup>
- The REACH regulation (1907/2006/EC) and the related list of substances with very high concern (SVHC) <sup>(3)</sup> for its supply chain

The products do not contain any of the banned substances as per IEC 62474, GADSL, or the SVHC list, see [www.vishay.com/how/leadfree](http://www.vishay.com/how/leadfree). Hence the products fully comply with the following directives:

- 2000/53/EC End-of-Life Vehicle Directive (ELV) and Annex II (ELV II)
- 2011/65/EU Restriction of the Use of Hazardous Substances Directive (RoHS) with amendment 2015/863/EU
- 2012/19/EU Waste Electrical and Electronic Equipment Directive (WEEE)

Vishay pursues the elimination of conflict minerals from its supply chain, see the Conflict Minerals Policy at [www.vishay.com/doc?49037](http://www.vishay.com/doc?49037).

## Notes

- <sup>(1)</sup> The IEC 62474 list of declarable substances is maintained in a dedicated database, which is available at <http://std.iec.ch/iec62474>
- <sup>(2)</sup> The Global Automotive Declarable Substance List (GADSL) is maintained by the American Chemistry Council, and available at [www.gadsl.org](http://www.gadsl.org)
- <sup>(3)</sup> The SVHC list is maintained by the European Chemical Agency (ECHA) and available at <http://echa.europa.eu/candidate-list-table>

## ASSEMBLY

The resistors are axial leaded for soldering. The terminals of the resistors are completely lead (Pb)-free. The special tin plating used, provides compatibility with lead (Pb)-free and lead-containing soldering processes.

Special lead forms may be available on request, please inquire at [ww1resistors@vishay.com](mailto:ww1resistors@vishay.com).

These components are high dissipation power resistors, customers are advised to use a high melting point solder.

## APPLICATION INFORMATION

The power dissipation of the resistor generates a temperature rise with respect to the ambient. The permissible dissipation is derated for temperatures above  $70\text{ }^\circ\text{C}$ , as shown in the derating diagram, in order to avoid overheating of the resistor. The heat dissipated from the resistor may affect adjacent components, hence proper clearance will be required in order to avoid overheating.

The resistive wire is hermetically encapsulated. All materials used are non-flammable and inorganic.

These resistors do not feature a limited lifetime when operated within the permissible limits. However, resistance value drift increasing over operating time may result in exceeding a limit acceptable to the specific application, thereby establishing a functional lifetime.

## RELATED PRODUCTS

For the related G200 product family, without CECC approval, see the datasheet:

- “G200 - Axial Vitreous Leaded Wirewound Resistors”  
[www.vishay.com/doc?21002](http://www.vishay.com/doc?21002)

In lower continuous power applications and less demanding environmental conditions the cement coated alternatives, like the AC series or the Z300 series, might be suitable, see the datasheets:


- “AC Series - Cemented Leaded Wirewound Resistors”  
[www.vishay.com/doc?28730](http://www.vishay.com/doc?28730)
- “Z300 - Industrial Axial Cemented Leaded Wirewound Resistors”  
[www.vishay.com/doc?21007](http://www.vishay.com/doc?21007)

For precision applications, there is the cement coated PAC series, see the datasheet:




- “PAC Series - Cemented Leaded Wirewound Precision Resistors”  
[www.vishay.com/doc?28731](http://www.vishay.com/doc?28731)



**DERATING** according to CECC 40201-801



**TEMPERATURE RISE**





The requirements stated in the Test Procedures And Requirements table are based on the required and permitted limits of CECC 40201-801. However, a number of improvements against those minimum requirements have been included. The testing temperatures LCT = -55 °C and UCT = 200 °C are established with the climatic category -55 / 200 / 56 as defined in CECC 40201-801.

TEST PROCEDURES AND REQUIREMENTS					
EN 60115-1 CLAUSE	IEC 60068-2 TEST METHOD (1)	TEST	PROCEDURE		REQUIREMENTS PERMISSIBLE CHANGE ( $\Delta R$ ) STABILITY CLASS 5 OR BETTER
4.5	-	Resistance	-		$\pm 2\%$ ; $\pm 5\%$
4.7	-	Voltage proof	<b>V-block-method; <math>U_{RMS} = U_{ins}</math>; 60 s</b>		No flashover or breakdown
			Type	$U_{ins}$	
			FDG	300 V	
			FDK	400 V	
			FDP	500 V	
4.8	-	Temperature coefficient	At (20 / -55 / 20) °C and (20 / 200 / 20) °C		+100 ppm/K to +180 ppm/K
4.13	-	Short time overload	Overload voltage = $\sqrt{10}$ x rated voltage		$\pm (0.5\% R + 0.05 \Omega)$ no visible damage
			Type	Duration	
			FDG	5 s	
			FDK	6 s	
			FDP	10 s	
4.16	21 (Ua1) 21 (Ub) 21 (Uc)	Robustness of terminations	Tensile, bending and torsion		$\pm (0.25\% R + 0.05 \Omega)$ no visible damage
4.17	20 (Ta)	Solderability	Solder bath method; SnPb40; non-activated flux (235 $\pm$ 5) °C; (2 $\pm$ 0.2) s		Good tinning ( $\geq 95\%$ covered) no visible damage
			Solder bath method; SnAg3Cu0.5; non-activated flux; (245 $\pm$ 5) °C; (3 $\pm$ 0.3) s		
4.18	20 (Tb, Method 1A)	Resistance to soldering heat	Unmounted components; (260 $\pm$ 3) °C; (10 $\pm$ 1) s		$\pm (0.25\% R + 0.05 \Omega)$ no visible damage
4.19	14 (Na)	Rapid change of temperature	30 min at LCT = -55 °C 30 min at UCT = 200 °C 5 cycles		$\pm (0.25\% R + 0.05 \Omega)$ no visible damage
4.21	27 (Ea)	Shock	Acceleration: 981 m/s <sup>2</sup> Pulse duration: 11 ms Wave form: half sine 3 successive shocks to be applied in each perpendicular direction		$\pm (0.25\% R + 0.05 \Omega)$ no visible damage
4.22	6 (Fc)	Vibration	Endurance by sweeping; 10 Hz to 2000 Hz; no resonance; amplitude $\leq 1.5$ mm or $\leq 200$ m/s <sup>2</sup> ; 6 h		$\pm (0.25\% R + 0.05 \Omega)$ no visible damage

TEST PROCEDURES AND REQUIREMENTS				
EN 60115-1 CLAUSE	IEC 60068-2 TEST METHOD <sup>(1)</sup>	TEST	PROCEDURE	REQUIREMENTS PERMISSIBLE CHANGE ( $\Delta R$ ) STABILITY CLASS 5 OR BETTER
4.23				
4.23.2	2 (Bb)	Climatic sequence	Dry heat 200 °C; 16 h	$\pm (0.5 \% R + 0.05 \Omega)$
4.23.3	30 (Db)		Damp heat, cyclic 55 °C; 24 h; 90 % to 100 % RH; 1 cycle	
4.23.4	1 (Ab)		Cold -55 °C; 2 h	
4.23.5	13 (M)		Low air pressure; 1.0 kPa; 2 h; 15 °C to 35 °C	
4.23.6	30 (Db)		Damp heat, cyclic 55 °C; 24 h; 95 % to 100 % RH; 5 cycles	
4.25.2	-	Endurance at room temperature	$P_{\text{test}} = 1.16 \times P_{70}$ $U_{\text{test}} = \sqrt{1.16 \times P_{70} \times R} \leq U_{\text{max.}}$ $t_{\text{on}} = 1.5 \text{ h}; t_{\text{off}} = 0.5 \text{ h}$ 25 °C; 1000 h 25 °C; 8000 h	$\pm (3.0 \% R + 0.05 \Omega)$ $\pm (6.0 \% R + 0.05 \Omega)$
4.25.3	-	Endurance at upper category temperature	$P_{\text{test}} = P_{\text{cat}} = 0.54 \times P_{70}$ $U_{\text{test}} = \sqrt{0.54 \times P_{70} \times R} \leq U_{\text{max.}}$ 200 °C; 1000 h	$\pm (3.0 \% R + 0.05 \Omega)$
4.24	78 (Cab)	Damp heat, steady state	(40 ± 2) °C; 56 days; (93 ± 3) % RH	$\pm (0.5 \% R + 0.05 \Omega)$

**Note**

<sup>(1)</sup> The quoted IEC standards are also released as EN standards with the same number and identical contents

DIMENSION AND MASS							
TYPE	$L_{\text{max.}}$ (mm)	$D_{\text{max.}}^{(1)}$ (mm)	d (mm)	B (mm)	A (mm)	$S_{\text{min.}}^{(2)}$ (mm)	MASS (g)
FDG	13.0	6.0	0.8	73.0 ± 1.0	83.0 ± 0.3	17.5	1.0
FDK	20.0	8.0	0.8	73.0 ± 1.0	83.0 ± 0.3	25.0	2.2
				88.0 ± 1.0	98.0 ± 0.3		
FDP	32.5	10.5	0.8	-	107.0 ± 2.0	40.0	6.5

**Notes**

<sup>(1)</sup> The body diameter is 0.5 mm larger for resistance values  $\leq 10 \Omega$

<sup>(2)</sup> Minimum pitch



## **Disclaimer**

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Vishay products are not designed for use in life-saving or life-sustaining applications or any application in which the failure of the Vishay product could result in personal injury or death unless specifically qualified in writing by Vishay. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.