

RF Power Feed-Through Capacitors with Mounting Tags, Class 1 Ceramic



FEATURES

- Small size
- Geometry minimizes inductance
- Wide range of capacitance values

APPLICATIONS

Filtering purposes in industrial and medical RF power equipment, where high voltages and high feed-through currents are required.

CAPACITANCE RANGE

400 pF to 1.5 nF

CAPACITANCE TOLERANCE

± 20 %; ± 10 %; ± 5 %

CERAMIC DIELECTRICS

R85 (TCC -750 ppm/K)

RATED VOLTAGE

7.0 kV_p

DIELECTRIC STRENGTH TEST

200 % of rated AC voltage (50 Hz, 5 minutes)

DISSIPATION FACTOR

Max. 0.05 %

Measuring frequencies:

1 MHz (< 1 nF); 300 kHz or 100 kHz (≥ 1 nF)

INSULATION RESISTANCE

Min. 100 000 MΩ (at 25 °C)

OPERATING TEMPERATURE RANGE

-55 °C to +100 °C

QUICK REFERENCE DATA

DESCRIPTION	VALUE		
Ceramic Class	1		
Ceramic Dielectric	R85		
Type	DF 030070	DF 030090	DF 030110
Voltage (V _p)	7000		
Min. Capacitance (pF)	400	700	800
Max. Capacitance (pF)	800	1200	1500
Mounting	Screw terminal		

MATERIAL

Capacitor elements made from class 1 ceramic dielectric with noble metal electrodes.

Connection terminals:

made from copper / brass, silver plated

For higher feed-through current, an additional feed-through conductor must be provided.

FINISH

Capacitor body completely protective lacquered.

The contoured insulating rims are additionally glazed.

MARKING


Type designator, capacitance value and tolerance, rated peak voltage, ceramic material code, production date code, manufacturer logo



SAP PART NUMBER AND ELECTRICAL DATA						
PART NUMBER	CERAMIC	CAP. VALUES (pF)	RATED VOLTAGE (kV _P)	RATED POWER ⁽¹⁾ (kvar)	RATED CURRENT (A _{RMS})	FEED-THROUGH CURRENT ⁽²⁾ (A)
TYPE DF 030070						
DF030070VY401##BJ1	R85	400	7	16	8	8
DF030070VY501##BJ1		500				
DF030070VY601##BJ1		600				
DF030070VY801##BJ1		800				
TYPE DF 030090						
DF030090VY701##BJ1	R85	700	7	20	8	8
DF030090VY102##BJ1		1000				
DF030090VY122##BJ1		1200				
TYPE DF 030110						
DF030110VY801##BJ1	R85	800	7	25	8	8
DF030110VY122##BJ1		1200				
DF030110VY152##BJ1		1500				

Notes

- ## 14th to 15th digit: Capacitance tolerance code ± 20 % = 38, ± 10 % = 36, ± 5 % = 33
- ⁽¹⁾ The surface temperature during operation must not exceed +100 °C
- ⁽²⁾ DC or low frequency RMS current (< 20 kHz)




MOUNTING GUIDELINES

- The connection to one electrode must be flexible in order to prevent the generation of physical force which could damage the capacitor elements. Such forces are often generated by the dimensional differences resulting from the normal physical tolerances of these components.
- The capacitor elements must not be used as a mechanical support for other devices or components.




DERATING DIAGRAMS


DF0130070VY401##BJ1




DF030070VY501##BJ1




DF0130070VY601##BJ1




DF0130070VY801##BJ1




DF030090VY701##BJ1




DF030090VY102##BJ1



DF030090VY122##BJ1




DF030110VY801##BJ1






DERATING DIAGRAMS

DF030110VY122##BJ1



DF030110VY152##BJ1



RELATED DOCUMENTS

General Information

www.vishay.com/doc?22071



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.