



## Custom Capabilities Watercooled RF Power Pot Capacitors



### OVERALL CAPABILITIES

- Production in Germany
- High quality, service, and flexibility
- ISO 9001, OHSAS 18001, environmental 14001 qualified
- STEP files available
- Operating temperature range -55 °C to +100 °C

### MATERIAL / PROCESS CAPABILITIES

- Wide range of capacitance values
- Numerous shapes and sizes available
- Fittings specifically designed for your application
- Selection of internal and external cooling
- Lead (Pb)-free available

### DIFFERENCE TWX AND TWXF



The TWX model is made with a contoured, glazed insulation rim designed for use in a relative clean, dry environment.


The TWXF types feature an umbrella shaped coating rim made from silicone elastomer to minimize the adverse effects of moisture, dust, and other impurities in the working environment, and to improve the characteristics of the electrical field.

CONTACT INFORMATION
For design assistance, contact: <a href="mailto:powcap@vishay.com">powcap@vishay.com</a>
Design request form: <a href="http://www.vishay.com/capacitors/ceramic/rf-watercooled/">www.vishay.com/capacitors/ceramic/rf-watercooled/</a>




ADDITIONAL CAPABILITIES EXAMPLES	
TOSW 118115 <a href="http://www.vishay.com/doc?22087">www.vishay.com/doc?22087</a>	TWIF 085175, TWIF 085215, TWIF 085260 <a href="http://www.vishay.com/doc?22166">www.vishay.com/doc?22166</a>
TWXFZ 106266 <a href="http://www.vishay.com/doc?22147">www.vishay.com/doc?22147</a>	TWXFZ 140266, TWXFZ 140316, TWXFZ 140376 <a href="http://www.vishay.com/doc?22132">www.vishay.com/doc?22132</a>

### EXTERNAL WATERCOOLED



### INTERNAL WATERCOOLED



ADDITIONAL CUSTOM EXAMPLES	
TDFZ 170	TWXF 135285

With many years of experience in the development, we can find the best solution for your project together!



## **Disclaimer**

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.