


# High Voltage Ceramic DC Disc Capacitors with Axial Leads, 10 kV<sub>DC</sub> to 30 kV<sub>DC</sub>



## FEATURES

- Class 1 and class 2 ceramic
- High insulation resistance
- Epoxy encapsulated
- Wide capacitance range
- Ceramic singlelayer capacitor
- Material categorization: for definitions of compliance please see [www.vishay.com/doc?99912](http://www.vishay.com/doc?99912)

**RoHS**  
COMPLIANT

## LINKS TO ADDITIONAL RESOURCES



QUICK REFERENCE DATA												
DESCRIPTION	VALUE											
Ceramic class	1				2				2			
Ceramic dielectric	N4700 (T3M)				X7R				Z5U			
Voltage (V <sub>DC</sub> )	10 000	15 000	20 000	30 000	10 000	15 000	20 000	30 000	10 000	15 000	20 000	30 000
Min. capacitance (pF)	470	390	220	180	180	100	100	100	1500	1000	680	470
Max. capacitance (pF)	2000	1500	1000	680	4700	3900	2700	2000	10 000	6800	5000	3300
Mounting	Axial											

## MARKING

Capacitance value and tolerance, rated DC voltage, T/C code, production date code, CM mark.

## MATERIAL

Capacitor elements made from class 1 or class 2 ceramic in a molded case, high temperature epoxy construction.  
Leads: tinned copper clad steel.

## DIELECTRIC STRENGTH


150 % of rated voltage (in dielectric fluid), charging current limited to 50 mA.

## DISSIPATION FACTOR $\tan \delta$

N4700 (T3M):  $\leq 2 \times 10^{-3}$  (1 kHz)

X7R, Z5U:  $\leq 20 \times 10^{-3}$  (1 kHz)

## DIMENSIONS in millimeters (inches)



## INSULATION RESISTANCE

Min. 200 000 M $\Omega$ , at 180 V<sub>DC</sub> or 1000  $\Omega$ F

## OPERATING TEMPERATURE RANGE

-30 °C to +85 °C

## RATED VOLTAGE <sup>(1)</sup>

- 660R10A### 10 kV<sub>DC</sub> (3.5 kV<sub>RMS</sub>)
- 660R15A### 15 kV<sub>DC</sub> (5.6 kV<sub>RMS</sub>)
- 660R20A### 20 kV<sub>DC</sub> (7.0 kV<sub>RMS</sub>)
- 660R30A### 30 kV<sub>DC</sub> (10.6 kV<sub>RMS</sub>)

### Note

<sup>(1)</sup> All kV<sub>RMS</sub> values up to 60 Hz



ORDERING INFORMATION				
660R30ACT47	30 kV <sub>DC</sub>	470 pF	± 20 %	X7R
MODEL	RATED VOLTAGE	CAPACITANCE VALUE	TOLERANCE	CERAMIC

SAP NUMBER AND ELECTRICAL DATA									
MODEL NUMBER	CERAMIC	CAP. VALUE (pF)	TOLERANCE (%)	RATED VOLTAGE (kV <sub>DC</sub> )	RATED VOLTAGE (kV <sub>RMS</sub> )	D MAX. (mm)	D MAX. (INCHES)	H MAX. (mm)	H MAX. (INCHES)
<b>660R10AZ###</b>									
660R10AZT47	N4700 (T3M)	470	± 20	10	3.5	21	0.83	13	0.50
660R10AZD10		1000				30	1.18		
660R10AZD20		2000				37	1.45		
<b>660R10AC###</b>									
660R10ACT18	X7R	180	± 20	10	3.5	21	0.83	13	0.50
660R10ACT22		220							
660R10ACT33		330							
660R10ACT47		470							
660R10ACT68		680							
660R10ACD10		1000				30	1.18	15	0.60
660R10ACD15		1500							
660R10ACD22		2200							
660R10ACD33		3300				37	1.45	13	0.50
660R10ACD47		4700							
<b>660R10AE###</b>									
660R10AED15	Z5U	1500	+ 80 / - 20	10	3.5	21	0.83	13	0.50
660R10AED22		2200							
660R10AED33		3300							
660R10AED47		4700				37	1.45	11	0.45
660R10AED68		6800							
660R10AES10		10 000							
<b>660R15AZ###</b>									
660R15AZT39	N4700 (T3M)	390	± 20	15	5.3	21	0.83	13	0.50
660R15AZT82		820				30	1.18		
660R15AZD15		1500				37	1.45		
<b>660R15AC###</b>									
660R15ACT10	X7R	100	± 20	15	5.3	21	0.83	13	0.50
660R15ACT22		220							
660R15ACT33		330							
660R15ACT47		470							
660R15ACT68		680						30	1.18
660R15ACD10		1000							
660R15ACD15		1500							
660R15ACD22		2200				37	1.45	17	0.65
660R15ACD33		3300							
660R15ACD39		3900							




SAP NUMBER AND ELECTRICAL DATA									
MODEL NUMBER	CERAMIC	CAP. VALUE (pF)	TOLERANCE (%)	RATED VOLTAGE (kV <sub>DC</sub> )	RATED VOLTAGE (kV <sub>RMS</sub> )	D MAX. (mm)	D MAX. (INCHES)	H MAX. (mm)	H MAX. (INCHES)
<b>660R15AE###</b>									
660R15AED10	Z5U	1000	+ 80 / - 20	15	5.3	21	0.83	13	0.50
660R15AED15		1500							
660R15AED22		2200							
660R15AED33		3300							
660R15AED47		4700							
660R15AED68		6800				37	1.45		
<b>660R20AZ###</b>									
660R20AZT22	N4700 (T3M)	220	± 20	20	7	21	0.83	15	0.60
660R20AZT68		680				30	1.18		
660R20AZD10		1000				37	1.45		
<b>660R20AC###</b>									
660R20ACT10	X7R	100	± 20	20	7	21	0.83	15	0.60
660R20ACT22		220							
660R20ACT33		330							
660R20ACT47		470						17	0.65
660R20ACT68		680							
660R20ACD10		1000				30	1.18	15	0.60
660R20ACD15		1500							
660R20ACD22		2200				37	1.45	19	0.70
660R20ACD25		2500							
660R20ACD27		2700						19	0.75
<b>660R20AE###</b>									
660R20AET68	Z5U	680	+ 80 / - 20	20	7	21	0.83	15	0.60
660R20AED10		1000						17	0.66
660R20AED15		1500							
660R20AED22		2200				30	1.18	15	0.60
660R20AED33		3300							
660R20AED47		4700							
660R20AED50		5000				37	1.45	19	0.75
								14	0.55
<b>660R30AZ###</b>									
660R30AZT18	N4700 (T3M)	180	± 20	30	10.6	21	0.83	20	0.80
660R30AZT47		470				30	1.18		
660R30AZT68		680				37	1.45		
<b>660R30AC###</b>									
660R30ACT10	X7R	100	± 20	30	10.6	21	0.83	20	0.80
660R30ACT22		220							
660R30ACT33		330							
660R30ACT47		470						19	0.75
660R30ACT68		680							
660R30ACD10		1000				30	1.18	20	0.80
660R30ACD15		1500							
660R30ACD20		2000				37	1.45		



SAP NUMBER AND ELECTRICAL DATA									
MODEL NUMBER	CERAMIC	CAP. VALUE (pF)	TOLERANCE (%)	RATED VOLTAGE (kV <sub>DC</sub> )	RATED VOLTAGE (kV <sub>RMS</sub> )	D MAX. (mm)	D MAX. (INCHES)	H MAX. (mm)	H MAX. (INCHES)
<b>660R30AE###</b>									
660R30AET47	Z5U	470	+ 80 / - 20	30	10.6	21	0.83	20	0.80
660R30AET68		680						19	0.75
660R30AET82		820						20	0.80
660R30AED10		1000				30	1.18	19	0.75
660R30AED12		1200							
660R30AED15		1500							
660R30AED18		1800							
660R30AED20		2000				37	1.45	19	0.75
660R30AED22		2200							
660R30AED25		2500							
660R30AED30		3000							
660R30AED33		3300							

**CAPACITANCE CHANGE VS. VOLTAGE** (typical)



RELATED DOCUMENTS	
General Information	<a href="http://www.vishay.com/doc?23140">www.vishay.com/doc?23140</a>



## Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.