



	<p>Ref. Certif. No.</p> <p><b>DE1-63499</b></p>
<p>IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME</p>	
<p><b>CB TEST CERTIFICATE</b></p>	
<p><b>Product</b></p> <p><b>Name and address of the applicant</b></p> <p><b>Name and address of the manufacturer</b></p> <p><b>Name and address of the factory</b></p> <p><i>Note: When more than one factory, please report on page 2</i></p> <p><b>Ratings and principal characteristics</b></p> <p><b>Trademark (if any)</b></p> <p><b>Customer's Testing Facility (CTF) Stage used</b></p> <p><b>Model / Type Ref.</b></p> <p><b>Additional information (if necessary may also be reported on page 2)</b></p> <p><b>A sample of the product was tested and found to be in conformity with</b></p> <p><b>As shown in the Test Report Ref. No. which forms part of this Certificate</b></p>	<p>Fixed capacitor for electromagnetic interference suppression and connection to the supply mains</p> <p>VISHAY Electronic GmbH Dr.-Felix-Zandman-Platz 1, 95100 Selb GERMANY</p> <p>VISHAY Electronic GmbH Dr.-Felix-Zandman-Platz 1, 95100 Selb GERMANY</p> <p>VISHAY Electronic Spol. s.r.o. zavod Sokolov Geschäftsbereich Draloric zavod Sokolov, Geschäftsbereich Draloric, Bergmannova 392, 356 04 DOLNI RYCHNOV CZECH REPUBLIC</p> <p><input type="checkbox"/> Additional Information on page 2</p> <p>10 pF to 15nF; X1/Y2; ±10% (K) or ±20% (M); X1: AC 400 V; Y2: AC 250/300 V; 10/085/21/C, 25/085/21/C, 25/125/21/C; Ceramic: C0G-R3L; X7R-Y5U ; Y5U</p> <p><b>CM</b></p> <p>30LV</p> <p><input type="checkbox"/> Additional Information on page 2</p> <p>IEC 60384-14:2013 IEC 60384-14:2013/AMD1:2016</p> <p>268097-TL3-1 to 268097-TL3-3</p>
<p>This CB Test Certificate is issued by the National Certification Body</p>	
<p><b>VDE Prüf- und Zertifizierungsinstitut GmbH</b> <b>VDE Testing and Certification Institute</b> Zertifizierungsstelle und internat. Angelegenheiten Certification Body and internat. Affairs</p> <p>Date: 2020-04-28</p> <p>Signature:  R. Nickel</p>	