

PTC Thermistors Motor Start Pellets


RoHS
COMPLIANT

FEATURES

- Rugged silver electrodes well suited for long life OEM pressure contact mounting
- Various pellet sizes for optimum inrush current and switching time
- Withstanding voltage is 2 times the maximum voltage rating
- UL approved pellets
- Material categorization: For definitions of compliance please see www.vishay.com/doc?99912

APPLICATIONS

- Single Phase motorstart assist in
- Refrigerator systems
- Airconditioning systems
- Heat-pumps
- Small compressors
- Inrush current generation

DESCRIPTION

These directly heated thermistors have a positive temperature coefficient and are primarily intended for inrush current generation. They consist of a high grade ceramic disk with two rugged pattern silver electrodes for contact pressure mounting. These ceramic pellets can be build into proprietary motor start devices for compressor, refrigerator and HVAC OEMs.

MOUNTING

The PTC thermistor pellets are suitable for pressure contact mounting in application specific housing assemblies. Examples of such assemblies can be found in the PTC305C series. Assembly housing must be appropriate for usage up to 180 °C surface temperature of the PTC pellets.

The pellets are not solderable.

MARKING

The pellets are not marked. Marking is available on request for customized parts.

SAFETY AGENCY RECOGNITION


Vishay Cera-Mite motor start PTC pellet thermistors are recognized by Underwriter Laboratories file E148885 in accordance with Standard for Thermistor Type Devices UL 1434; and Canadian Standards C22.2 No. 0-1991.

QUICK REFERENCE DATA		
PARAMETER	VALUE	UNIT
Resistance value at 25 °C	3.3 to 75	Ω
Tolerance on resistance value	± 30	%
Current ratings	4 to 16	A _{RMS}
Switching times (typical)	0.25 to 1.0	s
Maximum voltage rating	160 to 450	V _{RMS}
Operating temperature range	-10 to +85	°C
Storage temperature range	-25 to +105	°C

ELECTRICAL DATA AND ORDERING INFORMATION									
PART NUMBER	$R_{25}^{(1)}$ ± 30 % (Ω)	$R_{DYN}^{(2)}$ (Ω)	$V_{meas.}$ R_{DYN} (V_{RMS})	MAX. VOLTAGE ⁽³⁾ (V_{RMS})	MAX. CURRENT (A_{RMS})	SIZE Ø x T (mm)	UL ⁽⁴⁾	T_{SWITCH} (°C)	
PTC307C1674P	5.0	4.0	120	200	10	16 + 0.2/- 0.4 x 2.5 ± 0.25	Y	105	
PTC307C1700P	6.8	5.0	120	200	10		Y	105	
PTC307C1711P	10	7.2	120	200	10		Y	105	
PTC307C1668P	5.0	4.0	120	180	12	17.5 ± 0.3 x 2.5 ± 0.25	Y	120	
PTC307C1644P	6.8	5.0	120	200	10		Y	120	
PTC307C1651P	10	7.2	120	200	10		Y	120	
PTC307C1720P	20	13	120	320	8	20 + 0.2/- 0.8 x 2.5 ± 0.25	Y	120	
PTC307C1411P	3.3	2.6	120	160	12		Y	120	
PTC307C1484P	4.7	3.5	120	180	12		Y	120	
PTC307C1544P	5.6	4.1	120	180	12		Y	120	
PTC307C1399P	6.8	5.0	120	200	10		Y	120	
PTC307C1489P	10	7.2	120	230	9		Y	120	
PTC307C1476P	12	8.5	120	250	8.5		Y	120	
PTC307C1530P	15	10.5	120	300	8		Y	120	
PTC307C1531P	22	15	120	400	8		Y	120	
PTC307C1282P	33	22	120	355	6		Y	120	
PTC307C1533P	47	30	120	400	5		Y	120	
PTC307C1292P	68	42	120	430	4		Y	120	
PTC307C1487P	3.9	3.0	50	175	16		20 + 0.2/- 0.8 x 3.2 ± 0.25	Y	120
PTC307C1529P	12	10.3	100	350	8			Y	120
PTC307C1545P	14	12	100	320	8			Y	120
PTC307C1640P	30	15.9	240	380	12	Y		120	
PTC307C1740P	30	15.9	240	450	7	Y		120	
PTC307C1024P	38	25	240	400	9	20 + 0.2/- 0.8 x 5.0 ± 0.25	Y	120	
PTC307C1409P	50	35	240	400	7.5		Y	120	
PTC307C1410P	75	50	240	400	5.5		Y	120	

Notes

- R_{25} = zero power resistance measured at < 0.5 V_{DC} , standard tolerance ± 30 %, other tolerances and values on request
- R_{DYN} = nominal dynamic resistance during inrush, measured with $V_{meas.}$ applied, for information only
- The maximum voltage is the voltage that appears across the PTC in a motor start application. This is not the applied line voltage. Withstanding voltage of all UL approved types is minimum twice the specified maximum operating voltage.
- UL recognition following XGPU2 category of standard UL1434, file E148885

TYPICAL PTC CURRENT VS. TIME SHOWING DEFINITION OF R_{DYN} AND SWITCH TIME (t)




Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.