


Aluminum Capacitors Axial Capacitor Style



Component outlines

FEATURES

- Polarized aluminum electrolytic capacitors
- High CU product
- Miniature size
- Charge/discharge proof
- High ripple current capability
- Compliant to RoHS directive 2002/95/EC



RoHS
COMPLIANT

APPLICATIONS

- General purpose, industrial electronics, audio/video systems
- Coupling, smoothing, filtering, buffering and timing
- Portable and mobile units
- Vibration and shock resistant


QUICK REFERENCE DATA

DESCRIPTION	UNIT	LOW VOLTAGE	
Nominal case size (Ø D x L)	mm	4.5 x 10	6 x 10 to 10 x 25
Rated capacitance range C _R	µF	1.0 to 2200	
Capacitance tolerance	%	± 20	
Rated voltage range	V	6.3 to 100	
Category temperature range	°C	- 40 to + 85	
Endurance test at upper category temp.	h	1000	
Useful life at 105 °C and I _R applied	h	500	750
Useful life at 85 °C and I _R applied	h	2500	
Useful life at 40 °C and I _R applied	h	70 000	
Shelf life at (0 V, upper category temperature)	h	500	
Failure rate (0.8 U _R , 40 °C)	10 ⁻⁹ /h	≤ 130	
Based on sectional specification		IEC 60384-4/EN 130300	
Based on detailed specifications		similar to CECC 30301-044, similar to DIN 45910 Part 126, without quality assessment	
Climatic category IEC 68068		40/085/56 GPF	

SELECTION CHART FOR C_R, U_R > 100 V AND RELEVANT NOMINAL CASE SIZES (Ø D x L in mm)

C _R (µF)	U _R (V)							
	6.3	10	16	25	40	50	63	100
1.0	→	→	→	→	→	→	→	4.5 x 11
2.2	→	→	→	→	→	→	→	4.5 x 11
4.7	→	→	→	→	→	→	→	4.5 x 11
10	→	ELM	→	→	→	→	4.5 x 11	6 x 10
22	→	→	→	→	4.5 x 11	→	6 x 10	6.5 x 18
33	→	→	→	4.5 x 11	-	-	-	-
47	→	→	→	4.5 x 11	6 x 10	→	6.5 x 18	8 x 18
100	→	4.5 x 11	→	6 x 10	6.5 x 18	→	8 x 18	10 x 25
220	→	6 x 10	→	6.5 x 18	10 x 18	EBM	10 x 25	-
470	→	6.5 x 18	8 x 18	10 x 18	10 x 25	-	-	-
680	→	8 x 18	10 x 18	10 x 25	-	-	-	-
1000	8 x 18	10 x 18	10 x 25	-	-	-	-	-
1500	10 x 18	10 x 25	-	-	-	-	-	-
2200	10 x 25	-	-	-	-	-	-	-

DIMENSIONS in millimeters **AND AVAILABLE FORMS**



AXIAL STYLE: DIMENSIONS in millimeters, **MASS, PACKAGING QUANTITIES AND ORDERING CODE**

NOMINAL CASE SIZE $\varnothing D \times L$	$\varnothing d$	$\varnothing D_{max.}$	$L_{max.}$	$A_{min.}$	B	MASS APPROX. g	PACKAGING, ENDING OF ORDERING CODE, QUANTITIES			
							TAPED ON REEL		TAPED AMMO	
							CODE	PCS.	CODE	PCS.
4.5 x 11	0.6	5	11.0	15	63.5 ± 1.5	0.5	..A0W	3000	..B0W	1000
6 x 10	0.6	6.3	10.5	15	63.5 ± 1.5	0.7	..A0W	1000	..B0W	1000
6.5 x 18	0.8	6.9	18.5	25	73.0 ± 1.6	1.3	..A0W	1000	..B0W	1000
8 x 18	0.8	8.5	18.5	25	73.0 ± 1.6	1.7	..A0W	500	..B0W	500
10 x 18	0.8	10.5	18.5	25	73.0 ± 1.6	2.5	..A0W	500	..B0W	500
10 x 25	0.8	10.5	25.0	30	73.0 ± 1.6	3.3	..A0W	500	..B0W	500

Axial style capacitors are insulated.

ELECTRICAL DATA

SYMBOL	DESCRIPTION
U_R	rated voltage
C_R	rated capacitance at 100 Hz
$\tan \delta$	max. dissipation factor at 100 Hz
R_{ESR}	equivalent series resistance at 100 Hz, (calculated from $\tan \delta_{max.}$ and C_R)
Z	max. impedance at 10 kHz
I_R	rated alternating current (rms) at 100 Hz and upper category temperature
T_a	ambient temperature
T_{uc}	upper category temperature
RH	relative humidity
P	ambient pressure

Note

Unless otherwise specified, all electrical values apply at $T_a = 20\text{ }^\circ\text{C}$, $P = 80\text{ kPa}$ to 106 kPa , $RH = 45\%$ to 75% .

ORDERING EXAMPLE

The following table gives the ordering number.

The 16th place of ordering code refers to packaging for axial lead capacitors:

MALAEBM00GD422B...	EBM 2200 μF 6.3 V 10 x 25
MALAEBM00GD422BA0W	A = taped on reel
MALAEBM00GD422BB0W	B = taped ammo

Please see table "Axial Styles" for available versions.



ELECTRICAL DATA AND ORDERING INFORMATION							
U_R (V)	C_R 100 Hz (μ F)	NOMINAL CASE SIZE \varnothing D x L (mm)	$\tan \delta$ 100 Hz MAX.	R_{ESR} 100 Hz (Ω)	Z 10 kHz MAX. (Ω)	I_R 100 Hz T_{uc} (A)	CATALOG NUMBER MALA...
6.3	1000	8 x 18	0.25	0.400	0.500	0.44	EBM00FL410BB0W
	1500	10 x 18	0.25	0.270	0.320	0.56	EBM00GL415BB0W
	2200	10 x 25	0.29	0.210	0.160	0.71	EBM00GD422BB0W
10	100	4.5 x 11	0.20	3.200	2.000	0.10	ELM00BA310CB0W
	220	6 x 10	0.20	1.500	0.910	0.16	EBM00CK322CB0W
	470	6.5 x 18	0.20	0.680	0.430	0.31	EBM00DL347CB0W
	680	8 x 18	0.20	0.470	0.290	0.40	EBM00FL368CB0W
	1000	10 x 18	0.20	0.320	0.200	0.55	EBM00GL410CB0W
	1500	10 x 25	0.23	0.250	0.180	0.69	EBM00GD415CB0W
16	470	8 x 18	0.16	0.550	0.340	0.38	EBM00FL347DB0W
	680	10 x 18	0.16	0.380	0.240	0.50	EBM00GL368DB0W
	1000	10 x 25	0.16	0.260	0.180	0.66	EBM00GD410DB0W
25	33	4.5 x 11	0.14	6.700	3.500	0.07	ELM00BA233EB0W
	47	4.5 x 11	0.14	4.800	2.600	0.08	ELM00BA247EB0W
	100	6 x 10	0.14	2.300	1.200	0.15	EBM00CK310EB0W
	220	6.5 x 18	0.14	1.000	0.550	0.25	EBM00DL322EB0W
	470	10 x 18	0.14	0.480	0.260	0.45	EBM00GL347EB0W
	680	10 x 25	0.14	0.330	0.180	0.56	EBM00GD368EB0W
40	22	4.5 x 11	0.11	8.000	3.200	0.06	ELM00BA222GB0W
	47	6 x 10	0.11	3.800	1.500	0.11	EBM00CK247GB0W
	100	6.5 x 18	0.11	1.800	0.700	0.19	EBM00DL310GB0W
	220	10 x 18	0.11	0.800	0.320	0.33	EBM00GL322GB0W
	470	10 x 25	0.11	0.370	0.160	0.52	EBM00GD347GB0W
63	10	4.5 x 11	0.08	13.000	5.500	0.05	ELM00BA210JB0W
	22	6 x 10	0.08	5.800	2.500	0.09	EBM00CK222JB0W
	47	6.5 x 18	0.08	2.700	1.200	0.15	EBM00DL247JB0W
	100	8 x 18	0.08	1.300	0.550	0.25	EBM00FL310JB0W
	220	10 x 25	0.08	0.600	0.250	0.43	EBM00GD322JB0W
100	1.0	4.5 x 11	0.08	130.000	90.000	0.01	ELM00BA110LB0W
	2.2	4.5 x 11	0.08	58.000	41.000	0.02	ELM00BA122LB0W
	4.7	4.5 x 11	0.08	27.000	19.000	0.03	ELM00BA147LB0W
	10	6 x 10	0.08	13.000	9.000	0.07	EBM00CK210LB0W
	22	6.5 x 18	0.08	5.800	4.100	0.10	EBM00DL222LB0W
	47	8 x 18	0.08	2.700	1.900	0.16	EBM00FL247LB0W
	100	10 x 25	0.08	1.300	0.900	0.30	EBM00GD310LB0W

ADDITIONAL ELECTRICAL DATA		
PARAMETER	CONDITIONS	VALUE
Voltage		
Surge voltage	$U_R \leq 100$ V	$U_s = 1.15 \times U_R$
Reverse voltage	-	$U_{rev} \leq 1$ V
Current		
Leakage current	$U_R \leq 100$ V $U_R, 300$ s	$I_L/\mu A \leq 0.002 \times C_R/\mu F \times U_R/V + 3$

LOW TEMPERATURE BEHAVIOUR

Table for the calculation of the maximum 10 kHz impedance at low temperatures:

$$Z(10\text{ kHz}) [\Omega] = \frac{\text{Tabular value}}{C_R [\mu\text{F}]}$$

T _a (°C)	RATED VOLTAGE (V)							
	6.3	10	16	25	40	50	63	100
- 25	2100	1600	1250	680	390	375	240	200
- 40	7600	5700	3500	1870	1150	1100	650	500

In practical operation the lower limit of the series resistance and impedance is given by the ohmic part of the contact points and the foil resistance values. Therefore it will not always be possible to achieve calculated values below 0.05 Ω.

LIFETIME TABLE U_R ≤ 100 V

INTERRELATION BETWEEN ALTERNATING CURRENT, AMBIENT TEMPERATURE AND LIFETIME																				
I/I _R (FREQUENCY DEPENDENT)							LIFETIME MULTIPLIER L (depending on I/I _R and T _a)													
FREQUENCY [Hz]							AMBIENT TEMPERATURE T _a [°C]													
50	100	250	500	1000	> 2500	10 K	40	45	50	55	60	65	70	75	80	85	90	95	100	105
0	0	0	0	0	0	0	56	35	23	15	9.7	6.4	4.3	3.0	2.0	1.42	1.00	0.71	0.51	0.37
0.18	0.20	0.22	0.23	0.24	0.25	0.26	54	34	22	14	9.4	6.3	4.2	2.9	2.0	1.40	0.98	0.70	0.50	0.36
0.36	0.40	0.44	0.46	0.48	0.50	0.52	49	31	20	13	8.8	5.9	4.0	2.7	1.9	1.33	0.94	0.67	0.48	0.35
0.54	0.60	0.66	0.69	0.72	0.75	0.78	43	28	18	12	8.0	5.4	3.7	2.5	1.8	1.24	0.88	0.63	0.45	0.33
0.72	0.80	0.88	0.92	0.96	1.00	1.04	36	24	16	10	7.0	4.8	3.3	2.3	1.6	1.13	0.80	0.58	0.42	0.31
0.90	1.00	1.10	1.15	1.20	1.25	1.30	29	19	13	8.8	6.0	4.1	2.9	2.0	1.4	1.00	0.72	0.52	0.38	0.28
1.08	1.20	1.32	1.38	1.44	1.50	1.56	23	16	11	7.3	5.0	3.5	2.4	1.7	1.2	0.88	0.63	0.46	0.34	
1.26	1.40	1.54	1.61	1.68	1.75	1.82	18	12	8.5	5.9	4.1	2.9	2.0	1.5	1.0	0.75	0.55	0.40	0.29	
1.44	1.60	1.76	1.84	1.92	2.00	2.08	13	9.4	6.6	4.7	3.3	2.3	1.7	1.2	0.87	0.64	0.47	0.34		
1.62	1.80	1.98	2.07	2.16	2.25	2.34	10	7.1	5.1	3.6	2.6	1.9	1.4	1.0	0.72	0.53	0.39	0.29		
1.80	2.00	2.20	2.30	2.40	2.50	2.60	7.3	5.3	3.8	2.8	2.0	1.5	1.1	0.80	0.59	0.43	0.32			
1.98	2.20	2.42	2.53	2.64	2.75	2.86	5.3	3.9	2.9	2.1	1.6	1.2	0.85	0.63	0.47	0.35				
2.16	2.40	2.64	2.76	2.88	3.00	3.12	3.8	2.8	2.1	1.6	1.2	0.89	0.66	0.50	0.37	0.28				
2.34	2.60	2.86	2.99	3.12	3.25	3.38	2.7	2.1	1.6	1.2	0.89	0.67	0.51	0.39	0.29					
2.52	2.80	3.08	3.22	3.36	3.50	3.64	1.9	1.5	1.1	0.87	0.67	0.51	0.39	0.30						
2.70	3.00	3.30	3.45	3.60	3.75	3.90	1.4	1.1	0.82	0.64	0.49	0.38	0.30							
2.88	3.20	3.52	3.68	3.84	4.00	4.16	0.95	0.75	0.59	0.46	0.36	0.28								
3.06	3.40	3.74	3.91	4.08	4.25	4.42	0.66	0.53	0.42	0.34										
3.24	3.60	3.96	4.14	4.32	4.50	4.68	0.46	0.37												
3.42	3.80	4.18	4.37	4.56	4.75	4.94	0.32													

I_R 100 Hz alternating current [A] at upper category temperature T_{UC} taken from data sheet

I User current [A]

T_a Ambient temperature of capacitor [°C]

L Lifetime multiplier

Regard L as a function of ambient temperature (x-axis) and of current (y-axis); use the current-axis according to the frequency


 Aluminum Capacitors
 Axial Capacitor Style

Vishay Roederstein

TEST PROCEDURES AND REQUIREMENTS			
TEST		PROCEDURE (quick reference)	REQUIREMENTS
NAME OF TEST	REFERENCE		
Endurance	IEC 60384-4/ EN 130300 subclause 4.13	T_A = upper cat. temp.; U_R applied $6.3\text{ V} \leq U_R \leq 100\text{ V}$: 1000 h $T_A = 85\text{ }^\circ\text{C}$; U_R applied	$U_R = 6.3\text{ V}$: $-40\% \leq \Delta C/C \leq 25\%$ $U_R > 6.3\text{ V}$: $-30\% \leq \Delta C/C \leq 30\%$ $\tan \delta \leq 1.5 \times \text{spec. limit}$ $Z \leq 3 \times \text{spec. limit}$ $I_L (300\text{ s}) \leq \text{spec. limit}$
Useful life	CECC 30301 subclause 1.8.1	$T_A = 105\text{ }^\circ\text{C}$; U_R and I_R applied; $6.3\text{ V} \leq U_R \leq 100\text{ V}$ Cases 4.5 x 11: 500 h Cases 6 x 10 to 10 x 25: 750 h $T_A = 85\text{ }^\circ\text{C}$; U_R and I_R applied	$U_R = 6.3\text{ V}$: $-50\% \leq \Delta C/C \leq 45\%$ $U_R > 6.3\text{ V}$: $-45\% \leq \Delta C/C \leq 45\%$ $\tan \delta \leq 3 \times \text{spec. limit}$ $Z \leq 3 \times \text{spec. limit}$ $I_L (300\text{ s}) \leq \text{spec. limit}$ No short circuit, no open circuit Total failure percentage: $\leq 1\%$
Shelf life (storage at high temperature)	IEC 60384-4/ EN 130300 subclause 4.17	T_A = upper cat. temp.; no voltage applied $6.3\text{ V} \leq U_R \leq 100\text{ V}$ Cases 4.5 x 11 to 10 x 25: 500 h After test: U_R to be applied for 30 minutes 24 hours to 48 hours before measurement	$U_R = 6.3\text{ V}$: $-40\% \leq \Delta C/C \leq 25\%$ $U_R > 6.3\text{ V}$: $-30\% \leq \Delta C/C \leq 30\%$ $\tan \delta \leq 1.5 \times \text{spec. limit}$ $Z \leq 3 \times \text{spec. limit}$ $I_L (300\text{ s}) \leq 2 \times \text{spec. limit}$



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Material Category Policy

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as RoHS-Compliant fulfill the definitions and restrictions defined under Directive 2011/65/EU of The European Parliament and of the Council of June 8, 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment (EEE) - recast, unless otherwise specified as non-compliant.

Please note that some Vishay documentation may still make reference to RoHS Directive 2002/95/EC. We confirm that all the products identified as being compliant to Directive 2002/95/EC conform to Directive 2011/65/EU.

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as Halogen-Free follow Halogen-Free requirements as per JEDEC JS709A standards. Please note that some Vishay documentation may still make reference to the IEC 61249-2-21 definition. We confirm that all the products identified as being compliant to IEC 61249-2-21 conform to JEDEC JS709A standards.