





Suppression Film Capacitors Class X2 AC 440 V (MKT) - Radial Type

Dimensions in mm



| LEAD LENGTH X (mm) | ORDERING CODE*** |
|--------------------|------------------|
| 4 ⁻¹ | F1772-...-4004 |
| 6 ⁻¹ | F1772-...-4000 |
| 15 ⁻¹ | F1772-...-4015 |
| 30 ⁺⁵ | F1772-...-4030 |



MAXIMUM PULSE RISE TIME (dU/dt) in V/μs

| RATED VOLTAGE | PITCH (mm) | | | |
|---------------|------------|------|------|------|
| | 15.0 | 22.5 | 27.5 | 37.5 |
| AC 440 V | 200 | 150 | 100 | 100 |

RATED VOLTAGE

AC 440 V, 50 Hz/60 Hz

PERMISSIBLE DC VOLTAGE

DC 1000 V

TERMINALS

Radial tinned wire

COATING

Plastic case, epoxy resin sealed, flame retardant UL 94 V-0

CLIMATIC TESTING CLASS ACC.TO EN 60068-1

40/100/56

CAPACITANCE RANGE

E12 series 0.01 μF X2 - 1.0 μF X2
preferred values acc. to E6

FURTHER TECHNICAL DATA

See page 21 (Document No. 26504)

FEATURES

- Material categorization
For definitions of compliance please see www.vishay.com/doc?99912

CAPACITANCE TOLERANCE

Standard: ± 10 %

DISSIPATION FACTOR tan δ

< 1 % measured at 1 kHz

INSULATION RESISTANCE

FOR C ≤ 0.33 μF:

30 GΩ average value

15 GΩ minimum value

TIME CONSTANT

FOR C > 0.33 μF:

10 000 s average value

5000 s minimum value

TEST VOLTAGE

(Electrode/electrode): DC 2150 V/2 s

REFERENCE STANDARDS

EN 132 400, 1994

EN 60068-1

IEC 60384-14/2, 1993

UL 1283

UL 1414

CSA 22.2 No. 8-M 86

CSA 22.2 No. 1-M 90

DIELECTRIC

Polyester film

ELECTRODES


Metal evaporated

CONSTRUCTION

Metallized film capacitor

Internal series connection

Between interconnected terminations and case (foil method):
AC 2500 V for 2 s at 25 °C.



Impedance (Z) as a function of frequency (f) at T_a = 20 °C (average). Measurement with lead length 6 mm.



RoHS
COMPLIANT

F1772-4000

Vishay Roederstein

Suppression Film Capacitors
Class X2 AC 440 V (MKT) - Radial Type**APPROVALS**

| COUNTRY | SPECIFICATION | ELECTRICAL VALUES | APPROVAL REFERENCE | APPROVAL MARK |
|--------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------|-------------------------------------------------------------------|------------------------|-----------------|
| U.S.A. (for AC 250 V) | UL 1283 UL 1414 | 0.01 μ F X - 1.0 μ F X 0.01 μ F X - 1.0 μ F X | E 76297 E 100682 | |
| Canada (for AC 250 V) | C 22.2 No. 8-M 1986 C 22.2 No. 1-M 1994 | 0.01 μ F X - 1.0 μ F X 0.01 μ F X - 0.82 μ F X | LR 64546 LR 64546-8 | |
| CB TEST-CERTIFICATE (for AC 440 V) | | 0.01 μ F X2 - 1.0 μ F X2 | DE 1-8221 | |
| Germany | EN 132 400; 1999 IEC 60384-14, 2nd edition, 1995 | 0.01 μ F X2 - 1.0 μ F X2 | 40005095 | 10 |
| This approval mark together with the CB-Certificate replace all national approval marks of the following countries (they have already signed the CB-Agreement): | | | | |
| Austria | Belgium | Denmark | Finland | Sweden |
| France | Germany | Ireland | Italy | Switzerland |
| Netherlands | Israel | Portugal | Spain | Great Britain |
| Japan | Norway | China | Poland | Czech. Republic |
| Singapore | Rep. of Korea | Hungary | Iceland | Slovenia |

| CAPACITANCE | TOL. (%) | PITCH (mm) | BOX NO. | DIMENSIONS W x H x L (+ 0.2/- 0.4 mm) | WEIGHT LEAD LENGTH 6 ⁻¹ mm (g) | QUANTITY PACKAGE LEAD LENGTH 6 ⁻¹ mm (pcs) ⁽²⁾ | ORDERING CODE ⁽³⁾ |
|-----------------------------------|-------------|----------------------------|------------|---------------------------------------------|----------------------------------------------------|----------------------------------------------------------------------------------|------------------------------|
| 0.01 μF X2 | ± 10 | 15.0 | 06 | 6.3 x 12.3 x 17.8 | 2.0 | 500 | F1772-310-4 ... |
| 0.012 μ F X2 | ± 10 | 15.0 | 06 | 6.3 x 12.3 x 17.8 | 2.0 | 500 | F1772-312-4 ... |
| 0.015 μF X2 | ± 10 | 15.0 | 07 | 7.3 x 13.3 x 17.8 | 2.4 | 450 | F1772-315-4 ... |
| 0.018 μ F X2 | ± 10 | 15.0 | 07 | 7.3 x 13.3 x 17.8 | 2.4 | 450 | F1772-318-4 ... |
| 0.022 μF X2 | ± 10 | 15.0 | 08 | 8.3 x 14.3 x 17.8 | 2.7 | 325 | F1772-322-4 ... |
| 0.027 μ F X2 | ± 10 | 15.0 | 08 | 8.3 x 14.3 x 17.8 | 2.7 | 325 | F1772-327-4 ... |
| 0.033 μF X2 | ± 10 | 15.0 | 28 | 8.3 x 17.3 x 17.8 | 2.7 | 300 | F1772-333-4 ... |
| 0.039 μ F X2 | ± 10 | 22.5 ⁽¹⁾ | 09 | 6.3 x 14.3 x 26.3 | 3.3 | 260 | F1772-339-4 ... |
| 0.047 μF X2 | ± 10 | 22.5 ⁽¹⁾ | 11 | 7.3 x 15.3 x 26.3 | 4.1 | 235 | F1772-347-4 ... |
| 0.056 μ F X2 | ± 10 | 22.5 ⁽¹⁾ | 12 | 8.3 x 16.3 x 26.3 | 4.6 | 200 | F1772-356-4 ... |
| 0.068 μF X2 | ± 10 | 22.5 ⁽¹⁾ | 12 | 8.3 x 16.3 x 26.3 | 4.6 | 200 | F1772-368-4 ... |
| 0.082 μ F X2 | ± 10 | 22.5 ⁽¹⁾ | 12 | 8.3 x 16.3 x 26.3 | 4.6 | 200 | F1772-382-4 ... |
| 0.1 μF X2 | ± 10 | 22.5 ⁽¹⁾ | 13 | 10.3 x 18.3 x 26.3 | 6.7 | 170 | F1772-410-4 ... |
| 0.12 μ F X2 | ± 10 | 22.5 ⁽¹⁾ | 13 | 10.3 x 18.3 x 26.3 | 6.7 | 170 | F1772-412-4 ... |
| 0.15 μF X2 | ± 10 | 27.5 ⁽¹⁾ | 14 | 11.0 x 21.0 x 31.0 | 9.1 | 125 | F1772-415-4 ... |
| 0.18 μ F X2 | ± 10 | 27.5 ⁽¹⁾ | 14 | 11.0 x 21.0 x 31.0 | 9.1 | 125 | F1772-418-4 ... |
| 0.22 μF X2 | ± 10 | 27.5 ⁽¹⁾ | 15 | 13.0 x 23.3 x 31.3 | 12.9 | 110 | F1772-422-4 ... |
| 0.27 μ F X2 | ± 10 | 27.5 ⁽¹⁾ | 15 | 13.0 x 23.3 x 31.3 | 12.9 | 110 | F1772-427-4 ... |
| 0.33 μF X2 | ± 10 | 27.5 ⁽¹⁾ | 18 | 14.5 x 24.3 x 31.3 | 15.0 | 100 | F1772-433-4 ... |
| 0.39 μ F X2 | ± 10 | 37.5 ⁽¹⁾ | 14 | 12.0 x 22.3 x 41.3 | 15.2 | 90 | F1772-439-4 ... |
| 0.47 μF X2 | ± 10 | 37.5 ⁽¹⁾ | 16 | 14.0 x 24.3 x 41.3 | 18.9 | 80 | F1772-447-4 ... |
| 0.56 μ F X2 | ± 10 | 37.5 ⁽¹⁾ | 19 | 15.5 x 28.3 x 41.3 | 24.0 | 70 | F1772-456-4 ... |
| 0.68 μF X2 | ± 10 | 37.5 ⁽¹⁾ | 19 | 15.5 x 28.3 x 41.3 | 24.0 | 70 | F1772-468-4 ... |
| 0.82 μ F X2 | ± 10 | 37.5 ⁽¹⁾ | 20 | 17.9 x 32.4 x 41.3 | 31.6 | 60 | F1772-482-4 ... |
| 1.0 μF X2 | ± 10 | 37.5 ⁽¹⁾ | 42 | 19.8 x 39.9 x 42.3 | 44.2 | 55 | F1772-510-4 ... |

Preferred values in bold print.

Notes

- Inbuilt discharging resistor on request (with larger case dimensions).
- ⁽¹⁾ Different pitch on request.
- ⁽²⁾ Further information about packaging quantities with different lead length and/or taped versions.
See page 16 (Document No. 27608 Packaging Quantities). Use Box No. as reference
- ⁽³⁾ These capacitors can be delivered on continuous tape and reel - see page 14/15 (Document Number 27622).
The ordering code is F1772-...-4900 at H = 16.5 mm, F1772-...-4901 at H = 18.5 mm.



Suppression Film Capacitors
Class X2 AC 440 V (MKT) - Radial Type

Vishay Roederstein

APPLICATION NOTES

- For X2 electromagnetic interference suppression in **across the line applications** (50 Hz/60 Hz) with a maximum mains voltage of 440 V_{AC}.
- These capacitors are not intended for continuous pulse applications. For these situations, capacitors of the AC and pulse programs must be used.
- These capacitors can be used for series impedance application in case safety approvals are requested.
- The maximum ambient temperature must not exceed 100 °C.
- Rated voltage pulse slope:
If the pulse voltage is lower than the rated voltage, the values of the specific reference data can be multiplied by $620 V_{DC}$ and divided by the applied voltage.



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Vishay products are not designed for use in life-saving or life-sustaining applications or any application in which the failure of the Vishay product could result in personal injury or death unless specifically qualified in writing by Vishay. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.