

CERTIFICATE ENEC16/FI/19/10007/M1

Our Ref. HEL-CERT190100006-37



Certificate holder Vishay Electronica Portugal, Lda
Rua Magalhaes Lima 256
4760-363, Vila Nova de Famalicão, Portugal

Product Fixed capacitor for electromagnetic interference suppression and connection to the supply mains

Trademark (if any)

Type F340Y2

Rating and principal characteristics Y2; 305 V~; 0,001 µF - 1,0 µF (E6 series); 55/105/56/C <1750 mm²; 55/105/56/B ≥ 1750 mm²; IIIB

Is complying with the following European Standards EN 60384-14:2013
EN 60384-14:2013 + A1:2016

It is authorized to use the ENEC Mark in conjunction with the suffix 16, as shown above.

Validity This certificate is valid until 2028-01-09 provided that the Conditions for ENEC certification are met. This certificate includes the right to use the ENEC 16 mark under the condition that changes (if any) will be checked at SGS Fimko before the product is brought onto market and that the conditions for ENEC certification are met.

This certificate has been issued under the presumption and conditional on the fact that the licensee holds all necessary legal rights with regard to the product presented for testing and certification.

Date of issue 2023-01-09

SGS Fimko Ltd

Signature

Joonas Leinonen
Certification Manager

Page 1 of 2

This document is issued by the Company under its General Conditions of Service accessible at http://www.sgs.com/terms_and_conditions.htm. Attention is drawn to the limitation of liability, indemnification and jurisdiction issues defined therein.

Any holder of this document is advised that information contained hereon reflects the Company's findings at the time of its intervention only and within the limits of Client's instructions, if any. The Company's sole responsibility is to its Client and this document does not exonerate parties to a transaction from exercising all their rights and obligations under the transaction documents. Any unauthorized alteration, forgery or falsification of the content or appearance of this document is unlawful and offenders may be prosecuted to the fullest extent of the law.



SGS Fimko Ltd

Takomotie 8, FI-00380 Helsinki, Finland
t. +358 9 696 361 www.sgs.fi

Business ID 0978538-5

Member of the SGS Group (SGS SA)



Page 2 of 2 to Certificate: **ENEC16/FI/19/10007/M1**

Manufacturer Vishay Electronica Portugal, Lda
Rua Magalhaes Lima 256
4760-363, Vila Nova de Famalicão, Portugal

Manufacturing site 1. Vishay Electronica Portugal, Lda
Rua Magalhaes Lima 256
4760-363, Vila Nova de Famalicão, Portugal
2. Vishay Components India Private Limited
100% EOU Division,
Loni-Kahlbor, Near Pune (C. Rly), 412201, Pune, India

Additional information Tolerances: $\pm 5\%$, $\pm 10\%$ and $\pm 20\%$
Humidity robustness grade: IIIB

This certificate replaces the previous certificate
ENEC16/FI/19/10007/A1, dated 2022-05-22, due to new epoxy resin
added.

Following limitations apply -

As shown in the Test Report(s) No(s): 295111-8, 295111-8 Amendment-1



Page 2 of 2

This document is issued by the Company under its General Conditions of Service accessible at http://www.sgs.com/terms_and_conditions.htm. Attention is drawn to the limitation of liability, indemnification and jurisdiction issues defined therein.

Any holder of this document is advised that information contained hereon reflects the Company's findings at the time of its intervention only and within the limits of Client's instructions, if any. The Company's sole responsibility is to its Client and this document does not exonerate parties to a transaction from exercising all their rights and obligations under the transaction documents. Any unauthorized alteration, forgery or falsification of the content or appearance of this document is unlawful and offenders may be prosecuted to the fullest extent of the law.

SGS Fimko Ltd

Takomotie 8, FI-00380 Helsinki, Finland
t. +358 9 696 361 www.sgs.fi

Business ID 0978538-5

Member of the SGS Group (SGS SA)