



196 HVC ENYCAP™

COMMERCIAL:

Customer name	<input type="text"/>
Customer contact	<input type="text"/>
Customer address	<input type="text"/>
Telephone number	<input type="text"/>
Email	<input type="text"/>
Sales contact	<input type="text"/>
Competitor part	<input type="text"/>
Current solution	<input type="text"/>

CHARGE CONDITIONS:

Existing charge controller	<input type="text"/>
Min. charging voltage [V]	<input type="text"/>
Max. charging voltage [V]	<input type="text"/>
Charge mode (CC, CV, trickle mode)	<input type="text"/>
Available charging current [mA]	<input type="text"/>
Min. charging time till first backup [s]	<input type="text"/>
Min. temperature [°C]	<input type="text"/>
Max. temperature [°C]	<input type="text"/>
Further information	<input type="text"/>

APPLICATION:

Industry segment	<input type="text"/>
Function	<input type="text"/>
SOP	<input type="text"/>
Volume per year	<input type="text"/>
Target price (currency)	<input type="text"/>
Competitor	<input type="text"/>
Samples	<input type="text"/>

DISCHARGE CONDITIONS:

Back up time [h]	<input type="text"/>
Discharge conditions [mA]	<input type="text"/>
Min. hold up voltage [V]	<input type="text"/>
Continuous discharge	<input type="text"/>
Pulse discharge / on - off time	<input type="text"/>
Peak current [mA]	<input type="text"/>
Min. current [mA]	<input type="text"/>

MECHANICAL REQUIREMENTS:

Available space	Length [mm]	<input type="text"/>
	Width [mm]	<input type="text"/>
	Height [mm]	<input type="text"/>
Assembly form	<input type="text"/>	
Quality information	<input type="text"/>	
Safety approvals	<input type="text"/>	

OPERATING CONDITIONS:

Operating time [h]	<input type="text"/>
Cycles	<input type="text"/>
Life time expectation	<input type="text"/>