

# Aluminum Electrolytic Capacitors

## Power High Ripple Current Long Life 4-Terminal Snap-In



**ADDITIONAL RESOURCES**


Fig. 1

QUICK REFERENCE DATA	
DESCRIPTION	VALUE
Nominal case size (D x L in mm)	35 x 50 to 45 x 100
Rated capacitance range $C_R$	470 $\mu$ F to 2200 $\mu$ F
Tolerance on $C_R$	$\pm 20\%$
Rated voltage range, $U_R$	400 V to 450 V
Category temperature range	-40 °C to +105 °C
Endurance test at 105 °C	2000 h
Useful life at 105 °C	5000 h
Shelf life at 0 V, 105 °C	1000 h
Based on sectional specification	IEC 60384-4 / EN 130300
Climatic category IEC 60068	40 / 105 / 56

**FEATURES**

- Polarized aluminum electrolytic capacitors, non-solid electrolyte
- Large types, minimized dimensions, cylindrical aluminum case, insulated with a blue sleeve
- Pressure relief on the side of the aluminum case
- Very long useful life: 5000 h at 105 °C
- Temperature range up to 105 °C
- Stable mounting and keyed polarity
- High ripple current capability
- Material categorization: for definitions of compliance please see [www.vishay.com/doc?99912](http://www.vishay.com/doc?99912)


**RoHS  
COMPLIANT**
**APPLICATIONS**

- Switched mode power supplies
- Renewable energy power converters
- Energy storage in pulse systems

**MARKING**

The capacitors are marked (where possible) with the following information:

- Rated capacitance (in  $\mu$ F)
- Tolerance code on rated capacitance, code letter in accordance with IEC 60062 (M for  $\pm 20\%$ )
- Rated voltage (in V)
- Date code
- Name of manufacturer
- Code for factory of origin
- “-” sign to identify the negative terminal, visible from the top and side of the capacitor
- (Partial) ordering code
- Climatic category in accordance with IEC 60068

SELECTION CHART FOR $C_R$ , $U_R$ , AND RELEVANT NOMINAL CASE SIZES ( $\varnothing$ D x L in mm)		
$C_R$ ( $\mu$ F)	$U_R$ (V)	
	400	450
470	-	35 x 50
	-	40 x 40
560	35 x 50	35 x 60
	-	40 x 50
680	40 x 40	35 x 70
	35 x 60	35 x 80
820	40 x 50	40 x 60
	-	35 x 100
1000	35 x 70	40 x 80
	-	45 x 60
	35 x 80	-
1200	40 x 70	45 x 70
	45 x 60	-
	35 x 100	40 x 100
1500	45 x 70	45 x 80
	40 x 100	45 x 100
1800	45 x 80	-
	45 x 100	-
2200	45 x 100	-


**DIMENSIONS in millimeters AND AVAILABLE FORMS**
**4-TERMINAL SNAP-IN**


Fig. 2 - 4-Terminal snap-in




Fig. 3 - Mounting hole diagram

Dummy terminals (A and C) must be free from the electrical circuit.

Table 1

DIMENSIONS in millimeters, MASS AND PACKAGING QUANTITIES					
NOMINAL CASE SIZE Ø D x L	Ø D <sub>MAX.</sub>	L <sub>max.</sub>	MASS (g)	PACKAGING QUANTITIES (units per box)	CARDBOARD BOX DIMENSIONS L x W x H
35 x 50	36	52	72	50	390 x 198 x 60
35 x 60	36	62	91	50	390 x 198 x 70
35 x 70	36	72	103	50	377 x 375 x 97
35 x 80	36	82	115	50	377 x 375 x 107
35 x 100	36	102	151	50	377 x 375 x 127
40 x 40	41	42	70	50	440 x 223 x 60
40 x 50	41	52	94	50	440 x 223 x 70
40 x 60	41	62	118	25	230 x 230 x 80
40 x 70	41	72	134	25	230 x 230 x 90
40 x 80	41	82	150	25	230 x 230 x 100
40 x 100	41	102	176	25	230 x 230 x 120
45 x 60	46	62	150	36	377 x 375 x 87
45 x 70	46	72	170	36	377 x 375 x 97
45 x 80	46	82	190	36	377 x 375 x 107
45 x 100	46	102	250	36	377 x 375 x 127

ELECTRICAL DATA	
SYMBOL	DESCRIPTION
C <sub>R</sub>	Rated capacitance at 100 Hz
I <sub>R</sub>	Rated RMS ripple current at 100 Hz and 105 °C
I <sub>L5</sub>	Max. leakage current after 5 min at U <sub>R</sub>
ESR	Max. equivalent series resistance at 100 Hz
Z	Max. impedance at 10 kHz

**Note**

- Unless otherwise specified, all electrical values in Table 2 apply at T<sub>amb</sub> = 20 °C, P = 86 kPa to 106 kPa, RH = 45 % to 75 %

**ORDERING EXAMPLE**

Electrolytic capacitor 299 series

2200 µF / 400 V

**4-terminal snap-in:**

Ordering code: MAL2 299 56222 E3

Former 12NC: 2222 299 56222



Table 2

ELECTRICAL DATA AND ORDERING INFORMATION									
U <sub>R</sub> (V)	C <sub>R</sub> (µF)	NOMINAL CASE SIZE Ø D x L (mm)	I <sub>R</sub> 100 Hz 105 °C (A)	I <sub>L5</sub> 5 min (mA)	TYP. ESR 100 Hz (mΩ)	MAX. ESR 100 Hz (mΩ)	TYP. Z 10 kHz (mΩ)	MAX. Z 10 kHz (mΩ)	CATALOG NUMBER MAL2299.....
400	560	35 x 50	2.70	0.452	170	220	130	160	56561E3
	680	40 x 40	2.79	0.548	150	190	110	140	56681E3
	820	35 x 60	3.44	0.660	120	150	90	110	56821E3
	820	40 x 50	3.51	0.660	120	160	90	110	66821E3
	1000	35 x 70	3.88	0.804	100	130	70	90	56102E3
	1200	35 x 80	4.34	0.964	90	110	60	80	56122E3
	1200	40 x 70	4.50	0.964	90	110	60	80	66122E3
	1200	45 x 60	4.61	0.964	90	110	60	80	76122E3
	1500	35 x 100	5.54	1.204	70	90	50	60	56152E3
	1500	45 x 70	5.20	1.204	70	90	60	70	66152E3
	1800	40 x 100	6.02	1.444	50	70	40	50	56182E3
	1800	45 x 80	5.74	1.444	60	80	50	60	66182E3
	2200	45 x 100	6.77	1.764	50	60	40	50	56222E3
450	470	35 x 50	2.54	0.427	190	240	130	160	57471E3
	470	40 x 40	2.45	0.427	190	240	140	170	67471E3
	560	35 x 60	2.96	0.508	160	200	100	130	57561E3
	560	40 x 50	3.05	0.508	160	200	110	140	67561E3
	680	35 x 70	3.34	0.616	120	160	90	110	57681E3
	820	35 x 80	3.76	0.742	110	140	70	90	57821E3
	820	40 x 60	3.73	0.742	110	140	80	100	67821E3
	1000	35 x 100	4.74	0.904	90	110	60	80	57102E3
	1000	40 x 80	4.41	0.904	90	110	60	80	67102E3
	1000	45 x 60	4.34	0.904	90	120	60	80	77102E3
	1200	45 x 70	4.84	1.084	80	100	60	70	57122E3
	1500	40 x 100	5.67	1.354	60	80	40	50	57152E3
	1500	45 x 80	5.39	1.354	60	80	50	60	67152E3
	1800	45 x 100	6.36	1.624	50	70	40	50	57182E3

ADDITIONAL ELECTRICAL DATA		
PARAMETER	CONDITIONS	VALUE
<b>Voltage</b>		
Surge voltage	≥ 400 V versions	U <sub>s</sub> = 1.1 x U <sub>R</sub>
Reverse voltage		U <sub>rev</sub> ≤ 1 V
<b>Current</b>		
Leakage current	After 1 min at U <sub>R</sub>	I <sub>L1</sub> ≤ 0.006 C <sub>R</sub> x U <sub>R</sub> + 4 µA
	After 5 min at U <sub>R</sub>	I <sub>L5</sub> ≤ 0.002 C <sub>R</sub> x U <sub>R</sub> + 4 µA
<b>Inductance</b>		
Equivalent series inductance (ESL)	All case sizes	Ca. 20 nH



**RIPPLE CURRENT AND USEFUL LIFE**


Table 3

ENDURANCE TEST DURATION AND USEFUL LIFE	
ENDURANCE AT 105 °C (h)	USEFUL LIFE AT 105 °C (h)
2000	5000

**Note**

- Multiplier of useful life code: CCC206-5

CCC206-5



$I_A$  = Actual ripple current at 100 Hz  
 $I_R$  = Actual ripple current at 100 Hz and 105 °C

(1) Useful life at 105 °C and  $I_R$  applied: 5000 h

Fig. 4 - Multiplier of useful life as a function of ambient temperature and ripple current load

Table 4

MULTIPLIER OF RIPPLE CURRENT ( $I_R$ ) AS A FUNCTION OF FREQUENCY					
FREQUENCY (Hz)					
50	100	200	400	1000	10 000
$I_R$ MULTIPLIER					
0.9	1.0	1.2	1.3	1.4	1.5



Table 5

<b>TEST PROCEDURES AND REQUIREMENTS</b>			
<b>TEST</b>		<b>PROCEDURE (quick reference)</b>	<b>REQUIREMENTS</b>
<b>NAME OF TEST</b>	<b>REFERENCE</b>		
Endurance	IEC 60384-4 / EN130300 subclause 4.13	$T_{amb} = 105\text{ }^{\circ}\text{C}$ ; $U_R$ applied 2000 h	$\Delta C/C: \pm 10\%$ $ESR \leq 1.3 \times \text{spec. limit}$ $Z \leq 2 \times \text{spec. limit}$ $I_{L5} \leq \text{spec. limit}$
Useful life	CECC 30301 subclause 4.13	$T_{amb} = 105\text{ }^{\circ}\text{C}$ ; $U_R$ and $I_R$ applied; 5000 h	$\Delta C/C: \pm 30\%$ $ESR \leq 3 \times \text{spec. limit}$ $Z \leq 3 \times \text{spec. limit}$ $I_{L5} \leq \text{spec. limit}$ no short or open circuit, no visible damage total failure percentage: $\leq 3\%$
Shelf life	IEC 60384-4 / EN130300 subclause 4.17	$T_{amb} = 105\text{ }^{\circ}\text{C}$ ; no voltage applied; 1000 h  After test: $U_R$ to be applied for 30 min 24 h to 48 h before measurement	$\Delta C/C: \pm 10\%$ $ESR \leq 1.2 \times \text{spec. limit}$ $I_{L5} \leq 2 \times \text{spec. limit}$

Statements about product lifetime are based on calculations and internal testing. They should only be interpreted as estimations. Also due to external factors, the lifetime in the field application may deviate from the calculated lifetime. In general, nothing stated herein shall be construed as a guarantee of durability.



## Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.