


EMI Suppression Safety Capacitor, Ceramic Disc, Class X1, 440 V_{AC}, Class Y1, 300 V_{AC}



LINKS TO ADDITIONAL RESOURCES



QUICK REFERENCE DATA					
DESCRIPTION	VALUE				
Ceramic class	1		2		
Ceramic dielectric	U2J		Y5S		Y5U
Voltage (V _{AC})	300	440	300	440	300 440
Min. capacitance (pF)	10				
Max. capacitance (pF)	1500				
Mounting	Surface-mount (reflow soldering)				

OPERATING TEMPERATURE RANGE

-55 °C to +125 °C

TEMPERATURE CHARACTERISTICS

U2J, Y5S, Y5U

SECTIONAL SPECIFICATIONS

Climatic category (according to EN 60058-1)
55 / 125 / 21

MOLDING

According to UL 94 V-0
Epoxy resin, isolating, flame retardant
Halogen-free
Reinforced insulation
Moisture sensitivity level: MSL 2a

APPROVALS

IEC 60384-14
UL 60384-14
CQC 60384-14

FEATURES

- Complying with IEC 60384-14
- Singlelayer disc safety capacitors
- Mounting: surface-mount
- Material categorization:
for definitions of compliance please see
www.vishay.com/doc?99912



RoHS
COMPLIANT
HALOGEN
FREE

APPLICATIONS

- X1, Y1 according to IEC 60384-14
- Line-to-line filtering (Class X)
- Line-to-ground filtering (Class Y)
- Primary and secondary coupling (SMPS)
- Industrial and consumer
- EMI / RFI suppression and filtering

DESIGN

The capacitor consists of a ceramic disc which is copper / silver plated on both sides. Encapsulation is made of flame retardant epoxy resin in accordance with UL 94 V-0.

CAPACITANCE RANGE

10 pF to 1500 pF

RATED VOLTAGE U_R

IEC 60384-14:
(X1): 440 V_{AC}, 50 Hz
(Y1): 300 V_{AC}, 50 Hz
Annex H: 1500 V_{DC}

TEST VOLTAGE

Component test (100 %):
4000 V_{AC}, 50 Hz, 2 s
Random sampling test (destructive test):
4000 V_{AC}, 50 Hz, 60 s
Voltage proof of molding (destructive test):
4000 V_{AC}, 50 Hz, 60 s

INSULATION RESISTANCE

≥ 10 000 MΩ

CAPACITANCE TOLERANCE

± 10 % (code K)
± 20 % (code M)

DISSIPATION FACTOR

Class 1: max. 0.3 % (1 MHz)
Class 2: max. 2.5 % (1 kHz)

DIMENSIONS in millimeters					
10 pF TO 680 pF			1000 pF TO 1500 pF		
CAPACITANCE	W	L	T	B	K
10 pF to 680 pF	6.6 ± 0.5	11.9 ± 0.5	4.0 max.	3.0 ± 0.25	9.0 ± 0.25
1000 pF to 1500 pF	8.6 ± 0.5	11.2 ± 0.5	4.0 max.	3.0 ± 0.25	10.2 ± 0.25


Note

- For soldering recommendation please see www.vishay.com/doc?28572

TECHNICAL DATA				
CAPACITANCE (pF)	TOLERANCE (%)	SIZE CODE	PART NUMBER	
			MISSING DIGITS SEE ORDERING CODE BELOW	
10	± 10	A	SMDY1100KU2JARS	
22		A	SMDY1220KU2JARS	
33		A	SMDY1330KU2JARS	
47		A	SMDY1470KY5SARS	
100		A	SMDY1101KY5SARS	
220		A	SMDY1221KY5SARS	
330	± 20	A	SMDY1331MY5UARS	
470		A	SMDY1471MY5UARS	
680		A	SMDY1681MY5UARS	
1000		B	SMDY1102MY5UBRS	
1500		B		
				SMDY1152MY5UBRS

ORDERING CODE							
Example	SMDY1	152	M	Y5U	B	R	S
	Series	Capacitance value	Tolerance code	Temperature coefficient	Size code	Packaging Tape and reel	Internal code

PACKAGING	
CAPACITANCE	PACKAGING QUANTITIES (PCS)
10 pF to 680 pF	1000
1000 pF to 1500 pF	1000

CARRIER TAPE DIMENSIONS in millimeters


CAPACITANCE	W	A0	B0	K0	P1	P0	P2	T	E	F	D0	D1	10P0
10 pF to 680 pF	24.00 ± 0.30	7.25 ± 0.10	12.55 ± 0.10	4.10 ± 0.10	12.00 ± 0.10	4.00 ± 0.10	2.00 ± 0.10	0.35 ± 0.05	1.75 ± 0.10	11.5 ± 0.10	1.55 ± 0.05	1.5 min.	40 ± 0.20
1000 pF to 1500 pF	24.00 ± 0.30	9.25 ± 0.10	11.85 ± 0.10	4.10 ± 0.10	12.00 ± 0.10	4.00 ± 0.10	2.00 ± 0.10	0.35 ± 0.05	1.75 ± 0.10	11.5 ± 0.10	1.55 ± 0.05	1.5 min.	40 ± 0.20

APPROVALS

IEC 60384-14 - Safety tests
This approval together with CB test certificate substitutes all national approvals.

CB Certificate (www.vishay.com/doc?22268)

Y1-capacitor: CB test certificate:	DE1-69482	10 pF to 1.5 nF	300 V _{AC}	
X1-capacitor: CB test certificate:	DE1-69482	10 pF to 1.5 nF	440 V _{AC}	

VDE (www.vishay.com/doc?22269)

Y1-capacitor: VDE marks approval:	40059817	10 pF to 1.5 nF	300 V _{AC}	
X1-capacitor: VDE marks approval:	40059817	10 pF to 1.5 nF	440 V _{AC}	

DIN EN 60384-14 (VDE 0565-1-1):2014-04; EN 60384-14:2013-08
DIN EN 60384-14/A1 (VDE 0565-1-1/A1):2017-04; EN 60384-14:2013/A1:2016

Underwriters Laboratories Inc. / Canadian Standards Association (www.vishay.com/doc?22271)

Y1-capacitor: CSA test certificate:	2575309	10 pF to 1.5 nF	300 V _{AC}	
X1-capacitor: CSA test certificate:	2575309	10 pF to 1.5 nF	440 V _{AC}	

UL 60384-14, CSA E60384-1:14, CSA E60384-14:14
Fixed capacitors for electromagnetic interference suppression and connection to the supply mains.

CQC (www.vishay.com/doc?22270)

Y1-capacitor: CQC test certificate:	CQC25001476496	10 pF to 1.5 nF	300 V _{AC}	
X1-capacitor: CQC test certificate:	CQC25001476496	10 pF to 1.5 nF	440 V _{AC}	

MARKING	
<p>YY: year, ΔΔ: week, XXX: capacitance value, t: tolerance code ⁽¹⁾</p>	<p>PN: SMDY1102MY5UBRS Lot1: DC1: QTY: 1000 Lot2: DC2: PO: / Batch: SL: SO: / Region: 9520 Ser.No: MSL: 2a</p> <p>e3 Pb RoHS H/F MSL: 2a</p> <p>1/1</p>

Note

(1) Identify "XXX" and "t" by the ordering code

PERFORMANCE		
TEST	TEST CONDITION	TEST LIMITS
Visual and mechanical inspection	Optical inspection, dimensions measured with caliper	No visual damage, marking legible
Capacitance (C)	25 °C ± 3 °C; RH ≤ 75 %;	Capacitance within specified tolerance
Dissipation factor (DF)	1.0 V _{RMS} ± 0.2 V _{RMS} at 1 MHz for class 1 1.0 V _{RMS} ± 0.2 V _{RMS} at 1 kHz for class 2	Class 1: DF ≤ 0.3 %; Class 2: DF ≤ 2.5 %
Insulation resistance (IR)	Measured with 60 s ± 5 s after charging at 500 V _{DC}	Min. 10 000 MΩ
Dielectric strength	4000 V _{AC} at 50 Hz / 60 Hz for 1 min 50 mA max.	No failure
Solderability of termination	Immerse in solder bath for 2 s with 255 °C ± 5 °C after fluxing	95 % of the terminations are to be soldered
Impulse voltage	3 pulses of 8 kV	No failure
Life test	125 °C; 1000 V _{AC} at 50 Hz; 1000 h 125 °C; 2550 V _{DC} ; 1000 h	No visual damage
		ΔC/C < ± 15 %
		U2J: DF ≤ 0.5 %; Y5S / Y5U: DF ≤ 5 %
		IR ≥ 3000 MΩ
Humidity test	500 h + 48 h / - 0 h; 40 °C ± 2 °C; 90 % to 95 % RH; 440 V _{AC} at 50 Hz	No visual damage
		U2J: ΔC/C < ± 10 %; Y5S / Y5U: ΔC/C < ± 15 %
		U2J: DF ≤ 0.5 %; Y5S / Y5U: DF ≤ 5 %
		IR ≥ 3000 MΩ
	500 h + 48 h / - 0 h; 40 °C ± 2 °C; 90 % to 95 % RH; 1500 V _{DC}	No visual damage
		U2J: ΔC/C < ± 10 %; Y5S / Y5U: ΔC/C < ± 15 %
		U2J: DF ≤ 0.5 %; Y5S / Y5U: DF ≤ 5 %
		IR ≥ 3000 MΩ
	500 h + 48 h / - 0 h; 40 °C ± 2 °C; 90 % to 95 % RH; 0 V loading	No visual damage
		U2J: ΔC/C < ± 10 %; Y5S / Y5U: ΔC/C < ± 15 %
		U2J: DF ≤ 0.5 %; Y5S / Y5U: DF ≤ 5 %
		IR ≥ 3000 MΩ
		Dielectric strength: no failure

PERFORMANCE		
TEST	TEST CONDITION	TEST LIMITS
Robustness of termination	Shear test: 17.7 N for 10 s ± 1 s for soldered on PCB 	No damage to capacitor body and pin
	Bending test: 1 mm bending constant for 5 s ± 1 s 	
Resistance to soldering heat (solder bath)	Reflow soldering: peak 260 °C + 0 °C / - 5 °C The area of soldering 230 °C min., 20 s to 40 s	No visual damage U2J: ΔC/C < ± 5 %; Y5S / Y5U: ΔC/C < ± 20 % U2J: DF ≤ 0.3 %; Y5S / Y5U: DF ≤ 2.5 % IR ≥ 3000 MΩ Dielectric strength: no failure
Temperature cycling	-55 °C to +125 °C; 5 cycles	No visual damage ΔC/C < ± 30 % U2J: DF ≤ 0.5 %; Y5S / Y5U: DF ≤ 5 % IR ≥ 3000 MΩ Dielectric strength: no failure
Electrical characterization	25 °C and -55 °C, +125 °C	Capacitance within specified tolerance Class 1: DF ≤ 0.3 %; Class 2: DF ≤ 2.5 % IR ≥ 10 000 MΩ

STORAGE AND OPERATION RECOMMENDATIONS

The molding resin of the molding type ceramic capacitor does not form a perfect seal, avoid corrosive gas and direct sunlight, and use (storage) in the condition without moisture condensation.

This series is declared to MSL 2a.

Solder the enclosed capacitors within 168 h after opening the moisture-proof package.

After opening, store it in the packing condition at the time of delivery or in a similar state.

Temperature: 10 °C to 30 °C

Humidity: 60 % max.

If it has been more than 4 weeks since opening, or if the 10 % display of the HIC (humidity indicator card) is pink, perform baking according to J-STD-033B0.1.

RELATED DOCUMENTS	
CB Test Certificate	www.vishay.com/doc?22268
VDE Marks Approval	www.vishay.com/doc?22269
UL Test Certificate	www.vishay.com/doc?22271
CQC Test Certificate	www.vishay.com/doc?22270
Soldering Recommendation	www.vishay.com/doc?28572



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Vishay products are not designed for use in life-saving or life-sustaining applications or any application in which the failure of the Vishay product could result in personal injury or death unless specifically qualified in writing by Vishay. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.