


Pulse Load Carbon Film MINI-MELF Resistors for High Frequency Applications



CMA 0204 HF specialty MELF resistors combine the advanced pulse load capability and the suitability for RF applications in a single component. They are the perfect choice in high frequency circuit designs where the parasitic inductance of regular, helical trimmed resistors cannot be accepted, but where also pulse energies apply. Typical applications are in the fields of telecommunication equipment and industrial electronics.

FEATURES

- Specialty product for RF applications
- Low-inductance non-helical trimmed product
- Special carbon film technology
- ESD capability: 3 kV, human body model
- Suitable for more than 10 GHz
- Intrinsic sulfur resistance
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912



RoHS
COMPLIANT
HALOGEN
FREE
GREEN
(5-2008)

APPLICATIONS

- Telecommunication
- Industrial

| TECHNICAL SPECIFICATIONS | |
|---|---|
| DESCRIPTION | CMA 0204 HF |
| DIN size | 0204 |
| Metric size code | RC3715M |
| Resistance range | 50 Ω ; 47 Ω to 300 Ω |
| Resistance tolerance | $\pm 2 \%$ |
| Temperature coefficient | -250 ppm/K |
| Rated dissipation, P_{70} ⁽¹⁾ | 0.4 W |
| Operating voltage, U_{max} . AC _{RMS} /DC | Limited by P_{70} |
| Permissible film temperature, $\vartheta_{F max}$. ⁽¹⁾ | 155 °C |
| Operating temperature range ⁽¹⁾ | -55 °C to 155 °C |
| Permissible voltage against ambient (insulation): 1 min; U_{ins} | 300 V |
| Failure rate: FIT _{observed} | $\leq 0.1 \times 10^{-9}/h$ |

Note

⁽¹⁾ Please refer to APPLICATION INFORMATION below.

APPLICATION INFORMATION

When the resistor dissipates power, a temperature rise above the ambient temperature occurs, dependent on the thermal resistance of the assembled resistor together with the printed circuit board. The rated dissipation applies only if the permitted film temperature is not exceeded.

These resistors do not feature a limited lifetime when operated within the permissible limits. However, resistance value drift increasing over operating time may result in exceeding a limit acceptable to the specific application, thereby establishing a functional lifetime.

**MAXIMUM RESISTANCE CHANGE AT RATED DISSIPATION**

| OPERATION MODE | | STANDARD | POWER |
|---|-------------|---------------------|---------------------|
| Rated dissipation, P_{70} | CMA 0204 HF | 0.25 W | 0.4 W |
| Operating temperature range | | -55 °C to 125 °C | -55 °C to 155 °C |
| Permissible film temperature, ϑ_F max. | | 125 °C | 155 °C |
| Max. resistance change at P_{70} for resistance range, $ \Delta R/R $ after: | CMA 0204 HF | 50 Ω; 47 Ω to 300 Ω | 50 Ω; 47 Ω to 300 Ω |
| | 1000 h | ≤ 1 % | ≤ 2 % |
| | 8000 h | ≤ 2 % | ≤ 4 % |

Note

- The presented operation modes do not refer to different types of resistors, but actually show examples of different loads, that lead to different film temperatures and different achievable load-life stability (drift) of the resistance value. A suitable low thermal resistance of the circuit board assembly must be safeguarded in order to maintain the film temperature of the resistors within the specified limits. Please consider the application note "Thermal Management in Surface-Mounted Resistor Applications" (www.vishay.com/doc?28844) for information on the general nature of thermal resistance.

TEMPERATURE COEFFICIENT AND RESISTANCE RANGE

| TYPE / SIZE | TCR | TOLERANCE | RESISTANCE | E-SERIES |
|-------------|------------|-----------|---------------------|----------|
| CMA 0204 HF | -250 ppm/K | ± 2 % | 50 Ω; 47 Ω to 300 Ω | E24 |

PACKAGING

| TYPE / SIZE | CODE | QUANTITY | PACKAGING STYLE | WIDTH | PITCH | PACKAGING DIMENSIONS |
|-------------|---------|----------|--|-------|-------|----------------------|
| CMA 0204 HF | B3 = BL | 3000 | Antistatic blister tape acc. IEC 60286-3, Type 2a | 8 mm | 4 mm | Ø 180 mm / 7" |

PART NUMBER AND PRODUCT DESCRIPTION

Part Number: CMA0204AX1000GB300

| | | | | | | | | | | | | | | | | | |
|-------------|---|---|-----------------------|---|---|-------------------|---|---|--|---|---|-----------|---|-----------|---|---|---|
| C | M | A | 0 | 2 | 0 | 4 | A | X | 1 | 0 | 0 | 0 | G | B | 3 | 0 | 0 |
| TYPE / SIZE | | | VERSION | | | TCR | | | RESISTANCE | | | TOLERANCE | | PACKAGING | | | |
| CMA0204 | | | A = HF high frequency | | | X = no indication | | | 3 digit value 1 digit multiplier Multiplier 9 = *10 ⁻¹ 0 = *10 ⁰ | | | G = ± 2 % | | B3 | | | |

Product Description: CMA 0204 2 % HF BL 100R

| | | | | | |
|------|------|-----------|---------------------|-----------|--------------|
| CMA | 0204 | 2 % | HF | BL | 100R |
| TYPE | SIZE | TOLERANCE | VERSION | PACKAGING | RESISTANCE |
| CMA | 0204 | ± 2 % | HF = high frequency | BL | 100R = 100 Ω |

Note

- Products can be ordered using either the PART NUMBER or PRODUCT DESCRIPTION.



DESCRIPTION

Production of the CMA 0204 HF specialty MINI-MELF resistor is strictly controlled and follows an extensive set of instructions established for reproducibility. A homogeneous and dense carbon film is deposited on a high grade ceramic body (85 % Al_2O_3). Nickel plated steel termination caps are firmly pressed on the coated rods. A special laser is used to achieve the target value by smoothly cutting a non helical pattern with a resulting low inductivity in the resistive layer without damaging the ceramics. The resistor elements are covered by a protective coating designed for electrical, mechanical and climatic protection. The terminations receive a final pure matte tin on nickel plating. Four color code rings designate the resistance value and tolerance in accordance with **IEC 60062** ⁽¹⁾.

The result of the determined production is verified by an extensive testing procedure performed on 100 % of the individual resistors. Only accepted products are laid directly into the blister tape in accordance with **IEC 60286-3, Type 2a** ⁽¹⁾.

ASSEMBLY

The resistors are suitable for processing on automatic SMD assembly systems. They are suitable for automatic soldering using wave, reflow or vapor phase as shown in **IEC 61760-1** ⁽¹⁾. The encapsulation is resistant to all cleaning solvents commonly used in the electronics industry, including alcohols, esters and aqueous solutions. The suitability of conformal coatings, potting compounds and their processes, if applied, shall be qualified by appropriate means to ensure the long term stability of the whole system.

The resistors are completely lead (Pb)-free, the pure matte tin plating provides compatibility with lead (Pb)-free and lead containing soldering processes. Solderability is specified for 2 years after production or requalification, however, excellent solderability is proven after extended storage in excess of 10 years. The permitted storage time is 20 years. The immunity of the plating against tin whisker growth has been proven under extensive testing.

MATERIALS

Vishay acknowledges the following systems for the regulation of hazardous substances:

- IEC 62474, Material Declaration for Products of and for the Electrotechnical Industry, with the list of declarable substances given therein ⁽²⁾
- The Global Automotive Declarable Substance List (GADSL) ⁽³⁾
- The REACH regulation (1907/2006/EC) and the related list of substances with very high concern (SVHC) ⁽⁴⁾ for its supply chain

The products do not contain any of the banned substances as per IEC 62474, GADSL, or the SVHC list, see www.vishay.com/how/leadfree.

Hence the products fully comply with the following directives:

- 2000/53/EC End-of-Life Vehicle Directive (ELV) and Annex II (ELV II)
- 2011/65/EU Restriction of the Use of Hazardous Substances Directive (RoHS) with amendment 2015/863/EU
- 2012/19/EU Waste Electrical and Electronic Equipment Directive (WEEE)

Vishay pursues the elimination of conflict minerals from its supply chain, see the Conflict Minerals Policy at www.vishay.com/doc?49037.



APPROVALS

Where applicable the resistors are tested in accordance with **EN 140 401-803** which refers to **EN 60115-1**, **EN 60115-8** and the variety of environmental test procedures of the **IEC 60068** ⁽¹⁾ series.


Vishay Beyschlag has achieved “**Approval of Manufacturer**” in accordance with **IECQ 03-1**. The release certificate for “**Technology Approval Schedule**” in accordance with **CECC 240001** based on **IECQ 03-3-1** is granted for the Vishay Beyschlag manufacturing process.

Notes


- ⁽¹⁾ The quoted IEC standards are also released as EN standards with the same number and identical contents.
- ⁽²⁾ The IEC 62474 list of declarable substances is maintained in a dedicated database, which is available at <http://std.iec.ch/iec62474>.
- ⁽³⁾ The Global Automotive Declarable Substance List (GADSL) is maintained by the American Chemistry Council and available at www.gadsl.org.
- ⁽⁴⁾ The SVHC list is maintained by the European Chemical Agency (ECHA) and available at <http://echa.europa.eu/candidate-list-table>.

FUNCTIONAL PERFORMANCE

Derating - Standard Operation


Pulse load rating in accordance with IEC 60115-1, 4.27; 1.2 μs/50 μs; 5 pulses at 12 s intervals;
for permissible resistance change $\pm (0.5 \% R + 0.05 \Omega)$

1.2/50 Pulse

RF - Behavior

DIMENSIONS




| DIMENSIONS AND MASS | | | | | | |
|---------------------|-----------------|-----------------|-----------------------------|------------------------|------------|--------------|
| TYPE / SIZE | L (mm) | D (mm) | L ₁ min. (mm) | D ₁ (mm) | K (mm) | MASS (mg) |
| CMA 0204 HF | 3.6 + 0 / - 0.2 | 1.4 + 0 / - 0.1 | 1.8 | D + 0 / - 0.15 | 0.75 ± 0.1 | 19 |

Note

- Color code marking is applied according to IEC 60062 ⁽¹⁾ in four bands (E24 series). Each color band appears as a single solid line, voids are permissible if at least 2/3 of the band is visible from each radial angle of view. The last color band for tolerance is approximately 50 % wider than the other bands. Interrupted bands left and right of the 3rd full band indicate the special carbon film high frequency type.

PATTERN STYLES FOR MELF RESISTORS



| RECOMMENDED SOLDER PAD DIMENSIONS | | | | | | | | |
|-----------------------------------|----------------|-----------|-----------|-----------|------------------|-----------|-----------|-----------|
| TYPE / SIZE | WAVE SOLDERING | | | | REFLOW SOLDERING | | | |
| | G (mm) | Y (mm) | X (mm) | Z (mm) | G (mm) | Y (mm) | X (mm) | Z (mm) |
| CMA 0204 HF | 1.5 | 1.5 | 1.8 | 4.5 | 1.7 | 1.2 | 1.6 | 4.1 |

Notes

- The given solder pad dimensions reflect the considerations for board design and assembly as outlined e.g. in standards IEC 61188-5-x ⁽¹⁾, or in publication IPC-7351.

⁽¹⁾ The quoted IEC standards are also released as EN standards with the same number and identical contents.



HISTORICAL 12NC INFORMATION

- The resistors had a 12-digit numeric code starting with 2312.
- The subsequent 4 digits indicated the resistor type, specification and packaging; see the 12NC table.
- The remaining 4 digits indicated the resistance value:
 - The first 3 digits indicated the resistance value.
 - The last digit indicated the resistance decade in accordance with the 12NC Indicating Resistance Decade table.

Last Digit of 12NC Indicating Resistance Decade

| RESISTANCE DECADE | LAST DIGIT |
|------------------------------|------------|
| 10 Ω to 99.9 Ω | 9 |
| 100 Ω to 999 Ω | 1 |

Historical 12NC Example

The 12NC of a CMA 0204 HF resistor, value 50 Ω with $\pm 2\%$ tolerance, supplied in blister tape of 3000 units per reel was: 2312 158 25009.

HISTORICAL 12NC - Resistor Type and Packaging

| DESCRIPTION | | CODE 2312 |
|-------------|-----------|----------------------|
| | | BLISTER TAPE ON REEL |
| TYPE | TOL. | BL 3000 UNITS |
| CMA 0204 HF | $\pm 2\%$ | 158 2.... |



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Vishay products are not designed for use in life-saving or life-sustaining applications or any application in which the failure of the Vishay product could result in personal injury or death unless specifically qualified in writing by Vishay. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.