



Wirewound Resistors, Industrial Power, Adjustable Tapped Tubular



FEATURES

- Adjustable resistor or voltage divider
- High temperature silicon coating
- Can be used to quickly obtain odd resistance values
- One or more adjustable lugs can be provided for voltage divider applications
- Can be used as multi-tap resistor
- Material categorization:
for definitions of compliance please see www.vishay.com/doc?99912



Note

* This datasheet provides information about parts that are RoHS-compliant and/or parts that are non-RoHS-compliant. For example, parts with lead (Pb) terminations are not RoHS-compliant. Please see the information/tables in this datasheet for details.

STANDARD ELECTRICAL SPECIFICATIONS

| GLOBAL MODEL | HISTORICAL MODEL | POWER RATING $P_{25}^{\circ\text{C}}$ W | RESISTANCE RANGE Ω | TOLERANCE $\pm \%$ | WEIGHT (typical) g |
|--------------|------------------|--|------------------------------|-----------------------|-----------------------|
| HLA012 | HLA-12 | 12 | 1.0 to 10K | 5 | 6.69 |
| HLA020 | HLA-20 | 20 | 1.0 to 18K | 5 | 12.57 |
| HLA025 | HLA-25 | 25 | 1.0 to 23K | 5 | 20.72 |
| HLA026 | HLA-26 | 26 | 1.0 to 31K | 5 | 15.34 |
| HLA050 | HLA-50 | 50 | 1.0 to 57K | 5 | 42.08 |
| HLA051 | HLA-51 | 51 | 1.0 to 95K | 5 | 51.96 |
| HLA060 | HLA-60 | 60 | 1.0 to 74K | 5 | 65.64 |
| HLA065 | HLA-65 | 65 | 1.0 to 130K | 5 | 64.82 |
| HLA080 | HLA-80 | 80 | 1.0 to 111K | 5 | 121.58 |
| HLA100 | HLA-100 | 100 | 1.0 to 132K | 5 | 91.37 |
| HLA120 | HLA-120 | 120 | 1.0 to 180K | 5 | 183.82 |
| HLA130 | HLA-130 | 130 | 1.0 to 192K | 5 | 192.36 |
| HLA160 | HLA-160 | 160 | 1.0 to 249K | 5 | 245.86 |
| HLA175 | HLA-175 | 175 | 1.0 to 398K | 5 | 250.80 |
| HLA225 | HLA-225 | 225 | 1.0 to 337K | 5 | 309.97 |

TECHNICAL SPECIFICATIONS

| PARAMETER | UNIT | HLA RESISTOR CHARACTERISTICS |
|------------------------------------|-------------------------|--|
| Temperature Coefficient | ppm/ $^{\circ}\text{C}$ | ± 30 for 10 Ω and above; ± 50 for 1 Ω to 9.9 Ω ; ± 90 for 0.1 Ω to 0.99 Ω |
| Short Time Overload ⁽¹⁾ | - | 10 x rated power for 5 s |
| Maximum Working Voltage | V | $(P \times R)^{1/2}$ |
| Operating Temperature Range | $^{\circ}\text{C}$ | -55 to +350 |

Note

⁽¹⁾ Short time overload is rated without adjustable lug attached.

GLOBAL PART NUMBER INFORMATION

Global Part Numbering example: HLA22507Z200R0JJ


| | | | | | | | | | | | | | | | | | |
|--|----------------------------------|--|---|---|--|---|---|---|--|---|---|---|---|---|---|--|--|
| H | L | A | 2 | 2 | 5 | 0 | 7 | Z | 2 | 0 | 0 | R | 0 | J | J | | |
| GLOBAL MODEL | TERMINAL DESIGNATION | TERMINAL FINISH | VALUE | | TOLERANCE | | PACKAGING | | SPECIAL | | | | | | | | |
| HLA225 (see “Standard Electrical Specifications” table above for additional P/N’s | 02 05 06 07 14 15 | E = Lead (Pb-free) Z = tin / lead N = nickel | R = decimal K = thousand 10R00 = 10.0 Ω 1K000 = 1 kΩ | | J = ± 5.0 % K = ± 10.0 % Note (2) Tin / lead for type “Z”, lead (Pb)-free for type “N” | | E = lead (Pb)-free skin pack J (2) = skin pack (J01) | | (dash number) (up to 2 digits) from 1 to 99 as applicable | | | | | | | | |

Historical Part Numbering example: HLA-225-07Z 200 Ω 5 % J01

| | | | | |
|------------------|-----------------|------------------|-----------|-----------|
| HLA-225 | 07Z | 200 Ω | 5 % | J01 |
| HISTORICAL MODEL | TERMINAL/FINISH | RESISTANCE VALUE | TOLERANCE | PACKAGING |



DIMENSIONS



| GLOBAL MODEL | DIMENSIONS in inches [millimeters] | | | | | | | | | |
|-----------------|------------------------------------|-----------------------------|------------------|---------------------------|--|--|-------------------------|----------|----------------------------------|-------------------------|
| | A (MAX.) | CORE DIMENSIONS | | | TERMINAL SETBACK ± 0.031 [0.79] | DISTANCE BETWEEN TERMINALS (REF.) | TERMINAL DESIGNATION | | SLIDER MODEL NUMBER (1) | BRACKE T TYPE (1) |
| | | LENGTH ± 0.063 [1.59] | O.D. | I.D. ± 0.031 [0.79] | | | STANDARD | OPTIONAL | | |
| HLA012 | 0.406 [10.32] | 1.750 [44.45] | 0.313 [7.94] | 0.188 [4.76] | 0.094 [2.38] | 1.187 | 05Z | 14 N | 70 | 101, 204, 301 |
| HLA020 | 0.563 [14.29] | 2.000 [50.80] | 0.438 [11.11] | 0.313 [7.94] | 0.094 [2.38] | 1.437 | 02Z | 14 N | 71 | 101, 203, 301 |
| HLA025 | 0.688 [17.46] | 2.000 [50.80] | 0.563 [14.29] | 0.313 [7.94] | 0.094 [2.38] | 1.312 | 06Z | 15 N | 72 | 101, 203, 301 |
| HLA026 | 0.563 [14.29] | 3.000 [76.20] | 0.438 [11.11] | 0.313 [7.94] | 0.094 [2.38] | 2.437 | 02Z | 14 N | 71 | 101, 203, 301 |
| HLA050 | 0.688 [17.46] | 4.000 [101.60] | 0.563 [14.29] | 0.313 [7.94] | 0.094 [2.38] | 3.312 | 06Z | 15 N | 72 | 101, 203, 301 |
| HLA051 | 0.906 [23.02] | 3.500 [88.90] | 0.750 [19.05] | 0.500 [12.70] | 0.125 [2.38] | 2.75 | 06Z | 15 N | 73 | 102, 206, 303 |
| HLA060 | 0.906 [23.02] | 4.000 [101.60] | 0.750 [19.05] | 0.500 [12.70] | 0.125 [2.38] | 3.250 | 06Z | 15 N | 73 | 102, 206, 303 |
| HLA065 | 0.906 [23.02] | 4.500 [114.30] | 0.750 [19.05] | 0.500 [12.70] | 0.125 [2.38] | 3.750 | 06Z | 15 N | 73 | 102, 206, 303 |
| HLA080 | 1.313 [33.34] | 4.000 [101.60] | 1.125 [28.58] | 0.750 [19.05] | 0.219 [5.56] | 2.812 | 07Z | 15 N | 74 | 103, 205, 303 |
| HLA100 | 0.906 [23.02] | 6.500 [165.10] | 0.750 [19.05] | 0.500 [12.70] | 0.125 [2.38] | 5.750 | 06Z | 15 N | 73 | 102, 206, 303 |
| HLA120 | 1.313 [33.34] | 6.000 [152.40] | 1.125 [28.58] | 0.750 [19.05] | 0.219 [5.56] | 4.812 | 07Z | 15 N | 74 | 103, 205, 303 |
| HLA130 | 1.313 [33.34] | 6.500 [165.10] | 1.125 [28.58] | 0.750 [19.05] | 0.219 [5.56] | 5.312 | 07Z | 15 N | 74 | 103, 205, 303 |
| HLA160 | 1.313 [33.34] | 8.000 [203.20] | 1.125 [28.58] | 0.750 [19.05] | 0.219 [5.56] | 6.812 | 07Z | 15 N | 74 | 103, 205, 303 |
| HLA175 | 1.313 [33.34] | 215.90 [8.500] | 1.125 [28.58] | 0.750 [19.05] | 0.219 [5.56] | 7.312 | 07Z | 15 N | 74 | 103, 205, 303 |
| HLA225 | 1.313 [33.34] | 10.500 [266.70] | 1.125 [28.58] | 0.750 [19.05] | 0.219 [5.56] | 9.312 | 07Z | 15 N | 74 | 103, 205, 303 |

Note

(1) Brackets and sliders are available for mounting HLA series resistors - see Mounting Hardware.

ADJUSTABLE LUGS

The coating protects the resistance wire from shifting and shorting to other turns during adjustment. However, the following three steps should always be taken whenever adjustments are made:

1. Turn off power to avoid possible operator injury and damage to the unit.
2. Loosen adjustable lug until it will slide completely free, without touching the exposed wire.
3. When adjustment point has been selected, retighten lug only enough to assure a firm contact, do not tighten beyond this point. Failure to follow these three steps in order can result in damage to the resistor.

TERMINAL DIMENSIONS



| DIMENSION | TERMINAL STYLE | | | | | |
|-----------|------------------|-------------------|------------------|------------------|------------------|------------------|
| | 02 | 05 | 06 | 07 | 14 | 15 |
| A | 0.188 [4.76] | 0.188 [4.76] | 0.250 [6.35] | 0.375 [9.53] | 0.188 [4.76] | 0.250 [6.35] |
| B | 0.406 [10.32] | 0.438 [11.118] | 0.563 [14.29] | 0.625 [15.88] | 0.563 [14.29] | 0.594 [15.08] |
| C | 0.093 [2.36] | 0.104 [2.64] | 0.166 [4.22] | 0.173 [4.39] | 0.050 [1.27] | 0.065 [1.65] |
| D | 0.020 [0.51] | 0.020 [0.51] | 0.020 [0.51] | 0.020 [0.51] | 0.020 [0.51] | 0.031 [0.79] |

TERMINAL FINISH

"E" Finish - 100 % Sn coated steel. "Z" Finish - 60/40 Sn/Pb coated steel. "N" Finish - Nickel coated steel. Finish for terminal style 14 and 15 is limited to nickel plated steel (N).

MOUNTING HARDWARE

Mounting Hardware is available for HLA resistors, see "HL Brackets and Sliders" datasheet for more information: www.vishay.com/doc?30279.

MATERIAL SPECIFICATIONS

Element: copper-nickel alloy or nickel-chrome alloy, depending on resistance range

Core: ceramic, steatite


Coating: special high temperature silicone

Standard Terminals: model "E" terminals are tinned steel

Terminal Bands: steel

Part Marking: Dale, model, wattage, value, tolerance, date code

DERATING





Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Vishay products are not designed for use in life-saving or life-sustaining applications or any application in which the failure of the Vishay product could result in personal injury or death unless specifically qualified in writing by Vishay. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.