



Thick Film Chip Resistors, Industrial, Moisture Resistant



FEATURES

HALOGEN
FREE

- Manufactured to the DSCC drawings for military moisture resistant chip resistor products
- Designed to be resistant to the degrading effects of moisture while under power
- Construction is sulfur impervious against a high sulfur environment (ASTM B 809-95 test method)
- Same materials and construction as MIL-PRF-55342 chip resistors
- Termination: tin / lead wraparound termination over nickel barrier
- Operating temperature range: -65 °C to +155 °C
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912

STANDARD ELECTRICAL SPECIFICATIONS							
GLOBAL MODEL	DSCC DRAWING NUMBER	CASE SIZE	POWER RATING ⁽¹⁾ $P_{70\text{ }^\circ\text{C}}$ W	MAXIMUM WORKING VOLTAGE ⁽²⁾ V	RESISTANCE RANGE Ω	TOLERANCE $\pm \%$	TEMPERATURE COEFFICIENT $\pm \text{ppm}/^\circ\text{C}$
RCWP0201..69	07010	0201	0.05	30	10 to 47	5, 10	300
					47.5 to 1M	1, 2, 5, 10	100, 200, 300
RCWP0302..69	04007	0302	0.04	15	1 to 9.1	2, 5, 10	300
					10 to 22M	1, 2, 5, 10	100, 200, 300
RCWP0402..69	04008	0402	0.05	30	1 to 9.1	2, 5, 10	300
					10 to 22M	1, 2, 5, 10	100, 200, 300
RCWP0502..69	94025	0502	0.05	40	1 to 9.1	2, 5, 10	300
					10 to 22M	1, 2, 5, 10	100, 200, 300
RCWP0603..69	04009	0603	0.10	50	1 to 5.6	2, 5, 10	300
					5.62 to 22M	1, 2, 5, 10	100, 200, 300
RCWP0550..69	94012	0505	0.125	40	1 to 9.1	2, 5, 10	300
					10 to 22M	1, 2, 5, 10	100, 200, 300
RCWP0575..69	94015	0705 ⁽³⁾	0.15	50	1 to 5.6	2, 5, 10	300
					5.62 to 22M	1, 2, 5, 10	100, 200, 300
RCWP5100..69	94013	1005	0.20	75	1 to 5.6	2, 5, 10	300
					5.62 to 22M	1, 2, 5, 10	100, 200, 300
RCWP1206..69	94016	1206	0.25	100	1 to 5.6	2, 5, 10	300
					5.62 to 22M	1, 2, 5, 10	100, 200, 300
RCWP5150..69	94026	1505	0.35	125	1 to 5.6	2, 5, 10	300
					5.62 to 22M	1, 2, 5, 10	100, 200, 300
RCWP1100..69	94019	1010	0.50	75	1 to 5.6	2, 5, 10	300
					5.62 to 22M	1, 2, 5, 10	100, 200, 300
RCWP7225..69	94014	2208	0.60	175	1 to 5.6	2, 5, 10	300
					5.62 to 22M	1, 2, 5, 10	100, 200, 300
RCWP2010..69	94017	2010	0.80	150	1 to 5.6	2, 5, 10	300
					5.62 to 22M	1, 2, 5, 10	100, 200, 300
RCWP2512..69	94018	2512	1.00	200	1 to 5.6	2, 5, 10	300
					5.62 to 22M	1, 2, 5, 10	100, 200, 300

Notes


- Consult factory for extended resistance range
- These drawings can be viewed at: www.landandmaritime.dla.mil/Programs/MilSpec/ListDwgs.aspx?DocTYPE=DSCCdwg
- ⁽¹⁾ Power rating depends on max. temperature at the solder joint, the component placement density and the substrate material
- ⁽²⁾ Continuous working voltage shall be $\sqrt{P \times R}$ or maximum working voltage, whichever is less
- ⁽³⁾ MIL case size 0705 and EIA case size 0805 are dimensionally the same





GLOBAL PART NUMBER INFORMATION																	
Global Part Numbering: RCWP510010K0GMWB69 (preferred part numbering format)																	
R	C	W	P	5	1	0	0	1	0	K	0	G	M	W	B	6	9
GLOBAL MODEL	RESISTANCE VALUE	TOLERANCE CODE	TEMPERATURE COEFFICIENT	PACKAGING CODE (1)				SPECIAL									
(see Standard Electrical Specifications table)	R = Ω K = $k\Omega$ M = $M\Omega$ 10R0 = 10 Ω 1K30 = 1.3 $k\Omega$ 1M00 = 1.0 $M\Omega$	F = $\pm 1\%$ G = $\pm 2\%$ J = $\pm 5\%$ K = $\pm 10\%$	K = 100 ppm N = 200 ppm M = 300 ppm	TP = tin / lead, T/R, plastic tape (full reel; all sizes except 0201) S3 = tin / lead, T/R, plastic tape (1000 pieces; all sizes except 0201) WB = tin / lead, waffle tray S2 = tin / lead, T/R, plastic tape (500 pieces; all sizes except 0201) S6 = tin / lead, T/R, plastic tape (300 pieces; all sizes except 0201) UA = tin / lead, T/R, paper tape (full reel; 0201 only) UD = tin / lead, T/R, paper tape (1000 pieces; 0201 only) UC = tin / lead, T/R, paper tape (500 pieces; 0201 only) UB = tin / lead, T/R, paper tape (300 pieces; 0201 only)				69 = moisture resistant									

Notes

- For additional information on packaging, refer to the Surface Mount Resistor Packaging document (www.vishay.com/doc?31543)
- (1) Tape and reel packaging with plastic tape standard for all case sizes except 0201. For the 0201 case size, the product is only offered in tape and reel packaging with paper tape



MATERIAL SPECIFICATIONS	
Resistive element	Ruthenium oxide
Encapsulation	Epoxy
Substrate	96 % alumina
Termination	Solder-coated nickel barrier
Solder finish	Tin / lead solder alloy

DIMENSIONS in inches (millimeters)


GLOBAL MODEL	A (LENGTH)	B (WIDTH)	C (HEIGHT)	D (TOP TERM)	E (BOTTOM TERM)
RCWP0201...69	0.024 ± 0.002 (0.61 ± 0.05)	0.012 ± 0.002 (0.30 ± 0.05)	0.009 ± 0.002 (0.23 ± 0.05)	0.006 ± 0.003 (0.15 ± 0.08)	0.006 + 0.002 - 0.004 (0.15 + 0.05 - 0.10)
RCWP0302...69	0.034 ± 0.004 (0.86 ± 0.10)	0.021 ± 0.003 (0.53 ± 0.08)	0.013 ± 0.003 (0.33 ± 0.08)	0.007 ± 0.005 (0.18 ± 0.13)	0.008 ± 0.005 (0.20 ± 0.13)
RCWP0402...69	0.039 ± 0.003 (0.99 ± 0.08)	0.020 ± 0.003 (0.51 ± 0.08)	0.013 ± 0.003 (0.33 ± 0.08)	0.010 ± 0.005 (0.25 ± 0.13)	0.010 ± 0.005 (0.25 ± 0.13)
RCWP0502...69	0.055 ± 0.005 (1.40 ± 0.13)	0.023 ± 0.003 (0.58 ± 0.08)	0.015 ± 0.003 (0.38 ± 0.08)	0.010 ± 0.005 (0.25 ± 0.13)	0.015 ± 0.005 (0.38 ± 0.13)
RCWP0550...69	0.055 ± 0.005 (1.40 ± 0.13)	0.050 ± 0.005 (1.27 ± 0.13)	0.020 ± 0.005 (0.51 ± 0.13)	0.010 ± 0.005 (0.25 ± 0.13)	0.015 ± 0.005 (0.38 ± 0.13)
RCWP0575...69	0.080 ± 0.005 (2.03 ± 0.13)	0.050 ± 0.005 (1.27 ± 0.13)	0.020 ± 0.005 (0.51 ± 0.13)	0.016 ± 0.008 (0.41 ± 0.20)	0.015 ± 0.005 (0.38 ± 0.13)
RCWP0603...69	0.063 ± 0.005 (1.60 ± 0.13)	0.032 ± 0.005 (0.81 ± 0.13)	0.018 ± 0.005 (0.46 ± 0.13)	0.012 ± 0.005 (0.30 ± 0.13)	0.015 ± 0.005 (0.38 ± 0.13)
RCWP1100...69	0.105 ± 0.005 (2.67 ± 0.13)	0.100 ± 0.005 (2.54 ± 0.13)	0.020 ± 0.005 (0.51 ± 0.13)	0.015 ± 0.005 (0.38 ± 0.13)	0.015 ± 0.005 (0.38 ± 0.13)
RCWP1206...69	0.125 ± 0.005 (3.18 ± 0.13)	0.063 ± 0.005 (1.60 ± 0.13)	0.020 ± 0.005 (0.51 ± 0.13)	0.015 ± 0.005 (0.38 ± 0.13)	0.015 ± 0.005 (0.38 ± 0.13)
RCWP2010...69	0.197 ± 0.006 (5.00 ± 0.15)	0.098 ± 0.005 (2.49 ± 0.13)	0.020 ± 0.005 (0.51 ± 0.13)	0.020 ± 0.005 (0.51 ± 0.13)	0.020 ± 0.005 (0.51 ± 0.13)
RCWP2512...69	0.250 ± 0.006 (6.35 ± 0.15)	0.124 ± 0.005 (3.15 ± 0.13)	0.020 ± 0.005 (0.51 ± 0.13)	0.020 ± 0.005 (0.51 ± 0.13)	0.020 ± 0.005 (0.51 ± 0.13)
RCWP5100...69	0.105 ± 0.005 (2.67 ± 0.13)	0.050 ± 0.005 (1.27 ± 0.13)	0.020 ± 0.005 (0.51 ± 0.13)	0.015 ± 0.005 (0.38 ± 0.13)	0.015 ± 0.005 (0.38 ± 0.13)
RCWP5150...69	0.155 ± 0.005 (3.94 ± 0.13)	0.050 ± 0.005 (1.27 ± 0.13)	0.020 ± 0.005 (0.51 ± 0.13)	0.015 ± 0.005 (0.38 ± 0.13)	0.015 ± 0.005 (0.38 ± 0.13)
RCWP7225...69	0.230 ± 0.005 (5.84 ± 0.13)	0.075 ± 0.005 (1.91 ± 0.13)	0.020 ± 0.005 (0.51 ± 0.13)	0.020 ± 0.005 (0.51 ± 0.13)	0.020 ± 0.005 (0.51 ± 0.13)



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.