



Metal Film Resistors, Zero Ohm Jumper, Industrial



Product is End of Life Dec-2018
per PTN-DR-00011-2018, Rev 0

FEATURES

- Provides low resistance circuit interconnections
- Color band marking for ease of identification after mounting
- Flame retardant coating
- Compatible with automatic insertion equipment
- Tape and reel packaging
- Material categorization:



RoHS*
Available

for definitions of compliance please see www.vishay.com/doc?99912

Note

* This datasheet provides information about parts that are RoHS-compliant and / or parts that are non RoHS-compliant. For example, parts with lead (Pb) terminations are not RoHS-compliant. Please see the information / tables in this datasheet for details

STANDARD ELECTRICAL SPECIFICATIONS

GLOBAL MODEL	HISTORICAL MODEL	MAXIMUM RESISTANCE VALUE mΩ	MAXIMUM CURRENT A	
			AT + 25 °C	AT + 150 °C
FRJ50	FRJ-50	10	25	0

Note

- DSCC has created a drawing to support the need for an axial-leaded zero-ohm jumper product. Vishay Dale is listed as a resource on this drawing as follows:

DSCC DRAWING NUMBER	VISHAY DALE MODEL	MAXIMUM RESISTANCE mΩ	MAXIMUM CURRENT RATING A
A-A-55502	FRJ50	10	5

- This drawing can be viewed at: <http://www.landandmaritime.dla.mil/Programs/MilSpec/ListDwgs.aspx?DocTYPE=DSCCdwg>

TECHNICAL SPECIFICATIONS


PARAMETER	UNIT	FRJ50
Insulation Resistance - Dry	MΩ	10 000
Insulation Resistance - Wet	MΩ	100
Category Temperature Range	°C	-55 / +155
Dielectric Strength	V _{RMS}	500
	V _{RMS}	325
Failure Rate	10 ⁻⁹ /h	< 10
Weight	g	0.1

MATERIAL SPECIFICATIONS

Insulation Flammability	Self extinguishing 10 s after flame is removed	Solder plated copper	Tin-plated copper or tin/lead plated copper
-------------------------	--	----------------------	---

GLOBAL PART NUMBER INFORMATION

New Global Part Numbering: FRJ50R36 (preferred part numbering format)




Note

- For additional information on packaging, refer to the Through-Hole Resistor Packaging document (www.vishay.com/doc?31544)




DIMENSIONS in inches (millimeters)

FRJ50



MARKING



PACKAGING

Taped Lead and Reel Package

(52.4 mm inside tape spacing per EIA-296-E)

Notes

- Quantity per reel: 5000 pieces in 5000-piece increments
- A minimum of 12.0" (305 mm) bare tape leader shall be provided at each end of the reel
- Paper separator protection between layers of components
- Reel arbor hole is 1.25" (31.75 mm)



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Vishay products are not designed for use in life-saving or life-sustaining applications or any application in which the failure of the Vishay product could result in personal injury or death unless specifically qualified in writing by Vishay. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.